



Mini-Circuits

LTCC SURFACE MOUNT

Low Pass Filter


LFHK-530+

50Ω

DC to 530 MHz

THE BIG DEAL

- Low Insertion Loss, 1.5 dB Typ.
- Passband Return Loss, 14 dB Typ.
- Stopband Rejection, 76 dB Typ.
- 1008 Surface Mount Footprint
- Power Handling: 9 W
- Shielded Construction: Prevents De-Tuning & EMI
- Protected by US Patents 11,638,370 and 11,744,057




Generic photo used for illustration purposes only

APPLICATIONS

- Test and Measurement Equipment
- Microwave Transmitters / Receivers
- Harmonic Rejection
- Satellite Communications

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

The LFHK-530+ is a passive RF component designed for signal conditioning in low-frequency circuits. It utilizes ceramic-based construction to achieve stable electrical behavior across a broad operating range. The device supports bidirectional signal flow and is optimized for integration into compact layouts, making it suitable for dense PCB designs. Its surface-mount format aligns with standard automated assembly processes, and the internal structure is engineered to minimize parasitic effects that could impact performance at microwave frequencies. The component is built to maintain consistent characteristics under varying environmental conditions, contributing to overall system reliability.

ELECTRICAL SPECIFICATIONS^{1,2,3} AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	DC-F1	DC - 530	—	1.5	2.0	dB
	Freq. Cut-Off ⁴	Fc	670	—	3	—	
	Return Loss	DC-F1	DC - 530	9	14	—	
Stopband	Rejection	F2-F3	840 - 1250	20	31	—	dB
		F3-F4	1250 - 4000	66	76	—	
		F4-F5	4000 - 10000	—	71	—	
		F5-F6	10000 - 14500	—	60	—	
		F6-F7	14500 - 40000	—	24	—	

1. Tested in Evaluation Board P/N TB-LFHK-530+.

2. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

3. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.


4. Typical variation $\pm 5\%$.ABSOLUTE MAXIMUM RATINGS⁵

Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁶	9 W @ +25°C

5. Permanent damage may occur if any of these limits are exceeded.

6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1.1 W at +125°C.

TYPICAL FREQUENCY RESPONSE



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

 REV. OR
 ECO-027914
 LFHK-530+
 EDU5011
 URJ
 251209

PAGE 1 OF 5



LTCC SURFACE MOUNT

Low Pass Filter






LFHK-530+

Mini-Circuits

50Ω

DC to 530 MHz

TYPICAL PERFORMANCE GRAPHS





LTCC SURFACE MOUNT

Low Pass Filter

LFHK-530+

Mini-Circuits

50Ω

DC to 530 MHz

FUNCTIONAL DIAGRAM





Figure 1. LFHK-530+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1 ²	1	Connects to RF Input Port
RF2 ²	2	Connects to RF Output Port
GROUND	3	Connects to Ground on PCB, (See drawing PL-798)

CASE STYLE DRAWING



Weight: .019grms.

Dimensions are in inches (mm).

Tolerances: 2Pl. ± .01; 3Pl. ± .005

PRODUCT MARKING*: V5

*Marking may contain other features or characters for internal lot control.



LTCC SURFACE MOUNT

Low Pass Filter

LFHK-530+

Mini-Circuits

50Ω

DC to 530 MHz

SUGGESTED PCB LAYOUT




Figure 2. Suggested PCB Layout



LTCC SURFACE MOUNT

Low Pass Filter

LFHK-530+

50Ω

DC to 530 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	NL1008C-12 Lead Finish: Gold over Electroless Nickel
RoHS/REACH Status	Compliant
Tape and Reel	F75
Suggested Layout for PCB Design	PL-798
Evaluation Board	TB-LFHK-530+ Gerber File
Environmental Rating	ENV06T10

NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html








Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	0.16	0.21	0.26	32.44	30.75	29.22	32.65	30.83	29.35
50	0.27	0.32	0.38	23.72	23.21	22.87	23.73	23.21	22.87
100	0.38	0.45	0.51	19.15	19.09	19.15	19.14	19.08	19.15
200	0.60	0.68	0.77	14.88	15.14	15.50	14.88	15.14	15.51
530	1.16	1.38	1.67	32.32	29.55	26.46	29.58	27.77	25.43
670	2.63	3.34	4.46	18.68	15.37	11.70	16.51	14.04	10.98
840	31.33	32.43	33.84	0.60	0.71	0.83	0.57	0.68	0.80
1250	76.34	78.66	81.17	0.42	0.51	0.61	0.39	0.48	0.58
2000	93.79	95.69	95.84	0.34	0.42	0.51	0.32	0.41	0.50
2800	90.99	85.52	102.57	0.24	0.33	0.41	0.24	0.32	0.40
3800	86.92	87.16	89.58	0.26	0.36	0.44	0.25	0.35	0.43
4000	88.42	90.34	88.61	0.28	0.39	0.47	0.28	0.38	0.46
4500	90.64	92.75	95.18	0.36	0.48	0.57	0.34	0.46	0.54
5000	91.39	90.74	83.27	0.49	0.66	0.84	0.45	0.62	0.80
5500	84.63	86.13	89.71	0.52	0.66	0.77	0.46	0.60	0.70
6000	85.12	87.58	84.57	0.54	0.70	0.81	0.47	0.63	0.74
6850	86.76	89.49	87.92	0.59	0.76	0.88	0.52	0.69	0.81
7000	87.46	84.01	86.12	0.61	0.77	0.91	0.54	0.72	0.84
7500	86.69	84.30	84.35	0.66	0.80	0.92	0.60	0.75	0.86
8000	88.46	83.85	84.49	0.67	0.81	0.92	0.60	0.76	0.87
8100	87.71	84.07	84.50	0.68	0.81	0.92	0.60	0.76	0.87
9000	75.86	81.54	80.75	0.67	0.80	0.90	0.58	0.75	0.84
9300	78.55	80.54	80.14	0.62	0.78	0.88	0.56	0.73	0.83
10000	78.09	79.71	79.75	0.56	0.75	0.87	0.50	0.69	0.80
10200	78.09	77.68	78.21	0.55	0.75	0.88	0.49	0.69	0.81
11000	77.84	78.56	78.21	0.59	0.83	0.97	0.52	0.74	0.89
11800	71.59	70.31	67.83	0.73	1.00	1.19	0.63	0.91	1.09
12000	63.59	62.57	65.43	0.81	1.08	1.23	0.71	0.99	1.13
12500	66.94	68.59	67.63	0.86	1.12	1.28	0.79	1.06	1.21
13000	62.54	61.16	62.35	0.93	1.18	1.33	0.89	1.17	1.29
13500	59.33	62.57	65.14	0.95	1.19	1.35	0.95	1.21	1.33
14000	64.98	66.07	65.63	0.94	1.19	1.38	0.95	1.21	1.36
14500	62.59	62.78	62.35	0.95	1.23	1.49	0.95	1.28	1.55
15000	71.35	66.19	61.92	1.19	1.42	1.67	1.24	1.43	1.58
15500	57.05	58.96	52.96	1.38	1.99	2.81	1.18	1.70	2.39
16000	34.96	34.34	34.75	2.73	2.35	2.26	3.21	2.92	2.49
17000	27.18	27.39	28.77	1.76	2.18	2.49	1.79	2.13	2.28
18000	33.66	36.92	38.72	1.65	1.95	2.28	1.45	1.76	2.07
19000	33.88	37.26	42.07	2.64	2.40	2.19	2.53	2.30	2.12
20000	58.15	62.65	66.42	1.28	1.65	1.90	1.20	1.58	1.81
21000	66.25	63.54	58.09	1.36	1.90	2.45	1.33	1.99	2.62
22000	39.59	44.74	52.61	2.49	2.86	2.69	2.64	2.73	2.46
25000	71.24	71.40	72.97	1.34	1.94	2.28	1.08	1.64	1.98
30000	62.43	61.29	59.57	1.27	1.92	2.35	1.24	1.83	2.20
30500	59.13	57.79	56.18	1.41	2.12	2.64	1.33	1.95	2.40
31000	54.72	53.28	51.41	1.73	2.49	3.00	1.53	2.22	2.64
31500	50.02	50.82	49.22	2.20	2.95	3.29	1.80	2.53	2.89
32000	48.87	43.60	38.35	2.47	3.13	3.46	2.04	2.65	3.09
32500	36.82	34.25	36.50	2.48	3.19	3.49	2.18	2.87	3.14
33000	35.82	38.09	39.45	2.26	2.97	3.59	2.07	2.71	3.27
33500	38.90	39.72	39.90	2.18	3.05	4.10	1.98	2.85	3.80
34000	38.70	38.86	40.96	2.66	3.98	4.55	2.39	3.81	5.21
34500	38.55	42.23	46.17	3.91	3.68	3.35	4.36	5.60	4.60
35000	45.69	46.31	41.97	2.49	2.67	2.89	4.19	3.97	3.59
35500	42.45	38.05	38.25	2.08	2.53	2.90	2.81	3.26	3.34
36000	37.15	39.90	41.56	2.06	2.53	3.04	2.49	3.01	3.28
36500	41.46	42.66	42.91	2.06	2.64	3.27	2.19	2.85	3.22
37000	42.71	43.15	44.48	2.11	2.80	3.46	1.97	2.61	3.09
38000	46.29	46.82	47.63	2.48	3.45	3.93	1.82	2.74	3.07
40000	26.17	27.89	27.89	3.15	3.90	4.45	3.48	4.53	5.41

Typical Performance Data


FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-55°C	@+25°C	@+125°C
10	1.72	1.72	1.75
20	1.71	1.71	1.74
30	1.69	1.71	1.73
40	1.69	1.70	1.73
50	1.68	1.70	1.72
60	1.68	1.70	1.72
70	1.67	1.69	1.72
100	1.67	1.69	1.71
110	1.67	1.69	1.71
120	1.67	1.69	1.71
130	1.67	1.69	1.71
140	1.68	1.69	1.72
150	1.68	1.70	1.72
160	1.68	1.70	1.72
170	1.68	1.70	1.73
180	1.69	1.71	1.73
190	1.69	1.71	1.74
200	1.70	1.72	1.74
210	1.71	1.73	1.75
220	1.71	1.73	1.76
230	1.72	1.74	1.76
240	1.73	1.75	1.77
250	1.74	1.76	1.78
260	1.75	1.77	1.79
270	1.76	1.78	1.81
280	1.77	1.79	1.82
290	1.79	1.80	1.83
300	1.80	1.82	1.85
320	1.83	1.85	1.88
360	1.90	1.93	1.95
380	1.95	1.97	2.00
400	1.99	2.02	2.05
420	2.04	2.07	2.10
440	2.10	2.13	2.17
460	2.17	2.20	2.24
530	2.47	2.51	2.58

Typical Performance Curves



Outline Dimensions

NL1008C-12



Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3Pl. ± .005

SUGGESTED LAYOUT FOR PCB LAND PATTERN

PATTERN TO BE WITHIN ±.002

Notes:

1. Open style, Ceramic base.
2. Termination finish: **as shown below or indicated on Data sheet.**
For RoHS Case Styles: Gold plate over nickel plate. All models, (+) suffix.
3. Weight: .019 grams.
4. Pad tolerance is non-cumulative.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

Applicable Case Styles

FV1206-1
FV1206-3

Applicable Case Styles

FV1206-4
FV1206-5
FV1206-6
FV1206-7
FV1206-9

Applicable Case Styles

FV1206-11
FV1206-12
GE0805C-18
NL1008C-6
NL1008C-7
NL1008C-9
NL1008C-10
NL1008C-12

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

THIRD ANGLE PROJECTION		REVISIONS					
		REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
		OR	ECO-023057	NEW RELEASE	SEP 24	AGS	GT
		OR1	NPO-004738	ADDED NL1008C-10 CASE STYLE	OCT 24	AGS	GT
		OR2	ECO-023820	NOTES & TOLERANCES UPDATED	NOV 24	AGS	GT

SUGGESTED MOUNTING CONFIGURATION FOR
NL1008C-9,NL1008C-10 CASE STYLE



STACK-UP DIAGRAM



1. TOTAL FINISHED THICKNESS 0.0228±.004
2. B-VIA PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 2.
3. PTH PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 4.
4. INDICATED ON TOP VIEW PTH'S ARE PLUGGED WITH EPOXY AND CAPPED WITH COPPER FROM TOP SIDE.
5. L4 IS CONTINUOUS GROUND PLANE.

NOTES:

1. DIMENSIONS ARE IN INCHES ; [CD] DENOTES CRITICAL DIMENSIONS.
2. PCB IS MULTILAYER, SEE STACK-UP DIAGRAM AND SHEET-2 FOR ILLUSTRATION.
3. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON 6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
4. COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.




DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)




DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED		INITIALS		DATE		Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235							
DIMENSIONS ARE IN INCHES		DRAWN	AGS	14 SEP 24		PL, NL1008C-9/10, TB-LFHK-XXXX+							
TOLERANCES ON:		CHECKED	MD	16 SEP 24									
2 PL DECIMALS ±		APPROVED	GTP	17 SEP 24									
3 PL DECIMALS ± .002													
ANGLES ±													
FRACTIONS ±													
Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.													
ASHEETA1.DWG REV:A DATE:01/12/95						FILE: 98-PL-798							
						SIZE A		CODE IDENT 15542		DRAWING NO: 98-PL-798		REV: OR2	
						SCALE: 9:1		SHEET: 1 OF 2					


LAYER 1, SOLDER MASK & PTH




LAYER 2, B-VIA & PTH



LAYER 3 & PTH



LAYER 4 & PTH



 Mini-Circuits

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA2.DWG REV:A DATE: 01/12/94


ALL DIMENSIONS ARE IN INCHES EXCEPT OTHERWISE SPECIFIED

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-798	REV: OR2
-----------	---------------------	--------------------------	-------------


FILE: 98-PL-798	SCALE: 7.7:1	SHEET: 2 OF 2
--------------------	-----------------	------------------

Evaluation Board and Circuit

TB-LFHK-530+



STACK-UP DIAGRAM



Notes:

1. PCB Material: MEGTRON-6 R5775(G) OR Equivalent, Dielectric Constant=3.6
2. Total finished thickness: .023 inch
3. 50 Ohm 2.92mm Female End Launch Connector.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutectic Process 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Test B,B1, 95% Coverage
Thermal Shock	-55° to +125°C, 15 min dwell,250 cycles	MIL-STD-202, Method 107
Bend Test	1mm, deflection for 5 seconds Span of bending: 2.75"	--
High Temp Storage	125°C to 1000 Hrs	---