



Mini-Circuits

LTCC SURFACE MOUNT

## Low Pass Filter


LFHK-900+

50Ω

DC to 900 MHz

## THE BIG DEAL

- Low Insertion Loss, 2 dB Typ.
- Passband Return Loss, 12 dB Typ.
- Stopband Rejection, 79 dB Typ.
- 1008 Surface Mount Footprint
- Power Handling: 9 W
- Shielded Construction: Prevents De-Tuning & EMI
- Protected by US Patents 11,638,370 and 11,744,057



Generic photo used for illustration purposes only


## APPLICATIONS

- Test and Measurement Equipment
- Microwave Transmitters / Receivers
- Harmonic Rejection
- Satellite Communications

## PRODUCT OVERVIEW

The LFHK-900+ is a passive RF component designed for signal conditioning in low-frequency circuits. It utilizes ceramic-based construction to achieve stable electrical behavior across a broad operating range. The device supports bidirectional signal flow and is optimized for integration into compact layouts, making it suitable for dense PCB designs. It's surface-mount format aligns with standard automated assembly processes, and the internal structure is engineered to minimize parasitic effects that could impact performance at microwave frequencies. The component is built to maintain consistent characteristics under varying environmental conditions, contributing to overall system reliability.

## FUNCTIONAL DIAGRAM

ELECTRICAL SPECIFICATIONS<sup>1,2,3</sup> AT +25°C

| Parameter |                            | F#    | Frequency (MHz) | Min. | Typ. | Max. | Units |
|-----------|----------------------------|-------|-----------------|------|------|------|-------|
| Passband  | Insertion Loss             | DC-F1 | DC - 900        | —    | 2    | 2.5  | dB    |
|           | Freq. Cut-Off <sup>4</sup> | Fc    | 1000            | —    | 3    | —    |       |
|           | Return Loss                | DC-F1 | DC - 900        | —    | 12   | —    |       |
| Stopband  | Rejection                  | F2-F3 | 1300 - 2000     | 20   | 36   | —    | dB    |
|           |                            | F3-F4 | 2000 - 5000     | 67   | 79   | —    |       |
|           |                            | F4-F5 | 5000 - 15500    | —    | 60   | —    |       |
|           |                            | F5-F6 | 15500 - 19000   | —    | 48   | —    |       |
|           |                            | F6-F7 | 19000 - 50000   | —    | 25   | —    |       |

1. Tested in Evaluation Board P/N TB-LFHK-900+.

2. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

3. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

4. Typical variation ± 5%.


ABSOLUTE MAXIMUM RATINGS<sup>5</sup>

|                          |                 |
|--------------------------|-----------------|
| Operating Temperature    | -55°C to +125°C |
| Storage Temperature      | -55°C to +125°C |
| Input Power <sup>6</sup> | 9 W @ +25°C     |

5. Permanent damage may occur if any of these limits are exceeded.

6. Power rating applies only to signals within the passband. Power rating above +25°C operating temperature decreases linearly to 1.1 W at +125°C.

## TYPICAL FREQUENCY RESPONSE



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

 REV. OR  
 ECO-027914  
 LFHK-900+  
 EDU5009  
 URJ  
 251204

PAGE 1 OF 5



LTCC SURFACE MOUNT

# Low Pass Filter






LFHK-900+

Mini-Circuits

50Ω

DC to 900 MHz

## TYPICAL PERFORMANCE GRAPHS





LTCC SURFACE MOUNT

# Low Pass Filter

**LFHK-900+**

Mini-Circuits

50Ω

DC to 900 MHz

## FUNCTIONAL DIAGRAM





Figure 1. LFHK-900+ Functional Diagram

## PAD DESCRIPTION

| Function         | Pad Number | Description                                        |
|------------------|------------|----------------------------------------------------|
| RF1 <sup>2</sup> | 1          | Connects to RF Input Port                          |
| RF2 <sup>2</sup> | 2          | Connects to RF Output Port                         |
| GROUND           | 3          | Connects to Ground on PCB,<br>(See drawing PL-798) |

## CASE STYLE DRAWING



Weight: .019grms.

Dimensions are in inches (mm).

Tolerances: 2Pl. ± .01; 3Pl. ± .005

## PRODUCT MARKING\*: V4

\*Marking may contain other features or characters for internal lot control.



LTCC SURFACE MOUNT

# Low Pass Filter

LFHK-900+

Mini-Circuits

50Ω

DC to 900 MHz

## SUGGESTED PCB LAYOUT




Figure 2. Suggested PCB Layout



LTCC SURFACE MOUNT

# Low Pass Filter

**LFHK-900+**

50Ω

DC to 900 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

|                                 |                                                                                           |
|---------------------------------|-------------------------------------------------------------------------------------------|
| Performance Data & Graphs       | Data<br>Graphs<br>S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads |
| Case Style                      | NL1008C-12    Lead Finish: Gold over Electroless Nickel                                   |
| RoHS/REACH Status               | Compliant                                                                                 |
| Tape and Reel                   | F75                                                                                       |
| Suggested Layout for PCB Design | PL-798                                                                                    |
| Evaluation Board                | TB-LFHK-900+<br>Gerber File                                                               |
| Environmental Rating            | ENV06T10                                                                                  |

## NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)








## Typical Performance Data

| FREQ. | INSERTION LOSS |        |         | INPUT RETURN LOSS |        |         | OUTPUT RETURN LOSS |        |         |
|-------|----------------|--------|---------|-------------------|--------|---------|--------------------|--------|---------|
| (MHz) | (dB)           |        |         | (dB)              |        |         | (dB)               |        |         |
|       | @-55°C         | @+25°C | @+125°C | @-55°C            | @+25°C | @+125°C | @-55°C             | @+25°C | @+125°C |
| 10    | 0.13           | 0.17   | 0.22    | 32.25             | 31.22  | 29.90   | 32.81              | 31.51  | 30.14   |
| 50    | 0.23           | 0.27   | 0.32    | 21.95             | 21.61  | 21.34   | 21.98              | 21.65  | 21.36   |
| 100   | 0.35           | 0.39   | 0.45    | 17.13             | 17.05  | 17.02   | 17.17              | 17.10  | 17.07   |
| 200   | 0.55           | 0.60   | 0.66    | 13.27             | 13.46  | 13.74   | 13.31              | 13.51  | 13.81   |
| 500   | 0.63           | 0.74   | 0.88    | 32.35             | 30.64  | 28.21   | 27.60              | 26.52  | 25.26   |
| 900   | 1.60           | 1.88   | 2.26    | 12.93             | 12.58  | 12.37   | 12.67              | 12.32  | 12.14   |
| 1000  | 2.39           | 3.00   | 4.07    | 17.23             | 15.14  | 11.50   | 17.48              | 15.21  | 11.52   |
| 1300  | 35.95          | 36.91  | 38.17   | 0.55              | 0.63   | 0.75    | 0.55               | 0.62   | 0.75    |
| 2000  | 82.85          | 84.22  | 87.19   | 0.44              | 0.49   | 0.59    | 0.45               | 0.50   | 0.61    |
| 2800  | 91.63          | 93.82  | 93.33   | 0.31              | 0.38   | 0.47    | 0.32               | 0.38   | 0.48    |
| 3800  | 87.24          | 92.18  | 87.05   | 0.27              | 0.36   | 0.45    | 0.26               | 0.36   | 0.45    |
| 4000  | 89.16          | 91.36  | 93.00   | 0.28              | 0.38   | 0.46    | 0.27               | 0.37   | 0.47    |
| 4800  | 95.39          | 88.06  | 87.51   | 0.37              | 0.48   | 0.57    | 0.37               | 0.48   | 0.58    |
| 5000  | 90.84          | 85.71  | 88.54   | 0.40              | 0.51   | 0.60    | 0.40               | 0.51   | 0.62    |
| 5500  | 96.49          | 96.16  | 88.83   | 0.47              | 0.58   | 0.68    | 0.48               | 0.57   | 0.69    |
| 6000  | 95.57          | 90.59  | 89.00   | 0.60              | 0.74   | 0.98    | 0.59               | 0.68   | 0.87    |
| 6850  | 86.93          | 87.11  | 86.19   | 0.61              | 0.69   | 0.80    | 0.65               | 0.69   | 0.81    |
| 7000  | 88.64          | 87.81  | 84.04   | 0.62              | 0.70   | 0.81    | 0.66               | 0.69   | 0.82    |
| 7500  | 86.91          | 84.83  | 88.54   | 0.66              | 0.74   | 0.85    | 0.71               | 0.74   | 0.87    |
| 8000  | 87.48          | 83.22  | 84.59   | 0.70              | 0.79   | 0.91    | 0.75               | 0.79   | 0.93    |
| 8100  | 85.01          | 86.72  | 85.91   | 0.71              | 0.81   | 0.94    | 0.75               | 0.81   | 0.96    |
| 9000  | 85.98          | 90.88  | 86.94   | 0.68              | 0.80   | 0.89    | 0.72               | 0.81   | 0.93    |
| 9300  | 86.40          | 85.26  | 85.38   | 0.62              | 0.77   | 0.86    | 0.65               | 0.77   | 0.89    |
| 10000 | 84.27          | 85.85  | 83.34   | 0.53              | 0.71   | 0.81    | 0.53               | 0.70   | 0.83    |
| 10200 | 87.50          | 85.86  | 91.96   | 0.52              | 0.70   | 0.81    | 0.50               | 0.69   | 0.82    |
| 11000 | 67.45          | 69.58  | 71.42   | 0.55              | 0.75   | 0.88    | 0.50               | 0.71   | 0.87    |
| 11800 | 72.38          | 72.55  | 72.28   | 0.63              | 0.85   | 1.03    | 0.63               | 0.83   | 1.03    |
| 12000 | 70.13          | 70.69  | 68.51   | 0.69              | 0.91   | 1.10    | 0.70               | 0.90   | 1.11    |
| 12500 | 60.87          | 66.39  | 75.38   | 1.09              | 1.24   | 1.27    | 1.14               | 1.20   | 1.26    |
| 13000 | 79.58          | 80.60  | 79.77   | 0.96              | 1.10   | 1.22    | 1.05               | 1.12   | 1.27    |
| 13500 | 80.34          | 81.44  | 88.31   | 1.02              | 1.14   | 1.26    | 1.16               | 1.18   | 1.33    |
| 14000 | 76.87          | 77.58  | 76.22   | 1.04              | 1.15   | 1.27    | 1.18               | 1.18   | 1.35    |
| 14500 | 75.64          | 76.03  | 76.31   | 1.00              | 1.14   | 1.27    | 1.11               | 1.14   | 1.34    |
| 15000 | 75.43          | 75.36  | 74.22   | 0.95              | 1.12   | 1.27    | 1.00               | 1.09   | 1.31    |
| 15500 | 74.32          | 72.49  | 73.00   | 0.89              | 1.10   | 1.28    | 0.90               | 1.06   | 1.29    |
| 16000 | 70.17          | 70.71  | 72.49   | 0.87              | 1.12   | 1.32    | 0.85               | 1.09   | 1.32    |
| 17000 | 59.57          | 61.46  | 61.50   | 0.93              | 1.24   | 1.49    | 0.93               | 1.26   | 1.52    |
| 18000 | 63.25          | 66.24  | 65.79   | 1.15              | 1.39   | 1.58    | 1.17               | 1.43   | 1.63    |
| 19000 | 50.14          | 47.48  | 46.88   | 1.19              | 1.48   | 1.65    | 1.23               | 1.45   | 1.64    |
| 20000 | 44.71          | 46.69  | 47.10   | 1.42              | 1.73   | 2.03    | 1.45               | 1.54   | 1.90    |
| 21000 | 35.05          | 34.22  | 31.55   | 2.63              | 3.85   | 6.17    | 2.38               | 3.07   | 4.83    |
| 22000 | 27.16          | 30.70  | 35.21   | 3.63              | 3.08   | 2.83    | 5.86               | 4.16   | 3.48    |
| 25000 | 59.25          | 57.21  | 53.65   | 1.49              | 2.16   | 2.75    | 1.65               | 2.42   | 3.22    |
| 30000 | 61.67          | 59.48  | 57.43   | 1.68              | 2.35   | 3.17    | 1.93               | 2.64   | 3.52    |
| 31000 | 53.51          | 57.90  | 61.66   | 2.87              | 2.98   | 2.98    | 3.15               | 3.20   | 3.17    |
| 32000 | 60.86          | 63.07  | 74.45   | 2.01              | 2.68   | 2.92    | 1.91               | 2.38   | 2.67    |
| 35000 | 51.03          | 51.75  | 57.47   | 2.01              | 2.43   | 2.80    | 2.35               | 2.49   | 2.91    |
| 37000 | 44.76          | 45.42  | 49.83   | 2.07              | 2.73   | 3.23    | 2.18               | 2.90   | 3.53    |
| 39000 | 48.02          | 48.10  | 47.12   | 2.46              | 3.15   | 4.11    | 2.61               | 2.93   | 3.74    |
| 40000 | 44.62          | 43.66  | 43.37   | 3.61              | 4.54   | 5.80    | 3.90               | 4.21   | 6.04    |
| 41000 | 42.27          | 47.41  | 57.55   | 5.14              | 6.00   | 4.80    | 5.99               | 5.45   | 4.66    |
| 42000 | 56.91          | 49.11  | 42.04   | 2.76              | 3.05   | 3.57    | 2.99               | 3.32   | 3.86    |
| 43000 | 33.20          | 30.36  | 36.72   | 2.88              | 4.24   | 5.25    | 2.74               | 4.27   | 5.57    |
| 44000 | 55.26          | 52.54  | 50.78   | 3.17              | 3.74   | 4.46    | 4.09               | 4.74   | 4.76    |
| 45000 | 51.79          | 50.80  | 49.79   | 3.26              | 4.18   | 4.50    | 3.42               | 3.51   | 4.09    |
| 46000 | 49.03          | 50.76  | 50.83   | 3.27              | 3.94   | 4.74    | 3.64               | 4.70   | 5.74    |
| 47000 | 49.54          | 48.82  | 48.17   | 2.71              | 3.51   | 4.80    | 3.07               | 3.74   | 5.35    |
| 48000 | 39.84          | 34.19  | 31.86   | 4.50              | 7.13   | 7.28    | 7.30               | 10.99  | 7.35    |
| 49000 | 29.53          | 34.69  | 56.20   | 4.86              | 5.23   | 6.11    | 4.99               | 5.80   | 6.36    |
| 50000 | 56.16          | 60.10  | 43.99   | 3.15              | 3.91   | 4.51    | 2.95               | 3.90   | 4.36    |

*Typical Performance Data*

| FREQ. | GROUP DELAY |        |         |
|-------|-------------|--------|---------|
| (MHz) | (nsec)      |        |         |
|       | @-55°C      | @+25°C | @+125°C |
| 10    | 1.17        | 1.19   | 1.21    |
| 20    | 1.17        | 1.18   | 1.20    |
| 30    | 1.16        | 1.17   | 1.19    |
| 40    | 1.15        | 1.17   | 1.18    |
| 50    | 1.15        | 1.16   | 1.18    |
| 60    | 1.15        | 1.16   | 1.17    |
| 70    | 1.14        | 1.15   | 1.17    |
| 100   | 1.13        | 1.14   | 1.16    |
| 120   | 1.13        | 1.14   | 1.15    |
| 130   | 1.12        | 1.13   | 1.15    |
| 140   | 1.12        | 1.13   | 1.15    |
| 150   | 1.12        | 1.13   | 1.15    |
| 160   | 1.12        | 1.13   | 1.15    |
| 170   | 1.12        | 1.13   | 1.14    |
| 180   | 1.12        | 1.13   | 1.14    |
| 190   | 1.12        | 1.13   | 1.15    |
| 200   | 1.12        | 1.13   | 1.15    |
| 250   | 1.13        | 1.14   | 1.16    |
| 280   | 1.14        | 1.15   | 1.16    |
| 300   | 1.14        | 1.15   | 1.17    |
| 350   | 1.17        | 1.18   | 1.20    |
| 380   | 1.19        | 1.20   | 1.22    |
| 400   | 1.21        | 1.22   | 1.23    |
| 450   | 1.24        | 1.25   | 1.27    |
| 480   | 1.27        | 1.28   | 1.29    |
| 500   | 1.28        | 1.29   | 1.31    |
| 550   | 1.31        | 1.32   | 1.33    |
| 580   | 1.32        | 1.33   | 1.35    |
| 600   | 1.33        | 1.34   | 1.36    |
| 650   | 1.37        | 1.38   | 1.41    |
| 680   | 1.40        | 1.42   | 1.45    |
| 700   | 1.43        | 1.45   | 1.48    |
| 750   | 1.54        | 1.56   | 1.60    |
| 800   | 1.68        | 1.71   | 1.75    |
| 850   | 1.84        | 1.87   | 1.92    |
| 900   | 2.05        | 2.11   | 2.19    |


## Typical Performance Curves





## Outline Dimensions

## NL1008C-12



Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3Pl. ± .005

### SUGGESTED LAYOUT FOR PCB LAND PATTERN

PATTERN TO BE WITHIN ±.002

### Notes:

1. Open style, Ceramic base.
2. Termination finish: **as shown below or indicated on Data sheet.**  
For RoHS Case Styles: Gold plate over nickel plate. All models, (+) suffix.
3. Weight: .019 grams.
4. Pad tolerance is non-cumulative.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



## DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

### Applicable Case Styles

FV1206-1  
FV1206-3

### Applicable Case Styles

FV1206-4  
FV1206-5  
FV1206-6  
FV1206-7  
FV1206-9

### Applicable Case Styles

FV1206-11  
FV1206-12  
GE0805C-18  
NL1008C-6  
NL1008C-7  
NL1008C-9  
NL1008C-10  
NL1008C-12

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel                    |      |
|----------------|-------------------------|-------------------|-------------------------------------|------|
| 8              | 4                       | 7                 | Small quantity standards (see note) | 20   |
|                |                         |                   |                                     | 50   |
|                |                         |                   |                                     | 100  |
|                |                         |                   |                                     | 200  |
|                |                         |                   |                                     | 500  |
|                |                         |                   |                                     | 1000 |
|                |                         |                   | Standard                            | 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




**Distribution Centers NORTH AMERICA** 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010  
Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

| THIRD ANGLE PROJECTION |  | REVISIONS |            |                             |        |     |      |
|------------------------|--|-----------|------------|-----------------------------|--------|-----|------|
|                        |  | REV       | ECN No.    | DESCRIPTION                 | DATE   | DR  | AUTH |
|                        |  | OR        | ECO-023057 | NEW RELEASE                 | SEP 24 | AGS | GT   |
|                        |  | OR1       | NPO-004738 | ADDED NL1008C-10 CASE STYLE | OCT 24 | AGS | GT   |
|                        |  | OR2       | ECO-023820 | NOTES & TOLERANCES UPDATED  | NOV 24 | AGS | GT   |
|                        |  |           |            |                             |        |     |      |

SUGGESTED MOUNTING CONFIGURATION FOR  
NL1008C-9,NL1008C-10 CASE STYLE



STACK-UP DIAGRAM



1. TOTAL FINISHED THICKNESS 0.0228±.004
2. B-VIA PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 2.
3. PTH PRESENT FROM COPPER LAYER 1 TO COPPER LAYER 4.
4. INDICATED ON TOP VIEW PTH's ARE PLUGGED WITH EPOXY AND CAPPED WITH COPPER FROM TOP SIDE.
5. L4 IS CONTINUOUS GROUND PLANE.

NOTES:


1. DIMENSIONS ARE IN INCHES ; [CD] DENOTES CRITICAL DIMENSIONS.
2. PCB IS MULTILAYER, SEE STACK-UP DIAGRAM AND SHEET-2 FOR ILLUSTRATION.
3. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR MEGTRON 6 R-5775(G), CLOTH STYLE:1080 WITH DIELECTRIC THICKNESS .0051; COPPER: 1/2 OZ.+PLATING.  
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
4. COPPER LAYER 4 OF THE PCB ARE CONTINUOUS GROUND PLANE.




DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)




DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |          | INITIALS | DATE      |  <b>Mini-Circuits®</b><br>13 Neptune Avenue<br>Brooklyn NY 11235 |                     |                          |                  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|----------|-----------|-----------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|--------------------------|------------------|
| DIMENSIONS ARE IN INCHES<br>TOLERANCES ON:<br>2 PL DECIMALS ±<br>3 PL DECIMALS ± .002<br>ANGLES ±<br>FRACTIONS ±                                                                                                                                                                                                                                                                                                                                                                                                                                   | DRAWN    | AGS      | 14 SEP 24 |                                                                                                                                                     |                     |                          |                  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | CHECKED  | MD       | 16 SEP 24 |                                                                                                                                                     |                     |                          |                  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    | APPROVED | GTP      | 17 SEP 24 |                                                                                                                                                     |                     |                          |                  |
|  Mini-Circuits®<br>THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.<br>EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE<br>AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY<br>DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.<br>THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE<br>PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS. |          |          |           | SIZE<br>A                                                                                                                                           | CODE IDENT<br>15542 | DRAWING NO:<br>98-PL-798 | REV:<br>OR2      |
| ASHEETA1.DWG REV:A DATE:01/12/95                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |          |          |           | FILE:                                                                                                                                               | 98-PL-798           | SCALE:<br>9:1            | SHEET:<br>1 OF 2 |


LAYER 1, SOLDER MASK & PTH




LAYER 2, B-VIA & PTH



LAYER 3 & PTH



LAYER 4 & PTH



 Mini-Circuits

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA2.DWG REV:A DATE: 01/12/94

ALL DIMENSIONS ARE IN INCHES EXCEPT OTHERWISE SPECIFIED


| SIZE  | CODE IDENT | DRAWING NO:  | REV:          |
|-------|------------|--------------|---------------|
| A     | 15542      | 98-PL-798    | OR2           |
| FILE: | 98-PL-798  | SCALE: 7.7:1 | SHEET: 2 OF 2 |

# Evaluation Board and Circuit

TB-LFHK-900+



## STACK-UP DIAGRAM



### Notes:

1. PCB Material: MEGTRON-6 R5775(G) OR Equivalent, Dielectric Constant=3.6
2. Total finished thickness: .023 inch
3. 50 Ohm 2.92mm Female End Launch Connector.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification         | Test/Inspection Condition                                              | Reference/Spec                                                                                       |
|-----------------------|------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature | -55° to 125° C<br>Ambient Environment                                  | Individual Model Data Sheet                                                                          |
| Storage Temperature   | -55° to 125° C<br>Ambient Environment                                  | Individual Model Data Sheet                                                                          |
| Humidity              | 90 to 95% RH, 240 hours, 50°C                                          | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat    | Sn-Pb Eutectic Process 225°C peak<br>Pb-Free Process 245° - 250°C peak | J-STD-020C, Table 4-1, 4-2 and 5-2, Figure 5-1                                                       |
| Solderability         | 10X Magnification                                                      | J-STD-002, Test B,B1, 95% Coverage                                                                   |
| Thermal Shock         | -55° to +125°C, 15 min dwell, 250 cycles                               | MIL-STD-202, Method 107                                                                              |
| Bend Test             | 1mm, deflection for 5 seconds<br>Span of bending: 2.75"                | --                                                                                                   |
| High Temp Storage     | 125°C to 1000 Hrs                                                      | ---                                                                                                  |