

CASE STYLE: C07

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
LO Power	50mW
I&Q Current	40mA
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

LO (carrier)	13
RF (signal)	1
I (0°)(ref.)	8
Q (90°)*	5
ISOLATE**	10, 11
GROUND	2,3,4,6,7,9,12,14,15,16
CASE GROUND	2,3,4,6,7,9,12,14,15,16

*Q= I +90° for lower sideband suppression

**external variable capacitors can be connected at pins 10 & 11 to ground for improvement of sideband rejection.

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G	H	wt
.770	.810	.380	.410	.030	.200	.20	.14	grams
19.56	20.57	9.65	10.41	0.76	5.08	5.08	3.56	11.0

Features

- good carrier and sideband rejections
- excellent 3rd and 5th order harmonic suppression

Applications

- radar
- communications systems

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Modulator Electrical Specifications

FREQUENCY (MHz)				CONVERSION LOSS (dB)			CARRIER REJECTION (-dBc)		SIDE BAND REJECTION (-dBc)		HARMONIC SUPPRESSION (-dBc)			
RF (SIGNAL/ LO (CARRIER)		I&Q									3XI/Q		5XI/Q	
fL	fU	Min.	Max.	$\bar{x}$	σ	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.
137	143	DC	5	5.8	0.20	7.0	34	30	36	30	45	35	60	50


1. Operating LO power: 10±1dBm
2. 1dB Compression: 0dBm typical
3. Conversion Loss: (I + Q) power, dBm - RF power, dBm
4. Carrier and sideband rejections measured at -5dBm I/Q power.

Typical Performance Data

Carrier Freq. (MHz)	Conversion Loss $\bar{x}$ (dB)	Sideband Rejection ($\bar{x}$)		Carrier Rejection ($\bar{x}$)		3rd Harmonic Suppression ($\bar{x}$)		5th. Harmonic Suppression ($\bar{x}$)		DC Offset ($\bar{x}$) (mV)
		LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	
137.00	5.76	35.71	36.70	33.27	33.31	45.22	57.87	79.42	81.57	-0.08
137.46	5.75	35.67	36.51	33.24	33.30	45.22	58.08	79.42	79.88	-0.16
137.92	5.77	35.45	36.52	33.19	33.29	45.30	58.58	78.70	77.98	-0.06
138.23	5.76	35.18	36.15	33.22	33.28	45.40	58.58	79.20	79.38	-0.07
138.39	5.76	35.33	36.27	33.23	33.27	45.50	58.58	78.60	79.78	-0.13
138.85	5.77	35.21	36.25	33.15	33.26	45.69	58.78	80.69	77.68	-0.19
139.31	5.76	35.06	36.14	33.13	33.19	45.79	59.07	78.39	78.87	-0.08
139.62	5.77	35.13	36.06	33.15	33.25	45.80	59.27	77.00	78.97	-0.11
139.77	5.76	35.09	35.94	33.18	33.20	45.78	59.47	76.28	77.87	-0.07
140.08	5.76	35.13	35.90	33.15	33.19	45.89	59.77	77.39	77.17	-0.07
140.54	5.77	34.97	35.99	33.14	33.19	46.10	60.17	74.80	75.37	-0.18
140.85	5.76	34.94	36.12	33.09	33.22	45.98	60.37	77.28	76.87	-0.17
141.00	5.77	34.92	35.98	33.10	33.21	46.09	60.38	76.59	75.38	-0.17
141.46	5.76	34.90	36.02	33.10	33.13	46.20	60.78	75.40	75.98	-0.19
141.92	5.76	34.85	35.86	33.06	33.11	46.28	61.06	75.58	75.06	-0.17
142.23	5.75	34.85	35.95	33.05	33.16	46.39	61.28	76.29	74.88	-0.21
142.39	5.74	34.80	35.96	33.02	33.17	46.38	61.58	75.48	74.48	-0.11
142.69	5.75	34.72	35.93	33.04	33.11	46.30	61.58	74.60	73.38	-0.12
142.85	5.75	34.72	35.91	33.02	33.16	46.39	62.18	75.89	74.98	-0.10
143.00	5.75	34.65	36.01	33.02	33.11	46.49	61.58	75.59	72.48	-0.11



I&Q modulation block diagram



Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data


CARRIER FREQ. (MHz)	CONVERSION LOSS (dB)	SIDE BAND REJECTION		CARRIER REJECTION		3rd HARMONIC SUPPRESSION		5th HARMONIC SUPPRESSION		DC OFFSET (mV)
		LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	LSB (-dBc)	USB (-dBc)	
137.0	5.76	35.71	36.70	33.27	33.31	45.22	57.87	79.42	81.57	-0.08
137.5	5.75	35.67	36.51	33.24	33.30	45.22	58.08	79.42	79.88	-0.16
137.9	5.77	35.45	36.52	33.19	33.29	45.30	58.58	78.70	77.98	-0.06
138.2	5.76	35.18	36.15	33.22	33.28	45.40	58.58	79.20	79.38	-0.07
138.4	5.76	35.33	36.27	33.23	33.27	45.50	58.58	78.60	79.78	-0.13
138.8	5.77	35.21	36.25	33.15	33.26	45.69	58.78	80.69	77.68	-0.19
139.3	5.76	35.06	36.14	33.13	33.19	45.79	59.07	78.39	78.87	-0.08
139.6	5.77	35.13	36.06	33.15	33.25	45.80	59.27	77.00	78.97	-0.11
139.8	5.76	35.09	35.94	33.18	33.20	45.78	59.47	76.28	77.87	-0.07
140.1	5.76	35.13	35.90	33.15	33.19	45.89	59.77	77.39	77.17	-0.07
140.5	5.77	34.97	35.99	33.14	33.19	46.10	60.17	74.80	75.37	-0.18
140.8	5.76	34.94	36.12	33.09	33.22	45.98	60.37	77.28	76.87	-0.17
141.0	5.77	34.92	35.98	33.10	33.21	46.09	60.38	76.59	75.38	-0.17
141.5	5.76	34.90	36.02	33.10	33.13	46.20	60.78	75.40	75.98	-0.19
141.9	5.76	34.85	35.86	33.06	33.11	46.28	61.06	75.58	75.06	-0.17
142.2	5.75	34.85	35.95	33.05	33.16	46.39	61.28	76.29	74.88	-0.21
142.4	5.74	34.80	35.96	33.02	33.17	46.38	61.58	75.48	74.48	-0.11
142.7	5.75	34.72	35.93	33.04	33.11	46.30	61.58	74.60	73.38	-0.12
142.8	5.75	34.72	35.91	33.02	33.16	46.39	62.18	75.89	74.98	-0.10
143.0	5.75	34.65	36.01	33.02	33.11	46.49	61.58	75.59	72.48	-0.11

Typical Performance Curves


Conversion Loss




DC Offset




Sideband Rejection




Carrier Rejection



3rd Harmonic Suppression



5th Harmonic Suppression



Outline Dimensions

C07



CASE#	A	B	C	D	E	F	G	H	WT. GRAM
C07	.770 (19.56)	.810 (20.57)	.380 (9.65)	.410 (10.41)	.030 (.76)	.200 (5.08)	.20 (5.08)	.14 (3.56)	11.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver..
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Gross Leak	125°C Bubble Test	MIL-STD-202, Method 112, Condition D
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D