

Directional Coupler

LRDC-10-1

50Ω 5 to 500 MHz



CASE STYLE: QQQ130

Maximum Ratings


Operating Temperature	-40°C to 85 °C
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

INPUT	6
OUTPUT	1
COUPLED	4
GROUND	2,5
ISOLATE (DO NOT USE)	3

Outline Drawing



PCB Land Pattern




Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.390	.31	.225	.060	--	.100	.045
9.91	7.87	5.72	1.52	--	2.54	1.14
H	J	K	L	M	wt	
.420	.120	.060	.100	--	grams	
10.67	3.05	1.52	2.54	--	0.50	

Demo Board MCL P/N: TB-31 Suggested PCB Layout (PL-087)



- NOTES:
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/WCLStore/terms.jsp

Features

- low mainline loss, 0.9 dB typ.
- high directivity, 30 dB typ.

Applications

- VHF/UHF
- reflective power measurements
- communications
- signal sampling

Directional Coupler Electrical Specifications


FREQ. (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT, W	
	Nom.	Flatness	L		M		U		L		M		U			L	MU
f _L -f _U			Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Max.
5-500	10.7±0.5	±0.5	0.9	1.4	0.9	1.4	1.2	1.9	31	25	30	20	25	16	1.2	1.0	1.0

L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]
1. Mainline loss includes theoretical power loss at coupled port.


Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
5.00	0.87	10.56	34.05	32.58	21.08	21.19
9.00	0.86	10.55	34.98	34.24	21.38	21.44
22.00	0.86	10.57	34.87	34.86	21.43	21.53
38.00	0.87	10.61	34.30	33.52	21.31	21.52
55.00	0.89	10.62	34.06	31.49	21.16	21.52
80.00	0.92	10.61	33.94	28.84	20.90	21.53
130.00	0.97	10.68	33.37	25.10	20.17	21.41
280.00	1.01	10.66	27.76	19.24	17.58	20.72
420.00	1.25	10.69	22.09	16.25	15.45	19.95
500.00	1.36	10.67	19.44	15.06	14.47	19.60


LRDC-10-1
MAINLINE LOSS




LRDC-10-1
COUPLING & DIRECTIVITY



LRDC-10-1
RETURN LOSS



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) THAT ROUTES DC FROM RF PORTS TO GROUND.

Directional Coupler

LRDC-10-1

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
5.0	0.87	10.56	34.05	32.58	21.08	21.19
6.0	0.86	10.56	34.44	33.23	21.19	21.29
7.0	0.86	10.55	34.65	33.67	21.28	21.35
8.0	0.85	10.55	34.83	34.00	21.33	21.41
9.0	0.86	10.55	34.98	34.24	21.38	21.44
10.0	0.85	10.54	35.09	34.41	21.40	21.47
14.0	0.85	10.55	35.08	34.86	21.45	21.51
18.0	0.85	10.56	35.12	34.94	21.43	21.51
22.0	0.86	10.57	34.87	34.86	21.43	21.53
26.0	0.86	10.58	34.65	34.62	21.40	21.52
30.0	0.86	10.59	34.60	34.30	21.37	21.52
34.0	0.87	10.60	34.34	33.93	21.33	21.52
38.0	0.87	10.61	34.30	33.52	21.31	21.52
42.0	0.87	10.61	34.23	33.03	21.27	21.52
46.0	0.87	10.62	34.25	32.56	21.23	21.51
50.0	0.88	10.62	34.14	32.09	21.20	21.52
55.0	0.89	10.62	34.06	31.49	21.16	21.52
60.0	0.90	10.63	34.05	30.91	21.11	21.52
65.0	0.91	10.63	34.03	30.35	21.06	21.54
70.0	0.92	10.63	33.92	29.82	21.01	21.53
75.0	0.92	10.62	33.94	29.32	20.96	21.54
80.0	0.92	10.61	33.94	28.84	20.90	21.53
85.0	0.92	10.62	33.76	28.39	20.83	21.52
90.0	0.92	10.62	33.87	27.95	20.79	21.53
95.0	0.92	10.62	33.66	27.53	20.72	21.52
100.0	0.92	10.64	33.81	27.13	20.64	21.50
130.0	0.97	10.68	33.37	25.10	20.17	21.41
160.0	0.96	10.64	32.79	23.53	19.67	21.30
190.0	0.97	10.67	31.74	22.20	19.16	21.20
220.0	1.09	10.73	30.65	21.04	18.61	21.05
250.0	1.02	10.65	29.27	20.08	18.07	20.87
280.0	1.01	10.66	27.76	19.24	17.58	20.72
310.0	1.24	10.76	26.53	18.45	17.07	20.55
340.0	1.09	10.66	25.25	17.76	16.58	20.35
370.0	1.09	10.64	23.97	17.16	16.13	20.19
400.0	1.33	10.75	22.82	16.61	15.73	20.07
420.0	1.25	10.69	22.09	16.25	15.45	19.95
440.0	1.17	10.62	21.37	15.92	15.18	19.85
460.0	1.25	10.67	20.65	15.61	14.94	19.75
480.0	1.42	10.72	20.06	15.33	14.70	19.66
500.0	1.36	10.67	19.44	15.06	14.47	19.60

REV. X1
LRDC-10-1
060718
Page 1 of 1







IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Typical Performance Curves




Case Style


QQQ

QQQ130 (non-waterproof)
QQQ828 (washable)

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
QQQ130	.400 (10.16)	.31 (7.87)	.200 (5.08)	.10 (2.54)	.010 (.25)	.100 (2.54)	.050 (1.27)	.420 (10.67)	.120 (3.05)	.060 (1.52)	.100 (2.54)	.020 (.51)	.55
QQQ828			.050 (1.27)										.20

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100
		13	200,500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Note: Please consult individual model data sheet to determine device per reel availability.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/06/02	AV	DJ
A	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/16/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION FOR QQQ569 CASE STYLE, "cz" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS DATE

DIMENSIONS ARE IN INCHES
TOLERANCES ON:
2 PL DECIMALS ±
3 PL DECIMALS ± .005
ANGLES ±
FRACTIONS ±

DRAWN	AV	07/23/02
CHECKED	LC	08/06/02
APPROVED	DJ	08/06/02



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235


PL, cz, QQQ569, LRDC-J, TB-31

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-087	REV: A
FILE: 98PL087	SCALE: 6:1	SHEET: 1 OF 1	

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit




TB-31



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215