

Surface Mount

Directional Coupler

75Ω

5 to 600 MHz

LRDC-12-1-75J+

LRDC-12-1-75J

Maximum Ratings

Operating Temperature -40°C to 85°C


Storage Temperature -55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	6
OUTPUT	1
COUPLED	4
GROUND	2,5
ISOLATE (DO NOT USE)	3


Outline Drawing

Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (inch)

A	B	C	D	E	F	G
.390	.31	.225	.060	—	.100	.045
9.91	7.87	5.72	1.52	—	2.54	1.14
H	J	K	L	M	wt	
.420	.120	.060	.100	—	grams	
10.67	3.05	1.52	2.54	—	0.50	

Demo Board MCL P/N: TB-34 Suggested PCB Layout (PL-043)



- NOTES:
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.030" ± 0.002", COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 - DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- low mainline loss, 0.5 dB typ.
- high directivity, 21 dB typ.
- aqueous washable
- J-leads for strain relief and excellent solderability

Applications

- VHF/UHF
- signal sampling
- communications
- cable tv



CASE STYLE: QQQ569

PRICE: Contact Sales Dept.

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Directional Coupler Electrical Specifications




FREQ. (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)						DIRECTIVITY (dB)						VSWR (:1)	POWER INPUT, W	
			L		M		U		L		M		U			L	MU
	f _L -f _U	Nom.	Flatness	Typ.	Max.	Typ.	Max.	Typ.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.		
5-600	12.2±0.5	±0.6	0.4	0.8	0.5	1.0	0.8	1.5	20	17	21	18	20	12	1.3	1.0	1.0

L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]


1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB) In-Cpl	Directivity (dB)	Return Loss (dB)		
				In	Out	Cpl
5.00	0.68	12.25	27.30	24.93	36.02	24.62
6.00	0.67	12.24	27.29	25.25	37.90	24.76
8.00	0.66	12.24	27.30	25.59	41.55	24.92
10.00	0.67	12.24	27.29	25.75	45.26	24.96
100.00	0.69	12.26	25.97	24.35	29.52	24.21
200.00	0.71	12.27	23.92	21.73	23.91	23.15
300.00	0.77	12.28	22.07	19.81	20.80	21.77
400.00	0.79	12.20	20.71	18.62	19.03	20.45
500.00	0.84	12.11	19.85	18.13	18.22	19.44
600.00	0.92	12.05	19.38	18.26	18.28	18.73



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMERS THAT ROUTES DC FROM RF PORTS TO GROUND.

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M119986
LRDC-12-1-75J
W2/TD/CP/AM
141001

Directional Coupler

LRDC-12-1-75J

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	(dB) OUT	CPL
1	0.80	12.47	27.55	20.24	24.72	20.70
2	0.71	12.40	27.78	21.85	28.64	22.17
5	0.64	12.34	28.15	23.43	35.13	23.54
6	0.63	12.33	28.31	23.61	36.77	23.66
7	0.63	12.33	27.83	23.72	37.86	23.76
8	0.62	12.34	28.19	23.80	38.76	23.82
9	0.62	12.34	28.26	23.87	39.88	23.88
10	0.62	12.33	27.98	23.94	41.12	23.94
20	0.62	12.34	27.93	24.28	46.51	24.18
30	0.62	12.34	28.07	24.33	44.03	24.15
40	0.63	12.34	28.37	24.32	40.38	24.08
50	0.63	12.35	28.18	24.25	37.28	23.98
75	0.65	12.37	27.30	24.06	33.51	23.81
100	0.66	12.37	27.45	23.85	30.89	23.44
125	0.67	12.39	26.97	23.42	28.69	23.00
150	0.69	12.40	26.99	23.06	27.09	22.61
175	0.70	12.39	26.18	22.55	25.76	22.05
200	0.71	12.39	26.35	22.03	24.57	21.58
225	0.73	12.40	25.41	21.58	23.66	21.02
250	0.74	12.41	25.01	21.09	22.76	20.52
275	0.75	12.41	24.71	20.68	22.00	20.06
300	0.77	12.42	24.31	20.26	21.39	19.57
325	0.79	12.40	23.90	19.95	20.73	19.13
350	0.81	12.40	23.35	19.55	20.20	18.71
375	0.83	12.41	23.04	19.22	19.73	18.32
400	0.85	12.41	22.32	19.01	19.34	17.98
425	0.87	12.42	21.92	18.74	19.08	17.64
450	0.90	12.42	21.26	18.56	18.71	17.36
475	0.93	12.42	20.96	18.38	18.43	17.06
500	0.96	12.44	20.11	18.19	18.21	16.83
550	1.03	12.48	19.09	17.90	17.82	16.43
600	1.10	12.53	18.16	17.86	17.57	16.14
650	1.19	12.60	17.07	17.87	17.59	16.02
700	1.29	12.72	16.06	18.02	17.67	16.05
750	1.39	12.89	15.11	18.22	17.92	16.21
800	1.52	13.08	13.96	18.52	18.12	16.53
850	1.65	13.42	12.49	18.98	18.63	17.07
900	1.79	13.81	11.27	19.78	19.33	17.75
950	1.96	14.28	10.19	20.68	19.99	18.67
1000	2.15	14.85	9.18	21.92	20.42	19.76
1050	2.30	15.44	8.16	22.75	20.71	20.86
1100	2.49	16.04	7.02	24.12	21.07	21.90
1200	2.86	17.18	5.07	25.54	20.43	23.54
1300	3.18	17.80	4.31	24.24	19.36	23.97
1400	3.38	17.88	3.32	22.55	19.05	23.36
1500	3.39	17.61	3.18	21.53	19.00	22.01
1600	3.25	17.10	3.75	20.52	19.58	20.32
1700	3.12	16.66	3.53	19.55	20.10	18.57
1800	2.99	16.23	4.77	18.67	20.61	16.91
1900	2.96	16.00	3.68	18.10	20.82	15.46
2000	2.98	15.77	3.54	17.56	20.91	14.07

REV. X1

LRDC-12-1-75J

090708

Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Directional Coupler

LRDC-12-1-75J

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
1	0.97	12.64	26.75	17.14	19.16	17.35
2	0.92	12.61	27.45	18.89	22.55	19.03
5	0.79	12.50	27.93	20.89	26.52	20.96
6	0.75	12.47	27.66	21.38	27.55	21.42
7	0.71	12.43	27.99	21.90	28.64	21.88
8	0.68	12.41	28.16	22.38	29.73	22.32
9	0.66	12.40	28.20	22.79	30.85	22.74
10	0.65	12.38	28.21	23.16	32.08	23.11
20	0.58	12.33	28.43	25.24	46.12	24.74
30	0.56	12.31	28.30	26.15	40.07	25.19
40	0.56	12.31	28.49	26.96	36.20	25.42
50	0.56	12.32	27.91	27.66	33.96	25.55
75	0.57	12.31	28.05	28.06	33.36	25.59
100	0.57	12.32	27.77	26.55	35.72	25.49
125	0.58	12.31	26.96	24.84	31.71	25.09
150	0.59	12.32	27.36	24.24	27.95	24.73
175	0.59	12.32	26.71	24.30	26.76	24.10
200	0.60	12.31	26.34	24.22	26.57	23.59
225	0.61	12.32	25.73	23.35	26.17	22.84
250	0.62	12.31	25.35	21.95	24.43	22.00
275	0.63	12.31	24.79	21.22	22.96	21.28
300	0.64	12.31	24.29	20.76	22.22	20.43
325	0.65	12.30	24.00	20.49	21.63	19.77
350	0.67	12.30	23.29	19.86	21.05	19.07
375	0.69	12.28	22.84	19.19	20.25	18.47
400	0.71	12.30	22.14	18.76	19.67	17.96
425	0.73	12.29	21.77	18.31	19.20	17.50
450	0.75	12.28	21.06	17.95	18.83	17.12
475	0.78	12.28	20.76	17.59	18.38	16.73
500	0.80	12.30	19.69	17.36	17.81	16.42
550	0.87	12.32	18.61	17.13	17.27	15.86
600	0.93	12.37	17.51	16.54	16.77	15.43
650	1.01	12.42	16.35	16.67	16.61	15.21
700	1.10	12.54	15.05	17.10	16.74	15.20
750	1.20	12.69	14.07	17.14	16.82	15.37
800	1.31	12.92	12.73	17.89	17.21	15.90
850	1.44	13.22	11.19	18.82	17.89	16.68
900	1.58	13.65	9.71	20.42	19.10	17.67
950	1.75	14.24	8.36	22.22	20.60	18.94
1000	1.93	14.92	7.14	25.15	21.74	19.96
1050	2.13	15.73	5.86	24.92	22.52	20.66
1100	2.32	16.59	4.50	23.39	23.29	20.64
1200	2.72	18.05	2.32	19.21	22.98	20.21
1300	3.06	18.71	1.58	17.90	22.29	20.16
1400	3.22	18.45	1.13	18.16	22.11	20.61
1500	3.10	17.67	1.60	20.77	20.82	20.63
1600	2.84	16.83	2.61	27.40	18.55	20.60
1700	2.59	16.13	2.73	25.60	16.53	19.85
1800	2.43	15.61	4.22	24.96	15.64	18.32
1900	2.35	15.22	3.23	19.09	15.10	16.62
2000	2.44	15.07	3.04	16.42	15.77	14.11

REV. X1

LRDC-12-1-75J

090708

Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



Patent Pending

The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Directional Coupler

LRDC-12-1-75J

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +85°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING LOSS (dB)	DIRECTIVITY (dB)	RETURN LOSS (dB)		
				IN	OUT	CPL
1	1.03	12.63	26.42	18.42	22.01	18.65
2	0.87	12.51	26.93	20.21	25.27	20.38
5	0.74	12.41	27.25	22.28	30.66	22.29
6	0.72	12.42	27.29	22.51	31.84	22.55
7	0.71	12.40	27.49	22.72	32.66	22.70
8	0.71	12.40	27.63	22.82	33.36	22.85
9	0.70	12.40	27.59	22.90	33.89	22.96
10	0.70	12.40	27.46	23.00	34.33	23.03
20	0.69	12.41	27.72	23.29	37.04	23.40
30	0.69	12.40	27.38	23.06	36.90	23.53
40	0.70	12.40	27.84	22.79	35.44	23.44
50	0.71	12.42	27.08	22.38	33.61	23.43
75	0.72	12.43	27.03	21.90	29.82	23.05
100	0.74	12.44	26.87	22.11	27.72	22.67
125	0.75	12.46	26.54	22.47	26.87	22.15
150	0.77	12.48	26.59	22.65	26.38	21.75
175	0.78	12.48	25.89	22.05	25.34	21.24
200	0.80	12.48	25.83	21.21	23.74	20.79
225	0.81	12.49	25.32	20.78	22.55	20.35
250	0.83	12.49	24.96	20.57	21.82	19.89
275	0.85	12.51	24.54	20.59	21.48	19.54
300	0.87	12.51	24.16	20.36	21.22	19.12
325	0.89	12.51	23.80	19.99	20.57	18.89
350	0.91	12.52	23.24	19.56	19.97	18.60
375	0.94	12.53	22.92	19.29	19.47	18.31
400	0.96	12.54	22.37	19.30	19.24	18.10
425	0.99	12.54	22.20	19.23	19.12	17.83
450	1.01	12.55	21.34	19.14	18.98	17.69
475	1.04	12.56	21.34	18.96	18.83	17.45
500	1.08	12.59	20.38	18.74	18.51	17.26
550	1.15	12.64	19.63	18.55	18.16	16.97
600	1.24	12.71	18.96	18.70	18.11	16.72
650	1.32	12.79	18.10	18.58	18.12	16.62
700	1.43	12.92	17.25	18.51	18.02	16.62
750	1.54	13.09	16.71	18.61	18.15	16.60
800	1.66	13.33	15.91	18.56	18.17	16.78
850	1.78	13.57	14.68	18.78	18.33	17.18
900	1.92	13.90	13.66	19.39	18.71	17.76
950	2.06	14.28	12.89	19.90	18.89	18.59
1000	2.22	14.69	12.17	20.53	18.80	19.42
1050	2.38	15.14	11.38	21.58	18.82	20.41
1100	2.54	15.61	10.40	22.84	18.89	21.53
1200	2.88	16.48	8.68	27.18	18.62	23.98
1300	3.18	17.12	7.71	28.82	18.26	24.97
1400	3.41	17.46	6.37	25.03	18.46	24.39
1500	3.52	17.53	5.61	21.67	18.96	21.94
1600	3.51	17.31	5.88	19.49	20.21	19.83
1700	3.47	17.08	5.24	18.12	21.80	17.82
1800	3.40	16.83	6.19	17.31	22.81	16.16
1900	3.40	16.66	4.79	17.39	22.12	15.11
2000	3.44	16.58	4.25	17.37	20.79	14.11

REV. X1
LRDC-12-1-75J
090708
Page 3 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Directional Coupler


LRDC-12-1-75J

Typical Performance Curves


Insertion Loss




Insertion Loss vs. TEMPERATURE



Coupling Loss vs. TEMPERATURE



Directivity vs. TEMPERATURE




Directional Coupler


LRDC-12-1-75J

Typical Performance Curves


Return Loss




Return Loss In vs. TEMPERATURE



Return Loss Out vs. TEMPERATURE



Return Loss Cpl vs. TEMPERATURE



REV. X1
LRDC-12-1-75J
090708
Page 2 of 2



Mini-Circuits®


IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$


CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
QQQ569	.390 (9.90)	.31 (7.87)	.225 (5.72)	.060 (1.52)	-	.100 (2.54)	.045 (1.14)	.420 (10.67)	.120 (3.05)	.060 (1.52)	.100 (2.54)	-	.50

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
 - For RoHS Case Styles: Tin plate over Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.

Tape & Reel Packaging TR-F5



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Evaluation Board and Circuit



TB-34



Schematic Diagram

Notes:

1. 75 Ohm BNC Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215