

Ultra Wideband RF Transformer

NCR2-Series

50Ω 3W Up to 18 GHz

The Big Deal

- Microwave Frequency Balun
- Ultra-Wideband Frequency Coverage, from 3.5 up to 18 GHz
- Miniature Size LTCC Package



Generic photo used for illustration purposes only

CASE STYLE: NF1846-1

Product Overview

The Mini-Circuits NCR2 family of ultra-wideband balun transformers covers a frequency range spanning 3.5 to 18 GHz with an impedance ratio of 1:2. They are commonly used for unbalanced to balanced applications. LTCC construction provides exceptional reliability, thermal stability, and a high degree of repeatability. A small footprint (0.08 x 0.10") offers flexibility of integration with RF integrated circuits.

Key Features

Feature	Advantages
Ultra-wide bandwidth	The NCR2 family of LTCC baluns covers many popular microwave frequency bands and is ideal for applications such as satellite communications, point to point radio, and electronic surveillance.
LTCC construction	Low Temperature Ceramic Co-fired construction offers a high degree of repeatability, temperature stability, and high power handling capabilities.
Miniature footprint, 0.079"x0.098"x0.035"	The miniature footprint of these LTCC baluns makes them easy to integrate with RF integrated circuits.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



RF Transformer

50Ω 12000 to 18000 MHz

NCR2-183-4+



Generic photo used for illustration purposes only

CASE STYLE: NF1846-1

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Input RF Power	3W
Permanent damage may occur if any of these limits are exceeded.	

Pad Connections

PRIMARY DOT (Unbalanced Port)	2
SECONDARY DOT (Balanced)	6
SECONDARY (Balanced)	4
GND Externally	1,3,5

Features

- wideband, 12000 to 18000 MHz
- miniature size, 0.079"x0.098"x0.035"
- LTCC construction
- low cost
- aqueous washable

Applications


- Point to Point
- ISM
- Radio navigation
- SATCOM

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Product Marking: TP+

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	L
.079	.098	.035	.027	.028	.014	.014	.028
2.01	2.49	0.89	0.69	0.71	0.36	0.36	0.71
M	N	P	Q	R	S	T	wt
.035	.07	.014	.016	--	.050	.100	grams
0.89	1.78	0.36	0.41	--	1.27	0.03	0.020

Demo Board MCL P/N: TB-745+
Suggested PCB Layout (PL-425)

NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010"±.001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 35166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Electrical Specifications at 25°C



Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Impedance Ratio (secondary/primary)			2		
Frequency Range		12000	—	18000	MHz
Insertion Loss*	12000 - 18000	—	0.6	2.5	dB
Amplitude Unbalance	12000 - 18000	—	2.0	3.8	dB
Phase Unbalance†	12000 - 17000	—	10	20	Degree
	17000 - 18000	—	15	25	

* Insertion Loss is referenced to mid-band loss, 0.45 dB. Reference Demo Board TB-745+.


† Relative to 180°

Typical Performance Data at 25°C

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (Deg.)
12000.0	0.23	19.89	3.21	13.72
12500.0	0.24	20.93	3.23	7.42
13000.0	0.25	19.52	3.01	0.37
13600.0	0.19	24.37	2.67	6.28
14000.0	0.10	25.53	1.82	10.09
14600.0	0.04	26.96	0.97	13.36
15000.0	0.04	23.29	0.18	13.44
15500.0	0.13	20.15	0.70	13.04
16000.0	0.26	15.33	1.21	10.09
17950.0	0.82	9.78	2.28	12.08



configuration E1







Typical Performance Data

FREQUENCY (MHz)	AVERAGE INSERTION LOSS* (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE** (deg.)
12000	0.23	19.89	3.21	13.72
12100	0.23	19.67	3.26	12.02
12200	0.27	19.34	3.24	10.80
12300	0.24	19.60	3.28	9.20
12400	0.24	20.42	3.22	8.44
12500	0.24	20.93	3.23	7.42
12600	0.26	20.40	3.25	6.18
12700	0.28	19.04	3.20	4.29
12800	0.27	18.49	3.13	2.79
12900	0.27	18.58	3.05	1.06
13000	0.25	19.52	3.01	0.37
13200	0.21	21.84	2.99	2.38
13400	0.20	23.37	2.90	4.72
13600	0.19	24.37	2.67	6.28
13800	0.13	23.82	2.20	8.32
14000	0.10	25.53	1.82	10.09
14200	0.07	27.04	1.51	12.25
14400	0.04	30.20	1.14	12.85
14600	0.04	26.96	0.97	13.36
14800	0.05	23.49	0.71	13.22
15000	0.04	23.29	0.18	13.44
15250	0.09	20.34	0.18	14.12
15500	0.13	20.15	0.70	13.04
15600	0.14	19.11	0.69	13.57
15700	0.18	18.02	0.93	13.30
15800	0.22	17.21	1.10	10.86
15900	0.20	16.45	1.01	9.78
16000	0.26	15.33	1.21	10.09
16100	0.35	14.68	1.63	8.42
16200	0.32	14.65	1.74	5.73
16300	0.35	14.21	1.79	5.59
16400	0.45	13.61	2.08	5.26
16500	0.45	13.73	2.27	3.13
16600	0.46	13.55	2.17	2.18
16700	0.55	12.39	2.25	2.20
16800	0.60	11.74	2.35	0.08
16900	0.57	11.99	2.13	1.96
17000	0.57	11.80	1.99	2.01
17100	0.67	11.26	2.17	2.82
17200	0.66	11.45	2.19	5.02
17300	0.61	11.50	2.06	5.54
17400	0.71	10.78	2.27	5.01
17500	0.79	10.32	2.56	6.41
17650	0.76	10.51	2.40	8.90
17800	0.86	9.64	2.45	9.44
17950	0.82	9.78	2.28	12.08
18100	0.90	9.17	2.23	13.21

*Insertion Loss is referenced to mid-band loss, 0.45dB


**Relative to 180°

Typical Performance Data




Outline Dimensions

NF1846-1



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	P
NF1846-1	.079 (2.01)	.098 (2.49)	.035 (0.89)	.027 (0.69)	.028 (0.71)	.014 (0.36)	.012 (0.31)	-	-	-	.028 (0.71)	.035 (0.89)	.07 (1.78)	.014 (0.36)

CASE #.	Q	R	S	T	WT GRAMS
NF1846-1	.016 (0.41)	-	.050 (1.27)	.100 (2.54)	.020

Dimensions are in inches (mm). Tolerances $\pm .005$ unless specified.


Notes:

- Open style, ceramic base.
- Termination Finish:
For RoHS case style: Tin plate over Nickel plate.
All models, (+) suffix.



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000


Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.


Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION		REVISIONS				
	REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
	OR	M147198	NEW RELEASE	07/14/14	ITG	AVB

SUGGESTED MOUNTING CONFIGURATION
FOR NF1846-1 CASE STYLE, "06TE01" PIN CONNECTION.




NOTES:

1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .010"±.001". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED		INITIALS		DATE		Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235							
DIMENSIONS ARE IN INCHES		DRAWN	ITG	07/14/14		PL, 06TE01, NF1846-1, TB-745+							
TOLERANCES ON:		CHECKED	GF	07/14/14									
2 PL DECIMALS ±		APPROVED	AVB	07/14/14									
3 PL DECIMALS ± .005													
ANGLES ±													
FRACTIONS ±													
Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.													
ASHEETA1.DWG REV:A DATE:01/12/95						SIZE A		CODE IDENT 15542		DRAWING NO: 98-PL-425		REV: OR	
						FILE: 98PL425		SCALE: 15:1		SHEET: 1 OF 1			



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I