

# Engineering Development Model

## Power Splitter/Combiner

## LRPS-ED9779/1

### 2 Way-0°

#### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

**CASE STYLE : QQQ130**

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
<b>Frequency</b>		0.4		1000	MHz
<b>Isolation</b>	0.4 - 4 MHz		31		dB
	4 - 500 MHz		33		dB
	500 - 1000 MHz		20		dB
<b>Insertion Loss Above 3.0 dB</b>	0.4 - 4 MHz		0.23		dB
	4 - 500 MHz		0.25		dB
	500 - 1000 MHz		0.72		dB
<b>Phase Unbalance</b>	0.4 - 4 MHz		0.016		deg.
	4 - 500 MHz		0.045		deg.
	500 - 1000 MHz		0.388		deg.
<b>Amplitude Unbalance</b>	0.4 - 4 MHz		0.009		dB
	4 - 500 MHz		0.010		dB
	500 - 1000 MHz		0.135		dB
<b>VSWR</b>	SUM Port		1.07		(:1)
	OUT Ports		1.10		(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	2
PORT 1	4
PORT 2	6
GND EXT	1, 3, 5

#### Functional Diagram



# 2 Way-0° Power Splitter/Combiner

# LRPS-ED9779/1

## Typical Performance Data

FREQ. (MHz)	TOTAL LOSS <sup>1</sup> (dB)		AMP. UNBAL. (dB)	ISOLATION (dB) 1-2	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
0.4	3.31	3.32	0.01	24.18	0.01	0.4	1.10	1.31	1.31
0.5	3.29	3.30	0.01	25.44	0.02	0.5	1.09	1.27	1.27
0.9	3.24	3.25	0.00	28.71	0.01	0.9	1.06	1.20	1.19
1.0	3.23	3.24	0.01	29.29	0.05	1.0	1.05	1.19	1.18
2.0	3.18	3.19	0.01	33.48	0.00	2.0	1.03	1.13	1.13
3.0	3.17	3.17	0.01	36.18	0.01	3.0	1.03	1.11	1.11
4.0	3.16	3.17	0.01	38.09	0.01	4.0	1.02	1.10	1.10
5.0	3.16	3.17	0.01	39.63	0.00	5.0	1.02	1.10	1.09
6.0	3.16	3.17	0.01	40.66	0.01	6.0	1.02	1.09	1.09
7.0	3.16	3.16	0.00	41.43	0.00	7.0	1.02	1.09	1.09
8.0	3.16	3.16	0.00	42.02	0.02	8.0	1.02	1.09	1.09
9.0	3.15	3.16	0.01	42.32	0.01	9.0	1.02	1.09	1.08
10.0	3.15	3.16	0.01	42.53	0.01	10.0	1.02	1.08	1.08
20.0	3.17	3.17	0.00	41.46	0.00	20.0	1.02	1.08	1.08
30.0	3.18	3.18	0.01	39.41	0.02	30.0	1.03	1.08	1.08
40.0	3.18	3.19	0.01	37.93	0.02	40.0	1.03	1.08	1.08
50.0	3.19	3.19	0.00	36.65	0.01	50.0	1.03	1.08	1.08
60.0	3.20	3.20	0.01	35.52	0.05	60.0	1.04	1.08	1.08
70.0	3.20	3.21	0.01	34.62	0.02	70.0	1.04	1.08	1.07
80.0	3.21	3.22	0.00	33.73	0.04	80.0	1.04	1.08	1.07
90.0	3.22	3.22	0.00	32.99	0.08	90.0	1.05	1.07	1.07
100.0	3.22	3.23	0.01	32.31	0.05	100.0	1.05	1.07	1.07
125.0	3.24	3.24	0.00	30.86	0.05	125.0	1.06	1.07	1.07
150.0	3.26	3.26	0.00	29.59	0.09	150.0	1.06	1.07	1.07
175.0	3.26	3.27	0.01	28.54	0.05	175.0	1.07	1.07	1.06
200.0	3.28	3.28	0.01	27.62	0.11	200.0	1.08	1.06	1.06
225.0	3.29	3.29	0.00	26.81	0.09	225.0	1.08	1.06	1.05
250.0	3.31	3.32	0.01	26.08	0.09	250.0	1.09	1.06	1.05
275.0	3.32	3.33	0.01	25.42	0.11	275.0	1.10	1.05	1.05
300.0	3.33	3.34	0.01	24.83	0.06	300.0	1.10	1.05	1.04
325.0	3.34	3.36	0.01	24.30	0.07	325.0	1.11	1.04	1.04
350.0	3.36	3.38	0.02	23.83	0.05	350.0	1.11	1.04	1.04
375.0	3.36	3.39	0.03	23.38	0.07	375.0	1.12	1.04	1.03
400.0	3.38	3.41	0.03	22.99	0.08	400.0	1.12	1.03	1.03
500.0	3.44	3.49	0.05	21.74	0.03	500.0	1.14	1.02	1.04
600.0	3.50	3.57	0.07	20.98	0.05	600.0	1.15	1.03	1.06
700.0	3.56	3.66	0.10	20.62	0.17	700.0	1.15	1.06	1.09
800.0	3.64	3.79	0.15	20.52	0.33	800.0	1.15	1.10	1.14
900.0	3.76	3.95	0.19	20.08	0.59	900.0	1.17	1.15	1.20
1000.0	4.02	4.28	0.25	18.16	1.16	1000.0	1.28	1.24	1.28






<sup>1</sup> Total Loss = Insertion Loss + 3dB Splitter Loss



# 2 Way-0° Power Splitter/Combiner

# LRPS-ED9779/1

## Typical Performance Curves



REV. X2  
LRPS-ED9779/1  
100707  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




# Case Style


# QQQ

QQQ130 (non-waterproof)  
QQQ828 (washable)

## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
QQQ130	.400 (10.16)	.31 (7.87)	.200 (5.08)	.10 (2.54)	.010 (.25)	.100 (2.54)	.050 (1.27)	.420 (10.67)	.120 (3.05)	.060 (1.52)	.100 (2.54)	.020 (.51)	.55
QQQ828			.050 (1.27)										.20

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Ceramic.
- Termination finish:
  - For RoHS Case Styles: Tin plate over Nickel plate.
  - For RoHS-5 Case Styles: Tin-Lead plate.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F10



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
24	16	7	10,20,50,100
		13	200,500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)

Note: Please consult individual model data sheet to determine device per reel availability.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/05/02	GF	DJ
A	M102713	ADDED NOTE 2 & "...WITH SMOBC", QQQ130/828 WAS QQQ569/828 CASE STYLE	01/18/06	MMG	LC

SUGGESTED MOUNTING CONFIGURATION FOR  
QQQ130/828 CASE STYLE, "gn" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN GF	07/17/02
TOLERANCES ON:	CHECKED HY	08/01/02
2 PL DECIMALS ±	APPROVED DJ	08/05/02
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, gn, QQQ130/828, LRPS/SCL, TB-100

Mini-Circuits®  
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-057	A
FILE:	98PL057	SCALE:	6:1
SHEET:	1	OF	1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215