CERAMIC BALUN

RF Transformer

NCS1-332+

50Ω 700 to 3300 MHz 1:1 Ratio

FEATURES

- Wideband, 700 to 3300 MHz
- Low insertion los, 1.0 dB
- Tiny size 0805
- LTCC construction
- Low cost

Generic photo used for illustration purposes only

CASE STYLE: GE0805C-9

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

APPLICATIONS

- LTE
- WLAN
- ISM
- WiFi

ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Impedance Ratio			1		
Frequency Range		700		3300	MHz
Insertion Loss [1] (average)	700 - 3300	—	0.9	1.8	dB
	1500 - 2700	—	0.7	—	
Amplitude Unbalance	700 - 3300	—	0.5	1.5	dB
	1500 - 2700	—	0.2	—	
Phase Unbalance[2]	700 - 3300	—	8	15	Degree
	1500 - 2700	—	7	—	
Input Return Loss	700 - 3300	—	13	—	dB
	1500 - 2700	—	18	—	

1. Reference Demo Board TB-910+ with auto port extension and impedance conversion at secondary and secondary dot.
2. Relative to 180°

MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power[3]	3W at 25°C

3. Passband rating, derate linearly to 1W at 100°C ambient
Permanent damage may occur if any of these limits are exceeded.

CONFIGURATION R



PAD CONNECTIONS

PRIMARY DOT (Unbalanced Port)	1
GND or DC feed + RF GND	2
SECONDARY DOT (Balanced)	3
SECONDARY (Balanced)	4
NO CONNECTION	6
GND	5

OUTLINE DRAWING



PRODUCT MARKING: N/A

DEMO BOARD MCL P/N: TB-910+
SUGGESTED PCB LAYOUT (PL-583)



NOTES:
1. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR FR4, GRADE IT-180TC (ITEQ CORP.); DIELECTRIC THICKNESS: .016±.0015; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

OUTLINE DIMENSIONS (Inches / mm)

A	B	C	D	E	F
.079	.049	.033	.014	.012	.012
2.0	1.24	0.84	0.36	0.30	0.30

G	H	J	K		wt
.026	.014	.039	.110		grams
0.66	0.36	1.00	2.80		.008

TAPE & REEL INFORMATION: F74

TYPICAL PERFORMANCE DATA[3]

Frequency (MHz)	Insertion Loss (dB)	Input Return Loss (dB)	Amplitude Unbalance (dB)	Phase Unbalance (deg)
700	0.84	12.45	0.46	8.18
800	0.78	13.13	0.47	8.09
1000	0.71	13.87	0.44	7.83
1500	0.62	16.41	0.19	6.80
2000	0.59	23.12	0.02	4.43
2200	0.60	27.91	0.06	3.04
2400	0.63	32.26	0.05	1.56
2600	0.66	30.44	0.00	0.03
3000	0.76	24.12	0.28	3.18
3300	0.90	20.03	0.63	4.92

3. Measured with Agilent E5071B network analyzer using impedance conversion and port extension.









NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

RF Transformer NCS1-332+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE[1] (Deg)
500	1.22	9.43	0.30	8.31
550	1.07	10.48	0.36	8.27
600	0.96	11.33	0.41	8.24
650	0.89	11.97	0.44	8.21
700	0.84	12.45	0.46	8.18
750	0.81	12.83	0.47	8.12
800	0.78	13.13	0.47	8.09
850	0.76	13.36	0.47	8.03
900	0.74	13.50	0.47	7.97
950	0.73	13.68	0.45	7.93
1000	0.71	13.87	0.44	7.83
1050	0.70	13.99	0.42	7.78
1100	0.69	14.17	0.40	7.71
1150	0.68	14.36	0.38	7.65
1200	0.67	14.56	0.35	7.56
1250	0.66	14.81	0.33	7.44
1300	0.65	15.09	0.30	7.33
1350	0.65	15.34	0.27	7.23
1400	0.64	15.64	0.25	7.11
1450	0.63	16.02	0.22	6.98
1500	0.62	16.41	0.19	6.80
1550	0.62	16.85	0.17	6.62
1600	0.61	17.31	0.14	6.44
1650	0.60	17.84	0.11	6.22
1700	0.60	18.38	0.09	6.01
1750	0.60	18.97	0.07	5.77
1800	0.59	19.68	0.05	5.59
1850	0.59	20.43	0.03	5.28
1900	0.59	21.23	0.01	5.00
1950	0.59	22.15	0.01	4.67
2000	0.59	23.12	0.02	4.43
2050	0.59	24.12	0.04	4.13
2100	0.59	25.16	0.04	3.76
2150	0.60	26.48	0.05	3.38
2200	0.60	27.91	0.06	3.04
2250	0.61	29.11	0.06	2.69
2300	0.62	30.31	0.06	2.31
2350	0.62	31.42	0.06	1.95
2400	0.63	32.26	0.05	1.56
2450	0.63	32.48	0.04	1.16
2500	0.64	32.01	0.03	0.78
2550	0.65	31.47	0.02	0.37
2600	0.66	30.44	0.00	0.03
2650	0.67	29.31	0.03	0.44
2700	0.68	28.54	0.05	0.87
2750	0.69	27.79	0.08	1.29
2800	0.70	26.86	0.11	1.69
2850	0.72	26.19	0.14	2.09
2900	0.73	25.58	0.18	2.47
2950	0.75	24.84	0.23	2.83
3000	0.76	24.12	0.28	3.18
3050	0.78	23.56	0.32	3.51
3100	0.80	22.89	0.38	3.84
3150	0.82	22.12	0.44	4.14
3200	0.84	21.48	0.49	4.43
3250	0.87	20.77	0.56	4.71
3300	0.90	20.03	0.63	4.92
3350	0.93	19.32	0.70	5.11
3400	0.97	18.62	0.78	5.29
3450	1.01	17.91	0.86	5.42
3500	1.05	17.21	0.94	5.49

[1] Relative to 180°

Typical Performance Data









GE0805C-9

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE #	A	B	C	D	E	F	G	H	J	K	WT.GRAM
GE0805C-9	.079 (2.00)	.049 (1.25)	.037 (0.95)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.014 (0.35)	.039 (1.00)	.110 (2.80)	.008

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .005

Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
   For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.

This document and its contents are the property of Mini-Circuits.

Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R



ILLUSTRATION 1

Applicable Case Styles	
GE0805C	JC0603C
GE0805C-1	JC0603C-4
GE0805C-1AP	JC0603C-6
GE0805C-7	
GE0805C-9	
GE0805C-10	
GE0805C-11	
GE0805C-12	



ILLUSTRATION 2

Applicable Case Styles	
GE0805C-2	JC0603C-1
GE0805C-3	JC0603C-2
GE0805C-4	JC0603C-3
GE0805C-5	JC0603C-5
GE0805C-6	JC0603C-7
GE0805C-8	
GE0805C-15	

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	4000

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M167036	NEW RELEASE	03/27/18	ITG	BK

SUGGESTED MOUNTING CONFIGURATION
FOR GE0805C-9 CASE STYLE, "06TR02" PIN CODE



NOTES:

1. TRACE WIDTH & GAP PARAMETERS ARE SHOWN FOR FR4, GRADE IT-180TC (ITEQ CORP.); DIELECTRIC THICKNESS: .016±.0015; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	03/26/18
TOLERANCES ON:	CHECKED	GF	03/27/18
2 PL DECIMALS ±	APPROVED	BK	03/27/18
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, 06TR02, GE0805C-9, TB-910+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-583	OR

FILE:	SCALE:	SHEET:
98PL583	15:1	1 OF 1

Evaluation Board and Circuit



TB-910-332+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: FR4 or equivalent,
   Dielectric Constant=4.6,
   Thickness=.016 inch.

Mini-Circuits®

Mini-Circuits

Environmental Specifications ENV06

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A

This document and its contents are the property of Mini-Circuits.