Engineering Development Model

Frequency Mixer MBA-EE7756/22

Level 7 (LO Power +7 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : SM2

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		**Min.**	**Typ.**	**Max.**	**Units**
Frequency	**LO** (fL to fU)	1770		5400	MHz
	RF (fL to fU)	1770		5400	MHz
	IF	10		1000	MHz
Conversion Loss			6.5		dB
LO-RF Isolation			21		dB
LO-IF Isolation			20		dB

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	10
RF	5
IF	3
GROUND	1, 2, 4, 6, 7, 8, 9

Frequency Mixer MBA-EE7756/22

Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)		
		@LO (dBm)		
		+4	+7	+10
1770.0	1800.0	8.87	9.04	8.84
1950.0	1980.0	8.37	7.87	7.84
2050.0	2080.0	7.90	7.57	7.37
2100.0	2130.0	7.72	7.22	7.18
2430.0	2460.0	6.45	6.12	6.42
2760.0	2790.0	5.77	5.60	5.73
3090.0	3120.0	5.78	5.44	5.74
3420.0	3450.0	5.77	5.43	5.73
3600.0	3630.0	6.06	5.73	5.86
3650.0	3680.0	6.06	5.73	5.86
3700.0	3730.0	6.03	5.70	6.00
3750.0	3780.0	6.22	5.88	6.02
3800.0	3830.0	6.21	5.87	6.17
3900.0	3930.0	6.35	6.02	6.32
4000.0	4030.0	6.51	6.18	6.48
4050.0	4080.0	6.51	6.34	6.64
4080.0	4110.0	6.69	6.35	6.65
4100.0	4130.0	6.65	6.31	6.78
4150.0	4180.0	6.64	6.47	6.77
4200.0	4230.0	6.82	6.49	6.79
4300.0	4330.0	6.81	6.48	6.78
4400.0	4430.0	6.77	6.61	6.91
4410.0	4440.0	6.77	6.61	6.91
4500.0	4530.0	6.77	6.61	6.91
4600.0	4630.0	6.93	6.60	7.07
4700.0	4730.0	7.08	6.75	7.05
4740.0	4770.0	7.09	6.92	7.06
4770.0	4800.0	7.10	6.93	7.23
4800.0	4830.0	7.25	6.91	7.21
5070.0	5100.0	7.55	7.22	7.35
5400.0	5430.0	8.03	7.70	7.83

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+4	+7	+10	+4	+7	+10
1800.0	25.8	26.3	24.8	9.5	10.2	11.2
1980.0	24.7	25.2	23.7	9.2	9.8	10.0
2080.0	23.7	24.2	23.0	8.7	9.2	9.2
2130.0	23.0	23.5	22.7	8.5	9.0	9.0
2460.0	22.3	22.7	21.2	8.7	8.8	8.2
2790.0	27.8	25.2	22.8	10.5	9.8	8.8
3120.0	26.0	24.7	23.0	12.7	11.5	10.2
3450.0	23.5	22.8	21.7	14.8	13.0	11.5
3630.0	22.8	22.0	20.7	16.3	14.0	12.2
3680.0	22.5	22.0	20.8	16.7	14.5	12.7
3730.0	22.2	21.5	20.3	17.0	14.7	12.7
3780.0	22.0	21.5	20.3	17.8	15.3	13.0
3830.0	21.8	21.2	20.3	18.3	15.8	13.7
3930.0	21.0	20.8	19.8	20.0	17.2	14.7
4030.0	20.2	20.2	19.2	21.0	18.7	16.0
4080.0	20.0	19.8	18.7	21.2	19.0	16.5
4110.0	19.8	19.7	18.5	21.2	19.0	16.8
4130.0	19.8	19.7	18.3	21.3	19.3	17.0
4180.0	19.5	19.3	18.0	21.5	19.2	17.0
4230.0	19.7	19.2	17.8	22.2	19.7	17.3
4330.0	19.3	19.0	17.5	23.8	20.7	18.2
4430.0	19.3	19.0	17.3	26.7	22.7	19.5
4440.0	19.2	18.8	17.3	26.8	22.7	19.5
4530.0	19.0	18.5	17.3	29.5	24.7	21.2
4630.0	18.5	18.2	16.8	32.5	27.5	22.7
4730.0	18.3	18.2	17.0	31.7	33.2	25.3
4770.0	18.2	18.0	17.0	30.2	36.5	26.7
4800.0	18.3	18.3	17.0	29.0	42.0	28.3
4830.0	18.3	18.3	17.0	27.8	47.5	29.2
5100.0	17.8	18.7	17.8	20.5	24.8	30.0
5430.0	17.8	19.3	19.2	15.8	18.0	19.3

Typical Performance Data

RF/LO (MHz)	RF VSWR (:1) @LO (dBm)			LO VSWR (:1) @LO (dBm)			IF (MHz)	IF VSWR (:1) @LO (dBm)		
	+4	+7	+10	+4	+7	+10		+4	+7	+10
1800.0	5.03	3.95	3.82	3.47	3.01	3.26	10.0	1.14	1.08	1.23
1980.0	3.95	3.26	3.17	2.24	2.67	3.01	20.0	1.14	1.08	1.23
2080.0	3.46	2.93	2.93	1.90	2.46	2.93	30.0	1.15	1.09	1.23
2130.0	3.26	2.80	2.80	1.76	2.32	2.80	50.0	1.17	1.10	1.23
2460.0	2.28	2.13	2.28	1.43	1.95	2.41	70.0	1.20	1.12	1.24
2790.0	2.01	2.01	2.17	1.61	2.07	2.46	100.0	1.24	1.17	1.23
3120.0	1.43	1.58	1.71	1.87	2.20	2.67	109.5	1.25	1.18	1.27
3450.0	1.46	1.50	1.61	1.67	1.71	1.95	150.0	1.34	1.24	1.31
3630.0	1.67	1.65	1.71	1.61	1.69	2.01	209.1	1.45	1.35	1.38
3680.0	1.69	1.65	1.71	1.64	1.78	2.13	250.0	1.55	1.42	1.43
3730.0	1.69	1.67	1.71	1.64	1.78	2.13	308.6	1.67	1.54	1.54
3780.0	1.71	1.69	1.73	1.74	1.90	2.28	350.0	1.77	1.61	1.61
3830.0	1.71	1.71	1.73	1.78	1.92	2.41	408.2	1.92	1.74	1.71
3930.0	1.78	1.81	1.83	1.85	1.98	2.46	450.0	2.01	1.83	1.76
4030.0	1.92	1.95	1.98	1.92	1.98	2.32	500.0	2.17	1.95	1.90
4080.0	1.98	2.04	2.10	1.95	1.98	2.32	507.7	2.20	1.98	1.88
4110.0	2.07	2.13	2.20	1.98	1.92	2.24	550.0	2.32	2.10	2.01
4130.0	2.07	2.13	2.20	1.98	1.92	2.20	607.3	2.51	2.28	2.10
4180.0	2.20	2.24	2.32	1.92	1.87	2.17	650.0	2.56	2.36	2.20
4230.0	2.28	2.37	2.46	1.90	1.81	2.13	706.8	2.73	2.51	2.51
4330.0	2.46	2.51	2.61	1.83	1.73	1.95	750.0	2.86	2.67	2.46
4430.0	2.61	2.61	2.73	1.83	1.71	1.98	800.0	3.09	2.80	2.56
4440.0	2.61	2.61	2.73	1.81	1.73	2.10	806.4	3.09	2.80	2.56
4530.0	2.61	2.61	2.73	1.77	1.71	2.01	905.9	3.18	3.01	2.73
4630.0	2.61	2.56	2.73	1.78	1.74	2.13	1000.0	3.57	3.36	2.93
4730.0	2.56	2.46	2.67	1.92	1.90	2.28	1005.5	3.46	3.26	2.93
4770.0	2.61	2.51	2.73	1.95	1.92	2.28	1105.0	3.69	3.46	3.09
4800.0	2.56	2.46	2.67	2.07	2.04	2.46	1204.5	4.09	3.95	3.36
4830.0	2.61	2.46	2.67	2.01	1.98	2.28	1304.1	4.09	3.81	3.35
5100.0	2.93	2.73	2.93	2.41	2.24	2.46	1403.6	4.26	3.82	3.26
5430.0	3.81	3.46	3.57	2.07	1.95	2.01	1503.2	3.69	3.46	3.01

Typical Performance Curves

Conversion Loss



LO-RF Isolation



LO-IF Isolation



RF VSWR



LO VSWR



IF VSWR



Case Style SM2

SM2

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

ADJACENT GROUND PINS SHALL BE CONNECTED TO EACH OTHER AND TO GROUND PAD

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P
SM2	.250 (6.35)	.300 (7.62)	.095 (2.41)	.290 (7.37)	.050 (1.27)	.015 (0.38)	.050 (1.27)	.060 (1.52)	.030 (0.76)	.080 (2.03)	.300 (7.62)	.100 (2.54)	.020 (0.51)	.015 (0.38)

CASE #	Q	R	WT. GRAM
SM2	.070 (1.78)	.014 (0.36)	.3

Dimensions are in inches (mm). Tolerances: ± .005

Notes:

1. Case material: Plastic encapsulation on Ceramic base.
2. Termination finish:
   For RoHS Case Styles: Tin plate over Nickel plate.
   For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits

Tape & Reel Packaging TR-F34

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M82272	NEW RELEASE	08/02/02	GF	DJ
A	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/16/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION FOR SM2 CASE STYLE, "ld" PIN CONNECTION



NOTES:
1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	GF	07/18/02
TOLERANCES ON:	CHECKED	WL	08/02/02
2 PL DECIMALS ±	APPROVED	DJ	08/02/02
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, ld, SM2, MBA, TB-99

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-066	A

FILE:	SCALE:	SHEET:
98PL066	8:1	1 OF 1

Evaluation Board and Circuit



TB-99



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers RO4350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV02T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.