CERAMIC BALUN


# RF Transformer

# NCS3-72+

50Ω 250 to 760 MHz 1:3 Ratio

## FEATURES

- Wideband, 250 to 760 MHz
- Low phase unbalance 8 deg. and amplitude unbalance, 0.3 dB typ.
- Miniature size 0805, 0.079"x0.049"x0.033"
- Good matching VSWR, 1.5:1 typ.
- LTCC construction
- Low cost
- Aqueous washable



*Generic photo used for illustration purposes only*

CASE STYLE: GE0805C-9

***+RoHS Compliant***

*The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications*

## APPLICATIONS

- VHF/UHF
- Signal process
- Instrumentation

## ELECTRICAL SPECIFICATIONS AT 25°C

| Parameter | Frequency (MHz) | Min. | Typ. | Max. | Units |
|---|---|---|---|---|---|
| Impedance Ratio (Secondary/Primary) | | | 3 | | |
| Frequency Range | | 250 | | 760 | MHz |
| Insertion Loss[1] | 250 - 760 | — | 0.9 | 1.3 | dB |
| Amplitude Unbalance | 250 - 760 | — | 0.3 | 1.0 | dB |
| Phase Unbalance[2] | 250 - 760 | — | 5 | 10 | Degree |


1. Reference Demo Board TB-626+
2. Relative to 180°

## MAXIMUM RATINGS

| Parameter | Ratings |
|---|---|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature | -55°C to 100°C |
| RF Power[3] | 2W at 25°C |

3. Passband rating , derate linearly to 1W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

## CONFIGURATION J





*Internal open circuit

## PAD CONNECTIONS


| | |
|---|---|
| PRIMARY DOT (Unbalanced Port) | 2 |
| PRIMARY (GND) | 1,3 |
| SECONDARY DOT (Balanced) | 4 |
| SECONDARY (Balanced) | 6 |
| NO CONNECTION | 5 |

## OUTLINE DRAWING




## PRODUCT MARKING: N/A

## DEMO BOARD MCL P/N: TB-626+
## SUGGESTED PCB LAYOUT (PL-348)




NOTES:
1. TRACE WIDTH IS SHOWN FOR REFERENCE ONLY.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

## OUTLINE DIMENSIONS (Inches / mm)

| A | B | C | D | E | F |
|---|---|---|---|---|---|
| .079 | .049 | .033 | .014 | .012 | .012 |
| 2.0 | 1.24 | 0.84 | 0.36 | 0.30 | 0.30 |


| G | H | J | K | wt |
|---|---|---|---|---|
| .026 | .014 | .039 | .110 | grams |
| 0.66 | 0.36 | 1.00 | 2.80 | .008 |


## TAPE & REEL INFORMATION: F74


## TYPICAL PERFORMANCE DATA[3]

| Frequency (MHz) | Insertion Loss (dB) | Input Return Loss (dB) | Amplitude Unbalance (dB) | Phase Unbalance (deg) |
|---|---|---|---|---|
| 250 | 0.75 | 16.28 | 0.32 | 4.47 |
| 300 | 0.80 | 13.24 | 0.30 | 5.31 |
| 350 | 0.87 | 11.80 | 0.29 | 5.81 |
| 400 | 0.89 | 11.38 | 0.28 | 5.93 |
| 450 | 0.89 | 11.58 | 0.27 | 5.64 |
| 500 | 0.86 | 12.18 | 0.25 | 4.90 |
| 550 | 0.83 | 13.14 | 0.24 | 3.73 |
| 600 | 0.80 | 14.39 | 0.22 | 2.03 |
| 650 | 0.78 | 15.79 | 0.19 | 0.17 |
| 760 | 0.84 | 16.54 | 0.07 | 6.63 |

3. Measured with Agilent E5071B network analyzer using impedance conversion and port extension.




**NOTES**

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

# RF Transformer NCS3-72+

## *Typical Performance Data*


| FREQUENCY (MHz) | INSERTION LOSS* (dB) | INPUT RETURN LOSS (dB) | AMPLITUDE UNBALANCE (dB) | PHASE UNBALANCE** (deg) |
|---|---|---|---|---|
| 140 | 3.74 | 3.45 | 0.35 | 1.25 |
| 160 | 2.29 | 5.81 | 0.34 | 2.03 |
| 180 | 1.45 | 8.90 | 0.33 | 2.66 |
| 200 | 1.02 | 12.51 | 0.33 | 3.26 |
| 220 | 0.83 | 15.73 | 0.32 | 3.78 |
| 240 | 0.76 | 16.69 | 0.32 | 4.24 |
| 250 | 0.75 | 16.28 | 0.32 | 4.47 |
| 260 | 0.75 | 15.63 | 0.31 | 4.68 |
| 270 | 0.76 | 14.94 | 0.31 | 4.83 |
| 280 | 0.77 | 14.30 | 0.31 | 4.97 |
| 290 | 0.79 | 13.74 | 0.31 | 5.13 |
| 300 | 0.80 | 13.24 | 0.30 | 5.31 |
| 310 | 0.82 | 12.85 | 0.30 | 5.42 |
| 320 | 0.83 | 12.51 | 0.29 | 5.52 |
| 340 | 0.86 | 11.99 | 0.29 | 5.73 |
| 350 | 0.87 | 11.80 | 0.29 | 5.81 |
| 360 | 0.87 | 11.65 | 0.28 | 5.85 |
| 380 | 0.89 | 11.46 | 0.28 | 5.92 |
| 400 | 0.89 | 11.38 | 0.28 | 5.93 |
| 410 | 0.89 | 11.39 | 0.28 | 5.90 |
| 420 | 0.89 | 11.41 | 0.27 | 5.86 |
| 440 | 0.89 | 11.50 | 0.27 | 5.74 |
| 450 | 0.89 | 11.58 | 0.27 | 5.64 |
| 460 | 0.88 | 11.67 | 0.26 | 5.52 |
| 480 | 0.87 | 11.89 | 0.26 | 5.23 |
| 490 | 0.86 | 12.02 | 0.25 | 5.12 |
| 500 | 0.86 | 12.18 | 0.25 | 4.90 |
| 510 | 0.85 | 12.34 | 0.25 | 4.72 |
| 520 | 0.85 | 12.51 | 0.25 | 4.50 |
| 540 | 0.83 | 12.91 | 0.24 | 4.02 |
| 550 | 0.83 | 13.14 | 0.24 | 3.73 |
| 560 | 0.82 | 13.36 | 0.24 | 3.42 |
| 570 | 0.81 | 13.61 | 0.23 | 3.12 |
| 580 | 0.81 | 13.86 | 0.23 | 2.81 |
| 590 | 0.80 | 14.12 | 0.23 | 2.40 |
| 600 | 0.80 | 14.39 | 0.22 | 2.03 |
| 610 | 0.79 | 14.67 | 0.21 | 1.63 |
| 620 | 0.79 | 14.95 | 0.21 | 1.20 |
| 630 | 0.78 | 15.25 | 0.21 | 0.76 |
| 640 | 0.78 | 15.52 | 0.20 | 0.30 |
| 650 | 0.78 | 15.79 | 0.19 | 0.17 |
| 660 | 0.78 | 16.03 | 0.18 | 0.65 |
| 670 | 0.78 | 16.27 | 0.17 | 1.15 |
| 680 | 0.78 | 16.47 | 0.16 | 1.69 |
| 690 | 0.78 | 16.64 | 0.15 | 2.25 |
| 700 | 0.79 | 16.78 | 0.15 | 2.81 |
| 710 | 0.79 | 16.87 | 0.13 | 3.38 |
| 720 | 0.80 | 16.92 | 0.12 | 4.00 |
| 730 | 0.81 | 16.90 | 0.11 | 4.61 |
| 740 | 0.81 | 16.83 | 0.10 | 5.24 |
| 750 | 0.83 | 16.70 | 0.08 | 5.95 |
| 760 | 0.84 | 16.54 | 0.07 | 6.63 |
| 770 | 0.85 | 16.34 | 0.05 | 7.33 |
| 780 | 0.87 | 16.08 | 0.04 | 8.05 |
| 800 | 0.91 | 15.52 | 0.01 | 9.58 |
| 850 | 1.02 | 13.93 | 0.10 | 13.55 |


* Reference Demo Board TB-626+


**Phase Unbalance is relative to 180˚


# RF Transformer NCS3-72+

## *Typical Performance Data*











**GE0805C-9**

## Outline Dimensions




## PCB Land Pattern




Suggested Layout,
Tolerance to be within ±.002

| CASE # | A | B | C | D | E | F | G | H | J | K | WT.GRAM |
|---|---|---|---|---|---|---|---|---|---|---|---|
| GE0805C-9 | .079 (2.00) | .049 (1.25) | .037 (0.95) | .014 (0.35) | .012 (0.30) | .012 (0.30) | .026 (0.65) | .014 (0.35) | .039 (1.00) | .110 (2.80) | .008 |

**Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .005**

### Notes:

1. Open style, ceramic base.
2. Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
   For RoHS-5 Case Styles: Tin-Lead plate over Nickel plate. All models, no (+) suffix.


This document and its contents are the property of Mini-Circuits.

# Tape & Reel Packaging TR-F114

DEVICE ORIENTATION IN T&R





ILLUSTRATION 1

| Applicable Case Styles | |
|---|---|
| GE0805C | JC0603C |
| GE0805C-1 | JC0603C-4 |
| GE0805C-1AP | JC0603C-6 |
| GE0805C-7 | |
| GE0805C-9 | |
| GE0805C-10 | |
| GE0805C-11 | |
| GE0805C-12 | |





ILLUSTRATION 2

| Applicable Case Styles | |
|---|---|
| GE0805C-2 | JC0603C-1 |
| GE0805C-3 | JC0603C-2 |
| GE0805C-4 | JC0603C-3 |
| GE0805C-5 | JC0603C-5 |
| GE0805C-6 | JC0603C-7 |
| GE0805C-8 | |
| GE0805C-15 | |

| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel | |
|---|---|---|---|---|
| 8 | 4 | 7 | Small quantity standards (see note) | 20 |
| | | | | 50 |
| | | | | 100 |
| | | | | 200 |
| | | | | 500 |
| | | | | 1000 |
| | | | Standard | 4000 |

Note: Please Consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf


Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified


This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

| REVISIONS | | | | | |
|---|---|---|---|---|---|
| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
| OR | M132367 | NEW RELEASE | 07/20/11 | GF | ABD |
| A | M151441 | UPDATED TRACE WIDTH INFO | 06/05/15 | GF | WP |
| | | | | | |
| | | | | | |

# SUGGESTED MOUNTING CONFIGURATION FOR GE0805C-1 CASE STYLE, "06TJ01" PIN CODE




## NOTES:

1. TRACE WIDTH IS SHOWN FOR REFERENCE ONLY.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | | INITIALS | DATE |
|---|---|---|---|
| DIMENSIONS ARE IN INCHES | DRAWN | GF | 06/20/11 |
| TOLERANCES ON: | CHECKED | IL | 07/20/11 |
| 2 PL DECIMALS ± | APPROVED | ABD | 07/20/11 |
| 3 PL DECIMALS ± .005 | | | |
| ANGLES ± | | | |
| FRACTIONS ± | | | |


Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, 06TJ01, GE0805C-1, TB-626+


| SIZE | CODE IDENT | DRAWING NO: | REV: |
|---|---|---|---|
| A | 15542 | 98-PL-348 | A |

| FILE: | SCALE: | SHEET: |
|---|---|---|
| 98PL348 | 20:1 | 1 OF 1 |

# Evaluation Board and Circuit




TB-626+




Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: RO4350 or equivalent,
   Dielectric Constant=3.5, Thickness=.010 inch.

Mini-Circuits®


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

# Environmental Specifications ENV06

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|---|---|---|
| Operating Temperature | -55° to 100°C<br>Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C<br>Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |


This document and its contents are the property of Mini-Circuits.