

Engineering Development Model

Frequency Mixer

MCA-ED12552/2

Level 17 (LO Power +17 dBm)

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DZ883

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency	LO (fL to fU)	1675		2360	MHz
	RF (fL to fU)	1675		2360	MHz
	IF	80		465	MHz
Conversion Loss	Total Range		7.6		dB
LO-RF Isolation			43		dB
LO-IF Isolation			27		dB
IP3 Input			+26.78		dBm

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
LO	10
RF	5
IF	3
GROUND	1, 2, 4, 6, 7, 8, 9

Frequency Mixer

MCA-ED12552/2

Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)			LO (MHz)	RF (MHz)	IP3 Input (dBm)
		@LO (dBm)				@LO (dBm)			@LO (dBm)					@LO (dBm)
		+14	+17	+20		+14	+17	+20	+14	+17	+20			+17
1480.0	1205.0	8.86	8.09	7.57	1205.0	37.8	36.4	35.5	29.8	30.4	30.9	1205.0	1480.0	28.8
1512.5	1237.5	9.03	8.26	7.74	1237.5	37.4	36.1	35.0	29.2	29.7	30.2	1237.5	1512.5	38.1
1545.0	1270.0	8.93	8.24	7.77	1270.0	36.5	35.2	34.3	28.1	28.6	29.1	1270.0	1545.0	31.2
1577.5	1302.5	9.00	8.30	7.82	1302.5	35.5	34.3	33.4	27.0	27.5	28.0	1302.5	1577.5	25.5
1610.0	1335.0	8.75	8.11	7.68	1335.0	34.3	33.2	32.3	25.9	26.4	26.8	1335.0	1610.0	25.9
1642.5	1367.5	8.36	7.77	7.38	1367.5	32.4	31.4	30.5	24.6	24.9	25.2	1367.5	1642.5	27.0
1675.0	1400.0	8.37	7.83	7.47	1400.0	30.4	29.6	28.8	23.4	23.7	24.0	1400.0	1675.0	25.2
1707.5	1432.5	8.57	8.00	7.61	1432.5	29.1	28.4	27.7	23.5	23.8	23.9	1432.5	1707.5	27.9
1740.0	1465.0	8.70	8.12	7.71	1465.0	29.4	29.1	28.7	25.3	25.7	25.8	1465.0	1740.0	26.2
1772.5	1497.5	8.41	7.90	7.55	1497.5	31.2	31.2	31.1	26.8	27.0	27.1	1497.5	1772.5	28.6
1805.0	1530.0	8.03	7.60	7.32	1530.0	32.5	32.5	32.2	27.1	27.4	27.5	1530.0	1805.0	25.3
1837.5	1562.5	7.71	7.44	7.27	1562.5	33.1	33.0	32.6	27.5	28.9	30.6	1562.5	1837.5	29.4
1870.0	1595.0	7.88	7.61	7.45	1595.0	34.9	34.8	34.4	28.5	30.4	32.1	1595.0	1870.0	27.6
1902.5	1627.5	8.10	7.90	7.77	1627.5	38.2	38.7	38.8	27.9	29.4	30.8	1627.5	1902.5	28.3
1935.0	1660.0	7.90	7.74	7.65	1660.0	40.2	39.9	38.5	25.9	26.9	27.7	1660.0	1935.0	28.5
1967.5	1692.5	7.61	7.55	7.54	1692.5	37.9	37.6	36.5	24.8	25.7	26.5	1692.5	1967.5	29.2
2000.0	1725.0	7.52	7.49	7.51	1725.0	37.6	37.4	36.5	23.7	24.6	25.5	1725.0	2000.0	30.1
2030.0	1755.0	7.44	7.40	7.42	1755.0	39.1	38.9	38.0	23.5	24.5	25.4	1755.0	2030.0	30.1
2060.0	1785.0	7.54	7.52	7.56	1785.0	42.2	41.8	40.6	23.2	24.1	25.1	1785.0	2060.0	29.8
2090.0	1815.0	7.71	7.64	7.67	1815.0	45.7	45.2	43.7	23.2	24.1	24.9	1815.0	2090.0	28.0
2120.0	1845.0	7.55	7.49	7.51	1845.0	49.0	49.5	48.2	24.3	25.3	26.2	1845.0	2120.0	27.7
2150.0	1875.0	7.67	7.54	7.51	1875.0	49.9	51.4	50.5	25.2	26.3	27.3	1875.0	2150.0	29.6
2180.0	1905.0	7.63	7.42	7.34	1905.0	51.5	53.2	52.7	26.0	27.3	28.5	1905.0	2180.0	28.5
2210.0	1935.0	7.40	7.11	7.00	1935.0	54.5	56.0	56.5	27.1	28.8	30.4	1935.0	2210.0	27.2
2240.0	1965.0	7.62	7.20	7.02	1965.0	59.0	57.8	56.8	27.9	29.7	31.3	1965.0	2240.0	24.9
2270.0	1995.0	7.74	7.28	7.09	1995.0	68.5	65.4	62.4	28.5	30.0	31.2	1995.0	2270.0	23.0
2300.0	2025.0	8.07	7.45	7.16	2025.0	55.0	56.5	59.2	29.1	30.2	30.6	2025.0	2300.0	21.3
2330.0	2055.0	8.41	7.70	7.36	2055.0	51.4	52.3	54.2	29.7	30.2	30.2	2055.0	2330.0	20.5
2360.0	2085.0	8.60	7.77	7.35	2085.0	50.8	51.7	52.6	30.3	30.3	29.9	2085.0	2360.0	19.2
2390.0	2115.0	9.28	8.26	7.73	2115.0	50.5	51.0	51.0	31.3	30.9	30.3	2115.0	2390.0	18.4
2420.0	2145.0	9.32	8.24	7.69	2145.0	50.6	50.4	49.6	32.2	31.5	30.8	2145.0	2420.0	18.9
2450.0	2175.0	9.74	8.46	7.78	2175.0	49.7	49.2	48.0	33.1	32.0	31.2	2175.0	2450.0	19.6

Frequency Mixer

MCA-ED12552/2







Typical Performance Data

RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)		
	@LO (dBm)			@LO (dBm)				@LO (dBm)		
	+14	+17	+20	+14	+17	+20		+14	+17	+20
1205.0	2.84	2.57	2.36	1.41	1.41	1.42	4.0	1.60	1.65	1.75
1237.5	3.03	2.73	2.48	1.37	1.37	1.37	5.5	1.37	1.45	1.56
1270.0	2.80	2.53	2.31	1.38	1.38	1.39	7.0	1.26	1.36	1.46
1302.5	2.62	2.38	2.20	1.39	1.39	1.41	8.5	1.20	1.28	1.37
1335.0	2.76	2.48	2.27	1.38	1.38	1.38	10.0	1.14	1.20	1.26
1367.5	2.42	2.21	2.05	1.43	1.44	1.46	45.0	1.15	1.24	1.33
1400.0	2.48	2.26	2.10	1.44	1.46	1.46	80.0	1.28	1.46	1.64
1432.5	2.43	2.21	2.05	1.46	1.47	1.48	115.0	1.34	1.52	1.70
1465.0	2.24	2.07	1.95	1.52	1.54	1.58	150.0	1.36	1.48	1.60
1497.5	2.36	2.17	2.03	1.55	1.57	1.58	185.0	1.46	1.55	1.68
1530.0	2.12	1.99	1.88	1.68	1.70	1.72	220.0	1.53	1.60	1.73
1562.5	2.02	1.84	1.67	1.84	1.86	1.91	255.0	1.62	1.73	1.92
1595.0	1.84	1.63	1.48	1.95	1.98	1.98	290.0	1.69	1.80	1.99
1627.5	1.50	1.38	1.31	2.36	2.42	2.55	325.0	1.79	1.92	2.13
1660.0	1.47	1.37	1.32	2.77	2.85	2.87	360.0	1.78	1.86	1.99
1692.5	1.42	1.32	1.28	3.58	3.69	3.83	395.0	1.81	1.83	1.90
1725.0	1.36	1.28	1.26	5.31	5.55	6.15	430.0	1.85	1.84	1.90
1755.0	1.38	1.29	1.26	5.79	5.91	5.74	465.0	1.87	1.80	1.80
1785.0	1.35	1.25	1.23	8.16	8.32	8.44	500.0	2.00	1.86	1.79
1815.0	1.32	1.22	1.21	8.42	8.42	8.63	550.0	2.11	1.92	1.80
1845.0	1.38	1.23	1.18	6.92	6.80	6.79	600.0	2.43	2.16	1.98
1875.0	1.41	1.24	1.16	6.66	6.50	6.46	650.0	2.76	2.43	2.18
1905.0	1.43	1.24	1.15	5.40	5.27	5.17	700.0	3.02	2.62	2.34
1935.0	1.55	1.31	1.17	4.44	4.32	4.29	750.0	3.40	2.91	2.57
1965.0	1.63	1.37	1.20	4.02	3.92	3.85	800.0	3.76	3.19	2.79
1995.0	1.68	1.39	1.20	3.54	3.47	3.41	900.0	4.01	3.43	3.03
2025.0	1.75	1.43	1.23	3.12	3.06	3.04	1000.0	4.07	3.47	3.04
2055.0	1.83	1.48	1.25	2.89	2.85	2.81	1100.0	3.91	3.28	2.89
2085.0	1.87	1.51	1.26	2.66	2.63	2.60	1150.0	3.74	3.08	2.68
2115.0	1.90	1.53	1.27	2.43	2.40	2.40	1200.0	3.49	2.82	2.43
2145.0	1.98	1.57	1.30	2.30	2.28	2.26	1300.0	3.08	2.42	2.03
2175.0	2.02	1.59	1.31	2.18	2.16	2.13	1400.0	2.41	1.89	1.60


Frequency Mixer

MCA-ED12552/2


Typical Performance Curves




IF VSWR



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm.002$


CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
DZ883	.30 (7.62)	.250 (6.35)	.190 (4.83)	.266 (6.76)	.050 (1.27)	.050 (1.27)	.012 (0.30)	.029 (0.74)	.004 (0.10)	.085 (2.16)	.296 (7.52)	.030 (0.76)	0.5

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm.01$; 3Pl. $\pm.005$

Notes:

- Case material: Ceramic.
- Termination finish:
 - For RoHS Case Styles: Tin plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M81781	UPDATED PCB LAYOUT	06/07/02	GF	DJ
B	M82377	UPDATED DRAWING	07/31/02	AV	WL
C	M102713	ADDED NOTE 2 & "...WITH SMOBC"	01/17/06	MMG	IL
D	M135488	ADDED DZ1650, CHANGED PIN CONN.	02/02/12	GF	DJ


SUGGESTED MOUNTING CONFIGURATION FOR
DZ883, DZ885 & DZ1650 CASE STYLES, "10MX01" PIN CONNECTION



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

AV

05/08/02

TOLERANCES ON:

CHECKED

DB

05/16/02

2 PL DECIMALS ± .005


APPROVED

WL

05/16/02

ANGLES ±

FRACTIONS ±



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, 10MX01, DZ883/885/1650, TB-144

SIZE

CODE IDENT

DRAWING NO:

REV:

A

15542

98-PL-045

D

FILE: 98PL045

SCALE:


8:1

SHEET:


1 OF 1

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit




TB-144



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215