



Mini-Circuits®

MINIATURE CERAMIC

Fixed Attenuator

PAT-12+

50Ω 1 W 12 dB DC to 7 GHz

FEATURES

- Wideband, DC to 7 GHz
- Excellent VSWR Through Entire Band
- Miniature Size
- Aqueous Washable

APPLICATIONS

- Power Leveling
- Impedance Match Improvement



Generic photo used for illustration purposes only

CASE STYLE: AF320

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25°C

| Parameter | Condition (GHz) | Min. | Typ. | Max. | Unit |
|------------------------------------|-----------------|------|--------|------|------|
| Frequency Range | | DC | | 7 | GHz |
| Attenuation, Nominal | | | 12±0.6 | | dB |
| Attenuation, Flatness ¹ | DC - 1 | | | 0.5 | dB |
| | DC - 2.5 | | | 0.6 | |
| | DC - 7 | | | 1.8 | |
| VSWR | DC - 1 | | | 1.3 | :1 |
| | DC - 2.5 | | | 1.4 | |
| | DC - 7 | | | 1.5 | |
| Input Power ² | | | | 1.0 | W |

1. Flatness = variation over band divided by 2.

2. RF power at +25°C case temperature: 1 Watt. Derate linearly to 0.1 Watt at +100°C.

ABSOLUTE MAXIMUM RATINGS

| Parameter | Ratings |
|-----------------------|-----------------|
| Operating Temperature | -55°C to +100°C |
| Storage Temperature | -55°C to +100°C |

Permanent damage may occur if any of these limits are exceeded.

REV. J
ECO-024219
PAT-12+
MCL NY
250114





Mini-Circuits

MINIATURE CERAMIC

Fixed Attenuator


PAT-12+

50Ω 1 W 12 dB DC to 7 GHz

PIN CONNECTIONS

| | |
|--------|-----|
| INPUT | 1 |
| OUTPUT | 3 |
| GROUND | 2,4 |

DEMO BOARD MCL P/N: TB-319
SUGGESTED PCB LAYOUT (PL-208)




NOTES:


- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" \pm .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern




Suggested Layout,
Tolerance to be within $\pm .002$

OUTLINE DIMENSIONS (Inch mm)

| A | B | C | D | E | F | G |
|------|------|------|------|------|------|-------|
| .200 | .100 | .020 | .070 | .068 | .057 | .005 |
| 5.08 | 2.54 | 0.51 | 1.78 | 1.73 | 1.45 | 0.13 |
| H | J | K | L | M | N | wt |
| -- | .230 | .065 | .060 | .080 | .040 | grams |
| -- | 5.84 | 1.65 | 1.52 | 2.03 | 1.02 | 0.04 |

TAPE & REEL INFORMATION: F26

PRODUCT MARKING



Marking may contain other features or characters for internal lot control

Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 2 OF 2



Mini-Circuits

MINIATURE CERAMIC



Fixed Attenuator

PAT-12+

50Ω 1 W 12 dB DC to 2.5 GHz

TYPICAL PERFORMANCE DATA AND CHARTS

| Frequency (MHz) | Attenuation (dB) | VSWR (:1) |
|-----------------|------------------|-----------|
| 50.00 | 11.69 | 1.05 |
| 796.25 | 11.77 | 1.07 |
| 1542.50 | 11.88 | 1.09 |
| 2288.75 | 11.98 | 1.10 |
| 3035.00 | 12.18 | 1.11 |
| 3781.25 | 12.19 | 1.10 |
| 4527.50 | 12.26 | 1.09 |
| 5273.75 | 12.46 | 1.07 |
| 6020.00 | 12.73 | 1.09 |
| 7015.00 | 13.09 | 1.15 |



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data

| FREQUENCY (MHz) | ATTENUATION (dB) | RETURN LOSS (dB) |
|--------------------|---------------------|---------------------|
| 50.00 | 11.69 | 31.95 |
| 796.25 | 11.77 | 29.70 |
| 1542.50 | 11.88 | 27.06 |
| 2288.75 | 11.98 | 26.09 |
| 3035.00 | 12.18 | 25.75 |
| 3781.25 | 12.19 | 26.09 |
| 4527.50 | 12.26 | 27.58 |
| 5273.75 | 12.46 | 29.83 |
| 6020.00 | 12.73 | 27.35 |
| 7015.00 | 13.09 | 23.13 |

REV. X1
PAT-12+
061108
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED  RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




Patent Pending The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


Attenuation




Return Loss



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE # | A | B | C | D | E | F | G | H | J | K | L | M | N | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|---|----------------|----------------|----------------|----------------|----------------|----------|
| AF320 | .200 (5.08) | .100 (2.54) | .020 (0.51) | .070 (1.78) | .068 (1.73) | .057 (1.45) | .005 (0.13) | - | .230 (5.84) | .065 (1.65) | .060 (1.52) | .080 (2.03) | .040 (1.02) | .04 |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Ceramic.
- Termination material:
Nickel-Iron alloy 42.
- Termination finish:
For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. (See Data Sheet)
For RoHS-5 Case Styles: Tin-Lead plate.
- Termination (1):
May have diagonal cut. Input and output interchangeable for PAT models only.
- Special Tolerances: Termination width $\pm .005$ inch, termination thickness $\pm .002$ inch, cap diameter $\pm .005$ inch.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|-----------------------|----------|-----|------|
| OR | M100749 | NEW RELEASE | 09/19/05 | MMG | MM |
| A | M102713 | ADDED "...WITH SMOBC" | 01/12/06 | GT | IL |
| | | | | | |


[illegible]

1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" \pm .002"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit




TB-319



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|--|---|
| Operating Temperature | -54° to 100°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -65° to 150° C Ambient Environment | Individual Model Data Sheet |
| Autoclave | 15 psig, 100% RH, 121°C, 96 hours | JESD22-A102-C, Condition C |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Mechanical Shock | 1.5Kg, 0.5 ms, 5 shock pulses, Y1 direction only | MIL-STD-883, Method 2002, Condition B, except Y1 direction only |
| Vibration (Variable Frequency) | 50g peak | MIL-STD-883, Method 2007, Condition B |
| Constant Acceleration | Y1 plane only, 5 Kg | MIL-STD-883, Method 2001, Condition A, except Y1 plane only |
| Seal | Perfluorocarbon gross leak | MIL-STD-883, Method 1014, Condition C |
| HAST | 130°C, 85% RH, 96 hours | JESD22-A110 |
| Solderability | 10X Magnification | J-STD-002, Para 4.2.5, Test S, 95% Coverage |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1 |

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|-------------------------|
| Moisture Sensitivity: Level 1 | Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 260°C peak | J-STD-020 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |