


Plug-In

NON-CATALOG

Power Splitter/Combiner

PSC-10-1+

10 Way-0° 50Ω 1 to 150 MHz



CASE STYLE: E10

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.87W max.

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

SUM PORT	29
PORT 1	7
PORT 2	16
PORT 3	31
PORT 4	24
PORT 5	9
PORT 6	2
PORT 7	26
PORT 8	17
PORT 9	4
PORT 10	5
GROUND	all other pins
CASE GROUND	all other pins
NOT USED	15

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
1.580	1.620	.380	.410	.770	.810	.030
40.13	41.15	9.65	10.41	19.56	20.57	0.76
H	J	K	L	wt		
.200	.10	.20	.14	grams		
5.08	2.54	5.08	3.56	23.0		

Features

- low insertion loss, 0.4 dB typ.
- good isolation, 27 dB typ.
- excellent amplitude unbalance, 0.3 dB typ.
- rugged welded case

Applications

- HF/VHF
- amateur radio
- FM broadcasting

Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)			INSERTION LOSS (dB) ABOVE 10 dB			PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)								
	L		M	U	L		M	U	L		M	U						
	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.						
f _L -f _U																		
1-150	36	23	27	23	23	18	0.3	0.6	0.4	0.8	1.0	1.3	3	6	10	0.2	0.3	0.4

L = low range [f_L to 10 f_L] M = mid range [10 f_L to f_U/2] U = upper range [f_U/2 to f_U]

Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)	Amplitude Unbalance (dB)	Isolation (dB)		Phase Unbalance (deg.)	VSWR S	VSWR 1
			1-2	1-6			
1.00	10.48	0.04	33.61	52.48	0.24	1.12	1.37
5.00	10.31	0.04	37.77	59.69	0.40	1.07	1.17
10.00	10.31	0.03	38.38	60.63	0.67	1.08	1.14
20.00	10.34	0.03	36.88	57.86	1.29	1.11	1.13
50.00	10.47	0.06	31.99	51.48	3.16	1.20	1.12
60.00	10.51	0.08	30.90	50.14	3.76	1.24	1.11
70.00	10.57	0.08	29.99	49.39	4.32	1.26	1.11
80.00	10.61	0.09	29.29	48.27	4.93	1.29	1.10
90.00	10.66	0.10	28.72	47.59	5.42	1.31	1.09
100.00	10.68	0.13	28.31	46.91	6.06	1.33	1.08
110.00	10.70	0.13	28.05	46.24	6.58	1.34	1.07
120.00	10.71	0.14	27.91	45.72	7.11	1.34	1.07
130.00	10.73	0.16	27.91	45.17	7.57	1.33	1.06
140.00	10.76	0.17	28.06	44.65	8.11	1.31	1.06
150.00	10.79	0.20	28.36	44.21	8.72	1.30	1.06

1. Total Loss = Insertion Loss + 10dB splitter loss.



electrical schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



10 Way-0° Power Splitter/Combiner

PSC-10-1+

Typical Performance Data






FREQ. (MHz)	TOTAL LOSS ¹ (dB)	AMP. UNBAL. (dB)	ISOLATION (dB)		PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)	
			Adjacent	Opposite			S	OUTPUTS
1.0	10.48	0.04	33.61	52.48	0.24	1.0	1.12	1.37
2.0	10.39	0.05	35.36	55.65	0.23	2.0	1.09	1.27
3.0	10.34	0.04	36.45	57.79	0.25	3.0	1.08	1.22
4.0	10.31	0.05	37.22	59.02	0.37	4.0	1.07	1.19
5.0	10.31	0.04	37.77	59.69	0.40	5.0	1.07	1.17
6.0	10.31	0.02	38.10	60.56	0.50	6.0	1.07	1.16
7.0	10.31	0.03	38.30	60.66	0.54	7.0	1.08	1.15
8.0	10.30	0.04	38.41	61.19	0.57	8.0	1.08	1.15
9.0	10.31	0.04	38.44	60.48	0.71	9.0	1.08	1.15
10.0	10.31	0.03	38.38	60.63	0.67	10.0	1.08	1.14
12.0	10.30	0.04	38.22	60.26	0.82	12.0	1.09	1.14
14.0	10.31	0.03	37.95	59.67	0.96	14.0	1.09	1.14
16.0	10.32	0.03	37.64	59.23	1.05	16.0	1.10	1.14
18.0	10.32	0.03	37.26	58.30	1.16	18.0	1.10	1.13
20.0	10.34	0.03	36.88	57.86	1.29	20.0	1.11	1.13
22.0	10.34	0.04	36.54	57.06	1.42	22.0	1.12	1.13
24.0	10.36	0.03	36.12	56.71	1.58	24.0	1.12	1.13
26.0	10.35	0.04	35.77	55.77	1.69	26.0	1.13	1.13
28.0	10.36	0.04	35.41	55.76	1.89	28.0	1.13	1.13
30.0	10.37	0.04	35.07	55.25	1.99	30.0	1.14	1.13
35.0	10.39	0.04	34.16	54.00	2.29	35.0	1.16	1.13
40.0	10.40	0.05	33.38	53.07	2.58	40.0	1.17	1.12
45.0	10.43	0.05	32.64	52.37	2.92	45.0	1.19	1.12
50.0	10.47	0.06	31.99	51.48	3.16	50.0	1.20	1.12
55.0	10.48	0.05	31.42	51.12	3.42	55.0	1.22	1.12
60.0	10.51	0.08	30.90	50.14	3.76	60.0	1.24	1.11
65.0	10.54	0.08	30.42	49.80	4.05	65.0	1.25	1.11
70.0	10.57	0.08	29.99	49.39	4.32	70.0	1.26	1.11
75.0	10.59	0.09	29.62	48.84	4.63	75.0	1.28	1.10
80.0	10.61	0.09	29.29	48.27	4.93	80.0	1.29	1.10
85.0	10.63	0.11	29.00	47.97	5.22	85.0	1.30	1.10
90.0	10.66	0.10	28.72	47.59	5.42	90.0	1.31	1.09
95.0	10.67	0.11	28.49	47.25	5.77	95.0	1.32	1.09
100.0	10.68	0.13	28.31	46.91	6.06	100.0	1.33	1.08
105.0	10.69	0.14	28.16	46.57	6.22	105.0	1.33	1.08
110.0	10.70	0.13	28.05	46.24	6.58	110.0	1.34	1.07
115.0	10.70	0.15	27.95	45.97	6.80	115.0	1.34	1.07
120.0	10.71	0.14	27.91	45.72	7.11	120.0	1.34	1.07
130.0	10.73	0.16	27.91	45.17	7.57	130.0	1.33	1.06
140.0	10.76	0.17	28.06	44.65	8.11	140.0	1.31	1.06
150.0	10.79	0.20	28.36	44.21	8.72	150.0	1.30	1.06

¹ Total Loss = Insertion Loss+ 10 dB Splitter Loss

10 Way-0° Power Splitter/Combiner


Typical Performance Curves

PSC-10-1+



REV. X2
PSC-10-1+
100627
Page 1 of 1

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	WT, GRAM
E10	1.580 (40.13)	1.620 (41.15)	.380 (9.65)	.410 (10.41)	.770 (19.56)	.810 (20.57)	.030 (.76)	.200 (5.08)	.10 (2.54)	.20 (5.08)	.14 (3.56)	23.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead Pins 4 & 5. Pin numbers do not appear on unit, for reference only.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Gross Leak	125°C Bubble Test	MIL-STD-202, Method 112, Condition D
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D