

Engineering Development Model

Fixed Attenuator

NAT-EDU1961

DC Passing

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.




FF57

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C

Parameter	Min.	Typ.	Max.	Units
Freq.Range (Attenuation - 10 dB Typ)	100		500	MHz
Flatness		±0.5		MHz
Passband VSWR		1.20		(:1)

Functional Schematic

MAXIMUM RATINGS	
Operating Temperature	-5°C to 55°C
Storage Temperature	-5°C to 55°C
RF Power Input	10mW
Max DC Current	3A



PIN CONNECTIONS

Input	N Female
Output	N Male

DC Passing Fixed Attenuator

NAT-EDU1961




Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
100	9.96	33.40
120	10.01	33.34
140	10.05	33.31
150	10.07	33.32
170	10.09	33.40
190	10.11	33.56
200	10.11	33.67
220	10.11	33.95
240	10.11	34.24
250	10.12	34.34
270	10.12	34.49
290	10.12	34.55
300	10.12	34.55
320	10.13	34.58
340	10.13	34.75
350	10.14	34.83
370	10.14	34.81
390	10.14	34.80
400	10.15	34.81
420	10.16	34.75
440	10.17	34.67
450	10.18	34.64
470	10.20	34.68
500	10.24	34.89

DC Passing Fixed Attenuator

NAT-EDU1961

Typical Performance Curves




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. X1
NAT-EDU1961
URJ
151223
Page 1 of 1

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF57	--	.70 (17.78)	--	2.90 (73.66)	.82 (20.83)	90.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. Case material: Stainless steel.