

Non-Catalog Model

Power Splitter/Combiner

2 Way-90°

PSCQ-2-1.5

Important Note

This is a non-catalog model and can be manufactured on specific request.
Pricing and delivery information can be supplied upon request.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : A01

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1.4		1.7 MHz
Isolation	1.4 - 1.7 MHz	25	29	
Insertion Loss				
Average of Coupled Outputs less 3.0 dB	1.4 - 1.7 MHz		0.40	0.70 dB
Phase Unbalance	1.4 - 1.7 MHz		0.020	3.000 deg.
Amplitude Unbalance	1.4 - 1.7 MHz		0.554	1.200 dB
VSWR	SUM Port		1.01	(:1)
	OUT Ports		1.01	(:1)


Notes: Matched power rating: 1 Watt.

Internal load dissipation: 0.125 Watt.

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	2
PORT 2	5
GND EXT	3, 4, 7, 8
50Ω TERMINATION	6

Functional Diagram



2 Way-90° Power Splitter/Combiner

PSCQ-2-1.5

Typical Performance Data






FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2	AVG.					S	1	2
1.400	3.64	2.51	3.08	1.13	42.64	90.03	1.400	1.01	1.01	1.01
1.405	3.62	2.53	3.08	1.09	42.68	90.01	1.405	1.01	1.01	1.01
1.410	3.60	2.55	3.08	1.06	42.67	90.03	1.410	1.01	1.01	1.01
1.415	3.59	2.55	3.07	1.03	42.66	89.98	1.415	1.01	1.01	1.01
1.420	3.57	2.56	3.07	1.00	42.62	90.06	1.420	1.01	1.01	1.01
1.425	3.56	2.58	3.07	0.98	42.62	90.00	1.425	1.01	1.01	1.01
1.430	3.54	2.60	3.07	0.94	42.66	90.01	1.430	1.01	1.01	1.01
1.435	3.51	2.61	3.06	0.91	42.61	89.99	1.435	1.01	1.01	1.01
1.440	3.50	2.62	3.06	0.88	42.65	90.03	1.440	1.01	1.01	1.01
1.445	3.49	2.64	3.07	0.85	42.62	90.02	1.445	1.01	1.01	1.01
1.450	3.47	2.64	3.06	0.83	42.63	90.02	1.450	1.01	1.01	1.01
1.455	3.45	2.66	3.06	0.79	42.63	90.04	1.455	1.01	1.01	1.01
1.460	3.43	2.68	3.06	0.76	42.60	90.00	1.460	1.01	1.01	1.01
1.465	3.43	2.68	3.06	0.74	42.59	90.02	1.465	1.01	1.01	1.01
1.470	3.40	2.70	3.05	0.70	42.61	90.01	1.470	1.01	1.01	1.01
1.475	3.39	2.72	3.06	0.67	42.60	90.02	1.475	1.01	1.01	1.01
1.480	3.37	2.73	3.05	0.64	42.59	90.04	1.480	1.01	1.01	1.01
1.485	3.36	2.74	3.05	0.61	42.58	90.02	1.485	1.01	1.01	1.01
1.490	3.34	2.76	3.05	0.58	42.62	90.08	1.490	1.01	1.01	1.01
1.495	3.33	2.77	3.05	0.56	42.60	90.03	1.495	1.01	1.01	1.01
1.500	3.31	2.79	3.05	0.53	42.61	90.04	1.500	1.01	1.01	1.01
1.510	3.29	2.82	3.06	0.47	42.55	90.00	1.510	1.01	1.01	1.01
1.520	3.25	2.84	3.05	0.41	42.55	90.02	1.520	1.01	1.01	1.01
1.530	3.22	2.87	3.05	0.36	42.62	89.98	1.530	1.01	1.01	1.01
1.540	3.20	2.90	3.05	0.30	42.59	89.98	1.540	1.01	1.01	1.01
1.550	3.15	2.92	3.04	0.23	42.58	90.02	1.550	1.01	1.01	1.01
1.560	3.13	2.95	3.04	0.18	42.55	90.01	1.560	1.01	1.01	1.01
1.570	3.10	2.98	3.04	0.13	42.59	90.02	1.570	1.01	1.01	1.01
1.580	3.08	3.00	3.04	0.08	42.54	90.04	1.580	1.01	1.01	1.01
1.590	3.05	3.03	3.04	0.02	42.57	90.00	1.590	1.01	1.01	1.01
1.600	3.03	3.06	3.05	0.03	42.53	90.04	1.600	1.01	1.01	1.01
1.610	3.00	3.09	3.05	0.09	42.52	90.02	1.610	1.01	1.01	1.01
1.620	2.97	3.11	3.04	0.14	42.53	90.01	1.620	1.01	1.01	1.01
1.630	2.94	3.14	3.04	0.19	42.56	89.99	1.630	1.01	1.01	1.01
1.640	2.92	3.16	3.04	0.25	42.53	90.02	1.640	1.01	1.01	1.01
1.650	2.90	3.19	3.05	0.29	42.54	90.05	1.650	1.01	1.01	1.01
1.660	2.87	3.22	3.05	0.35	42.53	90.02	1.660	1.01	1.01	1.01
1.670	2.85	3.24	3.05	0.39	42.53	90.03	1.670	1.01	1.01	1.01
1.680	2.82	3.27	3.05	0.46	42.53	90.00	1.680	1.01	1.01	1.01
1.690	2.79	3.30	3.05	0.51	42.58	90.09	1.690	1.01	1.01	1.01
1.700	2.77	3.32	3.05	0.55	42.55	90.01	1.700	1.01	1.01	1.01

¹ Total Loss = Insertion Loss+ 3 dB Splitter Loss

2 Way-90° Power Splitter/Combiner

PSCQ-2-1.5


Typical Performance Curves



REV. X2
PSCQ-2-1.5
100628
Page 1 of 1

A01
A04
A05
A06

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	WT, GRAM
A01	.770 (19.56)	.800 (20.32)	.385 (9.78)	.400 (10.16)	.370 (9.40)	.400 (10.16)	.200 (5.08)	.20 (5.08)	.14 (3.56)	.031 (.79)	5.2
A04			.200 (5.08)	.210 (5.33)							3.7
A05			.240 (6.10)	.250 (6.35)							3.7
A06			.285 (7.24)	.310 (7.87)							5.2

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-045-01.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661