

Low Pass Filter

50Ω DC to 780 MHz

Maximum Ratings

Operating Temperature -55°C to +100°C

Storage Temperature -55°C to +100°C

RF Power Input 0.5 W max.

Permanent damage may occur if any of these limits are exceeded.

Features

- Rugged Shielded Case
- Other NLP Models Available with Wide Selection of Cut-Off Frequencies

Applications

- Lab Use
- Test Equipment
- Video Equipment

NLP-850+



Generic photo used for illustration purposes only

CASE STYLE: FF57

Connectors Model

N-Type NLP-850+


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)		VSWR (:1)	
(loss < 1 dB)	(loss 3 dB)	(loss > 20 dB)	(loss > 40 dB)	Passband Typ.	Stopband Typ.
DC-780	850	1100-1400	1400-2000	1.7	18


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.70	2.90	.82	grams
17.78	73.66	20.83	90.0

typical frequency response





electrical schematic



Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
$\bar{x}$	σ			
10.00	0.02	0.1	10.0	1.00
175.00	0.38	0.1	92.5	1.05
342.50	0.44	0.1	175.0	0.94
507.50	0.18	0.1	257.5	0.95
672.50	0.57	0.1	342.5	0.97
755.00	0.43	0.1	425.0	1.22
780.00	0.40	0.1	507.5	1.35
820.00	1.33	0.6	590.0	1.40
850.00	3.00	0.9	672.5	1.38
1010.00	17.47	1.1	755.0	1.85
1030.00	19.18	1.1	780.0	2.23
1050.00	20.83	1.1	790.0	2.22
1060.00	21.63	1.1	820.0	2.55
1070.00	22.41	1.1	840.0	2.57
1100.00	24.70	1.1	850.0	2.36
1110.00	25.52	1.1	1010.0	0.99
1150.00	28.51	1.2	1020.0	0.92
1350.00	43.25	1.6	1030.0	0.88
1360.00	44.10	1.9	1050.0	0.78
1380.00	45.39	1.8	1060.0	0.75
1400.00	47.43	2.2	1070.0	0.80
1420.00	48.89	2.1	1100.0	0.84
1667.50	69.86	3.1	1110.0	0.70
1750.00	70.13	6.6	1120.0	0.70
1835.00	69.30	4.7	1150.0	0.69
1900.00	67.90	2.7	1300.0	0.45
1920.00	70.63	3.5	1350.0	0.02
1930.00	69.67	2.6	1360.0	0.24
1950.00	74.71	7.2	1380.0	0.48
2000.00	68.74	4.9	1400.0	0.05



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
10.0	0.12	33.96	10.0	0.810
100.0	0.13	23.01	100.0	1.160
200.0	0.20	20.50	200.0	1.170
300.0	0.22	24.85	300.0	1.210
400.0	0.25	30.95	400.0	1.280
500.0	0.34	20.45	500.0	1.350
600.0	0.42	19.56	600.0	1.480
700.0	0.53	18.48	700.0	1.690
800.0	0.64	28.06	800.0	2.230
900.0	4.11	3.68	900.0	2.730
1000.0	14.94	0.65	1000.0	1.190
1100.0	24.71	0.37	1100.0	0.830
1150.0	28.96	0.31	1150.0	0.710
1200.0	32.87	0.29	1200.0	0.630
1250.0	36.52	0.29	1250.0	0.570
1300.0	39.91	0.26	1300.0	0.520
1400.0	46.08	0.26	1400.0	0.460
1500.0	51.50	0.27	1500.0	0.420
2000.0	70.11	0.32	2000.0	0.310
2500.0	75.80	0.34	2500.0	0.190
3000.0	78.70	0.37	3000.0	0.360

Coaxial Low Pass Filter

NLP-850+

Typical Performance Curves



IF/Rf MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



REV. X1
NLP-850+
070717
Page 1 of 1

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF57	--	.70 (17.78)	--	2.90 (73.66)	.82 (20.83)	90.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. Case material: Stainless steel.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I