


*Ultra Flat Gain, Low Noise/High Dynamic Range*  
**Monolithic Amplifier Die**

**PGA-105-D+**

50Ω    0.04 to 2.6 GHz

### The Big Deal

- Ultra Flat Gain
- Low Noise, High Dynamic Range
- Excellent Input and Output Return Loss  
without use of external matching components



### Product Overview

PGA-105-D+ (RoHS compliant) is an advanced ultra flat gain amplifier die fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the PGA-105-D+ has good input and output return loss over a broad frequency range without the need for external matching components.

### Key Features

Feature	Advantages
Broad Band: 0.04 to 2.6 GHz	Broadband covering primary wireless communications bands: Cellular, PCS, LTE, WiMAX
Ultra Flat Gain: ±0.2 dB typ. 0.1 to 2 GHz	Ideal for use in broad band or multi band applications where gain flatness is critical.
High IP3 Versus DC power Consumption: 37 dBm typical at 0.9 GHz 34 dBm typical at 2 GHz	The PGA-105-D+ provides good IP3 performance relative to device size and power consumption. The combination of the design and E-PHEMT Structure provides enhanced linearity over a broad frequency range as evidence in the IP3 being typically 14 dB above the P 1dB point. This feature makes this amplifier ideal for use in: <ul style="list-style-type: none"><li>• Driver amplifiers for complex waveform up converter paths</li><li>• Drivers in linearized transmit systems</li><li>• Secondary amplifiers in ultra High Dynamic range receivers</li></ul>
No External Matching Components Required	Unlike competing products, Mini-Circuits PGA-105-D+ provides outstanding gain flatness and Input and Output Return Loss of 23 dB up to 2.6 GHz without the need for any external matching components.
Low Noise Figure: 1.7 - 2.0 dB typ.	A unique feature of the PGA-105-D+ which separates this design from all competitors is the low noise figure performance in combination with the high dynamic range.
Unpackaged Die	Enables users to integrate the amplifier directly into hybrids


# *Ultra Flat Gain, Low Noise/High Dynamic Range* **Monolithic Amplifier Die**

**PGA-105-D+**

**50Ω    0.04 to 2.6 GHz**

## **Product Features**

- Excellent gain flatness,  $\pm 0.2$  dB over 0.1-2.0 GHz
- Gain, 15.0 dB typ. at 2 GHz
- High IP3, 37 dBm typ. at 0.9 GHz
- P1dB 18.4 dBm typ. at 2 GHz
- Low noise figure, 1.8 dB at 2 GHz
- No external matching components required



### **+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## **Typical Applications**


- Base station infrastructure
- Portable Wireless
- CATV & DBS
- MMDS & Wireless LAN
- LTE

*Ordering Information: Refer to Last Page*

## **General Description**

PGA-105-D+ (RoHS compliant) is an advanced ultra flat gain amplifier fabricated using E-PHEMT technology and offers extremely high dynamic range over a broad frequency range and with low noise figure. In addition, the PGA-105-D+ has good input and output return loss over a broad frequency range without the need for external matching components.

## **Simplified Schematic and Pad description**



Pad	Description
RF-IN	RF input pad. This pad requires the use of an external DC blocking capacitor chosen for the frequency of operation.
RF-OUT and DC-IN	RF output and bias pad. DC voltage is present on this pad; therefore a DC blocking capacitor is necessary for proper operation. An RF choke is needed to feed DC bias without loss of RF signal due to the bias connection, as shown in "Recommended Application Circuit", Fig. 2
GND	Connections to ground.

Note: 1. Bond Pad material - Gold  
2. Bottom of Die - Gold plated

**Electrical Specifications<sup>1</sup> at 25°C, 50Ω and 5V, unless noted**

Parameter	Condition (GHz)	Min.	Typ.	Max.	Units
Frequency range		0.04		2.6	GHz
Gain	0.04 0.5 0.9 2.0 2.6		16.2 14.9 14.9 15.1 15.3		dB
Gain flatness	0.1 - 2.0		±0.2		dB
Noise figure	0.04 0.5 0.9 2.0 2.6		1.5 2.0 1.9 1.8 1.8		
Input return loss	0.04 0.5 0.9 2.0 2.6		11.6 21.6 20.5 25.0 15.3		dB
Output return loss	0.04 0.5 0.9 2.0 2.6		12.6 23.7 22.4 12.5 9.1		dB
Reverse isolation	2.0		21.6		dB
Output power @1dB compression	0.04 0.5 0.9 2.0 2.6		19.8 19.6 19.4 18.4 18.6		dBm
Output IP3	0.04 0.5 0.9 2.0 2.6		33.7 36.6 36.9 33.7 32.2		dBm
Device operating voltage			5.0		V
Device operating current		53	65	77	mA
Device current variation vs voltage			0.016		mA/mV
Thermal resistance, junction-to-ground lead			102		°C/W

1. Measured on Mini-Circuits Die Characterization test board. See Characterization Test Circuit (Fig. 1)

**Typical Performance with Application Circuits (Die in industry standard SOT-89 package, See Application Note, AN-60-063)**

Frequency (GHz)	TB-678-105+							TB-733-105+ (unconditionally stable)								
	Gain	Noise Figure	Input Return Loss	Output Return Loss	Output Power @ 1dB comp.	Output IP3	Stability Factor	Stability Measure	Gain	Noise Figure	Input Return Loss	Output Return Loss	Output Power @ 1dB comp.	Output IP3	Stability Factor	Stability Measure
0.04	16.4	1.7	11.6	12.9	20.9	36.1	0.93	0.59	14.4	2.3	8.6	27.6	19.5	34.6	1.14	0.90
0.5	15.2	2.0	20.4	23.3	20.7	39.3	1.10	0.62	14.5	2.0	21.8	22.7	21.0	38.7	1.13	0.65
0.9	15.1	1.9	18.4	20.1	20.5	39.3	1.13	0.66	14.4	1.9	20.6	25.1	21.0	37.4	1.17	0.70
2	15.2	1.9	18.9	14.7	19.3	34.7	1.29	0.80	15.5	1.9	13.8	15.2	18.9	33.6	1.35	0.88
2.6	15.9	2.1	9.3	9.1	19.3	32.4	1.51	0.96	15.1	2.0	10.5	8.5	19.4	33.2	1.83	0.94

**Absolute Maximum Ratings<sup>2</sup>**

Parameter	Ratings
Operating Temperature (ground lead)	-40°C to 85°C
Operating Current at 5.0V	94 mA
Power Dissipation	0.47 W
Input Power (CW)	23 dBm (5 minutes max, 17 dBm (continuous))
DC Voltage on Pad 3	5.5 V


2. Permanent damage may occur if any of these limits are exceeded.

Performance of die measured in industry standard SOT-89 package.

Electrical maximum ratings are not intended for continuous normal operation.



## Characterization Test Circuit




**Fig 1. Block Diagram of Test Circuit used for Die characterization.**

Gain, Return loss, Output power at 1dB compression (P1 dB), output IP3 (OIP3) and noise figure measured using Agilent's N5242A PNA-X microwave network analyzer.


### Conditions:

1. Gain and Return loss: Pin= -25dBm
2. Output IP3 (OIP3): Two tones, spaced 1 MHz apart, 0 dBm/tone at output.

## Recommended Application Circuits




**Fig 2. Evaluation board TB-678-105+ includes case, connectors, and components soldered to PCB**



COMPONENT	VALUE	SIZE
DUT	Note 4	SOT-89
C1	330 pF	0402
C2,C3	0.001 uF	0402
C4	0.1 uF	0805
R1	422 Ohm	0402
R2	47.5 Ohm	0402
L1, L2	330 nH	0805
BIAS TEE	Mini-Circuits TCBT-14+	

**Fig 3. Evaluation board TB-733-105+ with unconditional stability (see applications)**

## Die Layout




**Fig 4 Die Layout**

## Critical Dimensions

Parameter	Values
Die Thickness, $\mu\text{m}$	100
Die Width, $\mu\text{m}$	760
Die Length, $\mu\text{m}$	1240
Bond Pad Size, $\mu\text{m}$	150 x 75


<sup>(4)</sup> Application Circuits bases on die packaged in industry standard SOT-89 package. For reference only.



## Assembly and Handling Procedure

1. Storage  
Dice should be stored in a dry nitrogen purged desiccators or equivalent.
2. ESD  
MMIC EPHEMPT amplifier dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.
3. Die Attach  
The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030HK-PT/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.
4. Wire Bonding  
Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as reasonable to minimize performance degradation due to undesirable series inductance.


## Assembly Diagram



### Recommended Wire Length, Typical

Wire	Wire Length (mm)	Wire Loop Height (mm)
RF-IN, RF-OUT + DC-IN	1.0	0.15
GROUND	0.30	0.15

## RF Reference Plane - No port extension



## **Additional Detailed Technical Information**

*additional information is available on our dash board.*

\*Known Good Dice ("KGD") means that the dice in question have been subjected to Mini-Circuits DC test performance criteria and measurement instructions and that the parametric data of such dice fall within a predefined range. While DC testing is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

## **ESD Rating\*\***

Human Body Model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD STM 5.1 - 2001

Machine Model (MM): Class M1 (pass 25V) in accordance with ANSI/ESD STM5.2-1999

**\*\* Tested in industry standard SOT-89 package.**

### **Additional Notes**

- Additional Notes**

  - A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
  - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
  - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)
  - D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
  - E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
  - F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



# MMIC Amplifier Die

PGA-105-D+

## Typical Performance Data

### Full 2-Port Extension

#### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 64mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
20	18.22	20.21	6.65	7.84	0.68	0.59	34.01	20.20	1.29
30	16.97	19.60	9.48	10.61	0.83	0.60	34.02	20.18	1.40
40	16.28	19.30	11.63	12.70	0.92	0.59	34.04	20.17	1.52
50	15.85	18.95	13.18	14.32	0.96	0.58	34.12	20.15	1.64
60	15.66	19.36	14.86	15.77	1.02	0.62	34.25	20.14	1.70
70	15.48	19.09	15.95	16.87	1.03	0.60	34.32	20.12	1.73
80	15.37	19.08	16.95	17.80	1.05	0.60	34.40	20.11	1.77
90	15.30	19.05	17.81	18.57	1.06	0.60	34.50	20.09	1.78
100	15.24	19.05	18.53	19.29	1.07	0.60	34.56	20.06	1.80
150	15.11	19.01	20.98	21.48	1.09	0.60	34.97	20.04	1.83
200	15.06	19.03	22.12	22.64	1.09	0.60	35.33	20.02	1.88
250	15.02	18.99	22.65	23.46	1.10	0.60	35.56	19.98	1.92
300	15.01	19.01	22.76	23.90	1.10	0.60	35.99	19.95	1.98
350	14.99	19.06	22.68	24.20	1.10	0.61	36.36	19.91	1.99
400	14.99	19.08	22.63	24.45	1.11	0.61	36.61	19.88	2.00
450	14.97	19.11	22.40	24.53	1.11	0.62	36.57	19.88	2.02
500	14.97	19.12	22.14	24.61	1.11	0.62	36.64	19.84	2.02
600	14.96	19.20	21.75	24.72	1.11	0.62	36.74	19.81	2.01
700	14.96	19.27	21.46	24.55	1.12	0.63	36.76	19.75	1.95
800	14.96	19.38	21.32	24.09	1.13	0.64	36.73	19.67	1.90
900	14.96	19.48	21.39	23.47	1.13	0.65	36.92	19.58	1.86
1000	14.97	19.59	21.69	22.66	1.14	0.65	36.51	19.47	1.84
1050	14.97	19.64	21.89	22.25	1.14	0.65	36.57	19.41	1.83
1100	14.97	19.72	22.28	21.76	1.15	0.66	36.44	19.36	1.83
1200	14.99	19.87	23.13	20.79	1.16	0.67	36.30	19.24	1.84
1300	15.00	20.01	24.45	19.84	1.16	0.67	36.06	19.12	1.83
1400	15.01	20.18	26.26	18.84	1.17	0.68	35.84	19.01	1.83
1500	15.03	20.38	29.19	17.89	1.18	0.69	35.43	18.90	1.84
1600	15.04	20.58	33.61	16.98	1.19	0.70	35.17	18.84	1.84
1700	15.05	20.80	41.57	16.00	1.20	0.71	34.84	18.76	1.84
1800	15.07	21.06	34.30	15.11	1.21	0.72	34.40	18.70	1.82
1900	15.09	21.36	28.53	14.24	1.22	0.73	34.12	18.65	1.81
2000	15.11	21.68	24.99	13.43	1.24	0.75	33.84	18.63	1.78
2100	15.13	22.06	22.24	12.64	1.25	0.76	33.57	18.59	1.76
2200	15.16	22.55	20.25	11.89	1.27	0.78	33.42	18.59	1.74
2300	15.19	23.04	18.63	11.19	1.30	0.80	33.17	18.60	1.74
2400	15.21	23.75	17.34	10.51	1.34	0.82	33.03	18.64	1.75
2500	15.24	24.61	16.35	9.87	1.41	0.84	32.79	18.72	1.77
2600	15.26	25.73	15.63	9.27	1.53	0.85	32.60	18.81	1.79
2700	15.26	27.22	15.29	8.67	1.73	0.86	32.40	18.92	1.85
2800	15.22	29.30	15.28	8.14	2.11	0.86	32.19	19.08	1.91
2900	15.14	32.50	15.75	7.63	2.97	0.85	32.09	19.28	1.93
3000	14.99	38.29	16.41	7.19	5.75	0.83	32.01	19.52	1.94



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-105-D+

12/4/2015

Page 1 of 6

# MMIC Amplifier Die

PGA-105-D+

## Typical Performance Data

### Full 2-Port Extension

#### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 60mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
20	18.19	20.26	6.60	7.82	0.68	0.60	33.42	19.85	1.27
30	16.93	19.53	9.44	10.60	0.83	0.60	33.51	19.84	1.38
40	16.24	19.29	11.61	12.68	0.92	0.60	33.70	19.84	1.50
50	15.81	19.26	13.46	14.26	0.98	0.61	33.81	19.84	1.62
60	15.62	19.12	14.57	15.71	1.01	0.60	33.87	19.83	1.68
70	15.44	19.05	15.89	16.86	1.03	0.60	33.95	19.82	1.72
80	15.33	19.03	16.90	17.77	1.05	0.60	34.09	19.84	1.75
90	15.26	19.00	17.74	18.56	1.06	0.60	34.14	19.82	1.77
100	15.20	19.00	18.51	19.26	1.07	0.60	34.23	19.82	1.79
150	15.07	19.00	20.95	21.45	1.09	0.60	34.84	19.80	1.81
200	15.01	18.98	22.06	22.58	1.09	0.60	35.29	19.79	1.86
250	14.98	19.02	22.69	23.37	1.10	0.61	35.82	19.76	1.91
300	14.96	19.00	22.73	23.85	1.10	0.61	36.39	19.73	1.96
350	14.95	19.06	22.62	24.16	1.11	0.61	36.70	19.70	1.97
400	14.95	19.06	22.56	24.43	1.11	0.61	36.79	19.68	1.98
450	14.93	19.11	22.37	24.54	1.11	0.62	36.69	19.68	2.00
500	14.92	19.09	22.13	24.72	1.11	0.62	36.63	19.65	2.00
600	14.92	19.17	21.65	24.83	1.11	0.63	36.94	19.62	1.99
700	14.92	19.24	21.41	24.78	1.12	0.63	37.24	19.58	1.94
800	14.91	19.34	21.24	24.40	1.13	0.64	36.85	19.49	1.91
900	14.92	19.43	21.31	23.79	1.13	0.65	36.52	19.41	1.86
1000	14.92	19.56	21.65	23.06	1.14	0.65	36.05	19.29	1.83
1050	14.93	19.62	21.81	22.65	1.14	0.66	35.89	19.21	1.81
1100	14.93	19.68	22.17	22.13	1.15	0.66	35.63	19.16	1.82
1200	14.94	19.83	23.02	21.19	1.16	0.67	35.33	19.03	1.82
1300	14.95	19.97	24.28	20.22	1.16	0.67	35.17	18.92	1.81
1400	14.96	20.13	26.03	19.21	1.17	0.68	34.98	18.78	1.81
1500	14.98	20.32	28.87	18.27	1.18	0.69	34.71	18.67	1.83
1600	14.99	20.53	33.08	17.32	1.19	0.70	34.34	18.61	1.82
1700	15.01	20.77	40.04	16.37	1.21	0.71	33.97	18.52	1.81
1800	15.03	21.05	34.88	15.44	1.22	0.72	33.78	18.46	1.82
1900	15.05	21.32	28.92	14.55	1.23	0.74	33.64	18.40	1.80
2000	15.07	21.66	25.24	13.76	1.24	0.75	33.29	18.37	1.77
2100	15.09	22.04	22.45	12.93	1.26	0.77	33.19	18.32	1.74
2200	15.12	22.52	20.43	12.20	1.28	0.79	33.03	18.33	1.74
2300	15.15	23.09	18.81	11.47	1.31	0.80	32.87	18.36	1.73
2400	15.18	23.73	17.50	10.81	1.35	0.82	32.59	18.41	1.74
2500	15.21	24.62	16.51	10.17	1.43	0.84	32.31	18.48	1.75
2600	15.22	25.75	15.79	9.55	1.55	0.86	32.18	18.55	1.77
2700	15.23	27.26	15.45	8.96	1.76	0.86	31.99	18.67	1.84
2800	15.19	29.43	15.45	8.42	2.18	0.87	31.94	18.81	1.90
2900	15.11	32.77	15.95	7.90	3.12	0.86	31.98	19.04	1.91
3000	14.96	38.75	16.62	7.45	6.18	0.84	32.01	19.29	1.91



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



# MMIC Amplifier Die

PGA-105-D+

## Typical Performance Data

### Full 2-Port Extension

#### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 68mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
20	18.25	20.34	6.70	7.86	0.68	0.61	33.22	20.47	1.31
30	16.99	19.60	9.50	10.62	0.83	0.59	33.39	20.46	1.42
40	16.31	19.35	11.66	12.72	0.92	0.60	33.49	20.45	1.53
50	15.88	19.39	13.24	14.43	0.98	0.62	33.57	20.45	1.65
60	15.69	18.97	14.84	15.75	1.00	0.58	33.70	20.44	1.71
70	15.51	19.12	15.99	16.89	1.03	0.60	33.77	20.43	1.74
80	15.41	19.08	16.99	17.82	1.05	0.60	33.87	20.42	1.78
90	15.33	19.08	17.84	18.59	1.06	0.60	33.94	20.40	1.80
100	15.28	19.05	18.59	19.32	1.06	0.60	34.04	20.39	1.81
150	15.14	19.04	20.99	21.55	1.09	0.60	34.58	20.37	1.84
200	15.09	19.02	22.14	22.69	1.09	0.60	35.05	20.36	1.89
250	15.06	19.06	22.65	23.51	1.10	0.60	35.71	20.31	1.93
300	15.05	19.07	22.80	23.88	1.10	0.61	36.34	20.28	1.98
350	15.03	19.08	22.75	24.17	1.10	0.61	36.87	20.25	1.99
400	15.02	19.09	22.65	24.42	1.10	0.61	36.87	20.24	2.01
450	15.01	19.12	22.41	24.53	1.11	0.61	36.79	20.24	2.03
500	15.01	19.18	22.13	24.62	1.11	0.62	36.88	20.21	2.03
600	15.00	19.22	21.76	24.60	1.11	0.62	37.12	20.18	2.01
700	15.00	19.31	21.49	24.42	1.12	0.63	37.53	20.13	1.96
800	15.00	19.40	21.37	23.87	1.12	0.64	37.69	20.03	1.91
900	15.00	19.49	21.44	23.21	1.13	0.64	37.53	19.95	1.87
1000	15.01	19.61	21.75	22.38	1.14	0.65	37.37	19.84	1.85
1050	15.01	19.68	21.98	21.95	1.14	0.65	37.29	19.78	1.85
1100	15.01	19.76	22.34	21.45	1.15	0.66	37.18	19.72	1.85
1200	15.02	19.89	23.20	20.50	1.15	0.66	36.80	19.59	1.86
1300	15.03	20.03	24.57	19.52	1.16	0.67	36.43	19.49	1.86
1400	15.04	20.20	26.42	18.56	1.17	0.68	36.06	19.35	1.85
1500	15.06	20.41	29.47	17.63	1.18	0.69	35.91	19.24	1.86
1600	15.07	20.61	34.28	16.70	1.19	0.70	35.73	19.17	1.87
1700	15.09	20.83	42.78	15.75	1.20	0.71	35.47	19.08	1.85
1800	15.10	21.09	34.07	14.85	1.21	0.72	35.29	19.03	1.84
1900	15.12	21.39	28.34	14.00	1.22	0.73	34.98	18.96	1.82
2000	15.14	21.72	24.82	13.20	1.23	0.75	34.58	18.93	1.80
2100	15.16	22.09	22.06	12.40	1.25	0.76	34.20	18.88	1.78
2200	15.19	22.52	20.13	11.67	1.26	0.78	33.79	18.89	1.77
2300	15.21	23.08	18.54	10.96	1.29	0.80	33.51	18.92	1.78
2400	15.23	23.76	17.23	10.30	1.33	0.81	33.17	18.94	1.79
2500	15.26	24.59	16.24	9.66	1.39	0.83	32.91	19.01	1.80
2600	15.28	25.73	15.53	9.05	1.51	0.85	32.72	19.08	1.81
2700	15.28	27.14	15.17	8.46	1.69	0.85	32.57	19.21	1.88
2800	15.25	29.25	15.16	7.94	2.07	0.85	32.51	19.35	1.93
2900	15.16	32.30	15.61	7.42	2.86	0.84	32.34	19.58	1.95
3000	15.01	37.54	16.28	7.00	5.20	0.82	32.26	19.83	1.96



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-105-D+

12/4/2015

Page 3 of 6

# MMIC Amplifier Die

# PGA-105-D+

## Typical Performance Data

### Without Full 2-Port Extension

#### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.00V, Id = 64mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
20	18.32	20.17	6.57	7.76	0.67	0.58	34.01	20.20	1.29
30	17.05	19.50	9.39	10.51	0.82	0.58	34.02	20.18	1.40
40	16.36	19.23	11.55	12.62	0.91	0.58	34.04	20.17	1.52
50	15.93	18.88	13.10	14.31	0.96	0.56	34.12	20.15	1.64
60	15.74	19.16	14.79	15.69	1.01	0.59	34.25	20.14	1.70
70	15.55	19.04	15.89	16.78	1.02	0.59	34.32	20.12	1.73
80	15.45	19.02	16.88	17.71	1.04	0.59	34.40	20.11	1.77
90	15.37	19.00	17.73	18.50	1.05	0.59	34.50	20.09	1.78
100	15.31	18.99	18.47	19.20	1.06	0.59	34.56	20.06	1.80
150	15.16	18.95	20.93	21.44	1.08	0.59	34.97	20.04	1.83
200	15.10	18.97	22.06	22.59	1.09	0.59	35.33	20.02	1.88
250	15.05	18.97	22.58	23.42	1.09	0.60	35.56	19.98	1.92
300	15.03	19.00	22.74	23.81	1.10	0.60	35.99	19.95	1.98
350	15.01	19.02	22.70	24.18	1.10	0.61	36.36	19.91	1.99
400	14.99	19.09	22.63	24.44	1.11	0.61	36.61	19.88	2.00
450	14.97	19.12	22.41	24.56	1.11	0.62	36.57	19.88	2.02
500	14.96	19.15	22.13	24.67	1.11	0.62	36.64	19.84	2.02
600	14.94	19.20	21.77	24.71	1.12	0.63	36.74	19.81	2.01
700	14.92	19.33	21.51	24.61	1.12	0.64	36.76	19.75	1.95
800	14.91	19.42	21.37	24.14	1.13	0.65	36.73	19.67	1.90
900	14.90	19.52	21.46	23.54	1.14	0.65	36.92	19.58	1.86
1000	14.89	19.65	21.78	22.74	1.15	0.66	36.51	19.47	1.84
1050	14.89	19.72	22.00	22.33	1.15	0.67	36.57	19.41	1.83
1100	14.89	19.81	22.36	21.83	1.16	0.67	36.44	19.36	1.83
1200	14.89	19.95	23.20	20.88	1.17	0.68	36.30	19.24	1.84
1300	14.89	20.11	24.59	19.93	1.18	0.69	36.06	19.12	1.83
1400	14.89	20.29	26.39	18.97	1.19	0.70	35.84	19.01	1.83
1500	14.90	20.49	29.31	18.01	1.20	0.71	35.43	18.90	1.84
1600	14.90	20.70	33.94	17.11	1.21	0.72	35.17	18.84	1.84
1700	14.90	20.96	41.71	16.16	1.23	0.73	34.84	18.76	1.84
1800	14.91	21.22	34.46	15.26	1.24	0.74	34.40	18.70	1.82
1900	14.92	21.52	28.75	14.41	1.26	0.75	34.12	18.65	1.81
2000	14.93	21.88	25.17	13.60	1.27	0.77	33.84	18.63	1.78
2100	14.94	22.25	22.42	12.82	1.29	0.78	33.57	18.59	1.76
2200	14.96	22.70	20.41	12.08	1.31	0.80	33.42	18.59	1.74
2300	14.98	23.23	18.83	11.39	1.35	0.81	33.17	18.60	1.74
2400	15.00	23.96	17.54	10.73	1.40	0.83	33.03	18.64	1.75
2500	15.02	24.81	16.57	10.10	1.48	0.85	32.79	18.72	1.77
2600	15.03	25.94	15.86	9.50	1.61	0.86	32.60	18.81	1.79
2700	15.02	27.43	15.52	8.91	1.83	0.87	32.40	18.92	1.85
2800	14.98	29.55	15.53	8.39	2.26	0.87	32.19	19.08	1.91
2900	14.89	32.71	16.01	7.88	3.18	0.86	32.09	19.28	1.93
3000	14.73	38.41	16.70	7.45	6.10	0.84	32.01	19.52	1.94



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-105-D+

12/4/2015

Page 4 of 6

# MMIC Amplifier Die

# PGA-105-D+

## Typical Performance Data

### Without Full 2-Port Extension

#### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 4.75V, Id = 60mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
20	18.28	20.06	6.53	7.72	0.67	0.57	33.42	19.85	1.27
30	17.02	19.46	9.36	10.51	0.82	0.58	33.51	19.84	1.38
40	16.33	19.20	11.53	12.61	0.91	0.58	33.70	19.84	1.50
50	15.89	18.99	13.25	14.17	0.96	0.58	33.81	19.84	1.62
60	15.70	19.18	14.56	15.65	1.00	0.60	33.87	19.83	1.68
70	15.51	18.99	15.84	16.78	1.02	0.59	33.95	19.82	1.72
80	15.41	18.98	16.83	17.70	1.04	0.59	34.09	19.84	1.75
90	15.33	18.94	17.71	18.48	1.05	0.59	34.14	19.82	1.77
100	15.27	18.94	18.47	19.20	1.06	0.59	34.23	19.82	1.79
150	15.12	18.95	20.85	21.41	1.08	0.59	34.84	19.80	1.81
200	15.06	18.94	22.03	22.54	1.09	0.60	35.29	19.79	1.86
250	15.01	18.96	22.61	23.38	1.10	0.60	35.82	19.76	1.91
300	14.99	18.95	22.70	23.87	1.10	0.60	36.39	19.73	1.96
350	14.97	19.01	22.59	24.14	1.10	0.61	36.70	19.70	1.97
400	14.96	19.05	22.59	24.47	1.11	0.61	36.79	19.68	1.98
450	14.93	19.09	22.33	24.59	1.11	0.62	36.69	19.68	2.00
500	14.92	19.11	22.08	24.72	1.11	0.62	36.63	19.65	2.00
600	14.90	19.19	21.69	24.85	1.12	0.63	36.94	19.62	1.99
700	14.88	19.27	21.44	24.83	1.12	0.64	37.24	19.58	1.94
800	14.87	19.37	21.28	24.42	1.13	0.65	36.85	19.49	1.91
900	14.86	19.50	21.37	23.90	1.14	0.66	36.52	19.41	1.86
1000	14.85	19.63	21.70	23.13	1.15	0.67	36.05	19.29	1.83
1050	14.85	19.69	21.86	22.72	1.15	0.67	35.89	19.21	1.81
1100	14.84	19.77	22.24	22.22	1.16	0.67	35.63	19.16	1.82
1200	14.84	19.92	23.11	21.26	1.17	0.68	35.33	19.03	1.82
1300	14.85	20.07	24.39	20.32	1.18	0.69	35.17	18.92	1.81
1400	14.85	20.26	26.13	19.36	1.19	0.70	34.98	18.78	1.81
1500	14.85	20.48	28.96	18.38	1.20	0.71	34.71	18.67	1.83
1600	14.86	20.67	33.20	17.46	1.22	0.72	34.34	18.61	1.82
1700	14.86	20.93	40.37	16.52	1.23	0.73	33.97	18.52	1.81
1800	14.87	21.19	35.04	15.59	1.24	0.74	33.78	18.46	1.82
1900	14.88	21.49	29.04	14.73	1.26	0.76	33.64	18.40	1.80
2000	14.89	21.86	25.47	13.92	1.28	0.77	33.29	18.37	1.77
2100	14.91	22.23	22.66	13.13	1.30	0.79	33.19	18.32	1.74
2200	14.93	22.72	20.62	12.39	1.33	0.80	33.03	18.33	1.74
2300	14.95	23.24	19.03	11.68	1.36	0.82	32.87	18.36	1.73
2400	14.96	23.96	17.72	11.02	1.42	0.84	32.59	18.41	1.74
2500	14.98	24.83	16.74	10.38	1.50	0.85	32.31	18.48	1.75
2600	15.00	26.00	16.02	9.78	1.64	0.87	32.18	18.55	1.77
2700	14.99	27.48	15.70	9.18	1.87	0.87	31.99	18.67	1.84
2800	14.94	29.71	15.70	8.66	2.33	0.88	31.94	18.81	1.90
2900	14.85	32.96	16.20	8.15	3.33	0.87	31.98	19.04	1.91
3000	14.69	39.00	16.89	7.70	6.65	0.85	32.01	19.29	1.91



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



REV. OR

PGA-105-D+

12/4/2015

Page 5 of 6

# MMIC Amplifier Die

# PGA-105-D+

## Typical Performance Data

### Without Full 2-Port Extension

#### Definitions:

Input Return Loss = -S11 (dB)

Gain(Power Gain) = S21 (dB)

Reverse Isolation = -S12 (dB)

Output Return Loss = -S22 (dB)

TEST CONDITIONS: Vd = 5.25V, Id = 68mA @Temperature = +25°C

FREQ. (MHz)	Gain (dB)	Isolation (dB)	Input Return Loss (dB)	Output Return Loss (dB)	Stability		IP-3 Output (dBm)	1dB Comp. Output (dBm)	Noise Figure (dB)
20	18.34	20.21	6.60	7.77	0.67	0.58	33.22	20.47	1.31
30	17.08	19.53	9.42	10.54	0.82	0.58	33.39	20.46	1.42
40	16.40	19.27	11.57	12.64	0.91	0.58	33.49	20.45	1.53
50	15.96	19.03	13.14	14.37	0.96	0.58	33.57	20.45	1.65
60	15.77	19.07	14.80	15.69	1.00	0.58	33.70	20.44	1.71
70	15.59	19.06	15.91	16.82	1.02	0.59	33.77	20.43	1.74
80	15.48	19.04	16.93	17.75	1.04	0.59	33.87	20.42	1.78
90	15.40	19.03	17.77	18.54	1.05	0.59	33.94	20.40	1.80
100	15.34	19.02	18.52	19.26	1.06	0.59	34.04	20.39	1.81
150	15.20	18.98	20.94	21.50	1.08	0.59	34.58	20.37	1.84
200	15.14	18.99	22.09	22.67	1.09	0.59	35.05	20.36	1.89
250	15.10	18.98	22.61	23.46	1.09	0.59	35.71	20.31	1.93
300	15.07	19.05	22.77	23.92	1.10	0.60	36.34	20.28	1.98
350	15.05	19.07	22.71	24.23	1.10	0.61	36.87	20.25	1.99
400	15.03	19.09	22.63	24.43	1.10	0.61	36.87	20.24	2.01
450	15.02	19.10	22.40	24.55	1.11	0.61	36.79	20.24	2.03
500	15.00	19.18	22.14	24.63	1.11	0.62	36.88	20.21	2.03
600	14.98	19.25	21.79	24.64	1.12	0.63	37.12	20.18	2.01
700	14.97	19.33	21.52	24.42	1.12	0.64	37.53	20.13	1.96
800	14.95	19.44	21.40	23.95	1.13	0.64	37.69	20.03	1.91
900	14.94	19.55	21.47	23.25	1.14	0.65	37.53	19.95	1.87
1000	14.93	19.69	21.87	22.48	1.15	0.66	37.37	19.84	1.85
1050	14.93	19.76	22.03	22.08	1.15	0.67	37.29	19.78	1.85
1100	14.93	19.81	22.38	21.53	1.16	0.67	37.18	19.72	1.85
1200	14.93	19.99	23.29	20.59	1.17	0.68	36.80	19.59	1.86
1300	14.93	20.14	24.64	19.64	1.18	0.69	36.43	19.49	1.86
1400	14.93	20.34	26.48	18.67	1.19	0.70	36.06	19.35	1.85
1500	14.93	20.52	29.64	17.74	1.20	0.70	35.91	19.24	1.86
1600	14.93	20.74	34.26	16.83	1.21	0.72	35.73	19.17	1.87
1700	14.94	20.99	42.81	15.90	1.23	0.73	35.47	19.08	1.85
1800	14.95	21.23	34.34	15.02	1.24	0.74	35.29	19.03	1.84
1900	14.95	21.56	28.54	14.15	1.25	0.75	34.98	18.96	1.82
2000	14.96	21.87	24.99	13.38	1.27	0.76	34.58	18.93	1.80
2100	14.97	22.28	22.31	12.58	1.29	0.78	34.20	18.88	1.78
2200	14.99	22.73	20.32	11.86	1.31	0.80	33.79	18.89	1.77
2300	15.01	23.28	18.75	11.16	1.34	0.81	33.51	18.92	1.78
2400	15.02	23.97	17.45	10.49	1.39	0.83	33.17	18.94	1.79
2500	15.04	24.77	16.47	9.88	1.46	0.84	32.91	19.01	1.80
2600	15.05	25.91	15.75	9.27	1.59	0.86	32.72	19.08	1.81
2700	15.04	27.36	15.41	8.69	1.79	0.86	32.57	19.21	1.88
2800	15.00	29.47	15.40	8.18	2.21	0.86	32.51	19.35	1.93
2900	14.91	32.56	15.87	7.67	3.08	0.85	32.34	19.58	1.95
3000	14.75	37.90	16.54	7.26	5.67	0.83	32.26	19.83	1.96



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS



REV. OR








PGA-105-D+

12/4/2015

Page 6 of 6








## Typical Performance Curves

## Full 2-Port Extension



## Typical Performance Curves

### Without Full 2-Port Extension



**Environmental Specifications****ENV80**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	