Plug-In

High Pass Filter

PHP-300+

50Ω 290 to 1200 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	1
OUTPUT	8
GROUND	2,3,4,5,6,7
CASE GROUND	2,3,4,5,6,7

Features

- rugged shielded case, hermetically sealed
- other standard and custom PHP models available with wide selection of fco

Applications

- lab use
- transmitters/receivers
- military/hi-rel application

Generic photo used for illustration purposes only

CASE STYLE: A01

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

High Pass Filter Electrical Specifications

STOPBAND (MHz)		fco (MHz) Nom.	PASSBAND (MHz)	VSWR (:1)	
(loss > 40 dB)	(loss > 20 dB)	(loss 3 dB)	(loss <1.5 dB)	Stopband Typ.	Passband Typ.
DC-145	145-190	245	290-1200	17	1.7

typical frequency response



electrical schematic



Outline Drawing



Outline Dimensions (inch / mm)

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K		wt
.200	.20	.14	.031		grams
5.08	5.08	3.56	0.79		5.2

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB) x̄	Insertion Loss (dB) σ	Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
10.0	74.21	2.4	0.1	110.0	3.17
30.0	74.57	4.0	0.2	120.0	2.56
50.0	75.03	6.1	0.2	130.0	1.73
70.0	75.11	1.9	0.2	145.0	1.50
90.0	77.67	5.6	0.2	150.0	2.07
100.0	71.90	4.0	0.2	155.0	1.11
110.0	64.71	1.1	0.2	160.0	3.42
120.0	61.50	1.0	0.2	165.0	2.57
130.0	54.50	0.9	0.2	170.0	2.97
145.0	47.14	0.4	0.1	175.0	2.43
150.0	44.66	0.4	0.1	180.0	3.14
160.0	39.74	0.4	0.1	190.0	3.21
170.0	34.99	0.4	0.1	195.0	3.62
175.0	32.61	0.4	0.1	200.0	4.11
180.0	30.36	0.4	0.1	205.0	4.38
190.0	25.67	0.4	0.1	210.0	4.71
195.0	23.38	0.4	0.1	220.0	5.85
205.0	18.79	0.4	0.3	230.0	7.34
220.0	11.96	0.4	0.7	240.0	8.94
230.0	7.65	0.3	1.6	245.0	9.28
240.0	4.02	0.3	3.6	265.0	7.19
245.0	2.69	0.2	5.4	285.0	4.93
265.0	0.66	0.1	22.9	290.0	4.53
285.0	0.52	0.1	19.6	780.0	0.87
290.0	0.52	0.1	18.7	850.0	0.75
850.0	0.28	0.1	27.8	920.0	0.72
990.0	0.33	0.1	19.6	990.0	0.72
1060.0	0.38	0.1	17.1	1060.0	0.75
1130.0	0.42	0.1	15.3	1130.0	0.56
1200.0	0.47	0.1	15.0	1200.0	0.68







Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Plug-In High Pass Filter PHP-300+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10.0	74.21	0.10
30.0	74.57	0.20
50.0	75.03	0.20
70.0	75.11	0.20
90.0	77.67	0.20
100.0	71.90	0.20
110.0	64.71	0.20
120.0	61.50	0.20
130.0	54.50	0.20
145.0	47.14	0.10
150.0	44.66	0.10
160.0	39.74	0.10
170.0	34.99	0.10
175.0	32.61	0.10
180.0	30.36	0.10
190.0	25.67	0.10
195.0	23.38	0.10
205.0	18.79	0.30
220.0	11.96	0.70
230.0	7.65	1.60
240.0	4.02	3.60
245.0	2.69	5.40
265.0	0.66	22.90
285.0	0.52	19.60
290.0	0.52	18.70
850.0	0.28	27.80
990.0	0.33	19.60
1060.0	0.38	17.10
1130.0	0.42	15.30
1200.0	0.47	15.00

FREQUENCY (MHz)	GROUP DELAY (nsec)
110.0	3.170
120.0	2.560
130.0	1.730
145.0	1.500
150.0	2.070
155.0	1.110
160.0	3.420
165.0	2.570
170.0	2.970
175.0	2.430
180.0	3.140
190.0	3.210
195.0	3.620
200.0	4.110
205.0	4.380
210.0	4.710
220.0	5.850
230.0	7.340
240.0	8.940
245.0	9.280
265.0	7.190
285.0	4.930
290.0	4.530
780.0	0.870
850.0	0.750
920.0	0.720
990.0	0.720
1060.0	0.750
1130.0	0.560
1200.0	0.680

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Plug-In High Pass Filter PHP-300+

Typical Performance Curves

Insertion Loss



Return Loss



Group Delay



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style A

A01
A04
A05
A06

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	WT, GRAM
A01	.770 (19.56)	.800 (20.32)	.385 (9.78)	.400 (10.16)	.370 (9.40)	.400 (10.16)	.200 (5.08)	.20 (5.08)	.14 (3.56)	.031 (.79)	5.2
A04			.200 (5.08)	.210 (5.33)							3.7
A05			.240 (6.10)	.250 (6.35)							3.7
A06			.285 (7.24)	.310 (7.87)							5.2

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .03; 3 Pl. ± .015

Notes:

1. Header material: C.R.S.
   Pin material: #52 alloy.
   Cover material: Cupro-Nickel.
2. Pin finish: Electro Tin-Silver.
3. Insulated spacer available. Request P/N B14-045-01.
4. Tolerance on pin diameter +/-.005 inch.
5. Glass meniscus 0.015 inch max.
6. Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits

Mini-Circuits

Environmental Specifications ENV01

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A

This document and its contents are the property of Mini-Circuits.

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Gross Leak	125°C Bubble Test	MIL-STD-202, Method 112, Condition D
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D

This document and its contents are the property of Mini-Circuits.