

Engineering Development Model

Power Splitter/Combiner

QCS-ED13415/1

2 Way-90°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : GE0805C-1

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C

Parameter		Min.	Typ.	Max.	Units
Frequency		1700		3100	MHz
Isolation	1700-3100 MHz		24		dB
Insertion Loss Average of Coupled Outputs above 3.0 dB	1700-3100 MHz		0.50		dB
Phase Unbalance	1700-3100 MHz		3.00		deg.
Amplitude Unbalance	1700-3100 MHz		0.35		dB
VSWR	SUM Port		1.20		(:1)
	OUT Ports		1.20		(:1)


MAXIMUM RATINGS

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS

SUM PORT	1
PORT 1 (0°)	4
PORT 2 (90°)	6
50 TERM. EXTERNAL	3
GND	2,5

Functional Diagram



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. X2
QCS-ED13415/1
8/12/2010
Page 1 of 1

2 Way-90° Power Splitter/Combiner

QCS-ED13415/1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (Deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1200.0	4.98	2.13	2.85	21.52	86.46	1200.0	1.10	1.38	1.11
1400.0	4.33	2.50	1.83	22.30	86.76	1400.0	1.06	1.35	1.07
1600.0	3.86	2.84	1.02	23.48	87.02	1600.0	1.02	1.32	1.04
1620.0	3.83	2.87	0.95	23.59	87.05	1620.0	1.02	1.31	1.03
1640.0	3.79	2.90	0.88	23.73	87.08	1640.0	1.01	1.31	1.03
1660.0	3.75	2.94	0.81	23.91	87.08	1660.0	1.01	1.31	1.02
1680.0	3.71	2.96	0.75	24.07	87.11	1680.0	1.01	1.30	1.02
1700.0	3.68	3.00	0.69	24.22	87.12	1700.0	1.01	1.30	1.02
1720.0	3.65	3.02	0.63	24.34	87.13	1720.0	1.01	1.30	1.01
1740.0	3.62	3.05	0.57	24.46	87.14	1740.0	1.01	1.29	1.01
1760.0	3.59	3.08	0.51	24.61	87.15	1760.0	1.01	1.29	1.01
1780.0	3.56	3.11	0.45	24.82	87.17	1780.0	1.02	1.28	1.01
1800.0	3.53	3.13	0.40	25.02	87.18	1800.0	1.02	1.28	1.01
1820.0	3.50	3.16	0.34	25.20	87.18	1820.0	1.02	1.28	1.02
1840.0	3.48	3.19	0.29	25.34	87.20	1840.0	1.02	1.27	1.02
1850.0	3.46	3.20	0.27	25.42	87.19	1850.0	1.03	1.27	1.02
1900.0	3.41	3.26	0.14	25.94	87.20	1900.0	1.03	1.26	1.03
1950.0	3.35	3.32	0.03	26.40	87.18	1950.0	1.04	1.25	1.04
1975.0	3.33	3.34	0.02	26.65	87.18	1975.0	1.04	1.25	1.05
1990.0	3.32	3.36	0.05	26.85	87.19	1990.0	1.04	1.24	1.05
2000.0	3.31	3.37	0.07	26.96	87.18	2000.0	1.05	1.24	1.05
2050.0	3.26	3.42	0.16	27.58	87.14	2050.0	1.05	1.23	1.06
2100.0	3.23	3.47	0.24	28.10	87.09	2100.0	1.06	1.22	1.07
2150.0	3.20	3.51	0.31	28.78	87.03	2150.0	1.07	1.21	1.08
2200.0	3.17	3.55	0.37	29.40	86.98	2200.0	1.07	1.20	1.09
2250.0	3.16	3.58	0.43	30.21	86.92	2250.0	1.08	1.19	1.10
2300.0	3.14	3.61	0.47	30.83	86.82	2300.0	1.08	1.17	1.11
2400.0	3.13	3.65	0.52	32.53	86.67	2400.0	1.09	1.15	1.13
2450.0	3.14	3.66	0.53	33.25	86.61	2450.0	1.10	1.14	1.13
2500.0	3.14	3.67	0.52	34.34	86.51	2500.0	1.10	1.13	1.14
2550.0	3.16	3.67	0.51	35.05	86.48	2550.0	1.11	1.11	1.14
2600.0	3.18	3.66	0.48	36.05	86.39	2600.0	1.11	1.10	1.14
2800.0	3.33	3.56	0.23	39.38	86.29	2800.0	1.11	1.06	1.14
3000.0	3.61	3.33	0.28	43.36	86.44	3000.0	1.09	1.04	1.11
3100.0	3.82	3.17	0.65	43.80	86.58	3100.0	1.07	1.04	1.08
3400.0	4.88	2.52	2.35	29.94	87.51	3400.0	1.05	1.06	1.05

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com








IF/RF MICROWAVE COMPONENTS

REV. X2
 QCS-ED13415/1
 9/1/2010
 Page 1 of 1

2 Way-90° Power Splitter/Combiner

QCS-ED13415/1

Typical Performance Curves




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




REV. X2
QCS-ED13415/1
9/1/2010
Page 1 of 1

IF/RF MICROWAVE COMPONENTS

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
GE0805C-1	.079 (2.00)	.049 (1.25)	.033 (0.84)	.014 (0.35)	.012 (0.30)	.012 (0.30)	.026 (0.65)	.014 (0.35)	.039 (1.00)	.110 (2.80)	.008

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Style: Tin-lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F74

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

Applicable Case Styles
GE0805C-1
GE0805C-1AP
JV1210C-1
GU2939

Applicable Case Styles
JV1210C
JV1210C-2
JV1210C-3
JV1210C-4
JV1210C-5
JV1210C-6
JV1210C-11

Applicable Case Styles
JC0603C-8
JC0603C-9
JV1210C-7
JV1210C-8
JV1210C-9
JV1210C-10
JV1210C-13
GE0805C-13
GE0805C-19
GE0805C-20

Tape Width, mm	Device Cavity Pitch, mm	Real Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	2000
				4000

Note: Small reel availability varies by model. Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M122595	NEW RELEASE	04/27/09	MMG	ABD

SUGGESTED MOUNTING CONFIGURATION FOR GE0805C-1 CASE STYLE, "06SQ07" PIN CODE



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010" $\pm$.001"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$
3 PL DECIMALS $\pm$.005
ANGLES $\pm$ 1°
FRACTIONS $\pm$

DRAWN

MMG

04/27/09

CHECKED

AV

04/27/09

APPROVED

ABD

04/27/09

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 06SQ07, GE0805C-1, TB-489+

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-304

REV:
OR



FILE: 98PL304

SCALE: 12:1

SHEET: 1 OF 1

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers RO4350 or equivalent,
Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A