

Engineering Development Model

Power Splitter/Combiner

2 Way-0°

RACK-2-ED12568/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : 99-01-949

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1600		2700 MHz
Isolation	1600 - 2700 MHz		22	dB
Insertion Loss Above 3.0 dB	1600 - 2700 MHz		0.50	dB
Phase Unbalance	1600 - 2700 MHz		0.239	deg.
Amplitude Unbalance	1600 - 2700 MHz		0.027	dB
VSWR	SUM Port		1.30	(:1)
	OUT Ports		1.25	(:1)

MAXIMUM RATINGS	
Operating Temperature	-5°C to 85°C
Storage Temperature	-40°C to 85°C

Functional Diagram



2 Way-0° Power Splitter/Combiner RACK-2-ED12568/1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1400.0	3.43	3.34	0.08	14.29	0.63	1400.0	1.39	1.15	1.13
1450.0	3.42	3.32	0.10	15.05	0.46	1450.0	1.34	1.17	1.11
1500.0	3.40	3.30	0.10	15.86	0.32	1500.0	1.29	1.18	1.10
1550.0	3.39	3.29	0.10	16.76	0.14	1550.0	1.25	1.19	1.10
1600.0	3.36	3.28	0.09	17.74	0.03	1600.0	1.21	1.20	1.11
1650.0	3.36	3.29	0.07	18.84	0.04	1650.0	1.18	1.21	1.11
1700.0	3.34	3.29	0.05	20.11	0.08	1700.0	1.15	1.20	1.13
1750.0	3.34	3.30	0.03	21.50	0.08	1750.0	1.14	1.19	1.15
1800.0	3.33	3.31	0.02	23.25	0.05	1800.0	1.13	1.17	1.17
1850.0	3.33	3.32	0.01	25.24	0.03	1850.0	1.11	1.15	1.17
1900.0	3.32	3.32	0.01	27.76	0.11	1900.0	1.10	1.12	1.17
1950.0	3.33	3.33	0.01	31.24	0.21	1950.0	1.09	1.08	1.17
2000.0	3.33	3.32	0.01	35.55	0.26	2000.0	1.07	1.05	1.15
2100.0	3.35	3.32	0.02	33.76	0.28	2100.0	1.03	1.04	1.10
2105.0	3.35	3.32	0.02	33.34	0.28	2105.0	1.03	1.04	1.10
2110.0	3.35	3.32	0.03	32.93	0.29	2110.0	1.03	1.05	1.09
2115.0	3.35	3.32	0.03	32.53	0.28	2115.0	1.03	1.05	1.09
2120.0	3.35	3.32	0.03	32.12	0.27	2120.0	1.03	1.05	1.09
2125.0	3.35	3.32	0.03	31.74	0.27	2125.0	1.04	1.06	1.08
2130.0	3.35	3.32	0.03	31.37	0.27	2130.0	1.04	1.06	1.08
2135.0	3.35	3.32	0.03	31.01	0.24	2135.0	1.04	1.06	1.08
2140.0	3.36	3.33	0.03	30.66	0.23	2140.0	1.05	1.07	1.07
2145.0	3.35	3.33	0.03	30.31	0.24	2145.0	1.05	1.07	1.07
2150.0	3.36	3.33	0.03	29.98	0.24	2150.0	1.06	1.08	1.07
2155.0	3.36	3.33	0.03	29.66	0.23	2155.0	1.06	1.08	1.06
2160.0	3.36	3.33	0.03	29.35	0.24	2160.0	1.07	1.08	1.06
2165.0	3.36	3.33	0.03	29.05	0.23	2165.0	1.07	1.09	1.06
2170.0	3.36	3.33	0.03	28.75	0.24	2170.0	1.08	1.09	1.05
2175.0	3.37	3.34	0.03	28.47	0.24	2175.0	1.08	1.09	1.05
2200.0	3.38	3.34	0.04	27.20	0.19	2200.0	1.11	1.11	1.05
2300.0	3.43	3.41	0.02	23.62	0.09	2300.0	1.24	1.18	1.14
2350.0	3.46	3.45	0.01	22.31	0.12	2350.0	1.32	1.22	1.21
2400.0	3.51	3.52	0.01	21.21	0.15	2400.0	1.41	1.25	1.28
2450.0	3.55	3.57	0.02	20.34	0.20	2450.0	1.50	1.27	1.35
2500.0	3.63	3.66	0.02	19.55	0.28	2500.0	1.59	1.30	1.42
2550.0	3.68	3.72	0.03	18.88	0.40	2550.0	1.68	1.32	1.48
2600.0	3.76	3.79	0.03	18.34	0.52	2600.0	1.77	1.34	1.54
2650.0	3.82	3.84	0.02	17.80	0.66	2650.0	1.84	1.37	1.58
2700.0	3.88	3.88	0.00	17.39	0.80	2700.0	1.90	1.39	1.60
2750.0	3.93	3.90	0.03	16.97	0.84	2750.0	1.96	1.43	1.60
2800.0	3.97	3.92	0.05	16.59	0.86	2800.0	1.99	1.46	1.58

¹ Total Loss = Insertion Loss + 3dB Splitter Loss

REV. X2

RACK-2-ED12568/1

100707

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350186, Brooklyn, New York 11235-0008 (718) 934-4500 Fax (718) 332-4661







The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



2 Way-0° Power Splitter/Combiner

RACK-2-ED12568/1

Typical Performance Curves



REV. X2
RACK-2-ED12568/1
100707
Page 1 of 1



Mini-Circuits®

RF/MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-5° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I