RDC-17-122-75X+

75Ω 17dB 5 to 1250 MHz

The Big Deal

- Low mainline loss, 0.8 dB
- · High directivity, 20 dB
- Good Return Loss, 24 dB
- Excellent coupling flatness, ±0.25 dB
- Supports DOCSIS® 3.1 Systems



CASE STYLE: TT231

Product Overview

Mini-Circuits RDC-17-122-75X+ surface-mount directional coupler provides 17 dB coupling with excellent flatness, low mainline loss, high directivity, and good return loss for 75Ω applications from 5 to 1250 MHz, supporting a variety of broadband applications including DOCSIS 3.1 systems and equipment. This model features core and wire construction with wrap-around terminations for good solderability and easy visual inspection.

Key Features

Feature	Advantages
Broadband, 5 to 1250 MHz	Supports bandwidth requirements for DOCSIS 3.1 systems and equipment.
Low mainline loss, 0.8 dB	Provides excellent through-path signal transmission and maintains low heat dissipation, avoiding the need for special heat sinking methods.
Power handling, up to 1W	Usable in systems with a variety of signal power requirements.
Excellent return loss, 24 dB typ.	Provides excellent matching for 50Ω systems.
High directivity, 20 dB	High directivity allows accurate signal sampling through the coupled port with minimal measurement error.
Top Hat feature	Improves speed and accuracy of pick and place assembly.

RDC-17-122-75X+

75Ω 17dB 5 to 1250 MHz

Features

- wideband, 5-1250 MHz
- excellent return loss, 24 dB typ.
- low mainline loss, 0.8 dB typ.
- high directivity, 20 dB typ.
- excellent coupling flatness, ±0.25 dB typ.
- aqueous washable

Applications

- DOCSIS 3.1
- cable tv

Electrical Specifications at 25°C



Generic photo used for illustration purposes only

CASE STYLE: TT2315

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Parameter	Condition (MHz)	Min.	Тур.	Max.	Unit
Frequency Range		5		1250	MHz
Mainline Loss ¹	5 - 1000	_	0.8	1.0	dB
Mairinie Loss	1000 - 1250	_	0.9	1.2	uБ
Coupling	5 - 1250	_	17.6	_	dB
Coupling Flatness (±)	5 - 1000	_	0.45	0.9	dB
Coupling Flattless (±)	1000 - 1250	_	0.25	0.6	uБ
	5 - 50	25	30	_	
Directivity	50 - 870	18	25	_	dB
	870 - 1250	11	16	_	
Return Loss (Input)	5 - 1250	18	24	_	dB
Return Loss (Output)	5 - 1250	18	25	_	dB
Return Loss (Coupling)	5 - 1250	18	24	_	dB
Input Power	5 - 1250	_	_	1.0	W

^{1.} Mainline loss includes theoretical power loss at coupled

Maximum Ratings


Parameter	Ratings
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

Permanent damage may occur if any of these limits are exceeded.


Pin Connections

Function	Pin Number
INPUT	1
OUTPUT	6
COUPLED	3
GROUND	2
75Ω TERM EXTERNAL	4
ISOLATE (DO NOT USE)	5

Product Marking




Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR DIRECTIONAL COUPLER WITH INTERNAL TRANSFORMER(S) AND EXTERNAL TERMINATION.


Outline Drawing



Outline Dimensions (inch)

F	Е	D	С	В	Α
.040	.050	.100	.140	.280	.250
1.02	1.27	2.54	3.56	7.11	6.35
wt.		K	J	Н	G
grams		.050	.310	.100	.040
0.35		1.27	7.87	2.54	1.02

Demo Board MCL P/N: TB-917+ Suggested PCB Layout (PL-452)



NOTES:

- NOTES:

 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 0Z. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

 2. 0603 SIZE CHIP RESISTOR FOOT PRINT SHOWN FOR REFERENCE, FOR RESISTOR VALUE REFER TO THE 17-917+.


 3. BOTTOM SIDE OF THE FCB IS CONTINUOUS GROUND PLANE.


- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)


DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)	Directivity (dB)		Return Loss (dB)	
, ,	In-Out	In-Cpl	, ,	In	Out	Cpl
5	0.72	17.98	28.79	20.90	22.55	20.74
20	0.59	17.75	32.44	24.13	27.41	23.94
50	0.60	17.72	36.13	24.60	28.37	24.18
100	0.62	17.72	40.69	25.14	29.38	24.52
200	0.64	17.74	45.55	25.90	31.66	25.31
400	0.67	17.75	35.63	26.23	30.64	25.95
600	0.71	17.74	25.23	27.35	28.80	27.49
870	0.79	17.72	20.73	27.88	27.88	24.20
1000	0.83	17.68	18.97	26.85	29.23	22.65
1250	0.94	17.47	15.91	26.17	46.02	20.26







Additional Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp


Typical Performance Data


FREQUENCY	INSERTION LOSS	COUPLING	DIRECTIVITY	RETURN LOSS		
(MHz)	(dB)	(dB)	(dB)	(dB)		
				IN	OUT	CPL
5	0.72	17.98	28.79	20.90	22.55	20.74
10	0.61	17.81	30.31	23.17	25.74	23.10
15	0.60	17.76	31.49	23.90	26.95	23.76
20	0.59	17.75	32.44	24.13	27.41	23.94
25	0.59	17.73	33.27	24.28	27.67	24.02
30	0.60	17.73	33.92	24.37	27.85	24.08
35	0.60	17.72	34.57	24.44	28.03	24.12
40	0.60	17.72	35.05	24.51	28.17	24.14
45	0.60	17.72	35.51	24.54	28.25	24.17
50	0.60	17.72	36.13	24.60	28.37	24.18
60	0.60	17.72	37.07	24.68	28.54	24.23
70	0.61	17.71	38.01	24.78	28.69	24.27
80	0.61	17.72	38.79	24.91	28.78	24.33
90	0.61	17.72	39.60	25.01	29.04	24.42
100	0.62	17.72	40.69	25.14	29.38	24.52
150	0.63	17.74	46.18	25.58	31.76	25.13
200	0.64	17.74	45.55	25.90	31.66	25.31
300	0.66	17.76	39.66	25.99	31.44	25.49
400	0.67	17.75	35.63	26.23	30.64	25.95
500	0.69	17.75	29.53	26.59	29.39	26.74
600	0.71	17.74	25.23	27.35	28.80	27.49
700	0.74	17.75	22.95	28.11	29.46	27.24
800	0.77	17.74	21.41	28.26	28.41	25.49
870	0.79	17.72	20.73	27.88	27.88	24.20
900	0.80	17.71	20.39	27.66	27.91	23.76
1000	0.83	17.68	18.97	26.85	29.23	22.65
1100	0.87	17.62	17.77	26.29	31.43	21.92
1200	0.92	17.53	16.54	25.90	37.33	20.89
1225	0.93	17.50	16.23	26.06	40.84	20.55
1250	0.94	17.47	15.91	26.17	46.02	20.26

Typical Performance Curves












Page 1 of 1

TT2315

Outline Dimensions



CASE #	A	В	С	D	Е	F	G	Н	J	K	WT. GRAMS
TT2315	.250 (6.35)	.280 (7.11)	.140 (3.56)	.100 (2.54)	.050 (1.27)	.040 (1.02)	.040 (1.02)	.100 (2.54)	.310 (7.87)	.050 (1.27)	.35

Dimensions are in inches (mm). Tolerances: 2Pl. ± .01; 3 Pl. ± .005

Notes:

1. Open style, Base material: Printed wiring laminate.

2. Termination finish: $3-5 \mu$ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.

All models, (+) suffix.

3. Top-Hat total thickness: .013 inches MAX.

4. Orientation Dot on Top Hat & PCB corresponds to Pin #1.






P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



THIRD ANGLE PROJECTION -------

		REVISIONS			
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M158078	NEW RELEASE	09/16/16	CA	IL

SUGGESTED MOUNTING CONFIGURATION FOR TT2315 CASE STYLE, "06DC03" PIN CODE



NOTES:

- 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- 2. 0603 SIZE CHIP RESISTOR FOOT PRINT SHOWN FOR REFERENCE, FOR RESISTOR VALUE REFER TO TB-917+.
- 3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.


DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)




DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE					• 4 ®		
DIMENSIONS ARE IN INCHES	DRAWN	CA	09/15/16		$\perp \mid$ Min:	1 - 0	ircu	1ts :3	Neptu	ne Avenue
TOLERANCES ON: 2 PL DECIMALS ±	CHECKED	IL	09/16/16	Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235					NI 11235	
3 PL DECIMALS ± .005 ANGLES ±	APPROVED	YL	09/16/16							
FRACTIONS ±				PL, 06DC03, TT2315,TB-917+						17+
	☐ Mini−Circuits ®					,		,		
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE			SIZE A	code ident 15542	DRAWING	98-PL	-452		REV:	
PARTY, IN WHOLE OR IN PART, WITHOU	ut written per	rmission of Mini	-CIRCUITS.	FILE:	98PL452	SCALE:	7:1	SHEET:		

Evaluation Board and Circuit






Schematic Diagram

Notes:

- 1. 75 Ohm BNC connectors.
- 2. PCB Material: RO4350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.



Mini-Circuits

Environmental Specifications

ENV02T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

ENV02T1 Rev: B

02/25/11

M130240 File: ENV02T1.pdf

This document and its contents are the property of Mini-Circuits.