

High Pass Filter Surface Mount

RHP-EDU2189

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : GP1212


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C

Parameter	Min.	Typ.	Max.	Units
Passband (Loss < 1.5 dB)	800		1800	MHz
Insertion loss 3 dB		685		MHz
Stopband (Loss > 40 dB) (Loss > 20 dB)	DC	350		MHz
	350	580.0		MHz
Passband VSWR		1.5		(:1)
Stopband VSWR		20		(:1)

Functional Schematic

MAXIMUM RATINGS

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	1.9 W





PIN CONNECTIONS

Input	2
Output	6
Ground	1,3,4,5,7,8

Typical Performance Data



FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	97.06	0.05	800	1.61
50	98.59	0.05	850	1.26
100	99.77	0.05	900	1.03
250	62.67	0.08	950	0.88
350	47.49	0.16	980	0.81
580	32.16	0.61	1000	0.76
584	30.11	0.63	1020	0.73
610	20.02	0.80	1050	0.67
680	3.53	4.79	1100	0.60
685	2.96	5.64	1130	0.57
700	1.78	8.74	1150	0.54
800	0.56	36.39	1200	0.50
1000	0.42	18.93	1250	0.46
1100	0.40	18.53	1300	0.42
1300	0.35	19.62	1350	0.39
1500	0.31	20.67	1400	0.37
1600	0.29	21.24	1450	0.35
1800	0.27	22.54	1500	0.33
2000	0.27	23.65	1550	0.31
2200	0.26	24.05	1600	0.29
2400	0.28	22.66	1650	0.28
2600	0.30	20.13	1700	0.27
2800	0.34	17.31	1750	0.26
3000	0.42	14.82	1800	0.25

Typical Performance Curves



Outline Dimensions

GP1212



CASE #	A	B	C	D	E	F	G	H	J	K	L	M
GP1212	.350 (8.89)	.350 (8.89)	.150 (3.81)	.175 (4.45)	.075 (1.91)	.100 (2.54)	.110 (2.79)	.040 (1.02)	.080 (2.03)	.050 (1.27)	.040 (1.02)	.195 (4.95)

CASE #	N	P	Q	R	WT. GRAM
GP1212	.390 (9.91)	.120 (3.05)	.390 (9.91)	.070 (1.78)	.5 +0.3 -0.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:

For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F78



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
16	12	7	10
			20
			50
			100
			200
		13	500, 1000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified