

Engineering Development Model

Power Splitter/Combiner RACK-3-ED10666A/2

3 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-940

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		700		1125 MHz
Isolation	700 - 1125 MHz		10	dB
Insertion Loss Above 4.8 dB	700 - 1125 MHz		0.1	dB
Phase Unbalance	700 - 1125 MHz		0.3	deg.
Amplitude Unbalance	700 - 1125 MHz		0.1	dB
VSWR	SUM Port		1.27	(:1)
	OUT Ports		5.00	(:1)

MAXIMUM RATINGS	
Operating Temperature	-5°C to 85°C
Storage Temperature	-40°C to 85°C

PIN CONNECTIONS	
SUM PORT	J1, N-TYPE, JACK
PORT 1	J3, SMA, PLUG
PORT 2	J4, SMA, PLUG
PORT 3	J5, SMA, PLUG

Functional Diagram



3 Way-0° Power Splitter/Combiner

RACK-3-ED10666A/2

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)			
	J1-J3	J1-J4	J1-J5		J3-J4	J3-J5	J4-J5			J1	J3	J4	J5
700.0	5.14	5.19	5.07	0.12	8.86	8.86	8.85	0.61	700.0	1.53	5.01	5.01	4.93
710.0	5.00	5.06	4.93	0.12	9.49	9.48	9.48	0.55	710.0	1.49	5.00	5.03	4.90
720.0	4.93	4.98	4.86	0.12	10.05	10.03	10.05	0.46	720.0	1.48	5.00	5.07	4.89
730.0	4.91	4.96	4.84	0.12	9.89	9.86	9.88	0.44	730.0	1.43	5.01	5.09	4.90
740.0	4.95	5.00	4.89	0.12	9.34	9.33	9.33	0.46	740.0	1.39	5.00	5.06	4.90
750.0	5.01	5.06	4.94	0.12	8.90	8.90	8.90	0.45	750.0	1.35	4.96	4.99	4.88
760.0	4.95	5.00	4.88	0.11	9.51	9.49	9.50	0.36	760.0	1.31	4.94	4.92	4.87
770.0	4.92	4.96	4.85	0.11	9.79	9.76	9.78	0.27	770.0	1.30	4.93	4.87	4.87
780.0	4.89	4.93	4.82	0.11	9.71	9.68	9.71	0.25	780.0	1.27	4.93	4.85	4.87
790.0	4.89	4.93	4.83	0.11	9.46	9.44	9.45	0.27	790.0	1.24	4.93	4.84	4.85
800.0	4.90	4.94	4.84	0.10	9.36	9.34	9.35	0.23	800.0	1.21	4.92	4.86	4.82
810.0	4.87	4.91	4.81	0.10	9.64	9.61	9.63	0.15	810.0	1.18	4.91	4.90	4.79
820.0	4.87	4.90	4.81	0.10	9.64	9.59	9.63	0.09	820.0	1.16	4.92	4.95	4.79
830.0	4.86	4.89	4.80	0.09	9.67	9.64	9.66	0.08	830.0	1.14	4.93	4.99	4.80
840.0	4.88	4.91	4.82	0.09	9.52	9.50	9.51	0.10	840.0	1.12	4.93	4.99	4.80
850.0	4.89	4.92	4.83	0.09	9.54	9.51	9.52	0.05	850.0	1.10	4.93	4.97	4.82
855.0	4.88	4.91	4.83	0.08	9.60	9.56	9.58	0.01	855.0	1.09	4.93	4.95	4.83
860.0	4.87	4.90	4.82	0.08	9.59	9.55	9.58	0.03	860.0	1.09	4.93	4.93	4.84
865.0	4.85	4.87	4.80	0.08	9.51	9.45	9.49	0.07	865.0	1.08	4.95	4.92	4.86
870.0	4.84	4.86	4.79	0.07	9.47	9.42	9.46	0.09	870.0	1.08	4.96	4.91	4.88
875.0	4.84	4.86	4.79	0.07	9.59	9.54	9.58	0.09	875.0	1.08	4.97	4.91	4.89
880.0	4.84	4.86	4.79	0.07	9.73	9.69	9.71	0.09	880.0	1.08	4.99	4.91	4.91
885.0	4.82	4.84	4.77	0.07	9.78	9.74	9.76	0.09	885.0	1.08	5.01	4.92	4.92
890.0	4.81	4.83	4.76	0.07	9.76	9.73	9.74	0.10	890.0	1.09	5.03	4.94	4.94
895.0	4.81	4.83	4.76	0.06	9.75	9.72	9.74	0.12	895.0	1.09	5.04	4.96	4.94
900.0	4.82	4.83	4.77	0.06	9.75	9.70	9.73	0.14	900.0	1.09	5.06	4.98	4.95
915.0	4.83	4.84	4.78	0.05	9.38	9.31	9.35	0.20	915.0	1.12	5.08	5.04	4.95
930.0	4.83	4.83	4.79	0.05	9.74	9.68	9.72	0.24	930.0	1.14	5.08	5.07	4.95
945.0	4.83	4.83	4.79	0.04	9.98	9.92	9.95	0.28	945.0	1.18	5.05	5.02	4.95
960.0	4.82	4.81	4.78	0.03	9.75	9.69	9.73	0.31	960.0	1.21	5.05	4.94	4.98
975.0	4.84	4.83	4.81	0.03	9.72	9.65	9.68	0.33	975.0	1.24	5.08	4.90	5.04
990.0	4.84	4.83	4.81	0.03	9.96	9.89	9.93	0.37	990.0	1.28	5.17	4.96	5.10
1005.0	4.84	4.82	4.82	0.02	9.75	9.67	9.71	0.38	1005.0	1.32	5.27	5.12	5.14
1020.0	4.85	4.82	4.83	0.03	9.84	9.76	9.79	0.40	1020.0	1.36	5.33	5.29	5.15
1035.0	4.85	4.82	4.83	0.04	10.34	10.16	10.19	0.44	1035.0	1.40	5.32	5.36	5.13
1050.0	4.86	4.81	4.84	0.04	10.08	9.99	10.02	0.45	1050.0	1.43	5.26	5.29	5.11
1065.0	4.87	4.82	4.86	0.05	9.85	9.76	9.79	0.45	1065.0	1.47	5.20	5.16	5.11
1080.0	4.88	4.82	4.88	0.06	10.31	10.21	10.24	0.48	1080.0	1.50	5.21	5.08	5.16
1095.0	4.89	4.82	4.88	0.07	10.33	10.23	10.26	0.49	1095.0	1.54	5.27	5.12	5.23
1110.0	4.91	4.83	4.91	0.08	10.03	9.92	9.95	0.47	1110.0	1.59	5.36	5.27	5.28
1125.0	4.94	4.85	4.94	0.09	10.29	10.17	10.21	0.48	1125.0	1.61	5.42	5.44	5.30

¹Total Loss = Insertion Loss + 4.8dB Splitter Loss



REV. X2

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site

RACK-3-ED10666A/2



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

9/1/2010






IF/RF MICROWAVE COMPONENTS

Page 1 of 1

3 Way-0° Power Splitter/Combiner

RACK-3-ED10666A/2

Typical Performance Curves





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-5° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I