NON-CATAL

Surface Mount **Amplifier**

RAMP-31-1+

 50Ω

1.5 to 30 MHz

Features

- Single +12V operation
- Excellent gain flatness, ±0.2 dB typ. usable to 70 MHz
- Output power up to +30 dBm typ.
- Small size

Applications

- Buffer amplifier
- Driver amplifier
- HF communications
- Lab, instrumentation, test equipment



Case Style: BL1543-1

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Тур.	Max.	Units
Frequency Range		1.5		30	MHz
Gain	1.5 - 30	28		31	dB
Gain Flatness	1.5 - 30		±0.2	±1.0	dB
Output Power at 1dB compression	1.5 - 30	27	30	_	dBm
Output third order intercept point IP3	1.5 - 30	40.5**	42*	_	dBm
Noise Figure	10 - 30	_	5.5	7.0	dB
Input VSWR	1.5 - 30	_	_	2.0	:1
Output VSWR	1.5 - 30	_	_	2.0	:1
DC Supply Voltage		11.75	12.0	12.25	V
Supply Current		_	310	325	mA

At 25°C with power out of each tone at 17 dBm

Maximum Ratings

•	
Parameter	Ratings
Operating Temperature	-40°C to 90°C
Storage Temperature	-55°C to 100°C
DC Voltage	13V
Input RF Power (no damage)	5 dBm

Permanent damage may occur if any of these limits are exceeded.

Pad Connections

Function	Pad Number
RF IN	1
RF OUT	12
DC INPUT	18
GROUND	All others and bottom pad

ESD Rating

ESD Class 1A 250 to <500V in accordance with JS-001-2014 Moisture Sensitivity: MSL3 in accordance with IPC/JEDECJ-STD-020C

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




^{-40°} to 90°C with power out of each tone at 17 dBm

NON-CATALO

RAMP-31-1+

Outline Drawing




Outline Dimensions (inch)

L	K	J	Н	G	F	E	D	С	В	Α
.140	.070		.040	.060	.160	.100		.25	1.42	.93
3.56	1.78		1.02	1.52	4.06	2.54	1.60	6.35	36.07	23.62
wt	W	V	U	Т	S	R	Q	Р	N	M
grams	.083	.065	.640	1.0	.620	.980	.065	.100	1.165	.970
6.5	2 11	1.65	16.26	25.40	15.75	24.80	1 65	2.54	20.50	24.64


Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

BL1543-1

Outline Dimensions



PCB Land Pattern



DENOTES METALLIZATION DENOTES SOLDER RESIST

CASE #	A	В	С	D	Е	F	G	Н	J	K	L	M
BL1543-1	.93 (23.62)	1.42 (36.07)	.25 (6.35)	.063 (1.60)	.100 (2.54)	.160 (4.06)	.060 (1.52)	.040 (1.02)		.070 (1.78)	.140 (3.56)	.970 (24.64)

CASE #	N	P	Q	R	S	T	U	V	W	WT. GRAM
BL1543-1	1.165 (29.59)	.100	.065 (1.65)	.980 (24.89)	.620	1.000 (25.40)	.640 (16.26)	.065 (1.65)	.083 (2.10)	6.5
	(29.39)	(2.34)	(1.05)	(24.03)	(13.73)	(23.40)	(10.20)	(1.05)	(2.10)	

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

1. Case material: Copper-Nickel alloy. Printed wiring laminate. Base material:

3-5µinch (.08-.13 microns) Gold over 120-240µinch (3.05-6.10 microns) Nickel plate. Termination finish:

All models, (+) suffix.




INTERNET http://www.minicircuits.com

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F89

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel		
56	32	13	100		

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET http://www.minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



ENV81



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	40° to 90° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 245°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2; Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

ENV81 Rev: OR

06/23/15

M151674 File: ENV81.pdf

This document and its contents are the property of Mini-Circuits.