

# Surface Mount Attenuator/Switch

50Ω Bi-Phase 2 to 400 MHz

RAS-1+



Generic photo used for illustration purposes only  
CASE STYLE: TT241


## Maximum Ratings

|   |                |
|---|----------------|
| Operating Temperature   | -40°C to 85°C  |
| Storage Temperature   | -55°C to 100°C |
| Control Current   | 30mA           |
| Permanent damage may occur if any of these limits are exceeded. |                |

## Pin Connections

|         |       |
|---------|-------|
| INPUT   | 4     |
| OUTPUT  | 1     |
| CONTROL | 5     |
| GROUND  | 2,3,6 |


## Outline Drawing




## Outline Dimensions (inch/mm)

| A    | B    | C    | D    | E     | F    |
|------|------|------|------|-------|------|
| .250 | .31  | .275 | .100 | .050  | .055 |
| 6.35 | 7.87 | 6.99 | 2.54 | 1.27  | 1.40 |
| G    | H    | J    | K    | wt    |      |
| .040 | .070 | .270 | .050 | grams |      |
| 1.02 | 1.78 | 6.86 | 1.27 | 0.50  |      |

## suggested control port biasing configuration



## Demo Board MCL P/N: TB-03 Suggested PCB Layout (PL-052)



## Features

- wideband, 2 to 400 MHz
- low conversion loss, 1.6 dB typ.
- excellent phase and amplitude unbalance

## Applications

- bi-phase modulator

## Attenuator/Switch Electrical Specifications




| FREQUENCY (MHz)                | CON     | INSERTION LOSS (dB) ±20 mA |             | MAX. INPUT PWR (dBm) ±20 mA | IN-OUT ISOLATION (dB) 0 mA |      |      | BI-PHASE X (±20 mA) Typ. |                                  |             |             |    |    |      |     |     |     |
|--------------------------------|---------|----------------------------|-------------|-----------------------------|----------------------------|------|------|--------------------------|----------------------------------|-------------|-------------|----|----|------|-----|-----|-----|
|                                |         | Mid-Band m                 | Total Range |                             | L                          | M    | U    | Δ AMP (dB)               | Phase (deg.) deviation from 180° |             |             |    |    |      |     |     |     |
| f <sub>L</sub> -f <sub>U</sub> |         | Typ.                       | Max.        | 1 dB compr.                 | no damage                  | Typ. | Min. | Typ.                     | Min.                             | Total Range | Total Range |    |    |      |     |     |     |
| 2-400                          | DC-0.05 | 1.4                        | 2.4         | 1.6                         | 3.2                        | 20*  | 25   | 65                       | 45                               | 45          | 28          | 32 | 22 | 0.10 | 0.1 | 1.0 | 2.0 |

L = low range [f<sub>L</sub> to 10 f<sub>L</sub>] M = mid range [10 f<sub>L</sub> to f<sub>U</sub>/2] U = upper range [f<sub>U</sub>/2 to f<sub>U</sub>] m = [2 f<sub>L</sub> to f<sub>U</sub>/2]  
\* 15 dBm from 2-10 MHz.


Performance specifications apply for input power up to 10 dB below stated 1 dB compression.

## Typical Performance Data

| Freq. (MHz) | I. Loss (dB) at 20mA | ±Control ΔΔAMP (dB) |      | 20mA ΔΔPhase (deg.) | Isolation (dB) (in-out) |    | Input R. Loss (dB) | Control Current (mA) | Attenuation (dB) |         |         | Phase Δ ref at 15mA Ctrl deg. |         |         | Input VSWR |         |         |
|-------------|----------------------|---------------------|------|---------------------|-------------------------|----|--------------------|----------------------|------------------|---------|---------|-------------------------------|---------|---------|------------|---------|---------|
|             |                      | 2                   | 200  |                     | 400                     | 2  |                    |                      | 200              | 400     | 2       | 200                           | 400     | 2       | 200        | 400     |         |
| X           | σ                    | X                   | X    | X                   | X                       | X  | X                  |                      | 2 MHz            | 200 MHz | 400 MHz | 2 MHz                         | 200 MHz | 400 MHz | 2 MHz      | 200 MHz | 400 MHz |
| 2.0         | 1.67                 | 0.000               | 0.01 | 179.9               | 78                      | 54 | 18.1               | 0.0000               | 72.7             | 39.0    | 30.6    | 27.2                          | -87.7   | -95.3   | 7.7        | 7.2     | 4.4     |
| 7.0         | 1.16                 | 0.001               | 0.00 | 180.0               | 68                      | 43 | 15.4               | 0.0003               | 64.4             | 39.2    | 30.7    | 22.2                          | -86.0   | -94.6   | 7.7        | 7.2     | 4.4     |
| 10.0        | 1.16                 | 0.001               | 0.00 | 180.0               | 66                      | 40 | 27.6               | 0.0005               | 56.5             | 39.0    | 30.8    | 28.6                          | -84.3   | -93.7   | 7.6        | 7.2     | 4.4     |
| 21.9        | 1.16                 | 0.001               | 0.00 | 180.0               | 58                      | 33 | 31.0               | 0.0012               | 50.4             | 39.0    | 30.7    | 17.6                          | -80.5   | -92.0   | 7.6        | 7.2     | 4.4     |
| 39.8        | 1.19                 | 0.001               | 0.00 | 180.1               | 53                      | 28 | 31.9               | 0.0019               | 47.8             | 39.0    | 30.7    | 14.1                          | -77.4   | -90.3   | 7.5        | 7.2     | 4.4     |
| 59.7        | 1.23                 | 0.001               | 0.00 | 180.1               | 50                      | 25 | 32.1               | 0.0054               | 42.5             | 37.9    | 30.6    | 8.2                           | -56.2   | -79.9   | 7.4        | 7.0     | 4.3     |
| 61.7        | 1.23                 | 0.001               | 0.00 | 180.1               | 50                      | 25 | 32.1               | 0.0100               | 38.4             | 35.8    | 30.1    | 7.6                           | -37.3   | -67.6   | 7.2        | 6.9     | 4.3     |
| 81.6        | 1.24                 | 0.001               | 0.00 | 180.2               | 47                      | 22 | 32.2               | 0.0157               | 35.1             | 33.1    | 29.0    | 8.8                           | -25.3   | -55.1   | 7.1        | 6.7     | 4.2     |
| 99.5        | 1.27                 | 0.001               | 0.00 | 180.2               | 46                      | 21 | 32.3               | 0.0284               | 30.6             | 28.7    | 26.3    | 8.8                           | -12.8   | -37.6   | 6.7        | 6.3     | 4.0     |
| 121.4       | 1.31                 | 0.001               | 0.01 | 180.3               | 44                      | 19 | 32.4               | 0.0433               | 27.3             | 25.3    | 23.7    | 9.2                           | -7.2    | -26.9   | 6.3        | 5.9     | 3.8     |
| 141.3       | 1.32                 | 0.001               | 0.01 | 180.4               | 42                      | 18 | 32.4               | 0.0722               | 23.2             | 21.2    | 20.0    | 9.3                           | -3.1    | -17.7   | 5.6        | 5.3     | 3.5     |
| 181.1       | 1.37                 | 0.001               | 0.01 | 180.6               | 39                      | 16 | 32.2               | 0.1012               | 20.7             | 18.6    | 17.6    | 9.0                           | -1.4    | -13.2   | 5.2        | 4.9     | 3.3     |
| 200.0       | 1.40                 | 0.001               | 0.01 | 180.6               | 39                      | 15 | 32.0               | 0.1898               | 16.1             | 14.1    | 13.3    | 8.2                           | 0.4     | -8.0    | 4.1        | 3.9     | 2.8     |
| 220.9       | 1.39                 | 0.001               | 0.01 | 180.8               | 38                      | 15 | 31.6               | 0.3008               | 13.1             | 11.2    | 10.6    | 7.4                           | 0.9     | -5.5    | 3.4        | 3.2     | 2.4     |
| 240.8       | 1.39                 | 0.001               | 0.01 | 180.9               | 36                      | 14 | 30.3               | 0.4259               | 10.9             | 9.2     | 8.8     | 6.7                           | 1.1     | -4.2    | 2.9        | 2.7     | 2.1     |
| 280.6       | 1.52                 | 0.001               | 0.05 | 181.1               | 35                      | 13 | 26.6               | 0.7017               | 8.3              | 6.9     | 6.6     | 5.4                           | 1.1     | -2.8    | 2.2        | 2.1     | 1.7     |
| 300.5       | 1.52                 | 0.001               | 0.04 | 181.1               | 35                      | 14 | 24.8               | 0.9968               | 6.8              | 5.6     | 5.4     | 4.4                           | 0.9     | -2.1    | 1.9        | 1.8     | 1.5     |
| 340.3       | 1.56                 | 0.001               | 0.03 | 181.4               | 33                      | 13 | 21.4               | 1.7486               | 4.8              | 3.9     | 4.0     | 3.0                           | 0.7     | -1.3    | 1.5        | 1.5     | 1.3     |
| 360.2       | 1.64                 | 0.002               | 0.06 | 181.6               | 32                      | 13 | 19.8               | 5.6920               | 2.5              | 2.1     | 2.3     | 0.9                           | 0.2     | -0.3    | 1.2        | 1.1     | 1.2     |
| 400.0       | 1.78                 | 0.003               | 0.09 | 181.7               | 31                      | 14 | 17.1               | 15.1258              | 1.8              | 1.5     | 1.8     | 0.0                           | 0.0     | 0.1     | 1.3        | 1.1     | 1.3     |



## electrical schematic



## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)




## Typical Performance Data

| FREQ.<br>(MHz) | INSERTION<br>LOSS<br>(dB)<br>at 20mA<br>Control<br>Current | AMP.<br>UNBAL.<br>(dB)<br>at ± 20mA<br>Control<br>Current | PHASE<br>UNBAL.<br>(deg.)<br>at ± 20mA<br>Control<br>Current | ISOLATION<br>at 0 mA<br>Control Current<br>(dB) |        | RETURN<br>LOSS<br>(dB)<br>Input |
|----------------|--|---|--|---|--------|---------------------------------|
|                |  |   |  | In-Out  | In-Con |                                 |
| 2.0            | 1.67   | 0.01  | 179.9  | 78  | 54     | 18.1                            |
| 7.0            | 1.16   | 0.00  | 180.0  | 68  | 43     | 15.4                            |
| 10.0           | 1.16   | 0.00  | 180.0  | 66  | 40     | 27.6                            |
| 21.9           | 1.16   | 0.00  | 180.0  | 58  | 33     | 31.0                            |
| 39.8           | 1.19   | 0.00  | 180.1  | 53  | 28     | 31.9                            |
| 59.7           | 1.23   | 0.00  | 180.1  | 50  | 25     | 32.1                            |
| 61.7           | 1.23   | 0.00  | 180.1  | 50  | 25     | 32.1                            |
| 81.6           | 1.24   | 0.00  | 180.2  | 47  | 22     | 32.2                            |
| 99.5           | 1.27   | 0.00  | 180.2  | 46  | 21     | 32.3                            |
| 121.4          | 1.31   | 0.01  | 180.3  | 44  | 19     | 32.4                            |
| 141.3          | 1.32   | 0.01  | 180.4  | 42  | 18     | 32.4                            |
| 181.1          | 1.37   | 0.01  | 180.6  | 39  | 16     | 32.2                            |
| 200.0          | 1.40   | 0.01  | 180.6  | 39  | 15     | 32.0                            |
| 220.9          | 1.39   | 0.01  | 180.8  | 38  | 15     | 31.6                            |
| 240.8          | 1.39   | 0.01  | 180.9  | 36  | 14     | 30.3                            |
| 280.6          | 1.52   | 0.05  | 181.1  | 35  | 13     | 26.6                            |
| 300.5          | 1.52   | 0.04  | 181.1  | 35  | 14     | 24.8                            |
| 340.3          | 1.56   | 0.03  | 181.4  | 33  | 13     | 21.4                            |
| 360.2          | 1.64   | 0.06  | 181.6  | 32  | 13     | 19.8                            |
| 400.0          | 1.78   | 0.09  | 181.7  | 31  | 14     | 17.1                            |


| CONTROL<br>CURRENT<br>(mA) | ATTENUATION<br>(dB) |         |         | PHASE UNBALANCE<br>REF AT 15 mA CONTROL<br>(deg.) |         |         | INPUT VSWR<br>(:1) |         |         |
|----------------------------|---------------------|---------|---------|---|---------|---------|--------------------|---------|---------|
|                            | 2 MHz               | 200 MHz | 400 MHz | 2 MHz   | 200 MHz | 400 MHz | 2 MHz              | 200 MHz | 400 MHz |
| 0.0000                     | 72.7                | 39.0    | 30.6    | 27.2  | -87.7   | -95.3   | 7.7                | 7.2     | 4.4     |
| 0.0003                     | 64.4                | 39.2    | 30.7    | 22.2  | -86.0   | -94.6   | 7.7                | 7.2     | 4.4     |
| 0.0005                     | 56.5                | 39.0    | 30.8    | 28.6  | -84.3   | -93.7   | 7.6                | 7.2     | 4.4     |
| 0.0012                     | 50.4                | 39.0    | 30.7    | 17.6  | -80.5   | -92.0   | 7.6                | 7.2     | 4.4     |
| 0.0019                     | 47.8                | 39.0    | 30.7    | 14.1  | -77.4   | -90.3   | 7.5                | 7.2     | 4.4     |
| 0.0054                     | 42.5                | 37.9    | 30.6    | 8.2   | -56.2   | -79.9   | 7.4                | 7.0     | 4.3     |
| 0.0100                     | 38.4                | 35.8    | 30.1    | 7.6   | -37.3   | -67.6   | 7.2                | 6.9     | 4.3     |
| 0.0157                     | 35.1                | 33.1    | 29.0    | 8.8   | -25.3   | -55.1   | 7.1                | 6.7     | 4.2     |
| 0.0284                     | 30.6                | 28.7    | 26.3    | 8.8   | -12.8   | -37.6   | 6.7                | 6.3     | 4.0     |
| 0.0433                     | 27.3                | 25.3    | 23.7    | 9.2   | -7.2    | -26.9   | 6.3                | 5.9     | 3.8     |
| 0.0722                     | 23.2                | 21.2    | 20.0    | 9.3   | -3.1    | -17.7   | 5.6                | 5.3     | 3.5     |
| 0.1012                     | 20.7                | 18.6    | 17.6    | 9.0   | -1.4    | -13.2   | 5.2                | 4.9     | 3.3     |
| 0.1898                     | 16.1                | 14.1    | 13.3    | 8.2   | 0.4     | -8.0    | 4.1                | 3.9     | 2.8     |
| 0.3008                     | 13.1                | 11.2    | 10.6    | 7.4   | 0.9     | -5.5    | 3.4                | 3.2     | 2.4     |
| 0.4259                     | 10.9                | 9.2     | 8.8     | 6.7   | 1.1     | -4.2    | 2.9                | 2.7     | 2.1     |
| 0.7017                     | 8.3                 | 6.9     | 6.6     | 5.4   | 1.1     | -2.8    | 2.2                | 2.1     | 1.7     |
| 0.9968                     | 6.8                 | 5.6     | 5.4     | 4.4   | 0.9     | -2.1    | 1.9                | 1.8     | 1.5     |
| 1.7486                     | 4.8                 | 3.9     | 4.0     | 3.0   | 0.7     | -1.3    | 1.5                | 1.5     | 1.3     |
| 5.6920                     | 2.5                 | 2.1     | 2.3     | 0.9   | 0.2     | -0.3    | 1.2                | 1.1     | 1.2     |
| 15.1258                    | 1.8                 | 1.5     | 1.8     | 0.0   | 0.0     | 0.1     | 1.3                | 1.1     | 1.3     |

## Typical Performance Curves


Insertion Loss @ 20 mA




Amplitude Unbalance @ ± 20mA




Phase Unbalance @ ± 20mA




Isolation @ 0 mA




Return Loss Input




Attenuation



Phase Unbalance ref @ 15 mA




Input VSWR




## TT241

### Outline Dimensions



### PCB Land Pattern



| CASE # | A              | B             | C             | D              | E              | F              | G              | H              | J              | K              | WT. GRAM |
|--------|----------------|---------------|---------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| TT241  | .250<br>(6.35) | .31<br>(7.87) | .27<br>(6.99) | .100<br>(2.54) | .050<br>(1.27) | .055<br>(1.40) | .040<br>(1.02) | .070<br>(1.78) | .270<br>(6.86) | .050<br>(1.27) | .50      |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Ceramic.
- Termination finish:
  - For RoHS Case Styles: 2-10 $\mu$  inch (.05-.25 microns) Gold plate over 100-300  $\mu$  inch (2.54-7.62 microns) Nickel plate. All models, (+) suffix.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F50



| <b>Tape Width,<br/>mm</b> | <b>Device Cavity<br/>Pitch, mm</b> | <b>Reel Size,<br/>inches</b> | <b>Devices per Reel</b> |
|---------------------------|------------------------------------|------------------------------|-------------------------|
| 24                        | 12                                 | 13                           | 500                     |

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

| REV | ECN No. | DESCRIPTION  | DATE     | DR  | AUTH |
|-----|---------|--|----------|-----|------|
| A   | M101143 | ADDED "gk" PIN CONNECTION, TT100 CASE STYLE & NOTE 2 | 10/10/05 | MMG | DJ   |
| B   | M102713 | ADDED "...WITH SMOBC"                                | 01/17/06 | MMG | IL   |
| C   | M108637 | REMOVED "PIN 1", ADDED INDEX ON UNIT                 | 12/01/06 | MYG | FL   |

**SUGGESTED MOUNTING CONFIGURATION  
FOR BH292, CD541/542/636/637, TT100/240 CASE  
STYLES, "gk", "ht", "hu", "nd", "w" PIN CONNECTIONS**



- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.  
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE     |
|----------------------------|----------|----------|
| DIMENSIONS ARE IN INCHES   | MMG      | 07/17/02 |
| TOLERANCES ON:             | WL       | 08/02/02 |
| 2 PL DECIMALS ±            | DJ       | 08/05/02 |
| 3 PL DECIMALS ± .005       |          |          |
| ANGLES ±                   |          |          |
| FRACTIONS ±                |          |          |

**Mini-Circuits®** 13 Neptune Avenue  
Brooklyn NY 11235


**PL, gk/ht/hu/nd/w, BH292,  
CD541/542/636/637, TT100/240, TB-03**

|                         |                            |                                 |                  |
|-------------------------|----------------------------|---------------------------------|------------------|
| SIZE<br><b>A</b>        | CODE IDENT<br><b>15542</b> | DRAWING NO:<br><b>98-PL-052</b> | REV:<br><b>C</b> |
| FILE:<br><b>98PL052</b> | SCALE:<br><b>8:1</b>       | SHEET:<br><b>1 OF 1</b>         |                  |


Mini-Circuits®  
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

# Evaluation Board and Circuit

For Pin Connections and DUT Orientation Refer to  
Data Sheet of the DUT




TB-03



Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition   | Reference/Spec   |
|--------------------------------|---|--|
| Operating Temperature          | -40° to 85°C<br>Ambient Environment   | Individual Model Data Sheet  |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment   | Individual Model Data Sheet  |
| Humidity                       | 90 to 95% RH, 240 hours, 50°C   | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock                  | -55° to 100°C, 100 cycles   | MIL-STD-202, Method 107, Condition A-3, except +100°C  |
| Solder Reflow Heat             | Sn-Pb Eutetic Process: 225°C peak<br>Pb-Free Process 245° - 250°C peak  | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1  |
| Solderability                  | 10X Magnification   | J-STD-002, 95% Coverage  |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)   | MIL-STD-202, Method 204, Condition D   |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes   | MIL-STD-202, Method 213, Condition A   |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215  |