

Surface Mount High Pass Filter

RHP-700+

50Ω 700 to 3000 MHz

The Big Deal

- Low insertion loss
- High rejection
- Good return loss



Generic photo used for illustration purposes only
CASE STYLE: GP1212

Product Overview

RHP-700+ is a 50Ω high pass filter fabricated using SMT technology. This high pass filter covers from 700-3000 MHz. This filter is built with high Q capacitors and air-coil inductors for superior performance. This filter is developed for square kilometer array telescope systems for radio astronomy. It has repeatable performance across lots and consistent performance across temperature.

Key Features

Feature	Advantages
Low insertion loss	Can be used in high performance applications such as radio astronomy.
Good rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad frequency band.
Small size, 0.35" x 0.35" x 0.15"	The small surface mount package enables the RHP-700+ to be used in compact designs.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount High Pass Filter

50Ω 700 to 3000 MHz

RHP-700+



Generic photo used for illustration purposes only
CASE STYLE: GP1212


Features

- Low insertion loss
- High rejection
- Good return loss


Applications

- Radio telescope applications
- Aeronautical / aviation
- Wireless communications service
- Maritime

Functional Schematic



Typical Frequency Response



Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	Rejection Loss	DC-F1	DC-500	20	30	-	dB
	VSWR	DC-F1	DC-500	-	20	-	:1
Pass Band	Insertion Loss	F2-F3	700-3000	-	0.6	2.0	dB
	VSWR	F2-F3	700-3000	-	1.5	1.8	:1

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5 W max.





Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	99.92	434.30
280	51.65	347.44
500	35.33	48.26
540	17.82	28.03
575	7.77	9.74
600	3.11	3.65
618	1.49	2.08
638	0.79	1.42
700	0.42	1.06
1000	0.20	1.12
1320	0.17	1.16
1670	0.16	1.19
1870	0.15	1.16
1990	0.14	1.12
2200	0.13	1.06
2380	0.15	1.07
2540	0.17	1.14
2760	0.23	1.26
2900	0.29	1.35
3000	0.33	1.41

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
ECO-005139
RHP-700+
EDU1702
URJ
201128
Page 2 of 3


Pad Connections

INPUT	2
OUTPUT	6
GROUND	1, 3, 4, 5, 7, 8

Demo Board MCL P/N: TB-332
Suggested PCB Layout (PL-176)



Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G	H
.350	.350	.150	.175	.075	.100	.110	.040
8.89	8.89	3.81	4.45	1.93	2.54	2.79	1.02

J	K	L	M	N	P	Q	R	Wt.
.080	.050	.040	.195	.390	.120	.390	.070	grams
2.03	1.27	1.02	4.95	9.91	3.05	9.91	1.78	.50

Note: Please refer to case style drawing for details

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
1	104.05	99.92	102.62	0.04	0.04	0.04	0.04	0.04	0.04
5	118.29	110.00	100.81	0.03	0.04	0.03	0.04	0.04	0.04
10	103.54	112.78	97.35	0.03	0.03	0.03	0.03	0.03	0.03
30	99.61	100.48	104.43	0.01	0.01	0.01	0.01	0.02	0.01
40	99.42	113.03	104.86	0.00	0.01	0.01	0.01	0.01	0.01
45	106.67	99.96	102.64	0.00	0.01	0.01	0.01	0.01	0.01
50	98.28	108.10	96.03	0.00	0.00	0.00	0.00	0.01	0.01
70	104.91	99.91	106.80	0.01	0.00	0.00	0.01	0.00	0.00
100	96.37	96.42	97.02	0.02	0.01	0.00	0.02	0.01	0.00
200	66.44	66.32	66.34	0.02	0.01	0.02	0.02	0.01	0.02
215	63.22	63.11	62.91	0.02	0.02	0.03	0.02	0.01	0.03
235	59.27	59.24	59.12	0.01	0.02	0.04	0.01	0.01	0.03
300	48.59	48.75	48.79	0.02	0.06	0.08	0.01	0.05	0.07
355	41.86	42.03	42.17	0.06	0.10	0.13	0.05	0.09	0.11
375	39.95	40.11	40.25	0.07	0.12	0.15	0.07	0.11	0.14
440	37.20	37.34	37.54	0.15	0.21	0.25	0.16	0.21	0.24
480	51.43	51.97	52.90	0.23	0.30	0.35	0.24	0.30	0.35
500	35.62	35.33	34.98	0.27	0.36	0.41	0.30	0.38	0.44
510	29.82	29.62	29.37	0.31	0.40	0.46	0.34	0.42	0.49
530	21.44	21.28	21.08	0.41	0.52	0.60	0.46	0.57	0.65
545	16.36	16.20	16.00	0.56	0.69	0.79	0.63	0.76	0.88
555	13.29	13.14	12.94	0.74	0.90	1.02	0.83	0.99	1.13
580	6.71	6.62	6.45	1.91	2.18	2.44	2.07	2.36	2.65
595	3.82	3.81	3.71	3.64	4.02	4.42	3.85	4.27	4.72
602	2.83	2.86	2.81	4.85	5.28	5.75	5.09	5.56	6.09
622	1.17	1.28	1.32	9.72	10.22	10.87	10.03	10.57	11.26
628	0.92	1.05	1.11	11.52	12.02	12.69	11.83	12.34	13.02
638	0.66	0.79	0.87	14.79	15.22	15.92	14.95	15.35	15.91
652	0.48	0.61	0.70	19.58	19.92	20.55	18.97	19.04	19.20
700	0.30	0.42	0.49	27.06	30.37	33.38	23.60	23.75	23.68
770	0.19	0.31	0.39	62.38	34.77	27.12	33.67	29.42	25.36
780	0.18	0.30	0.37	43.07	32.26	25.96	34.64	29.24	24.86
805	0.17	0.28	0.36	33.36	28.45	23.89	33.23	28.14	23.73
830	0.15	0.26	0.35	29.92	26.49	22.78	30.41	26.78	22.87
900	0.12	0.23	0.31	26.81	24.59	22.35	27.34	25.25	22.73
1000	0.08	0.20	0.27	25.94	25.22	24.94	26.45	25.86	25.36
1010	0.08	0.19	0.26	25.85	25.31	25.24	26.25	25.83	25.53
1100	0.05	0.17	0.25	24.93	25.53	26.09	25.18	25.39	25.31
1200	0.04	0.17	0.25	23.69	24.17	23.36	23.79	23.38	22.14
1300	0.02	0.17	0.26	23.10	22.66	20.99	22.96	21.48	19.68
1400	0.01	0.17	0.27	22.97	21.59	19.53	22.63	20.24	18.24
1500	0.00	0.17	0.29	22.83	21.06	18.83	22.19	19.55	17.51
1600	0.01	0.16	0.28	23.09	20.96	18.73	22.20	19.30	17.28
1700	0.01	0.17	0.28	24.05	21.34	19.03	22.67	19.34	17.36
1800	0.02	0.16	0.28	25.01	22.22	19.87	23.13	19.74	17.82
1900	0.03	0.15	0.27	25.67	23.24	20.96	23.29	20.29	18.50
2000	0.04	0.14	0.26	26.85	24.91	22.67	23.99	21.22	19.58
2100	0.04	0.15	0.26	27.99	27.02	25.05	24.71	22.38	20.91
2200	0.05	0.13	0.25	28.24	30.27	28.75	24.66	23.48	22.50
2260	0.05	0.14	0.26	27.51	31.44	31.43	24.37	24.10	23.58
2300	0.05	0.14	0.26	26.86	31.47	32.38	24.07	24.40	24.20
2355	0.05	0.14	0.27	25.78	30.16	32.34	23.59	24.55	24.78
2400	0.05	0.15	0.28	24.88	28.49	30.20	23.20	24.48	24.97
2500	0.05	0.16	0.30	22.99	25.12	25.90	21.99	23.41	24.13
2600	0.03	0.19	0.34	20.99	22.20	22.51	20.65	21.71	22.40
2700	0.02	0.21	0.36	19.17	19.91	20.10	19.10	19.87	20.35
2800	0.01	0.25	0.40	17.48	18.10	18.27	17.58	18.25	18.58
2900	0.05	0.29	0.46	15.94	16.60	16.79	16.14	16.85	17.09
2950	0.07	0.32	0.47	15.29	15.97	16.14	15.57	16.29	16.48
3000	0.08	0.33	0.51	14.72	15.42	15.57	14.91	15.64	15.87







Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
700	1.86	1.84	1.83
705	1.82	1.80	1.79
710	1.78	1.76	1.75
715	1.73	1.72	1.71
720	1.69	1.68	1.67
725	1.65	1.64	1.62
730	1.60	1.59	1.58
735	1.56	1.55	1.54
740	1.52	1.51	1.50
745	1.48	1.47	1.46
750	1.45	1.43	1.42
755	1.41	1.40	1.39
760	1.38	1.37	1.35
765	1.35	1.33	1.32
770	1.32	1.31	1.29
775	1.29	1.28	1.27
780	1.26	1.25	1.24
785	1.23	1.22	1.21
790	1.21	1.20	1.19
795	1.19	1.17	1.16
800	1.16	1.15	1.14
805	1.14	1.13	1.12
810	1.12	1.11	1.10
815	1.10	1.09	1.08
820	1.08	1.07	1.06
825	1.06	1.05	1.04
830	1.04	1.03	1.02
835	1.02	1.01	1.00
840	1.00	0.99	0.98
895	0.84	0.83	0.82
900	0.83	0.82	0.81
945	0.74	0.73	0.72
950	0.73	0.72	0.71
985	0.67	0.66	0.65
990	0.66	0.65	0.65
1030	0.60	0.60	0.59
1035	0.60	0.59	0.58
1040	0.59	0.58	0.58
1045	0.58	0.58	0.57
1050	0.58	0.57	0.57
1055	0.57	0.57	0.56
1060	0.57	0.56	0.56
1065	0.56	0.56	0.55
1070	0.56	0.55	0.55
1170	0.46	0.46	0.45
1485	0.31	0.30	0.29
1490	0.30	0.29	0.29
1835	0.22	0.21	0.21
2005	0.20	0.20	0.19
2010	0.20	0.19	0.18
2015	0.19	0.18	0.17
2070	0.21	0.20	0.19
2090	0.23	0.22	0.23
2100	0.22	0.21	0.21
2105	0.21	0.20	0.20
2120	0.19	0.19	0.19
2880	0.14	0.13	0.13
2885	0.14	0.14	0.13
2995	0.14	0.13	0.12
3000	0.14	0.14	0.10

High Pass Filter

RHP-700+

Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS




REV. OR
RHP-700+
130415
Page 1 of 2

High Pass Filter

RHP-700+

Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com





IF/RF MICROWAVE COMPONENTS



REV. OR
RHP-700+
130415
Page 2 of 2

Outline Dimensions

GP1212



CASE #	A	B	C	D	E	F	G	H	J	K	L	M
GP1212	.350 (8.89)	.350 (8.89)	.150 (3.81)	.175 (4.45)	.075 (1.91)	.100 (2.54)	.110 (2.79)	.040 (1.02)	.080 (2.03)	.050 (1.27)	.040 (1.02)	.195 (4.95)

CASE #	N	P	Q	R	WT. GRAM
GP1212	.390 (9.91)	.120 (3.05)	.390 (9.91)	.070 (1.78)	.5 +0.3 -0.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:

For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F78



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
16	12	7	10
			20
			50
			100
			200
		13	500, 1000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	R59289	NEW RELEASE (FROM RAVON)	02/05	DK	HH
A	M101151	ADDED "RBP" & CORRECTED PIN	10/10/05	MMG	DJ
		CONNECTION TO DESCRIPTION OF PL-DWG.			
B	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/20/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION
 FOR GP731 CASE STYLE, "qf" PIN CONNECTION.



- NOTES: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	DK (RAVON)	10 FEB 05
	CHECKED	RZ (RAVON)	10 FEB 05
	APPROVED	HH (RAVON)	10 FEB 05



Mini-Circuits®
 13 Neptune Avenue
 Brooklyn NY 11235

PL, qf, GP731, RBP, TB-332


Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEETA1.DWG REV:A DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-176	B
FILE:	98PL176	SCALE:	5:1
		SHEET:	1 OF 1

Evaluation Board and Circuit



TB-332



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215