

+10 to +37 dBm Limiter

RLM-43-5W+

50Ω Broadband 20 to 4000 MHz



CASE STYLE: TT1224

The Big Deal

- Broadband, 20 MHz to 4 GHz
- Low output power leakage, +12 dBm
- Excellent limiting range, +10 to +37 dBm
- 0.3 dB Δ output / 1 dB Δ input

Product Overview

Mini-Circuits' RLM-43-5W+ is a passive PIN diode RF limiter ideal for protecting sensitive receiver circuitry from high-power signals, while allowing low-powered signals to be received.

Providing limiting range from +10 to +37 dBm and +12 dBm typical output power, the RLM-43-5W+ is ideal for many situations where unwanted signals prevail such as manufacturing sites, train tunnels, radar transceivers and more. The limiter is housed in a durable, surface mount plastic enclosure measuring 0.25 x 0.31 x 0.16", accommodating tight PCB layouts.

Key Features

| Feature | Advantages |
|--|---|
| Wideband operation, from 20 to 4000 MHz | Ideal for a variety of applications where there is a need to protect sensitive receiver circuitry from unwanted signals as well as control ESD and power surges on the network. |
| Excellent limiting range from +10 to +37dBm | Prevents undesired signals from passing through the network and damaging sensitive electronic components. |
| 0.3 dB Δ output / 1 dB Δ input | Low delta output per 1 dB delta input maintains signal stability in the presence of volatile input signal conditions. |
| Rapid recovery, 33ns | Minimal downtime after unwanted signals are removed with very quick restoration of standard operating levels. |
| Low loss insertion, 0.36 dB | Preserves the strength of low-power signals in the receive path. |
| low-output power loss, +12 dBm | Low output power prevents saturation of receiver circuitry and provides extra protection for sensitive components. |

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



+10 to +37 dBm Limiter

50Ω Broadband 20 to 4000 MHz

RLM-43-5W+



Generic photo used for illustration purposes only

CASE STYLE: TT1224

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings


| | |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C |
| Storage Temperature | -55°C to 100°C |
| RF Input Power | 5W |

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

| | |
|--------|---------|
| INPUT | 1 |
| OUTPUT | 4 |
| GROUND | 2,3,5,6 |


Outline Drawing



Outline Dimensions (inch/mm)

| A | B | C | D | E | F | G | H |
|------|------|------|------|------|------|------|-------|
| .25 | .31 | .16 | .100 | .040 | .055 | .060 | .065 |
| 6.35 | 7.87 | 4.06 | 2.54 | 1.02 | 1.40 | 1.52 | 1.65 |
| J | K | L | M | N | P | Q | wt. |
| .300 | .060 | .160 | .025 | .100 | .110 | .070 | grams |
| 7.62 | 1.52 | 4.06 | 0.64 | 2.54 | 2.79 | 1.78 | 0.16 |

Demo Board MCL P/N: TB-393 Suggested PCB Layout (PL-258)



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wideband, 20 to 4000 MHz
- low insertion loss 0.36 dB typ.
- fast recovery time, 33nsec typ.
- excellent VSWR 1.2:1 typ.
- low output power, 12 dBm typ.

Applications







- military, hi-rel applications
- stabilizing generator outputs
- reducing amplitude variations
- protects low noise amplifiers and other devices from ESD or input power damage

Electrical Specifications

| Parameter | Condition | Min. | Typ. | Max. | Units |
|-----------------------|--|------|------|------|-------|
| Frequency Range | | 20 | | 4000 | MHz |
| Linear Range | | | | | |
| Max Input Power | less than 1 dB compression | — | 5 | — | dBm |
| Insertion Loss | less than +5 dBm input power | — | 0.36 | 0.85 | dB |
| VSWR | less than +5 dBm input power | — | 1.2 | 1.58 | :1 |
| Limiting Range | | | | | |
| Input Power | >1dB compression filtered signal frequency | +10 | — | +37 | dBm |
| Output Power | | — | +12 | — | dBm |
| Δ Output/ Δ 1dB Input | Input Power Range (dBm) | | | | |
| | 10 to 20 | — | 0.3 | — | |
| | 20 to 30 | — | 0.1 | — | dB/dB |
| | 30 to 37 | — | 0.1 | — | |
| Recovery Time | 2 watt pulse 50 μsec pw 1kHz duty cycle recovery to within 90% of final value @ -5 dBm | — | 33 | — | nsec |
| Response Time | -30 to +33 dBm input 50 μsec PW 1 kHz duty cycle | — | 21 | — | nsec |

Typical Performance Data

| Freq. (MHz) | I. Loss (dB) in Linear Range at -10 dBm | VSWR (:1) in Linear Range at -10 dBm | Power Output (dBm) | | | | Δ Output / Δ 1dB Input | | |
|-------------|---|--------------------------------------|--------------------|---------------|---------------|---------------|------------------------|----------------------|----------------------|
| | | | +10 dBm Input | +20 dBm Input | +30 dBm Input | +37 dBm Input | +10 to +20 dBm Input | +20 to +30 dBm Input | +30 to +37 dBm Input |
| 20.00 | 0.15 | 1.36 | 8.22 | 10.72 | 11.78 | 12.86 | 0.25 | 0.11 | 0.15 |
| 50.00 | 0.05 | 1.13 | 8.27 | 10.81 | 11.75 | 12.76 | 0.25 | 0.09 | 0.14 |
| 90.00 | 0.04 | 1.06 | 8.12 | 10.61 | 11.44 | 12.55 | 0.25 | 0.08 | 0.16 |
| 200.00 | 0.04 | 1.03 | 8.13 | 10.57 | 11.52 | 13.21 | 0.24 | 0.09 | 0.24 |
| 500.00 | 0.05 | 1.02 | 8.44 | 10.44 | 12.86 | 12.94 | 0.20 | 0.24 | 0.01 |
| 1000.00 | 0.09 | 1.02 | 8.94 | 12.06 | 12.60 | 13.38 | 0.31 | 0.05 | 0.11 |
| 1200.00 | 0.10 | 1.04 | 8.25 | 11.59 | 12.68 | 13.19 | 0.33 | 0.11 | 0.07 |
| 1400.00 | 0.13 | 1.06 | 8.14 | 11.77 | 12.51 | 13.13 | 0.36 | 0.07 | 0.09 |
| 1600.00 | 0.15 | 1.10 | 8.02 | 11.89 | 12.45 | 13.01 | 0.39 | 0.06 | 0.08 |
| 2000.00 | 0.21 | 1.24 | 8.22 | 10.90 | 11.21 | 13.29 | 0.27 | 0.03 | 0.30 |
| 2500.00 | 0.35 | 1.39 | 8.42 | 6.91 | 10.75 | 12.12 | -0.15 | 0.38 | 0.20 |
| 3000.00 | 0.32 | 1.33 | 8.35 | 4.20 | 9.54 | 11.41 | -0.42 | 0.53 | 0.27 |
| 3500.00 | 0.37 | 1.17 | 8.08 | 2.96 | 9.03 | 11.87 | -0.51 | 0.61 | 0.41 |
| 3800.00 | 0.46 | 1.26 | 7.85 | 1.89 | 8.66 | 11.89 | -0.60 | 0.68 | 0.46 |
| 4000.00 | 0.56 | 1.36 | 7.99 | 0.95 | 8.47 | 11.51 | -0.70 | 0.75 | 0.43 |



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

| FREQUENCY (MHz) | LOW INPUT POWER | | | POWER OUTPUT (dBm) | | | | DELTA OUTPUT/1dB DELTA INPUT (dB/dB) | | |
|--------------------|------------------------|-------|--------|--------------------|------------------|------------------|------------------|--------------------------------------|-------------------------|-------------------------|
| | INSERTION LOSS (dB) | VSWR | | +10 dBm INPUT | +20 dBm INPUT | +30 dBm INPUT | +37 dBm INPUT | +10 to +20 dBm INPUT | +20 to +30 dBm INPUT | +30 to +37 dBm INPUT |
| | | Input | Output | | | | | | | |
| | | (:1) | | | | | | | | |
| 20.0 | 0.15 | 1.36 | 1.37 | 8.22 | 10.72 | 11.78 | 12.86 | 0.25 | 0.11 | 0.15 |
| 30.0 | 0.09 | 1.23 | 1.23 | 8.26 | 10.79 | 11.79 | 12.82 | 0.25 | 0.10 | 0.15 |
| 50.0 | 0.05 | 1.13 | 1.13 | 8.27 | 10.81 | 11.75 | 12.76 | 0.25 | 0.09 | 0.14 |
| 70.0 | 0.04 | 1.09 | 1.09 | 8.22 | 10.73 | 11.56 | 12.54 | 0.25 | 0.08 | 0.14 |
| 90.0 | 0.04 | 1.06 | 1.06 | 8.12 | 10.61 | 11.44 | 12.55 | 0.25 | 0.08 | 0.16 |
| 140.0 | 0.04 | 1.03 | 1.03 | 8.16 | 10.60 | 11.46 | 12.87 | 0.24 | 0.09 | 0.20 |
| 200.0 | 0.04 | 1.03 | 1.02 | 8.13 | 10.57 | 11.52 | 13.21 | 0.24 | 0.09 | 0.24 |
| 250.0 | 0.04 | 1.02 | 1.02 | 8.21 | 10.45 | 11.46 | 13.28 | 0.22 | 0.10 | 0.26 |
| 300.0 | 0.04 | 1.02 | 1.02 | 8.14 | 10.44 | 11.64 | 13.34 | 0.23 | 0.12 | 0.24 |
| 350.0 | 0.04 | 1.02 | 1.02 | 8.10 | 10.53 | 12.25 | 13.19 | 0.24 | 0.17 | 0.13 |
| 400.0 | 0.04 | 1.02 | 1.02 | 8.02 | 10.35 | 12.19 | 12.99 | 0.23 | 0.18 | 0.11 |
| 450.0 | 0.04 | 1.02 | 1.02 | 7.99 | 10.19 | 12.47 | 12.83 | 0.22 | 0.23 | 0.05 |
| 500.0 | 0.05 | 1.02 | 1.02 | 8.44 | 10.44 | 12.86 | 12.94 | 0.20 | 0.24 | 0.01 |
| 550.0 | 0.06 | 1.02 | 1.02 | 7.83 | 9.97 | 12.22 | 12.44 | 0.21 | 0.23 | 0.03 |
| 600.0 | 0.06 | 1.02 | 1.03 | 8.01 | 10.45 | 12.49 | 12.90 | 0.24 | 0.20 | 0.06 |
| 650.0 | 0.06 | 1.03 | 1.03 | 8.42 | 10.34 | 12.59 | 12.76 | 0.19 | 0.23 | 0.02 |
| 700.0 | 0.08 | 1.03 | 1.03 | 7.61 | 9.95 | 12.52 | 12.49 | 0.23 | 0.26 | 0.00 |
| 750.0 | 0.10 | 1.03 | 1.03 | 8.35 | 12.18 | 12.40 | 13.32 | 0.38 | 0.02 | 0.13 |
| 800.0 | 0.13 | 1.03 | 1.04 | 8.27 | 10.29 | 12.79 | 12.74 | 0.20 | 0.25 | -0.01 |
| 900.0 | 0.11 | 1.02 | 1.03 | 7.64 | 10.07 | 12.75 | 12.75 | 0.24 | 0.27 | 0.00 |
| 1000.0 | 0.09 | 1.02 | 1.02 | 8.94 | 12.06 | 12.60 | 13.38 | 0.31 | 0.05 | 0.11 |
| 1100.0 | 0.09 | 1.03 | 1.03 | 7.81 | 9.89 | 12.39 | 12.57 | 0.21 | 0.25 | 0.03 |
| 1200.0 | 0.10 | 1.04 | 1.04 | 8.25 | 11.59 | 12.68 | 13.19 | 0.33 | 0.11 | 0.07 |
| 1300.0 | 0.12 | 1.05 | 1.05 | 8.18 | 11.63 | 12.52 | 13.29 | 0.35 | 0.09 | 0.11 |
| 1400.0 | 0.13 | 1.06 | 1.06 | 8.14 | 11.77 | 12.51 | 13.13 | 0.36 | 0.07 | 0.09 |
| 1500.0 | 0.14 | 1.08 | 1.08 | 8.12 | 11.92 | 12.79 | 13.34 | 0.38 | 0.09 | 0.08 |
| 1600.0 | 0.15 | 1.10 | 1.10 | 8.02 | 11.89 | 12.45 | 13.01 | 0.39 | 0.06 | 0.08 |
| 1700.0 | 0.16 | 1.13 | 1.13 | 8.05 | 11.80 | 12.02 | 13.32 | 0.38 | 0.02 | 0.19 |
| 1800.0 | 0.17 | 1.16 | 1.16 | 8.15 | 11.84 | 11.77 | 13.28 | 0.37 | -0.01 | 0.22 |
| 1900.0 | 0.19 | 1.20 | 1.20 | 8.12 | 11.62 | 11.37 | 13.27 | 0.35 | -0.03 | 0.27 |
| 2000.0 | 0.21 | 1.24 | 1.23 | 8.22 | 10.90 | 11.21 | 13.29 | 0.27 | 0.03 | 0.30 |
| 2100.0 | 0.23 | 1.28 | 1.27 | 8.23 | 10.06 | 10.98 | 13.10 | 0.18 | 0.09 | 0.30 |
| 2200.0 | 0.24 | 1.31 | 1.30 | 8.25 | 9.42 | 10.87 | 12.81 | 0.12 | 0.15 | 0.28 |
| 2300.0 | 0.27 | 1.35 | 1.34 | 8.28 | 8.38 | 10.64 | 12.73 | 0.01 | 0.23 | 0.30 |
| 2400.0 | 0.29 | 1.37 | 1.37 | 8.35 | 7.37 | 10.48 | 12.34 | -0.10 | 0.31 | 0.27 |
| 2500.0 | 0.35 | 1.39 | 1.39 | 8.42 | 6.91 | 10.75 | 12.12 | -0.15 | 0.38 | 0.20 |
| 2600.0 | 0.33 | 1.40 | 1.39 | 8.44 | 6.49 | 10.31 | 12.03 | -0.20 | 0.38 | 0.25 |
| 2700.0 | 0.32 | 1.40 | 1.38 | 8.54 | 6.19 | 10.40 | 12.17 | -0.24 | 0.42 | 0.25 |
| 2800.0 | 0.33 | 1.39 | 1.38 | 8.48 | 5.50 | 9.78 | 11.29 | -0.30 | 0.43 | 0.22 |
| 2900.0 | 0.32 | 1.36 | 1.34 | 8.13 | 4.78 | 9.84 | 11.26 | -0.34 | 0.51 | 0.20 |
| 3000.0 | 0.32 | 1.33 | 1.31 | 8.35 | 4.20 | 9.54 | 11.41 | -0.42 | 0.53 | 0.27 |
| 3100.0 | 0.32 | 1.29 | 1.26 | 8.27 | 4.24 | 9.86 | 11.40 | -0.40 | 0.56 | 0.22 |
| 3200.0 | 0.32 | 1.24 | 1.21 | 8.26 | 3.48 | 9.47 | 11.43 | -0.48 | 0.60 | 0.28 |
| 3300.0 | 0.33 | 1.21 | 1.16 | 8.04 | 4.13 | 9.91 | 11.50 | -0.39 | 0.58 | 0.23 |
| 3400.0 | 0.35 | 1.18 | 1.12 | 8.03 | 3.17 | 9.15 | 11.58 | -0.49 | 0.60 | 0.35 |
| 3500.0 | 0.37 | 1.17 | 1.10 | 8.08 | 2.96 | 9.03 | 11.87 | -0.51 | 0.61 | 0.41 |
| 3600.0 | 0.39 | 1.18 | 1.12 | 7.85 | 2.92 | 9.56 | 11.57 | -0.49 | 0.66 | 0.29 |
| 3700.0 | 0.43 | 1.21 | 1.17 | 8.15 | 1.79 | 8.66 | 11.69 | -0.64 | 0.69 | 0.43 |
| 3800.0 | 0.46 | 1.26 | 1.22 | 7.85 | 1.89 | 8.66 | 11.89 | -0.60 | 0.68 | 0.46 |
| 3900.0 | 0.51 | 1.31 | 1.29 | 8.00 | 1.05 | 8.36 | 11.34 | -0.70 | 0.73 | 0.43 |
| 4000.0 | 0.56 | 1.36 | 1.33 | 7.99 | 0.95 | 8.47 | 11.51 | -0.70 | 0.75 | 0.43 |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

REV. A
 RLM-43-5W+
 4/8/2015
 Page 1 of 2

Surface Mount Limiter







RLM-43-5W+

Typical Performance Data


| POWER INPUT | POWER OUTPUT | POWER INPUT | POWER OUTPUT | POWER INPUT | POWER OUTPUT |
|-------------|--------------|-------------|--------------|-------------|--------------|
| @ 30 MHz | | @ 2000 MHz | | @ 4000 MHz | |
| (dBm) | | (dBm) | | (dBm) | |
| -10 | -10.09 | -10 | -10.21 | -10 | -10.56 |
| 10 | 8.27 | 10 | 8.28 | 10 | 7.90 |
| 20 | 10.81 | 20 | 8.38 | 20 | -0.48 |
| 30 | 11.75 | 30 | 10.64 | 30 | 7.76 |
| 37 | 12.76 | 37 | 12.73 | 37 | 11.35 |




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

| CASE # | A | B | C | D | E | F | G | H | J | K | L |
|--------|---------------|---------------|---------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| TT1224 | .25 (6.35) | .31 (7.87) | .16 (4.06) | .100 (2.54) | .040 (1.02) | .055 (1.40) | .060 (1.52) | .065 (1.65) | .300 (7.62) | .060 (1.52) | .160 (4.06) |

| CASE # | M | N | P | Q | WT. GRAM |
|--------|---------------|----------------|----------------|----------------|----------|
| TT1224 | .025 (.64) | .100 (2.54) | .110 (2.79) | .070 (1.78) | .16 |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Case material: Plastic.
2. Termination: 2-10 μ inch (.05-.25 microns) Gold over 100-300 μ inch (2.54-7.62 microns) Nickel plate




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F2



| Tape Width, mm | Device Cavity Pitch, mm | Reel Size, inches | Devices per Reel See note |
|----------------|-------------------------|-------------------|------------------------------|
| 16 | 12 | 7 | 10 |
| | | | 20 |
| | | | 50 |
| | | | 100 |
| | | | 200 |
| | | 13 | 500 |

Note: Please consult individual model data sheet to determine device per reel availability

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION




REVISIONS

| REV | ECN No. | DESCRIPTION | DATE | DR | AUTH |
|-----|---------|-------------|----------|----|------|
| OR | M108897 | NEW RELEASE | 01/04/07 | AV | DJ |
| | | | | | |
| | | | | | |

**SUGGESTED MOUNTING CONFIGURATION
FOR TT1224 CASE STYLE "rv" PIN CONNECTION**

.066 TRACE WIDTH, 3 PL.
(SEE NOTE BELOW)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

| UNLESS OTHERWISE SPECIFIED | INITIALS | DATE |
|----------------------------|----------|----------|
| DRAWN | AV | 12/14/06 |
| CHECKED | IL | 01/04/07 |
| APPROVED | DJ | 01/04/07 |


Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, rv, TT1224, RMK-3-662+, TB-393


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

| SIZE | CODE IDENT | DRAWING NO: | REV: |
|--------|------------|-------------|------|
| A | 15542 | 98-PL-258 | OR |
| FILE: | 98PL258 | SCALE: | 8:1 |
| SHEET: | 1 | OF | 1 |

Evaluation Board and Circuit




TB-393



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|--------------------------------|---|--|
| Operating Temperature | -40° to 85°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Humidity | 90 to 95% RH, 240 hours, 50°C | MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours |
| Thermal Shock | -55° to 100°C, 100 cycles | MIL-STD-202, Method 107, Condition A-3, except +100°C |
| Solder Reflow Heat | Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak | J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1 |
| Solderability | 10X Magnification | J-STD-002, 95% Coverage |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes | MIL-STD-202, Method 213, Condition A |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215 |