

Surface Mount Low Pass Filter

RLP-290+

50Ω DC to 290 MHz

The Big Deal

- Low Insertion Loss (1.2 dB typical)
- Good VSWR (1.4:1 typical)
- High Rejection
- Very small size (0.35" x 0.35" x 0.10")



Generic photo used for illustration purposes only
CASE STYLE: GP731

Product Overview

The RLP-290+ is a Lowpass filter fabricated using SMT technology. Covering DC to 290 MHz, this model offers low passband insertion loss of 1.2 dB typical, good matching within the passband and high rejection. In addition it has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Good VSWR, 1.4:1 typical in passband	This provides well matched input and output ports.
Sharp roll off shape factor, 1.2	Sharp shape factor helps in adjacent channel rejection and hence increased selectivity.
More than 40 dB rejection up to 950 MHz	This enables the filter to attenuate spurious signals and reject harmonics over a broad frequency band.
Small size, 0.35" x 0.35" x 0.10"	The surface mount package enables the RLP-290+ to be used in compact designs.
Shielded case	Reduced interference with and from the surrounding components.

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Surface Mount Low Pass Filter

50Ω DC to 290 MHz

RLP-290+



Generic photo used for illustration purposes only
CASE STYLE: GP731


Features

- High rejection
- Sharp insertion loss roll off
- Good VSWR, 1.4:1 typical in passband
- Aqueous washable


Applications

- TV Broad casting
- Wireless communications
- VHF/UHF receivers / transmitters
- Military

Functional Schematic



Typical Frequency Response



Electrical Specifications at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	—	1.2	1.8	dB
	Freq. Cut-Off	F2	—	3.0	—	dB
	VSWR	DC-F1	—	1.4	1.9	:1
Stop Band	Rejection Loss	F3-F4	20	26	—	dB
	VSWR	F3-F4	—	12	—	:1

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5W max.




Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)	Frequency (MHz)	Group Delay (nsec)
0.5	0.03	1.01	0.5	1.64
20.0	0.06	1.07	100.0	1.74
44.0	0.11	1.17	130.0	1.84
102.0	0.24	1.31	159.0	2.02
224.0	0.47	1.26	184.0	2.31
280.0	0.95	1.25	215.0	2.70
285.0	1.03	1.22	225.0	2.89
290.0	1.15	1.23	231.0	3.01
310.0	2.74	1.60	245.0	3.40
320.0	6.12	2.44	260.0	3.97
330.0	13.55	4.83	265.0	4.22
350.0	37.82	13.09	270.0	4.53
450.0	36.93	64.35	275.0	4.91
500.0	41.92	78.97	277.0	5.08
540.0	50.40	82.73	278.0	5.18
600.0	55.13	86.86	282.0	5.58
950.0	48.42	82.73	285.0	5.93
1000.0	43.62	78.97	286.0	6.06
1400.0	29.35	69.49	288.0	6.33
1600.0	26.12	57.91	290.0	6.64

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M174392
RLP-290+
EDR-9914AUF1
RAV/URJ/NY
200819
Page 2 of 3

Pad Connections


INPUT	2
OUTPUT	6
GROUND	1,3,4,5,7,8

Demo Board MCL P/N: TB-332
Suggested PCB Layout (PL-176)




- NOTES: 1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Outline Drawing



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

Outline Dimensions (Inch mm)

A	B	C	D	E	F	G	H	J
.350	.350	.100	.175	.075	.100	.110	.040	.080
8.89	8.89	2.54	4.45	1.91	2.54	2.79	1.02	2.03
K	L	M	N	P	Q	R		wt
.050	.040	.195	.390	.120	.390	.070		grams
1.27	1.02	4.95	9.91	3.05	9.91	1.78		0.25

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp







Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
	(dB)			(dB)			(dB)		
(MHz)	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
0.5	0.02	0.03	0.03	49.71	47.80	45.88	50.35	48.15	46.31
1.0	0.02	0.03	0.03	48.47	47.24	45.58	49.05	47.57	46.10
10.0	0.01	0.03	0.02	33.89	34.73	35.72	33.78	34.78	36.17
50.0	0.11	0.13	0.14	21.24	21.13	20.93	21.17	21.23	21.24
75.0	0.16	0.20	0.22	19.06	18.45	17.76	19.20	18.60	17.88
100.0	0.21	0.25	0.29	17.88	17.32	16.64	18.26	17.57	16.70
150.0	0.26	0.31	0.35	19.31	18.97	18.68	20.22	19.90	19.51
200.0	0.31	0.38	0.43	23.00	22.72	22.39	26.13	26.55	26.96
225.0	0.44	0.53	0.59	18.94	18.35	18.05	19.55	19.10	18.91
250.0	0.58	0.71	0.81	17.14	16.16	15.37	17.27	16.33	15.57
275.0	0.77	0.92	1.05	19.48	18.54	17.55	20.53	19.64	18.60
276.0	0.78	0.93	1.06	19.66	18.73	17.74	20.91	20.04	18.99
277.0	0.78	0.94	1.08	19.85	18.96	17.95	21.32	20.46	19.41
278.0	0.80	0.96	1.09	20.03	19.13	18.13	21.76	20.94	19.87
279.0	0.81	0.98	1.11	20.20	19.32	18.34	22.23	21.46	20.38
280.0	0.83	0.99	1.14	20.33	19.49	18.52	22.76	22.02	20.94
281.0	0.84	1.01	1.15	20.47	19.66	18.69	23.29	22.63	21.57
282.0	0.86	1.04	1.18	20.56	19.78	18.83	23.84	23.28	22.23
283.0	0.88	1.06	1.20	20.62	19.86	18.96	24.42	23.94	22.93
284.0	0.90	1.08	1.23	20.65	19.90	19.03	24.94	24.61	23.67
285.0	0.92	1.10	1.25	20.62	19.91	19.07	25.44	25.25	24.42
286.0	0.94	1.12	1.28	20.53	19.87	19.04	25.79	25.82	25.13
287.0	0.96	1.15	1.30	20.40	19.76	18.98	26.00	26.19	25.72
288.0	1.00	1.18	1.35	20.19	19.60	18.84	25.93	26.29	26.00
289.0	1.02	1.21	1.38	19.96	19.39	18.67	25.65	26.06	26.02
290.0	1.05	1.25	1.41	19.69	19.12	18.44	25.12	25.53	25.67
291.0	1.08	1.29	1.45	19.35	18.79	18.18	24.39	24.76	24.92
292.0	1.11	1.32	1.50	18.99	18.46	17.88	23.54	23.81	23.99
293.0	1.15	1.36	1.54	18.58	18.10	17.54	22.65	22.82	22.93
294.0	1.19	1.40	1.59	18.18	17.72	17.19	21.72	21.80	21.86
295.0	1.23	1.45	1.64	17.75	17.30	16.83	20.78	20.80	20.80
296.0	1.27	1.50	1.70	17.32	16.91	16.44	19.87	19.81	19.77
297.0	1.31	1.55	1.76	16.89	16.49	16.07	18.99	18.86	18.77
298.0	1.36	1.61	1.82	16.45	16.08	15.68	18.12	17.97	17.84
299.0	1.42	1.67	1.89	16.02	15.69	15.31	17.30	17.12	16.95
300.0	1.47	1.74	1.97	15.59	15.30	14.96	16.49	16.29	16.10
301.0	1.54	1.82	2.06	15.16	14.91	14.59	15.71	15.50	15.30
310.0	2.58	2.97	3.33	11.48	11.67	11.75	9.51	9.38	9.16
320.0	6.00	6.58	7.16	6.78	7.27	7.64	4.14	4.22	4.19
330.0	13.41	14.11	14.86	3.31	3.67	3.94	1.58	1.75	1.84
340.0	23.61	24.40	25.25	1.86	2.10	2.27	0.84	1.00	1.09
350.0	36.25	37.12	38.13	1.24	1.40	1.51	0.59	0.72	0.81
400.0	37.20	37.38	37.63	0.41	0.49	0.54	0.25	0.34	0.39
500.0	42.35	42.63	42.92	0.23	0.28	0.31	0.15	0.23	0.27
600.0	54.04	53.79	53.92	0.20	0.24	0.27	0.13	0.20	0.24
700.0	47.20	47.22	47.31	0.19	0.23	0.26	0.11	0.19	0.23
800.0	51.02	50.90	51.04	0.19	0.23	0.26	0.12	0.20	0.23
810.0	52.21	52.55	52.57	0.20	0.24	0.27	0.12	0.19	0.24
820.0	53.73	53.86	53.95	0.19	0.23	0.26	0.11	0.20	0.23
830.0	55.03	55.49	55.78	0.18	0.22	0.26	0.11	0.19	0.23
840.0	56.48	56.84	57.07	0.19	0.22	0.26	0.11	0.19	0.23
850.0	59.38	59.33	59.39	0.19	0.23	0.27	0.10	0.18	0.22
860.0	62.38	62.86	63.70	0.19	0.23	0.27	0.11	0.19	0.23
900.0	60.13	59.13	59.49	0.18	0.22	0.27	0.10	0.19	0.23
950.0	49.30	49.01	48.87	0.18	0.23	0.27	0.10	0.20	0.23
1000.0	44.39	44.35	44.16	0.18	0.23	0.27	0.10	0.19	0.24
1050.0	41.08	41.08	40.95	0.18	0.23	0.28	0.10	0.20	0.24
1100.0	38.80	38.78	38.65	0.18	0.23	0.28	0.09	0.19	0.24
1150.0	37.02	36.99	36.93	0.19	0.24	0.30	0.09	0.20	0.25
1200.0	35.50	35.50	35.29	0.18	0.25	0.30	0.08	0.19	0.25
1250.0	34.08	34.13	33.96	0.19	0.26	0.32	0.08	0.20	0.26
1300.0	32.82	32.79	32.63	0.19	0.27	0.33	0.08	0.20	0.26
1350.0	31.61	31.58	31.45	0.20	0.28	0.35	0.08	0.21	0.26
1400.0	30.69	30.64	30.55	0.20	0.29	0.36	0.06	0.20	0.27
1450.0	30.54	30.49	30.41	0.22	0.32	0.40	0.08	0.22	0.31
1500.0	27.23	27.27	27.28	0.21	0.31	0.40	0.07	0.21	0.29
1550.0	26.77	26.78	26.80	0.21	0.31	0.41	0.05	0.20	0.28
1600.0	26.08	26.06	26.06	0.22	0.34	0.44	0.05	0.21	0.29


Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
0.5	1.56	1.67	1.71
1.0	1.59	1.67	1.71
5.0	1.67	1.69	1.66
10.0	1.69	1.68	1.68
15.0	1.65	1.66	1.67
20.0	1.68	1.67	1.67
25.0	1.68	1.66	1.66
30.0	1.66	1.66	1.65
35.0	1.65	1.65	1.64
40.0	1.66	1.64	1.65
45.0	1.66	1.67	1.67
50.0	1.66	1.64	1.65
55.0	1.66	1.66	1.64
60.0	1.68	1.68	1.66
65.0	1.68	1.68	1.68
70.0	1.69	1.70	1.69
75.0	1.71	1.69	1.69
80.0	1.70	1.70	1.69
85.0	1.72	1.71	1.69
90.0	1.73	1.70	1.69
95.0	1.74	1.72	1.71
100.0	1.75	1.74	1.72
150.0	2.01	1.99	1.99
200.0	2.53	2.54	2.53
220.0	2.82	2.82	2.83
240.0	3.33	3.32	3.33
260.0	4.02	4.02	4.02
261.0	4.07	4.07	4.07
262.0	4.13	4.13	4.13
263.0	4.19	4.19	4.19
264.0	4.26	4.26	4.27
265.0	4.31	4.31	4.32
266.0	4.37	4.37	4.39
267.0	4.44	4.44	4.45
268.0	4.52	4.52	4.53
269.0	4.58	4.59	4.61
270.0	4.66	4.67	4.69
271.0	4.73	4.75	4.77
272.0	4.81	4.84	4.87
273.0	4.89	4.93	4.95
274.0	4.98	5.00	5.05
275.0	5.05	5.10	5.13
276.0	5.14	5.17	5.19
277.0	5.24	5.27	5.32
278.0	5.31	5.36	5.40
279.0	5.42	5.45	5.49
280.0	5.52	5.54	5.59
281.0	5.62	5.65	5.71
282.0	5.71	5.75	5.81
283.0	5.82	5.87	5.92
284.0	5.92	5.97	6.03
285.0	6.03	6.08	6.17
286.0	6.15	6.20	6.29
287.0	6.31	6.35	6.42
288.0	6.41	6.46	6.53
289.0	6.56	6.62	6.70
290.0	6.70	6.77	6.85

Typical Performance Curves





Typical Performance Curves



Outline Dimensions

GP731



CASE #	A	B	C	D	E	F	G	H	J	K	L	M
GP731	.350 (8.89)	.350 (8.89)	.100 (2.54)	.175 (4.45)	.075 (1.91)	.100 (2.54)	.110 (2.79)	.040 (1.02)	.080 (2.03)	.050 (1.27)	.040 (1.02)	.195 (4.95)

CASE #	N	P	Q	R	WT. GRAM
GP731	.390 (9.91)	.120 (3.05)	.390 (9.91)	.070 (1.78)	.4 +0.3 -0.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:

For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F78



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note
16	12	7	10
			20
			50
			100
			200
		13	500, 1000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	R59289	NEW RELEASE (FROM RAVON)	02/05	DK	HH
A	M101151	ADDED "RBP" & CORRECTED PIN	10/10/05	MMG	DJ
		CONNECTION TO DESCRIPTION OF PL-DWG.			
B	M102713	UPDATED NOTES, ADDED "...WITH SMOBC"	01/20/06	GT	IL

SUGGESTED MOUNTING CONFIGURATION

FOR GP731 CASE STYLE, "qf" PIN CONNECTION.



- NOTES:

1. TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .025" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS ±

3 PL DECIMALS ± .005

ANGLES ±

FRACTIONS ±

INITIALS

DATE

DRAWN DK (RAVON) 10 FEB 05

CHECKED RZ (RAVON) 10 FEB 05

APPROVED HH (RAVON) 10 FEB 05

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, qf, GP731, RBP, TB-332

SIZE A

CODE IDENT 15542

DRAWING NO: 98-PL-176


REV: B

FILE: 98PL176


SCALE: 5:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-332



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215