

Engineering Development Model

Voltage Controlled Oscillator

ROS-ED14587/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-1277

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	1657		1715	MHz
Tuning Voltage	.4		5.4	V
Power Output		3		dBm
Phase Noise				
at 1 kHz offset		-86		dBc/Hz
at 10 KHz offset		-113		dBc/Hz
at 100 KHz offset		-133		dBc/Hz
at 1000 kHz offset		-152		dBc/Hz
Pulling at 12 dBm PK-PK all phases		.6		MHz
Pushing at Vcc ± 5%		.4		MHz/V
Tuning Sensitivity		17-21		MHz/V
Harmonic Suppression		-28		dBc
3 dB Modulation Bandwidth		31,000		kHz
Supply Voltage		4.75		V
Supply Current			35	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+6V
Absolute Tuning Voltage (Vtune)	+7V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com








IF/RF MICROWAVE COMPONENTS

REV. X1
ROS-ED14587/1
9/1/2011
Page 1 of 1


Typical Performance Data

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ OFFSET (kHz)	PHASE NOISE (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C	F2	F3	F4			
0.00	28.30	1630.13	1625.58	1621.52	2.38	2.88	3.08	-30.19	-24.62	-28.68	-0.86	1	-86
0.38	24.28	1639.82	1635.67	1632.02	2.51	3.01	3.20	-29.97	-24.38	-28.80	-0.56	10	-113
0.77	22.35	1648.58	1644.60	1641.07	2.62	3.11	3.28	-29.62	-24.30	-29.26	-0.44	100	-133
1.15	21.43	1656.92	1653.00	1649.51	2.67	3.19	3.37	-29.46	-24.34	-29.17	-0.37	1000	-152
1.54	21.04	1665.07	1661.17	1657.66	2.77	3.31	3.51	-28.92	-24.40	-29.10	-0.33		
1.92	20.91	1673.17	1669.23	1665.68	2.87	3.38	3.57	-28.80	-24.09	-29.73	-0.29		
2.31	20.86	1681.25	1677.27	1673.66	2.98	3.45	3.59	-28.94	-24.50	-29.36	-0.27		
2.69	20.67	1689.29	1685.27	1681.60	3.05	3.50	3.62	-28.91	-24.49	-29.73	-0.25		
3.08	20.25	1697.20	1693.16	1689.45	3.09	3.56	3.68	-29.09	-25.15	-29.98	-0.24		
3.46	19.57	1704.89	1700.84	1697.10	3.10	3.61	3.74	-28.98	-24.86	-30.27	-0.24		
3.85	18.70	1712.27	1708.21	1704.46	3.16	3.63	3.78	-28.34	-25.27	-30.10	-0.23		
4.23	17.66	1719.27	1715.21	1711.45	3.20	3.67	3.77	-28.73	-25.58	-30.16	-0.22		
4.62	16.56	1725.85	1721.80	1718.03	3.23	3.70	3.79	-28.77	-25.65	-30.56	-0.20		
5.01	15.52	1732.03	1727.97	1724.19	3.28	3.73	3.80	-28.42	-26.04	-30.10	-0.16		
5.39	14.61	1737.84	1733.77	1729.97	3.33	3.76	3.79	-28.66	-26.19	-30.53	-0.11		
5.78	13.88	1743.34	1739.25	1735.42	3.35	3.78	3.79	-29.08	-25.64	-30.58	-0.07		
6.16	13.30	1748.60	1744.47	1740.61	3.35	3.79	3.78	-29.13	-26.37	-30.38	-0.02		
6.55	12.86	1753.68	1749.51	1745.59	3.36	3.81	3.79	-28.80	-26.36	-30.73	0.01		
6.93	12.53	1758.61	1754.40	1750.41	3.38	3.82	3.77	-28.59	-26.23	-30.56	0.05		
7.32	12.24	1763.43	1759.16	1755.11	3.41	3.83	3.74	-28.74	-26.85	-30.62	0.08		

Typical Performance Curves




THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
E	M105563	ADDED "rl" PIN CONNECTION	06/02/06	MMG	DJ
F	M105640	CORRECTED NOTE 2	06/08/06	MMG	MM
G	M124395	ADDED "RAMP"	09/09	EM	HH
G	R77589	ADDED "RAMP"	09/09	EM	HH


SUGGESTED MOUNTING CONFIGURATION FOR
CK605 CASE STYLE, "kg/rl/16AM01" PIN CONNECTION

NOTES:

- TRACE WIDTH IS SHOWN FOR FR4 WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE BOTTOM IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

AV

08/07/00

CHECKED

SK

08/08/00

APPROVED

DB

08/08/00

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL,kg/rl/16AM01,CK605,ROS/LAVI/RAMP

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-012


REV:
G

FILE: 98PL012

SCALE: 5:1


SHEET: 1 OF 1

Diagram of the TB-10 test cell showing the internal layout. The central component is the DUT (Device Under Test). The cell is labeled with VCC, RF OUT, and V TUNE ports. The Mini-Circuits 201-02B label is visible on the right side. An INDEX line points to a specific location on the DUT.



Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215