

X5 Frequency Multiplier

RMK-5-2751+

50Ω Output 2250 to 2750 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Input Power	20 dBm

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

INPUT	1
OUTPUT	4
GROUND	2,3,5,6


Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G	H
.25	.31	.16	.100	.040	.055	.060	.065
6.35	7.87	4.06	2.54	1.02	1.40	1.52	1.65
J	K	L	M	N	P	Q	wt.
.300	.060	.160	.025	.100	.110	.070	grams
7.62	1.52	4.06	0.64	2.54	2.79	1.78	0.16

Demo Board MCL P/N: TB-393 Suggested PCB Layout (PL-258)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
■ DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
□ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

Features

- low conversion loss, 22 dB typ.
- high rejection of adjacent harmonics, 58 dBc typ.
- aqueous washable

Applications

- synthesizers
- local oscillators
- satellite up and down converters



Generic photo used for illustration purposes only
CASE STYLE: TT1224

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200
13"	500

Electrical Specifications at 25°C

Parameter	Min.	Typ.	Max.	Unit
Multiplier Factor		5		
Frequency Range, Input (F1)	450	—	550	MHz
Frequency Range, Output (F5)	2250	—	2750	MHz
Input Power	—	17	—	dBm
Conversion Loss	—	22	24.5	dB
Harmonic Output*	F1	3.0	4.8	—
	F2	38	67.8	—
	F3	-7	-3.0	—
	F4	40	54	—
	F6	40	57	—
	F7	4	7	—








* Harmonics of input frequency below the power level of F5

Typical Performance Data

Frequency	Input (MHz)	Output (MHz)	Conv. Loss (dB) F5	Harmonic Rejection Below F5, (dB) at RF Input Power 17 dBm						
				F1	F2	F3	F4	F6	F7	
450.00	2250.00	21.33	8.82	75.33	1.05	63.74	57.22	7.39		
455.00	2275.00	21.35	8.72	74.80	0.88	63.16	57.40	7.62		
460.00	2300.00	21.40	8.54	74.41	0.77	62.42	57.40	7.79		
465.00	2325.00	21.36	8.35	74.01	0.54	61.76	57.77	8.26		
470.00	2350.00	21.33	8.18	73.54	0.38	61.04	57.83	8.28		
475.00	2375.00	21.30	7.96	72.89	0.25	60.45	57.95	8.51		
480.00	2400.00	21.26	7.82	72.47	0.07	59.80	58.03	8.73		
485.00	2425.00	21.20	7.71	72.21	-0.06	59.31	57.94	8.82		
490.00	2450.00	21.25	7.46	72.09	-0.35	58.94	58.08	9.03		
495.00	2475.00	21.28	7.30	71.94	-0.53	58.64	58.17	9.34		
500.00	2500.00	21.37	7.08	71.91	-0.67	58.16	58.31	9.55		
505.00	2525.00	21.46	6.84	71.50	-0.95	57.71	58.38	9.80		
510.00	2550.00	21.53	6.58	71.19	-1.24	57.31	58.48	10.15		
515.00	2575.00	21.60	6.34	70.76	-1.45	57.06	58.65	10.32		
520.00	2600.00	21.62	6.17	70.53	-1.64	56.67	58.85	10.42		
525.00	2625.00	21.66	5.92	70.40	-1.89	56.27	58.95	10.60		
530.00	2650.00	21.63	5.84	70.50	-1.99	55.92	59.04	10.56		
535.00	2675.00	21.65	5.63	70.45	-2.20	55.63	59.32	10.87		
540.00	2700.00	21.76	5.42	70.35	-2.40	55.20	59.71	10.79		
545.00	2725.00	21.90	5.14	70.26	-2.72	54.99	60.08	11.20		
550.00	2750.00	22.14	4.80	70.14	-3.02	54.73	60.27	11.43		



RMK-5-2751+



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Multiplier (X5)

RMK-5-2751+

Typical Performance Data

FREQUENCY (MHz)							CONVERSION LOSS (dB)	RF IN = +17 dBm					
								HARMONIC OUTPUT* (-dBc)					
X1 OUTPUT	X2 OUTPUT	X3 OUTPUT	X4 OUTPUT	X5 OUTPUT	X6 OUTPUT	X7 OUTPUT	X5 OUTPUT	X1 OUTPUT	X2 OUTPUT	X3 OUTPUT	X4 OUTPUT	X6 OUTPUT	X7 OUTPUT
450	900	1350	1800	2250	2700	3150	21.33	8.82	75.33	1.05	63.74	57.22	7.39
455	910	1365	1820	2275	2730	3185	21.35	8.72	74.80	0.88	63.16	57.40	7.62
460	920	1380	1840	2300	2760	3220	21.40	8.54	74.41	0.77	62.42	57.40	7.79
465	930	1395	1860	2325	2790	3255	21.36	8.35	74.01	0.54	61.76	57.77	8.26
470	940	1410	1880	2350	2820	3290	21.33	8.18	73.54	0.38	61.04	57.83	8.28
475	950	1425	1900	2375	2850	3325	21.30	7.96	72.89	0.25	60.45	57.95	8.51
480	960	1440	1920	2400	2880	3360	21.26	7.82	72.47	0.07	59.80	58.03	8.73
485	970	1455	1940	2425	2910	3395	21.20	7.71	72.21	-0.06	59.31	57.94	8.82
490	980	1470	1960	2450	2940	3430	21.25	7.46	72.09	-0.35	58.94	58.08	9.03
495	990	1485	1980	2475	2970	3465	21.28	7.30	71.94	-0.53	58.64	58.17	9.34
500	1000	1500	2000	2500	3000	3500	21.37	7.08	71.91	-0.67	58.16	58.31	9.55
505	1010	1515	2020	2525	3030	3535	21.46	6.84	71.50	-0.95	57.71	58.38	9.80
510	1020	1530	2040	2550	3060	3570	21.53	6.58	71.19	-1.24	57.31	58.48	10.15
515	1030	1545	2060	2575	3090	3605	21.60	6.34	70.76	-1.45	57.06	58.65	10.32
520	1040	1560	2080	2600	3120	3640	21.62	6.17	70.53	-1.64	56.67	58.85	10.42
525	1050	1575	2100	2625	3150	3675	21.66	5.92	70.40	-1.89	56.27	58.95	10.60
530	1060	1590	2120	2650	3180	3710	21.63	5.84	70.50	-1.99	55.92	59.04	10.56
535	1070	1605	2140	2675	3210	3745	21.65	5.63	70.45	-2.20	55.63	59.32	10.87
540	1080	1620	2160	2700	3240	3780	21.76	5.42	70.35	-2.40	55.20	59.71	10.79
545	1090	1635	2180	2725	3270	3815	21.90	5.14	70.26	-2.72	54.99	60.08	11.20
550	1100	1650	2200	2750	3300	3850	22.14	4.80	70.14	-3.02	54.73	60.27	11.43

* Harmonic Output below power level of X5 Output.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site










The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


IF/RF MICROWAVE COMPONENTS

REV. OR
RMK-5-2751+
7/7/2011
Page 1 of 1


Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L
TT1224	.25 (6.35)	.31 (7.87)	.16 (4.06)	.100 (2.54)	.040 (1.02)	.055 (1.40)	.060 (1.52)	.065 (1.65)	.300 (7.62)	.060 (1.52)	.160 (4.06)

CASE #	M	N	P	Q	WT. GRAM
TT1224	.025 (.64)	.100 (2.54)	.110 (2.79)	.070 (1.78)	.16

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Case material: Plastic.
2. Termination: 2-10 μ inch (.05-.25 microns) Gold over 100-300 μ inch (2.54-7.62 microns) Nickel plate




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F2



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel See note
16	12	7	10
			20
			50
			100
		200	
		13	500

Note: Please consult individual model data sheet to determine device per reel availability

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M108897	NEW RELEASE	01/04/07	AV	DJ

SUGGESTED MOUNTING CONFIGURATION
FOR TT1224 CASE STYLE "rv" PIN CONNECTION

.066 TRACE WIDTH, 3 PL.
(SEE NOTE BELOW)



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

AV

12/14/06

TOLERANCES ON:

CHECKED

IL

01/04/07

2 PL DECIMALS ± .005


APPROVED

DJ

01/04/07

ANGLES ±

FRACTIONS ±



THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, rv, TT1224, RMK-3-662+, TB-393

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-258


REV:
OR

FILE: 98PL258


SCALE: 8:1

SHEET: 1 OF 1

Evaluation Board and Circuit




TB-393



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215