

Engineering Development Model

Voltage Controlled Oscillator

ROSA-ED7426A/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-1366

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	140		250	MHz
Tuning Voltage	0		18	V
Power Output		0		dBm
Phase Noise	at 1 kHz offset	-88		dBc/Hz
	at 10 KHz offset	-113		dBc/Hz
	at 100 KHz offset	-133		dBc/Hz
	at 1000 kHz offset	-153		dBc/Hz
Pulling at 12 dBm PK-PK all phases		.25		MHz
Pushing at Vcc ± 5%		1		MHz/V
Tuning Sensitivity		7-11		MHz/V
Harmonic Suppression		-20		dBc
3 dB Modulation Bandwidth		80,000		kHz
Supply Voltage		5		V
Supply Current			20	mA

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 85°C
Absolute Supply Voltage (Vcc)	+6V
Absolute Tuning Voltage (Vtune)	+20V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS








REV. X1
ROSA-ED7426A/1
12/17/2008
Page 1 of 1

Typical Performance Data

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ OFFSET (kHz)	PHASE NOISE (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C	F2	F3	F4			
0.00	14.72	128.64	127.30	126.66	-2.37	-2.18	-2.15	-17.28	-32.12	-44.98	-0.26	1	-88
1.00	10.56	140.67	139.78	139.46	-0.64	-0.32	-0.11	-16.92	-31.89	-43.31	-0.51	10	-113
2.00	9.60	150.02	149.70	149.63	-0.13	0.11	0.38	-16.96	-32.65	-36.80	-1.28	100	-133
3.00	8.96	159.30	158.91	158.53	-0.20	0.06	0.44	-17.49	-33.25	-34.61	-1.15	1000	-153
4.00	8.32	167.94	167.36	166.98	-0.33	-0.08	0.38	-17.76	-33.20	-32.92	-1.02		
5.00	8.00	176.13	175.55	175.04	-0.52	-0.27	0.25	-18.11	-33.54	-31.89	-0.77		
6.00	7.68	184.19	183.62	183.04	-0.79	-0.52	0.02	-18.54	-33.91	-31.15	-0.90		
7.00	8.32	192.26	191.62	191.04	-1.12	-0.80	-0.28	-19.17	-34.11	-31.07	-1.02		
8.00	8.00	200.38	199.55	198.98	-1.45	-1.04	-0.61	-19.73	-34.73	-31.90	-1.28		
9.00	8.00	208.38	207.49	206.85	-1.67	-1.24	-0.97	-20.99	-35.01	-32.27	-1.41		
10.00	7.68	216.38	215.36	214.66	-1.95	-1.31	-1.11	-22.10	-35.23	-33.44	-1.54		
11.00	7.36	224.19	223.04	222.14	-2.08	-1.33	-1.03	-24.01	-34.85	-34.29	-1.66		
12.00	7.04	232.06	230.46	229.50	-1.83	-1.19	-0.87	-25.45	-35.16	-35.22	-1.54		
13.00	7.04	239.55	237.57	236.61	-1.47	-0.96	-0.70	-26.60	-35.90	-35.82	-1.66		
14.00	6.72	246.66	244.54	243.58	-1.11	-0.79	-0.58	-26.67	-36.21	-36.28	-1.15		
15.00	6.72	253.57	251.33	250.37	-0.81	-0.63	-0.44	-26.25	-35.69	-36.92	-1.28		
16.00	7.04	260.29	258.11	256.90	-0.52	-0.56	-0.31	-25.89	-34.48	-37.63	-1.28		
17.00	6.08	267.20	264.58	263.17	-0.52	-0.41	-0.14	-25.00	-33.58	-38.06	-0.90		
18.00	6.08	273.54	270.53	269.12	-0.39	-0.16	0.05	-24.12	-32.90	-38.56	-1.02		
19.00	5.44	279.30	276.10	274.62	-0.15	0.06	0.28	-23.29	-32.11	-38.51	-1.15		
20.00	5.44	284.93	281.41	279.62	-0.08	0.24	0.49	-22.32	-31.71	-38.73	-1.02		

Typical Performance Curves





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215