

Power Splitter/Combiner

RPS-ED16041/1

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-1799

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		10		2100 MHz
Isolation	10-2100 MHz		20	dB
Insertion Loss Above 3.0 dB	10-2100 MHz		0.55	dB
Phase Unbalance	10-2100 MHz		1.00	deg.
Amplitude Unbalance	10-2100 MHz		0.15	dB
VSWR	SUM Port		1.80	(:1)
	OUT Ports		1.55	(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	2
PORT 1	6
PORT 2	4
GND EXT	1,3,5

Functional Diagram








Typical Performance Data


FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	ISOLATION (dB) 1-2	PHASE UNBAL. (Deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
10.0	3.58	3.58	0.00	18.87	0.00	10.0	1.99	1.58	1.58
20.0	3.58	3.58	0.01	19.23	0.01	20.0	1.98	1.58	1.58
30.0	3.58	3.58	0.00	19.29	0.01	30.0	1.98	1.58	1.58
40.0	3.58	3.58	0.01	19.32	0.01	40.0	1.98	1.58	1.58
50.0	3.57	3.58	0.01	19.35	0.01	50.0	1.98	1.58	1.58
60.0	3.57	3.58	0.01	19.37	0.01	60.0	1.98	1.59	1.58
70.0	3.57	3.58	0.00	19.39	0.01	70.0	1.98	1.59	1.59
80.0	3.57	3.58	0.00	19.41	0.01	80.0	1.97	1.59	1.59
90.0	3.57	3.58	0.01	19.43	0.02	90.0	1.97	1.59	1.59
100.0	3.57	3.58	0.01	19.47	0.02	100.0	1.97	1.59	1.59
190.0	3.56	3.57	0.01	19.63	0.00	190.0	1.95	1.59	1.59
280.0	3.56	3.57	0.01	19.86	0.00	280.0	1.94	1.59	1.59
370.0	3.55	3.56	0.01	20.14	0.02	370.0	1.91	1.59	1.59
460.0	3.53	3.55	0.02	20.50	0.04	460.0	1.88	1.58	1.58
550.0	3.52	3.55	0.02	20.99	0.09	550.0	1.85	1.56	1.57
640.0	3.49	3.51	0.02	21.36	0.10	640.0	1.80	1.56	1.56
730.0	3.46	3.49	0.03	21.96	0.12	730.0	1.76	1.54	1.54
820.0	3.44	3.47	0.03	22.72	0.13	820.0	1.70	1.52	1.53
910.0	3.42	3.45	0.03	23.67	0.16	910.0	1.65	1.51	1.51
1000.0	3.39	3.42	0.03	24.87	0.14	1000.0	1.59	1.49	1.49
1100.0	3.36	3.39	0.03	26.36	0.14	1100.0	1.52	1.47	1.47
1200.0	3.33	3.37	0.04	27.76	0.12	1200.0	1.45	1.45	1.45
1300.0	3.31	3.35	0.04	28.30	0.11	1300.0	1.37	1.42	1.42
1400.0	3.29	3.33	0.04	27.31	0.09	1400.0	1.29	1.40	1.39
1500.0	3.28	3.32	0.05	25.19	0.03	1500.0	1.21	1.37	1.36
1600.0	3.28	3.33	0.05	22.86	0.02	1600.0	1.14	1.34	1.33
1700.0	3.28	3.34	0.05	20.69	0.12	1700.0	1.07	1.32	1.30
1800.0	3.31	3.36	0.06	18.80	0.22	1800.0	1.08	1.29	1.27
1900.0	3.34	3.41	0.06	17.13	0.35	1900.0	1.16	1.26	1.24
2000.0	3.40	3.47	0.07	15.64	0.54	2000.0	1.27	1.23	1.20
2100.0	3.49	3.56	0.08	14.35	0.75	2100.0	1.39	1.21	1.17
2180.0	3.57	3.66	0.08	13.40	0.94	2180.0	1.52	1.19	1.15
2260.0	3.68	3.77	0.09	12.53	1.15	2260.0	1.65	1.18	1.14
2340.0	3.81	3.91	0.10	11.72	1.40	2340.0	1.81	1.17	1.13
2420.0	3.96	4.06	0.11	10.98	1.67	2420.0	1.99	1.18	1.14
2500.0	4.13	4.25	0.12	10.30	2.02	2500.0	2.19	1.19	1.15

¹Total Loss = Insertion Loss + 3dB Splitter Loss


Typical Performance Curves



Evaluation Board and Circuit



TB-713+



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent.
Dielectric Constant=3.50, Thickness=.03"inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215