



Mini-Circuits

SURFACE MOUNT 

Power Splitter/Combiner

SBTC-2-20LX+


2 Way-0° 50Ω 200 to 2000 MHz

FEATURES

- Wideband Frequency, 200 to 2000 MHz
- Excellent Amplitude Unbalance, 0.2 dB Typ.
- Small Size, 0.166x0.150x0.155"
- Temperature Stable LTCC Base
- Small Size
- Low Cost
- Aqueous Washable
- Protected by US Patent 6,963,255

APPLICATIONS

- Cellular/GSM
- UHF/VHF Receivers/Transmitters
- PCN/PCS
- GPS



Generic photo used for illustration purposes only

CASE STYLE: AT1739

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		200		2000	MHz
Insertion Loss Above 3.0 dB	200-2000		0.8	2.2	dB
	800-1000		0.5	0.9	
	500-1500		0.5	1.5	
	1800-2000		1.2	2.2	
Isolation	200-2000	14	20		dB
	800-1000	16	22		
	500-1500	15	22		
	1800-2000	15	20		
Phase Unbalance	200-2000			10	Degree
	800-1000			3	
	500-1500			5	
	1800-2000			10	
Amplitude Unbalance	200-2000			0.8	dB
	800-1000			0.5	
	500-1500			0.7	
	1800-2000			0.6	

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
Power Input (as a Splitter)	0.5 W max.
Internal Dissipation	0.125 W max.

Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
ECO-015187
SBTC-2-20LX+
MCL NY
251007

PAGE 1 OF 3



Mini-Circuits

SURFACE MOUNT 

Power Splitter/Combiner

SBTC-2-20LX+


2 Way-0° 50Ω 200 to 2000 MHz

PIN CONNECTIONS

SUM PORT	6
PORT 1	3
PORT 2	4
GROUND	1,2
NOT USED	5

PRODUCT MARKING: PZ

DEMO BOARD MCL P/N: TB-SBTC-2-20LX+
SUGGESTED PCB LAYOUT (PL-152)




NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS $0.020" \pm 0.0015"$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.


2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

OUTLINE DRAWING



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

OUTLINE DIMENSIONS (Inches/mm)

A	B	C	D	E	F
.166	.150	.155	.050	.037	.025
4.22	3.81	3.94	1.27	0.94	0.64
G	H	J	K	K	wt
.012	.060	.184	.030	.004	grams
0.30	1.52	4.67	0.76	0.10	0.10

TAPE & REEL INFORMATION: F76



Mini-Circuits

SURFACE MOUNT top hat

Power Splitter/Combiner

SBTC-2-20LX+


2 Way-0° 50Ω 200 to 2000 MHz

TYPICAL PERFORMANCE DATA


Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR (:1)		
	S-1	S-2				S	1	2
200	3.56	3.30	0.26	26.85	1.44	1.38	1.58	1.50
300	3.57	3.36	0.21	39.72	0.88	1.37	1.44	1.40
400	3.55	3.38	0.17	32.31	0.56	1.38	1.35	1.33
500	3.58	3.45	0.13	27.04	0.36	1.37	1.29	1.28
600	3.62	3.52	0.10	23.52	0.22	1.40	1.25	1.25
800	3.58	3.56	0.03	20.65	0.20	1.39	1.17	1.16
1000	3.61	3.68	0.07	19.36	0.41	1.37	1.12	1.08
1200	3.69	3.84	0.15	19.24	0.93	1.34	1.14	1.04
1400	3.76	3.98	0.22	20.40	1.78	1.30	1.23	1.13
1500	3.84	4.07	0.23	21.76	2.34	1.29	1.29	1.18
1600	3.92	4.16	0.24	24.12	2.94	1.28	1.35	1.23
1700	4.02	4.25	0.24	28.51	3.61	1.27	1.40	1.29
1800	4.15	4.36	0.21	31.25	4.31	1.27	1.45	1.34
1900	4.33	4.49	0.18	26.03	4.98	1.32	1.49	1.38
2000	4.57	4.66	0.16	20.75	5.63	1.40	1.51	1.42

1. Total Loss = Insertion Loss + 3 dB splitter loss.


TOTAL LOSS



ISOLATION



VSWR



NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



2 Way-0° Power Splitter/Combiner

SBTC-2-20LX+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +25°C

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (Deg)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
40.0	4.02	3.19	0.83	12.82	3.62	40.0	1.75	3.54	2.79
50.0	3.88	3.16	0.71	13.82	3.61	50.0	1.62	3.00	2.45
100.0	3.60	3.21	0.39	18.71	2.63	100.0	1.41	1.96	1.77
150.0	3.53	3.24	0.29	23.02	1.89	150.0	1.37	1.66	1.56
200.0	3.50	3.26	0.24	27.38	1.35	200.0	1.36	1.51	1.46
250.0	3.48	3.27	0.21	32.24	0.97	250.0	1.36	1.42	1.40
300.0	3.47	3.28	0.19	35.80	0.72	300.0	1.36	1.36	1.35
350.0	3.47	3.29	0.18	33.42	0.48	350.0	1.35	1.32	1.32
400.0	3.46	3.31	0.15	30.06	0.26	400.0	1.35	1.28	1.29
450.0	3.47	3.31	0.16	27.53	0.08	450.0	1.35	1.24	1.27
500.0	3.46	3.33	0.13	25.65	0.03	500.0	1.35	1.21	1.24
550.0	3.47	3.34	0.13	24.16	0.17	550.0	1.35	1.18	1.22
600.0	3.47	3.36	0.12	22.97	0.31	600.0	1.35	1.15	1.20
650.0	3.48	3.37	0.11	21.99	0.42	650.0	1.35	1.12	1.18
700.0	3.49	3.39	0.10	21.15	0.52	700.0	1.35	1.10	1.16
750.0	3.50	3.41	0.09	20.45	0.58	750.0	1.35	1.08	1.14
800.0	3.51	3.43	0.08	19.84	0.67	800.0	1.35	1.07	1.12
850.0	3.52	3.45	0.07	19.33	0.69	850.0	1.35	1.06	1.10
900.0	3.53	3.48	0.05	18.90	0.73	900.0	1.35	1.07	1.09
950.0	3.54	3.50	0.04	18.53	0.75	950.0	1.35	1.08	1.07
1000.0	3.56	3.53	0.03	18.24	0.79	1000.0	1.36	1.10	1.06
1050.0	3.57	3.56	0.01	17.98	0.80	1050.0	1.36	1.13	1.05
1100.0	3.59	3.59	0.00	17.79	0.77	1100.0	1.36	1.16	1.05
1150.0	3.61	3.61	0.00	17.66	0.76	1150.0	1.36	1.19	1.06
1200.0	3.63	3.65	0.02	17.59	0.70	1200.0	1.37	1.22	1.07
1250.0	3.66	3.68	0.02	17.58	0.67	1250.0	1.37	1.26	1.09
1300.0	3.68	3.72	0.04	17.64	0.59	1300.0	1.37	1.29	1.11
1350.0	3.71	3.75	0.04	17.74	0.50	1350.0	1.37	1.32	1.13
1400.0	3.73	3.79	0.06	17.94	0.35	1400.0	1.37	1.36	1.15
1450.0	3.76	3.82	0.06	18.19	0.24	1450.0	1.37	1.40	1.17
1500.0	3.79	3.86	0.07	18.53	0.12	1500.0	1.37	1.43	1.19
1550.0	3.82	3.89	0.07	18.98	0.05	1550.0	1.37	1.47	1.22
1600.0	3.86	3.93	0.07	19.51	0.19	1600.0	1.37	1.51	1.24
1650.0	3.89	3.97	0.08	20.19	0.33	1650.0	1.36	1.54	1.26
1700.0	3.93	4.01	0.08	20.98	0.49	1700.0	1.35	1.57	1.28
1750.0	3.97	4.05	0.08	21.91	0.66	1750.0	1.35	1.60	1.31
1800.0	4.02	4.09	0.07	22.91	0.82	1800.0	1.34	1.63	1.33
1850.0	4.07	4.14	0.07	23.78	1.04	1850.0	1.33	1.66	1.35
1900.0	4.13	4.19	0.06	24.27	1.19	1900.0	1.33	1.67	1.36
1950.0	4.19	4.24	0.05	24.03	1.38	1950.0	1.33	1.68	1.38
2000.0	4.26	4.30	0.04	22.96	1.51	2000.0	1.33	1.69	1.39
2050.0	4.35	4.36	0.01	21.38	1.68	2050.0	1.35	1.69	1.40
2100.0	4.45	4.44	0.01	19.67	1.80	2100.0	1.37	1.68	1.41
2150.0	4.56	4.53	0.04	18.00	1.89	2150.0	1.41	1.67	1.41
2200.0	4.69	4.64	0.06	16.47	1.89	2200.0	1.46	1.64	1.41
2250.0	4.85	4.75	0.09	15.07	1.90	2250.0	1.52	1.61	1.41
2300.0	5.02	4.90	0.12	13.82	1.78	2300.0	1.60	1.57	1.41
2350.0	5.24	5.06	0.18	12.70	1.56	2350.0	1.69	1.53	1.40
2400.0	5.46	5.24	0.22	11.71	1.30	2400.0	1.80	1.48	1.39
2450.0	5.73	5.46	0.27	10.82	0.88	2450.0	1.92	1.43	1.38
2500.0	6.01	5.70	0.31	10.03	0.24	2500.0	2.05	1.38	1.38
2550.0	6.34	5.98	0.36	9.32	0.50	2550.0	2.19	1.32	1.37
2600.0	6.70	6.28	0.42	8.71	1.53	2600.0	2.34	1.27	1.37

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR
SBTC-2-20LX+
7/19/2012
Page 1 of 3

2 Way-0° Power Splitter/Combiner

SBTC-2-20LX+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = -40°C

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (Deg)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
40.0	4.05	3.21	0.84	12.83	3.55	40.0	1.74	3.56	2.81
50.0	3.89	3.18	0.72	13.79	3.54	50.0	1.61	3.03	2.47
100.0	3.60	3.20	0.40	18.61	2.63	100.0	1.42	2.00	1.80
150.0	3.52	3.22	0.30	22.95	1.91	150.0	1.38	1.69	1.59
200.0	3.47	3.23	0.24	27.33	1.40	200.0	1.36	1.53	1.48
250.0	3.45	3.24	0.21	32.47	1.03	250.0	1.36	1.45	1.42
300.0	3.44	3.25	0.19	37.36	0.81	300.0	1.36	1.39	1.38
350.0	3.43	3.25	0.18	34.53	0.56	350.0	1.36	1.34	1.34
400.0	3.43	3.26	0.17	30.65	0.38	400.0	1.36	1.30	1.31
450.0	3.42	3.26	0.16	27.95	0.22	450.0	1.36	1.26	1.29
500.0	3.41	3.27	0.14	25.91	0.10	500.0	1.36	1.23	1.26
550.0	3.42	3.28	0.14	24.32	0.04	550.0	1.36	1.20	1.24
600.0	3.42	3.30	0.13	23.11	0.17	600.0	1.36	1.17	1.22
650.0	3.42	3.30	0.12	22.10	0.25	650.0	1.36	1.15	1.20
700.0	3.42	3.32	0.10	21.25	0.35	700.0	1.36	1.12	1.18
750.0	3.43	3.33	0.10	20.52	0.43	750.0	1.36	1.10	1.16
800.0	3.44	3.35	0.09	19.91	0.44	800.0	1.36	1.08	1.14
850.0	3.44	3.37	0.07	19.36	0.40	850.0	1.36	1.07	1.12
900.0	3.44	3.38	0.06	18.92	0.47	900.0	1.37	1.07	1.11
950.0	3.45	3.41	0.04	18.51	0.52	950.0	1.37	1.08	1.09
1000.0	3.46	3.43	0.03	18.21	0.61	1000.0	1.37	1.10	1.07
1050.0	3.48	3.46	0.02	17.98	0.64	1050.0	1.37	1.12	1.06
1100.0	3.49	3.48	0.01	17.81	0.58	1100.0	1.37	1.15	1.06
1150.0	3.51	3.50	0.01	17.66	0.53	1150.0	1.37	1.18	1.06
1200.0	3.52	3.53	0.01	17.56	0.50	1200.0	1.38	1.21	1.07
1250.0	3.54	3.56	0.02	17.54	0.47	1250.0	1.38	1.24	1.08
1300.0	3.55	3.58	0.03	17.63	0.34	1300.0	1.37	1.28	1.10
1350.0	3.57	3.61	0.04	17.79	0.18	1350.0	1.37	1.31	1.12
1400.0	3.59	3.64	0.05	17.95	0.03	1400.0	1.37	1.35	1.14
1450.0	3.62	3.67	0.05	18.17	0.12	1450.0	1.37	1.38	1.16
1500.0	3.64	3.70	0.06	18.52	0.22	1500.0	1.37	1.42	1.18
1550.0	3.67	3.73	0.06	18.99	0.34	1550.0	1.37	1.46	1.20
1600.0	3.70	3.77	0.07	19.51	0.45	1600.0	1.36	1.49	1.23
1650.0	3.73	3.80	0.07	20.17	0.57	1650.0	1.36	1.53	1.25
1700.0	3.76	3.83	0.07	20.99	0.74	1700.0	1.35	1.56	1.27
1750.0	3.79	3.87	0.08	21.94	0.89	1750.0	1.34	1.59	1.30
1800.0	3.83	3.90	0.07	22.90	1.05	1800.0	1.33	1.61	1.31
1850.0	3.88	3.94	0.06	23.73	1.35	1850.0	1.33	1.64	1.33
1900.0	3.93	3.99	0.06	24.34	1.49	1900.0	1.33	1.66	1.35
1950.0	3.97	4.03	0.06	24.49	1.64	1950.0	1.33	1.67	1.37
2000.0	4.05	4.09	0.05	23.79	1.78	2000.0	1.35	1.69	1.39
2050.0	4.13	4.15	0.02	22.19	1.99	2050.0	1.37	1.70	1.40
2100.0	4.21	4.22	0.01	20.26	2.22	2100.0	1.38	1.69	1.40
2150.0	4.30	4.30	0.00	18.46	2.30	2150.0	1.41	1.66	1.41
2200.0	4.42	4.41	0.01	16.86	2.22	2200.0	1.46	1.64	1.41
2250.0	4.56	4.50	0.06	15.40	2.22	2250.0	1.53	1.62	1.41
2300.0	4.72	4.63	0.09	14.09	2.20	2300.0	1.60	1.59	1.41
2350.0	4.90	4.77	0.13	12.95	2.04	2350.0	1.68	1.55	1.40
2400.0	5.10	4.93	0.17	11.96	1.85	2400.0	1.78	1.50	1.39
2450.0	5.34	5.12	0.22	11.06	1.54	2450.0	1.90	1.45	1.38
2500.0	5.61	5.35	0.25	10.22	1.08	2500.0	2.04	1.39	1.38
2550.0	5.91	5.61	0.30	9.49	0.50	2550.0	2.19	1.34	1.38
2600.0	6.23	5.89	0.34	8.85	0.31	2600.0	2.35	1.30	1.38

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS

REV. OR
SBTC-2-20LX+
7/19/2012
Page 2 of 3

2 Way-0° Power Splitter/Combiner

SBTC-2-20LX+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =0 dBm @Temperature = +85°C

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (Deg)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
40.0	4.01	3.18	0.83	12.86	3.65	40.0	1.76	3.51	2.77
50.0	3.87	3.16	0.70	13.89	3.62	50.0	1.62	2.98	2.44
100.0	3.60	3.21	0.38	18.77	2.63	100.0	1.41	1.94	1.75
150.0	3.52	3.24	0.28	22.98	1.85	150.0	1.37	1.63	1.54
200.0	3.50	3.27	0.23	27.24	1.33	200.0	1.36	1.50	1.45
250.0	3.49	3.28	0.21	31.84	0.95	250.0	1.36	1.41	1.39
300.0	3.48	3.30	0.18	34.75	0.73	300.0	1.35	1.35	1.34
350.0	3.48	3.31	0.17	32.78	0.45	350.0	1.35	1.30	1.31
400.0	3.47	3.32	0.15	29.76	0.26	400.0	1.35	1.26	1.28
450.0	3.48	3.33	0.15	27.34	0.10	450.0	1.35	1.22	1.25
500.0	3.48	3.35	0.13	25.50	0.04	500.0	1.35	1.19	1.23
550.0	3.49	3.37	0.12	24.06	0.21	550.0	1.35	1.17	1.21
600.0	3.50	3.38	0.12	22.91	0.34	600.0	1.34	1.14	1.19
650.0	3.51	3.40	0.11	21.94	0.45	650.0	1.34	1.11	1.16
700.0	3.52	3.42	0.10	21.14	0.58	700.0	1.34	1.09	1.15
750.0	3.54	3.45	0.09	20.45	0.67	750.0	1.34	1.07	1.13
800.0	3.56	3.47	0.09	19.86	0.64	800.0	1.34	1.06	1.11
850.0	3.55	3.49	0.06	19.32	0.59	850.0	1.35	1.06	1.09
900.0	3.56	3.51	0.05	18.90	0.64	900.0	1.35	1.07	1.07
950.0	3.58	3.55	0.03	18.54	0.71	950.0	1.35	1.09	1.06
1000.0	3.60	3.58	0.02	18.24	0.89	1000.0	1.35	1.12	1.05
1050.0	3.63	3.63	0.00	18.00	0.97	1050.0	1.36	1.14	1.05
1100.0	3.66	3.65	0.01	17.83	0.88	1100.0	1.36	1.17	1.06
1150.0	3.68	3.68	0.00	17.73	0.84	1150.0	1.36	1.20	1.07
1200.0	3.70	3.71	0.01	17.66	0.83	1200.0	1.37	1.24	1.08
1250.0	3.73	3.75	0.02	17.66	0.83	1250.0	1.38	1.27	1.10
1300.0	3.75	3.79	0.04	17.72	0.67	1300.0	1.38	1.31	1.12
1350.0	3.78	3.82	0.04	17.87	0.45	1350.0	1.38	1.34	1.15
1400.0	3.81	3.87	0.06	18.08	0.24	1400.0	1.39	1.38	1.17
1450.0	3.84	3.90	0.06	18.38	0.08	1450.0	1.39	1.42	1.19
1500.0	3.88	3.94	0.06	18.74	0.05	1500.0	1.39	1.45	1.22
1550.0	3.91	3.98	0.07	19.23	0.08	1550.0	1.39	1.49	1.24
1600.0	3.95	4.02	0.07	19.81	0.20	1600.0	1.38	1.53	1.26
1650.0	3.99	4.07	0.08	20.56	0.27	1650.0	1.38	1.56	1.28
1700.0	4.03	4.11	0.08	21.43	0.41	1700.0	1.37	1.59	1.30
1750.0	4.07	4.15	0.08	22.50	0.55	1750.0	1.36	1.62	1.32
1800.0	4.12	4.20	0.08	23.63	0.74	1800.0	1.36	1.65	1.34
1850.0	4.18	4.24	0.06	24.62	1.05	1850.0	1.35	1.67	1.36
1900.0	4.24	4.29	0.05	25.03	1.14	1900.0	1.35	1.68	1.37
1950.0	4.29	4.34	0.05	24.50	1.30	1950.0	1.34	1.69	1.39
2000.0	4.37	4.41	0.04	23.12	1.50	2000.0	1.35	1.69	1.40
2050.0	4.47	4.49	0.02	21.39	1.73	2050.0	1.37	1.69	1.40
2100.0	4.57	4.57	0.00	19.51	1.81	2100.0	1.39	1.68	1.40
2150.0	4.69	4.67	0.03	17.72	1.88	2150.0	1.44	1.66	1.41
2200.0	4.83	4.79	0.04	16.12	1.88	2200.0	1.49	1.62	1.41
2250.0	4.99	4.92	0.07	14.72	1.86	2250.0	1.56	1.59	1.41
2300.0	5.18	5.08	0.10	13.49	1.77	2300.0	1.65	1.55	1.40
2350.0	5.41	5.26	0.15	12.41	1.53	2350.0	1.75	1.50	1.39
2400.0	5.65	5.47	0.18	11.45	1.23	2400.0	1.87	1.45	1.38
2450.0	5.94	5.70	0.24	10.59	0.82	2450.0	2.00	1.40	1.38
2500.0	6.24	5.97	0.27	9.84	0.21	2500.0	2.15	1.34	1.37
2550.0	6.60	6.27	0.33	9.17	0.43	2550.0	2.30	1.29	1.37
2600.0	6.97	6.59	0.38	8.59	1.45	2600.0	2.46	1.24	1.37

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS


REV. OR
SBTC-2-20LX+
7/19/2012
Page 3 of 3

2 Way-0° Power Splitter/Combiner


SBTC-2-20LX+

Typical Performance Curves


Total Loss




Total Loss S-1 vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE



Phase Unbalance vs. TEMPERATURE



Isolation 1-2 vs. TEMPERATURE



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site www.minicircuits.com
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS


minicircuits.com

REV. OR
SBTC-2-20LX+
7/19/2012
Page 1 of 2

2 Way-0° Power Splitter/Combiner

SBTC-2-20LX+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site www.minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


IF/RF MICROWAVE COMPONENTS




REV. OR
SBTC-2-20LX+
7/19/2012
Page 2 of 2

Outline Dimensions

AT1739



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
AT1739	.166 (4.22)	.150 (3.81)	.155 (3.94)	.050 (1.27)	.037 (0.94)	.025 (0.64)	.012 (0.30)	.060 (1.52)	.184 (4.67)	.030 (0.76)	.004 (0.10)	.10

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, Ceramic base.
- Termination finish:
For RoHS Case Styles: Tin plate.
For RoHS-5 Case Styles: Tin-Lead plate.
- Top-hat thickness .013 max.
- Orientation Dot on Top Hat & Marking on the Substrate both refers to Pin #6 of the Unit.



P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F76

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
12	8	7	20
			50
			100
			200
			500
		13	1000
			2000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION




REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M90456	NEW RELEASE	01/16/04	AV	WP
A	M102713	ADDED "...WITH SMOBC"	01/12/06	GF	IL

SUGGESTED MOUNTING CONFIGURATION FOR AT1029 CASE STYLE, "nc" PIN CONNECTION



- NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $0.020" \pm 0.0015"$; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$
 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, nc, AT1029, SBTC, TB-274

 SIZE
A

 CODE IDENT
15542

 DRAWING NO:
98-PL-152



 REV:
A

FILE: 98PL152

SCALE: 10:1

SHEET: 1 OF 1

Evaluation Board and Circuit



Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215