


Engineering Development Model

Voltage Controlled Oscillator

ROSA-ED9046C/2

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DU674

ELECTRICAL SPECIFICATIONS 50Ω				
Parameter	Min.	Typ.	Max.	Units
Frequency	860		940	MHz
Tuning Voltage	1		11	V
Power Output		+8		dBm
Phase Noise				
at 1 kHz offset		-88		dBc/Hz
at 10 KHz offset		-118		dBc/Hz
at 100 KHz offset		-138		dBc/Hz
at 1000 kHz offset		-158		dBc/Hz
Pulling at 12 dB PK-PK all phases		1.1		MHz
Pushing at Vcc±5%		1		MHz/V
Tuning Sensitivity		7 - 20		MHz/V
Harmonic Suppression		-16		dBc
3 dB Modulation Bandwidth		13000		kHz
Supply Voltage		12		V
Supply Current			35	mA

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Supply Voltage (Vcc)	+14V
Absolute Tuning Voltage (Vtune)	+13V

PIN CONNECTIONS	
RF OUT	10
VCC	14
V-TUNE	2
GROUND	1,3,4,5,6,7,8,9,11,12,13,15,16

Voltage Controlled Oscillator

ROSA-ED9046C/2






Typical Performance Data

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ OFFSET (KHz)	PHASE NOISE (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C	F2	F3	F4			
0.4	21.05	822.7	819.5	816.2	8.51	8.55	8.15	-11.5	-37.4	-44.9	0.20	1	-88
0.8	18.50	830.1	826.6	823.1	8.54	8.63	8.31	-12.4	-36.4	-44.5	0.09	10	-118
1.1	17.42	837.0	833.2	829.5	8.61	8.72	8.42	-13.3	-36.0	-43.9	0.02	100	-138
1.5	16.98	843.7	839.6	835.8	8.75	8.84	8.53	-14.2	-35.1	-43.6	0.05	1000	-158
1.9	16.89	850.2	846.0	842.0	8.90	8.99	8.68	-15.1	-34.6	-42.8	0.11		
2.3	16.76	856.7	852.4	848.3	9.06	9.16	8.86	-16.0	-34.2	-41.2	0.14		
2.7	16.66	863.1	858.7	854.5	9.23	9.35	9.04	-16.9	-33.4	-39.7	0.17		
3.0	16.44	869.4	865.0	860.8	9.50	9.57	9.23	-17.6	-31.9	-40.1	0.20		
3.4	16.15	875.5	871.1	866.9	9.67	9.73	9.40	-18.4	-31.3	-44.6	0.21		
3.8	15.81	881.4	877.1	873.0	9.73	9.79	9.47	-19.5	-31.3	-50.7	0.22		
4.2	15.37	887.2	883.0	878.9	9.74	9.80	9.49	-20.5	-31.3	-57.3	0.22		
4.6	14.99	892.8	888.7	884.7	9.72	9.76	9.46	-21.6	-31.5	-62.3	0.22		
4.9	14.56	898.3	894.2	890.3	9.66	9.69	9.38	-22.6	-31.9	-62.5	0.23		
5.3	14.13	903.6	899.6	895.8	9.59	9.59	9.28	-23.7	-32.2	-62.4	0.23		
5.7	13.72	908.7	904.8	901.0	9.51	9.47	9.17	-24.7	-32.8	-62.1	0.24		
6.1	13.30	913.7	909.9	906.1	9.42	9.38	9.07	-25.8	-33.3	-62.1	0.25		
6.5	12.76	918.5	914.7	911.0	9.36	9.29	8.99	-26.8	-33.7	-61.7	0.26		
6.8	12.29	923.1	919.4	915.7	9.31	9.22	8.94	-27.7	-34.4	-61.1	0.29		
7.2	11.77	927.5	923.8	920.2	9.23	9.17	8.90	-28.5	-35.2	-59.7	0.30		
7.6	10.82	931.8	928.0	924.4	9.15	9.22	8.89	-29.2	-35.4	-62.2	0.32		
8.0	11.08	935.9	932.2	928.5	9.07	9.09	8.91	-29.6	-35.8	-61.5	0.34		
8.4	10.41	939.8	936.1	932.5	8.99	9.03	8.83	-30.0	-36.9	-59.8	0.35		
8.7	9.91	943.6	939.9	936.3	8.92	8.96	8.78	-30.3	-37.8	-57.5	0.39		
9.1	9.52	947.2	943.5	939.9	8.83	8.90	8.74	-30.8	-38.5	-55.4	0.40		
9.5	9.07	950.6	947.0	943.4	8.76	8.83	8.70	-31.1	-39.3	-56.7	0.42		
9.9	8.71	953.8	950.3	946.7	8.70	8.77	8.64	-31.4	-40.3	-58.4	0.43		
10.3	8.30	956.8	953.4	949.9	8.65	8.71	8.59	-31.7	-41.6	-60.7	0.45		
10.6	7.94	959.7	956.4	953.0	8.62	8.65	8.54	-31.8	-43.2	-61.6	0.46		
11.0	7.58	962.4	959.3	955.9	8.60	8.59	8.49	-31.9	-44.7	-61.4	0.44		
11.4	7.27	965.2	962.1	958.7	8.54	8.54	8.45	-32.0	-47.1	-61.5	0.44		
11.8	6.92	967.9	964.7	961.4	8.45	8.50	8.42	-32.0	-49.3	-58.4	0.44		
12.2	6.52	970.2	967.2	964.0	8.51	8.47	8.38	-32.0	-50.4	-48.8	0.40		
12.5	6.47	972.4	969.6	966.4	8.48	8.41	8.37	-31.9	-50.4	-58.9	0.43		
12.9	6.08	974.8	972.0	968.8	8.35	8.40	8.33	-31.6	-48.1	-56.1	0.41		
13.3	5.76	977.0	974.1	971.0	8.27	8.39	8.33	-31.4	-45.5	-51.1	0.39		
13.7	5.47	979.1	976.2	973.2	8.23	8.40	8.32	-31.4	-43.6	-47.3	0.37		
14.1	5.20	981.1	978.2	975.2	8.21	8.41	8.32	-31.3	-42.2	-44.8	0.36		
14.4	4.90	983.0	980.1	977.2	8.22	8.43	8.33	-31.2	-41.0	-42.7	0.34		
14.8	4.64	984.7	981.8	979.0	8.26	8.45	8.34	-31.3	-39.5	-40.6	0.30		


Voltage Controlled Oscillator

ROSA-ED9046C/2


Typical Performance Data



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K
DU674	.91 (23.11)	.91 (23.11)	.31 (7.87)	.220 (5.59)	.125 (3.18)	.125 (3.18)	.070 (1.78)	.05 (1.27)	.125 (3.18)	.193 (4.90)

CASE #	L	M	N	P	Q	R	S	T	WT. GRAM
DU674	.950 (24.13)	.950 (24.13)	.070 (1.78)	.064 (1.63)	.145 (3.68)	.145 (3.68)	-	-	3.5

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.



INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F69

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
44	32	13	125

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
HAST	130°C, 85% RH, 96 hours	JESD22-A110
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process, 245°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 20-2000 Hz, 4 times in each of three axes (total 12)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215