LUMPED LC SURFACE MOUNT

High Pass Filter

SCHF-27+

50Ω 27 to 1000 MHz

THE BIG DEAL

- Low Insertion Loss
- High Rejection
- Small Size, 19.05 x 9.65 mm




Generic photo used for illustration purposes only

APPLICATIONS

- HF/VHF
- Lab use
- Receivers/Transformers

FUNCTIONAL DIAGRAM



PRODUCT OVERVIEW

Mini-Circuits' SCHF-27+ is a 50Ω high pass filter fabricated using SMT technology. This SMT model offers lower insertion loss, good return loss, higher stopband rejection and a wider passband 27 to 1000 MHz. This filter is built with high Q capacitors and wire wound inductors for superior performance. It has repeatable performance across lots and consistent performance acros temperature. The unit comes housed in a miniature plastic package measuring just 19.05 x 9.65 mm, ideal for dense circuit board layouts.

ELECTRICAL SPECIFICATIONS[1,2] AT +25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	F3-F4	27 - 1000	—	0.6	1.0	dB
	Return Loss	F3-F4	27 - 1000	—	20.8	—	dB
Stopband	Rejection	DC-F1	DC - 17	40	52	—	dB
		F1-F2	17 - 19	20	32	—	


1. Tested on Evaluation Board P/N TB-SCHF-27+ with connectors and feedline de-embedded with thru-line compensation.
2. This filter is bi-directional RF1 and RF2 ports may be interchanged. See S-Parameters for actual performance.

ABSOLUTE MAXIMUM RATINGS[3]

Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
Input Power[4]	5 W Max. @ 25°C

3. Permanent damage may occur if any of these limits are exceeded.
4. Power rating applies only to signals within the passband.

TYPICAL FREQUENCY RESPONSE



REV. B
ECO-030974
SCHF-27+
EDU2767_1
MCINU
260827


High Pass Filter

SCHF-27+


50Ω 27 to 1000 MHz

TYPICAL PERFORMANCE GRAPHS AT +25°C


SCHF-27+
INSERTION LOSS




SCHF-27+
INSERTION LOSS (Zoomed)



SCHF-27+
RETURN LOSS



SCHF-27+
RETURN LOSS (zoomed)



High Pass Filter

SCHF-27+

50Ω 27 to 1000 MHz

FUNCTIONAL DIAGRAM





Figure 1. SCHF-27+ Functional Diagram

PAD DESCRIPTION

Function	Pad Number	Description
RF1[2]	1	Connects to RF Input Port
RF2[2]	8	Connects to RF Output Port
GROUND	2,3,4,5,6,7	Connects to Ground on PCB, (See drawing PL-049)

SUGGESTED PCB LAYOUT



NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.


2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Figure 2. Suggested PCB Layout

CASE STYLE DRAWING



Suggested Layout
Tolerance to be within±.002

Weight: 1.6 grams
Dimensions are in inches (mm). Tolerances: 2Pl. ± .01 [.76]; 3Pl. ± .005 [.38]

PRODUCT MARKING*: SCHF-27

*Marking may contain other features or characters for internal lot control.

High Pass Filter

SCHF-27+

50Ω 27 to 1000 MHz

ADDITIONAL DETAILED INFORMATION IS AVAILABLE ON OUR DASHBOARD

CLICK HERE

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file) De-embedded to device pads
Case Style	YY161 Lead Finish: Tin over Nickel Plate
RoHS/REACH Status	Compliant
Tape and Reel	F5
Suggested Layout for PCB Design	PL-049
Evaluation Board	TB-SCHF-27+ Gerber File
Environmental Rating	ENV02T1
MSL Level	MSL1

NOTES

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html

Surface Mount High Pass Filter SCHF-27+


Typical Performance Data

FREQ. (MHz)	Insertion Loss (dB)	Input Return Loss (dB)	Output Return Loss (dB)
1.0	68.60	0.00	0.00
2.0	63.22	0.01	0.01
3.0	60.51	0.01	0.01
4.0	59.17	0.01	0.02
5.0	58.97	0.02	0.02
6.0	59.54	0.02	0.03
7.0	61.29	0.03	0.04
8.0	64.58	0.04	0.04
9.0	70.59	0.05	0.05
10.0	86.61	0.06	0.06
11.0	77.11	0.07	0.08
12.0	81.01	0.09	0.10
13.0	74.14	0.11	0.11
14.0	63.23	0.13	0.14
15.0	57.95	0.15	0.16
16.0	56.67	0.18	0.19
16.5	58.59	0.20	0.21
17.0	65.92	0.22	0.23
17.5	56.54	0.24	0.25
18.0	47.27	0.26	0.27
18.5	40.95	0.28	0.30
19.0	35.82	0.31	0.33
19.5	31.37	0.35	0.37
20.0	27.32	0.39	0.41
20.5	23.57	0.45	0.47
21.0	20.01	0.53	0.56
21.5	16.63	0.66	0.69
22.0	13.40	0.88	0.91
22.5	10.35	1.25	1.29
23.0	7.56	1.91	1.96
23.5	5.17	3.04	3.10
24.0	3.31	4.86	4.94
24.5	2.06	7.52	7.62
25.0	1.32	11.10	11.25
25.5	0.92	15.72	16.01
26.0	0.72	21.85	22.68
26.5	0.62	29.61	36.20
27.0	0.56	29.08	32.69
27.5	0.53	25.63	26.73
28.0	0.50	24.01	24.69
30.0	0.41	25.03	25.46
40.0	0.26	25.22	24.94
45.0	0.24	24.48	24.34
50.0	0.22	25.38	25.29
75.0	0.18	36.13	35.36
100.0	0.18	50.43	43.47
150.0	0.19	35.39	35.20
200.0	0.21	31.52	31.34
250.0	0.22	29.22	29.25
300.0	0.24	27.40	27.46
350.0	0.26	25.93	26.19
400.0	0.27	24.80	25.10
450.0	0.29	23.75	23.99
500.0	0.32	22.89	23.07
550.0	0.33	22.09	22.22
600.0	0.36	21.32	21.52
700.0	0.40	20.04	20.20
800.0	0.45	19.00	19.09
900.0	0.50	18.21	18.25
1000.0	0.53	17.56	17.51


FREQ. (MHz)	Group Delay (ns)
27.0	63.83
27.5	57.36
28.0	51.39
28.5	46.28
29.0	42.06
29.5	38.58
30.0	35.69
30.5	33.25
31.0	31.13
31.5	29.28
32.0	27.62
32.5	26.15
33.0	24.81
33.5	23.59
34.0	22.47
34.5	21.44
35.0	20.48
35.5	19.60
36.0	18.77
36.5	18.02
37.0	17.31
37.5	16.65
38.0	16.02
38.5	15.43
39.0	14.88
39.5	14.37
40.0	13.89
40.5	13.42
41.0	13.00
45.0	10.27
50.0	8.01
75.0	3.47
100.0	2.10
125.0	1.48
150.0	1.16
175.0	0.97
200.0	0.83
225.0	0.78
250.0	0.72
275.0	0.67
300.0	0.64
325.0	0.61
350.0	0.59
375.0	0.57
400.0	0.56
425.0	0.54
450.0	0.54
475.0	0.53
500.0	0.52
525.0	0.51
550.0	0.51
575.0	0.51
600.0	0.50
650.0	0.50
700.0	0.49
750.0	0.49
800.0	0.48
850.0	0.48
900.0	0.48
1000.0	0.48

Typical Performance Curves


INSERTION LOSS
INPUT POWER = 0 dBm




INPUT RETURN LOSS
INPUT POWER = 0 dBm



OUTPUT RETURN LOSS
INPUT POWER = 0 dBm




GROUP DELAY
INPUT POWER = 0 dBm




Case Style YY

Outline Dimensions

YY101
YY109
YY161



PCB Land Pattern



Suggested Layout
Tolerance to be within ±.002

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	WT. GRAMS
YY101*	.75 (19.05)	.38 (9.65)	.20 (5.08)	.010 (0.25)	.050 (1.27)	.020 (0.51)	.200 (5.08)	.075 (1.91)	.600 (15.24)	.450 (11.43)	-- --	.470 (11.94)	.100 (2.54)	.150 (3.81)	.148 (3.76)	1.6
YY109*			.20 (5.08)							.720 (18.29)	-- --	.740 (18.80)				1.6
YY161			.28 (7.11)							.450 (11.43)	-- --	.470 (11.94)				1.6

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

Notes:


1. Case material: Plastic.
2. Termination finish:
   For RoHS Case Styles: Tin plate over Nickel plate.
   For RoHS-5 Case Styles: Tin-Lead plate.
3. Special Tolerances: Termination thickness ± .003 inch.
4. * Denotes: For SCM mixers, long termination version (case YY109) is available upon request, consult factory. To order short termination version (case YY101) add -NL suffix.

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

Tape & Reel Packaging TR-F5

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	16	13	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf


Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M81561	NEW RELEASE	09/11/02	GF	ABD
A	M101145	ADDED YY101 CASE STYLE & NOTE 2	10/07/05	MMG	ABD
B	M102713	ADDED "...WITH SMOBC"	01/16/06	GT	IL
C	M165986	TB-187+ (WAS TB-187)	02/01/18	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR YY101/YY161 CASE STYLE, "cr" PIN CONNECTION



NOTES:
1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" ± .002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	GF	08/12/02
TOLERANCES ON:	CHECKED	AV	09/11/02
2 PL DECIMALS ±	APPROVED	ABD	09/11/02
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, cr, YY101/YY161, SCLF, TB-187+


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-049	C

FILE:	SCALE:	SHEET:
98PL049	5:1	1 OF 1

Evaluation Board and Circuit



TB-187



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers RO4350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV02T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.