

2 Way-0° Power Splitter/Combiner

SCN-2-35

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR (:1)		
	S-1	S-2				S	1	2
10	3.56	3.54	0.02	0.10	3.56	2.00	1.97	1.98
50	3.55	3.54	0.01	0.05	3.54	2.01	1.96	1.97
100	3.56	3.55	0.01	0.02	3.58	2.00	1.95	1.96
500	3.57	3.59	0.02	0.27	4.25	1.96	1.78	1.79
750	3.58	3.59	0.01	0.31	4.88	1.94	1.63	1.63
800	3.59	3.59	0.00	0.40	5.02	1.93	1.60	1.60
875	3.60	3.59	0.01	0.42	5.24	1.93	1.55	1.55
900	3.59	3.59	0.00	0.45	5.32	1.93	1.54	1.54
1000	3.60	3.59	0.01	0.57	5.63	1.92	1.49	1.48
1100	3.60	3.60	0.00	0.65	5.96	1.92	1.44	1.43
1125	3.60	3.60	0.00	0.68	6.04	1.92	1.42	1.42
1175	3.60	3.60	0.00	0.71	6.20	1.91	1.40	1.40
1200	3.60	3.60	0.00	0.74	6.29	1.91	1.39	1.39
1400	3.61	3.60	0.01	0.85	6.98	1.90	1.30	1.30
1600	3.61	3.59	0.02	0.97	7.72	1.87	1.23	1.23
1700	3.61	3.59	0.02	1.03	8.11	1.86	1.20	1.20
1800	3.61	3.58	0.03	1.10	8.52	1.84	1.17	1.17
1900	3.60	3.57	0.03	1.16	8.93	1.82	1.15	1.15
2000	3.59	3.55	0.04	1.28	9.38	1.79	1.14	1.14
2050	3.59	3.55	0.04	1.31	9.61	1.78	1.13	1.14
2100	3.58	3.54	0.04	1.31	9.85	1.77	1.13	1.13
2150	3.57	3.53	0.04	1.37	10.10	1.75	1.13	1.13
2200	3.57	3.53	0.04	1.38	10.36	1.74	1.12	1.13
2225	3.56	3.53	0.03	1.42	10.50	1.73	1.12	1.13
2250	3.56	3.52	0.04	1.45	10.63	1.72	1.12	1.13
2275	3.56	3.52	0.04	1.46	10.77	1.71	1.12	1.13
2300	3.55	3.51	0.04	1.48	10.92	1.70	1.12	1.13
2350	3.54	3.50	0.04	1.52	11.21	1.68	1.12	1.13
2400	3.53	3.49	0.04	1.56	11.53	1.66	1.13	1.13
2450	3.52	3.48	0.04	1.60	11.86	1.64	1.13	1.13
2500	3.51	3.47	0.04	1.65	12.20	1.61	1.13	1.14
2550	3.50	3.45	0.05	1.66	12.57	1.59	1.13	1.14
2600	3.49	3.44	0.05	1.72	12.94	1.57	1.13	1.14
2650	3.48	3.43	0.05	1.76	13.35	1.54	1.13	1.14
2700	3.47	3.41	0.06	1.77	13.77	1.51	1.13	1.14
2750	3.45	3.40	0.05	1.84	14.23	1.48	1.13	1.14
2800	3.45	3.38	0.07	1.89	14.73	1.45	1.13	1.13
2825	3.44	3.38	0.06	1.88	14.98	1.44	1.12	1.13
2850	3.43	3.37	0.06	1.91	15.24	1.42	1.12	1.13
2900	3.42	3.35	0.07	1.96	15.80	1.39	1.12	1.13
2950	3.41	3.34	0.07	1.99	16.45	1.36	1.11	1.12
3000	3.40	3.33	0.07	2.03	17.09	1.33	1.11	1.12
3100	3.38	3.30	0.08	2.10	18.67	1.27	1.10	1.11
3200	3.37	3.28	0.09	2.18	20.61	1.21	1.09	1.10
3300	3.36	3.27	0.09	2.22	23.29	1.15	1.09	1.08
3400	3.36	3.27	0.09	2.28	27.13	1.12	1.10	1.08
3500	3.38	3.28	0.10	2.36	34.73	1.14	1.12	1.09
3600	3.42	3.31	0.11	2.43	42.16	1.20	1.15	1.10
3700	3.47	3.35	0.12	2.50	29.68	1.29	1.18	1.14
3800	3.53	3.41	0.12	2.56	24.76	1.41	1.22	1.18
3900	3.62	3.49	0.12	2.64	21.68	1.54	1.27	1.24
4000	3.74	3.60	0.13	2.71	19.39	1.70	1.34	1.30
4250	4.14	3.98	0.16	2.92	15.77	2.19	1.52	1.48
4500	4.68	4.50	0.19	3.08	13.57	2.86	1.74	1.70

¹ Total Loss = Insertion Loss+ 3dB Splitter Loss



2 Way-0° Power Splitter/Combiner

SCN-2-35

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -55°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR (:1)		
	S-1	S-2				S	1	2
10	3.54	3.53	0.01	0.10	3.54	2.01	1.97	1.99
50	3.52	3.53	0.01	0.15	3.50	2.02	1.96	1.98
100	3.54	3.51	0.02	0.27	3.56	2.00	1.97	1.96
500	3.49	3.53	0.04	0.11	4.17	1.97	1.80	1.82
750	3.49	3.49	0.00	0.47	4.79	1.94	1.66	1.65
800	3.49	3.49	0.00	0.35	4.93	1.94	1.63	1.62
875	3.49	3.49	0.00	0.40	5.13	1.93	1.58	1.57
900	3.48	3.48	0.00	0.38	5.21	1.93	1.57	1.56
1000	3.48	3.49	0.01	0.22	5.51	1.93	1.51	1.51
1100	3.47	3.48	0.01	0.39	5.83	1.92	1.46	1.46
1125	3.47	3.48	0.01	0.35	5.91	1.91	1.45	1.44
1175	3.47	3.48	0.01	0.29	6.07	1.91	1.43	1.42
1200	3.46	3.48	0.02	0.27	6.14	1.92	1.41	1.41
1400	3.45	3.49	0.04	0.38	6.78	1.91	1.32	1.33
1600	3.44	3.48	0.04	0.52	7.47	1.90	1.23	1.26
1700	3.44	3.46	0.02	0.61	7.84	1.89	1.21	1.22
1800	3.43	3.45	0.02	0.60	8.25	1.87	1.19	1.21
1900	3.44	3.45	0.01	0.69	8.62	1.87	1.16	1.18
2000	3.42	3.44	0.02	0.76	9.04	1.86	1.14	1.18
2050	3.43	3.44	0.01	0.77	9.25	1.85	1.14	1.17
2100	3.42	3.43	0.01	0.79	9.48	1.85	1.14	1.18
2150	3.41	3.43	0.02	0.87	9.73	1.83	1.14	1.18
2200	3.41	3.41	0.00	0.95	9.98	1.83	1.14	1.18
2225	3.42	3.41	0.01	0.92	10.10	1.82	1.14	1.18
2250	3.42	3.41	0.01	0.91	10.22	1.82	1.14	1.18
2275	3.42	3.41	0.01	0.92	10.36	1.82	1.14	1.18
2300	3.41	3.40	0.01	0.93	10.49	1.81	1.14	1.18
2350	3.41	3.39	0.02	0.94	10.76	1.80	1.14	1.19
2400	3.40	3.38	0.02	0.92	11.07	1.79	1.15	1.20
2450	3.39	3.37	0.02	0.90	11.40	1.77	1.15	1.20
2500	3.37	3.35	0.02	0.92	11.75	1.74	1.15	1.20
2550	3.36	3.33	0.03	0.96	12.11	1.71	1.15	1.20
2600	3.36	3.32	0.04	0.92	12.47	1.70	1.16	1.21
2650	3.35	3.31	0.04	0.90	12.87	1.68	1.16	1.21
2700	3.33	3.28	0.05	0.87	13.29	1.65	1.16	1.20
2750	3.32	3.27	0.05	0.82	13.73	1.62	1.16	1.20
2800	3.31	3.26	0.05	0.81	14.22	1.60	1.16	1.20
2825	3.29	3.25	0.04	0.84	14.49	1.58	1.15	1.20
2850	3.28	3.23	0.05	0.82	14.76	1.57	1.15	1.19
2900	3.26	3.20	0.05	0.82	15.36	1.52	1.14	1.18
2950	3.24	3.18	0.06	0.84	16.03	1.48	1.13	1.17
3000	3.21	3.16	0.05	0.82	16.72	1.43	1.12	1.15
3100	3.18	3.11	0.07	0.84	18.35	1.34	1.09	1.12
3200	3.14	3.07	0.07	0.83	20.55	1.23	1.07	1.08
3300	3.11	3.04	0.07	0.78	23.23	1.14	1.07	1.03
3400	3.10	3.03	0.07	0.78	27.86	1.06	1.11	1.04
3500	3.11	3.04	0.07	0.80	36.98	1.11	1.16	1.10
3600	3.15	3.09	0.06	0.73	36.62	1.22	1.20	1.16
3700	3.22	3.15	0.07	0.78	27.73	1.36	1.25	1.24
3800	3.30	3.23	0.07	0.81	23.77	1.51	1.31	1.33
3900	3.41	3.35	0.07	0.84	20.86	1.69	1.37	1.42
4000	3.55	3.49	0.06	0.87	18.86	1.89	1.44	1.52
4250	3.98	3.89	0.09	0.99	15.59	2.46	1.61	1.74
4500	4.44	4.32	0.12	1.17	13.52	3.09	1.75	1.91

¹ Total Loss = Insertion Loss+ 3dB Splitter Loss



2 Way-0° Power Splitter/Combiner

SCN-2-35

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +100°C


FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)	VSWR (:1)		
	S-1	S-2				S	1	2
10	3.57	3.55	0.02	0.13	3.58	2.00	1.96	1.97
50	3.56	3.54	0.02	0.04	3.57	2.00	1.96	1.96
100	3.56	3.58	0.02	0.26	3.59	2.01	1.93	1.96
500	3.61	3.63	0.02	0.62	4.26	1.97	1.76	1.77
750	3.64	3.65	0.01	0.90	4.90	1.95	1.61	1.61
800	3.65	3.64	0.01	1.04	5.05	1.95	1.58	1.57
875	3.65	3.65	0.00	1.17	5.28	1.95	1.53	1.53
900	3.65	3.65	0.00	1.24	5.36	1.94	1.52	1.51
1000	3.66	3.65	0.01	1.40	5.69	1.93	1.46	1.46
1100	3.67	3.66	0.01	1.60	6.03	1.93	1.41	1.41
1125	3.68	3.67	0.01	1.65	6.11	1.93	1.40	1.39
1175	3.69	3.67	0.02	1.68	6.28	1.93	1.38	1.37
1200	3.69	3.67	0.02	1.74	6.37	1.93	1.36	1.35
1400	3.70	3.67	0.03	2.08	7.11	1.90	1.29	1.27
1600	3.70	3.65	0.05	2.42	7.90	1.87	1.22	1.19
1700	3.71	3.65	0.06	2.64	8.30	1.85	1.19	1.16
1800	3.70	3.63	0.07	2.84	8.74	1.82	1.16	1.13
1900	3.69	3.61	0.08	3.02	9.19	1.78	1.14	1.11
2000	3.66	3.59	0.07	3.27	9.68	1.74	1.13	1.09
2050	3.66	3.58	0.08	3.36	9.93	1.71	1.12	1.08
2100	3.65	3.57	0.08	3.46	10.19	1.69	1.11	1.08
2150	3.64	3.56	0.08	3.60	10.45	1.67	1.11	1.07
2200	3.63	3.56	0.07	3.67	10.73	1.65	1.10	1.07
2225	3.62	3.55	0.07	3.74	10.88	1.63	1.10	1.07
2250	3.61	3.55	0.06	3.80	11.03	1.62	1.10	1.07
2275	3.61	3.54	0.07	3.83	11.18	1.60	1.10	1.06
2300	3.60	3.54	0.06	3.90	11.34	1.59	1.10	1.06
2350	3.59	3.53	0.06	3.99	11.65	1.56	1.10	1.06
2400	3.57	3.51	0.06	4.09	11.99	1.53	1.10	1.06
2450	3.56	3.50	0.06	4.18	12.34	1.50	1.10	1.06
2500	3.55	3.49	0.06	4.28	12.70	1.47	1.10	1.07
2550	3.53	3.48	0.05	4.34	13.10	1.44	1.10	1.07
2600	3.52	3.47	0.05	4.43	13.49	1.41	1.10	1.07
2650	3.51	3.46	0.05	4.49	13.90	1.38	1.10	1.07
2700	3.50	3.45	0.05	4.57	14.33	1.35	1.10	1.08
2750	3.49	3.44	0.05	4.64	14.80	1.31	1.10	1.09
2800	3.49	3.44	0.05	4.71	15.31	1.28	1.10	1.09
2825	3.47	3.42	0.05	4.71	15.56	1.27	1.10	1.10
2850	3.47	3.42	0.05	4.76	15.81	1.25	1.10	1.10
2900	3.46	3.42	0.04	4.84	16.37	1.23	1.10	1.11
2950	3.46	3.41	0.05	4.87	17.01	1.20	1.10	1.12
3000	3.46	3.41	0.05	4.95	17.63	1.18	1.11	1.13
3100	3.45	3.40	0.05	5.05	19.14	1.14	1.11	1.14
3200	3.46	3.40	0.06	5.16	20.92	1.11	1.12	1.16
3300	3.48	3.42	0.06	5.23	23.36	1.12	1.13	1.19
3400	3.50	3.43	0.07	5.35	26.74	1.15	1.14	1.20
3500	3.53	3.45	0.08	5.45	32.68	1.20	1.15	1.22
3600	3.58	3.49	0.09	5.57	44.44	1.26	1.16	1.22
3700	3.62	3.52	0.10	5.70	32.84	1.33	1.17	1.23
3800	3.68	3.56	0.12	5.83	26.69	1.40	1.19	1.23
3900	3.74	3.62	0.12	6.00	23.18	1.48	1.22	1.22
4000	3.83	3.69	0.14	6.15	20.55	1.58	1.25	1.22
4250	4.10	3.94	0.16	6.75	16.41	1.89	1.40	1.22
4500	4.52	4.35	0.18	7.32	13.81	2.37	1.60	1.34

¹ Total Loss = Insertion Loss+ 3dB Splitter Loss




Typical Performance Curves


Total Loss




Total Loss S-1 vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE






Phase Unbalance vs. TEMPERATURE




Isolation 1-2 vs. TEMPERATURE




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206-1	.126 (3.20)	.063 (1.60)	.035 (0.89)	.024 (0.61)	.022 (0.56)	.011 (0.28)	.039 (0.99)	.024 (0.61)	.042 (1.07)	.123 (3.12)	--	--	--	--	.020

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging

TR-F75

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1

Applicable Case Styles
FV1206-1 FV1206-3




ILLUSTRATION 2

Applicable Case Styles
FV1206-4 FV1206-5 FV1206-6 FV1206-7 FV1206-9 JC0603C-1




ILLUSTRATION 3

Applicable Case Styles
NL1008C-6 FV1206-12 NL1008C-9 NL1008C-10

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits ISO 9001 & ISO 14001 Certified

Mini-Circuits[®]


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
A	M86650	UPDATED NOTE 2	04/18/03	GF	DJ
B	M86880	CHANGED APPEARANCE	05/05/03	IL	ABD
C	M91639	REMOVED NOTE 2, UPDATED DIMENSIONS	04/14/04	AV	DJ
D	M102713	ADDED "...WITH SMOBC"	01/16/06	GF	IL


**SUGGESTED MOUNTING CONFIGURATION
FOR FV1206-1 CASE STYLE, "pa" PIN CONNECTION.**



RESISTOR R1: 100 Ohm, 1206 SIZE

NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS 0.020" ± 0.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.

2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN GF	04/11/03
TOLERANCES ON:	CHECKED IL	04/15/03
2 PL DECIMALS ±	APPROVED ABD	04/15/03
3 PL DECIMALS ± .005		
ANGLES ±		
FRACTIONS ±		



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235



PL, pa, FV1206-1, SCN, TB-252

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-129	D
FILE:	98PL129	SCALE:	10:1
		SHEET:	1 OF 1

Evaluation Board and Circuit


For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A