

Engineering Development Model

Power Splitter/Combiner 4 Way-0°

SCA-ED10669A/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DZ943

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		5		1300	MHz
Isolation	5-50 MHz		34		dB
	50-650 MHz		27		dB
	650-1300 MHz		21		dB
Insertion Loss Above 6.0 dB	5-50 MHz		0.40		dB
	50-650 MHz		0.65		dB
	650-1300 MHz		1.25		dB
Phase Unbalance	5-50 MHz		0.25		deg.
	50-650 MHz		0.90		deg.
	650-1300 MHz		2.40		deg.
Amplitude Unbalance	5-50 MHz		0.30		dB
	50-650 MHz		0.35		dB
	650-1300 MHz		0.50		dB
VSWR	SUM Port		1.25		(:1)
	OUT Ports		1.20		(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	3
PORT 1	6
PORT 2	7
PORT 3	9
PORT 4	10
GROUND	1,2,4,5,8

Functional Diagram



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MIN-CIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS



REV. X1
SCA-ED10669A/1
12/16/2008
Page 1 of 1

4 Way-0° Power Splitter/Combiner

SCA-ED10669A/1






Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4		1-2	2-3	3-4			S	1	2	3	4
5.00	6.37	6.22	6.35	6.52	0.30	29.32	36.36	33.10	0.65	5.00	1.05	1.33	1.28	1.29	1.34
10.00	6.37	6.24	6.36	6.52	0.28	31.21	38.25	34.59	0.32	10.00	1.04	1.29	1.25	1.25	1.30
15.00	6.38	6.25	6.36	6.52	0.27	31.60	38.71	34.87	0.22	15.00	1.03	1.27	1.24	1.24	1.29
20.00	6.38	6.25	6.36	6.51	0.27	31.56	38.76	34.85	0.14	20.00	1.04	1.27	1.23	1.24	1.28
25.00	6.38	6.25	6.36	6.52	0.27	31.41	38.67	34.74	0.12	25.00	1.04	1.27	1.23	1.24	1.28
30.00	6.39	6.25	6.37	6.53	0.27	31.24	38.54	34.57	0.13	30.00	1.04	1.27	1.23	1.24	1.28
35.00	6.39	6.26	6.37	6.53	0.27	31.07	38.42	34.35	0.12	35.00	1.04	1.27	1.23	1.24	1.28
40.00	6.40	6.27	6.38	6.54	0.27	30.91	38.29	34.12	0.13	40.00	1.04	1.27	1.23	1.23	1.28
45.00	6.41	6.27	6.38	6.55	0.27	30.76	38.16	33.87	0.13	45.00	1.04	1.27	1.23	1.23	1.28
50.00	6.42	6.28	6.39	6.55	0.27	30.62	38.05	33.60	0.18	50.00	1.04	1.27	1.23	1.23	1.27
75.00	6.45	6.31	6.42	6.58	0.28	29.95	37.64	32.27	0.21	75.00	1.05	1.27	1.22	1.23	1.27
100.00	6.47	6.33	6.45	6.61	0.29	29.32	37.33	31.00	0.27	100.00	1.06	1.26	1.22	1.22	1.27
125.00	6.50	6.35	6.48	6.64	0.29	28.71	37.11	29.87	0.35	125.00	1.07	1.26	1.22	1.22	1.26
150.00	6.52	6.36	6.50	6.66	0.29	28.13	36.91	28.86	0.40	150.00	1.08	1.26	1.22	1.22	1.26
175.00	6.54	6.38	6.52	6.68	0.30	27.56	36.75	27.95	0.47	175.00	1.08	1.26	1.21	1.21	1.26
200.00	6.55	6.40	6.54	6.70	0.30	27.01	36.61	27.14	0.54	200.00	1.09	1.25	1.21	1.21	1.25
225.00	6.57	6.42	6.56	6.72	0.30	26.48	36.46	26.39	0.56	225.00	1.10	1.25	1.21	1.20	1.25
250.00	6.59	6.43	6.57	6.73	0.30	25.95	36.32	25.71	0.65	250.00	1.12	1.25	1.20	1.20	1.25
275.00	6.61	6.45	6.60	6.76	0.31	25.45	36.16	25.09	0.70	275.00	1.13	1.25	1.20	1.20	1.24
300.00	6.62	6.46	6.61	6.77	0.31	24.94	35.98	24.51	0.78	300.00	1.14	1.25	1.20	1.19	1.24
325.00	6.64	6.48	6.63	6.79	0.31	24.45	35.77	23.97	0.83	325.00	1.15	1.25	1.19	1.19	1.24
350.00	6.66	6.49	6.65	6.81	0.31	23.96	35.52	23.45	0.89	350.00	1.17	1.24	1.19	1.18	1.23
375.00	6.67	6.51	6.67	6.83	0.32	23.48	35.23	22.97	0.95	375.00	1.18	1.24	1.18	1.18	1.23
400.00	6.69	6.53	6.69	6.85	0.32	23.01	34.91	22.50	0.99	400.00	1.19	1.24	1.18	1.17	1.23
425.00	6.71	6.55	6.71	6.87	0.33	22.56	34.56	22.06	1.07	425.00	1.21	1.24	1.17	1.17	1.22
450.00	6.73	6.56	6.73	6.89	0.33	22.11	34.19	21.64	1.13	450.00	1.22	1.24	1.17	1.16	1.22
500.00	6.77	6.60	6.78	6.94	0.34	21.26	33.41	20.87	1.22	500.00	1.26	1.23	1.16	1.15	1.21
525.00	6.80	6.62	6.80	6.97	0.34	20.86	33.00	20.50	1.26	525.00	1.27	1.23	1.15	1.15	1.21
550.00	6.82	6.64	6.82	6.99	0.35	20.47	32.60	20.16	1.31	550.00	1.29	1.23	1.15	1.14	1.20
575.00	6.84	6.66	6.85	7.02	0.36	20.10	32.21	19.83	1.38	575.00	1.30	1.22	1.14	1.14	1.20
600.00	6.87	6.68	6.88	7.05	0.37	19.75	31.81	19.52	1.43	600.00	1.32	1.22	1.13	1.13	1.19
650.00	6.92	6.73	6.93	7.10	0.38	19.11	31.08	18.94	1.57	650.00	1.35	1.21	1.12	1.12	1.18
675.00	6.94	6.75	6.96	7.13	0.39	18.82	30.73	18.69	1.62	675.00	1.36	1.20	1.11	1.11	1.17
700.00	6.97	6.77	6.99	7.16	0.39	18.55	30.41	18.44	1.68	700.00	1.38	1.19	1.10	1.10	1.17
725.00	7.00	6.79	7.02	7.19	0.40	18.30	30.10	18.22	1.75	725.00	1.39	1.19	1.09	1.10	1.16
750.00	7.02	6.81	7.04	7.22	0.40	18.07	29.83	18.01	1.84	750.00	1.40	1.18	1.08	1.09	1.15
800.00	7.07	6.86	7.11	7.28	0.42	17.67	29.34	17.65	1.98	800.00	1.42	1.16	1.07	1.08	1.14
825.00	7.11	6.89	7.14	7.31	0.43	17.51	29.13	17.49	2.02	825.00	1.43	1.15	1.06	1.07	1.13
850.00	7.13	6.91	7.17	7.35	0.44	17.36	28.92	17.35	2.11	850.00	1.44	1.14	1.05	1.07	1.12
875.00	7.16	6.94	7.20	7.38	0.44	17.24	28.76	17.22	2.17	875.00	1.44	1.13	1.05	1.07	1.11
900.00	7.19	6.96	7.23	7.41	0.45	17.14	28.62	17.12	2.25	900.00	1.45	1.12	1.05	1.06	1.10
950.00	7.24	7.00	7.30	7.47	0.47	17.00	28.39	16.96	2.45	950.00	1.45	1.10	1.06	1.07	1.09
975.00	7.27	7.03	7.33	7.50	0.48	16.96	28.31	16.90	2.51	975.00	1.46	1.08	1.07	1.07	1.08
1000.00	7.30	7.05	7.37	7.54	0.48	16.94	28.25	16.86	2.56	1000.00	1.45	1.07	1.08	1.08	1.06
1025.00	7.33	7.08	7.40	7.58	0.50	16.96	28.20	16.83	2.66	1025.00	1.45	1.07	1.09	1.08	1.06
1050.00	7.36	7.10	7.44	7.61	0.51	16.98	28.17	16.82	2.74	1050.00	1.45	1.06	1.10	1.09	1.04
1100.00	7.43	7.15	7.51	7.69	0.54	17.10	28.14	16.83	2.95	1100.00	1.44	1.06	1.12	1.11	1.03
1200.00	7.57	7.27	7.68	7.85	0.59	17.55	28.12	16.96	3.35	1200.00	1.40	1.09	1.17	1.15	1.02
1300.00	7.74	7.42	7.89	8.05	0.63	18.23	27.94	17.16	3.75	1300.00	1.35	1.15	1.22	1.19	1.06


¹Total Loss = Insertion Loss + 6dB Splitter Loss




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
DZ943	.30 (7.62)	.250 (6.35)	.190 (4.83)	.266 (6.76)	.050 (1.27)	.050 (1.27)	.012 (0.30)	.029 (0.74)	.004 (0.10)	.085 (2.16)	.296 (7.52)	.030 (0.76)	0.5

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Plastic.
- Base: Ceramic.
- Termination finish:
 - For RoHS Case Styles: Tin plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F34



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
16	12	7	Small quantity standard (see note)	20
				50
				100
				200
		13	Standard	500
				1000

Note: Availability of small reel quantity varies by model.
Refer to pricing and availability on individual model dashboard.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M103787	NEW RELEASE (FROM RAVON)	03/06	RZ	HH
A	M121588	UPDATE GROUND PLANE	02/09	EM	KN
A	R75766	UPDATE GROUND PLANE	02/09	EM	KN

**SUGGESTED MOUNTING CONFIGURATION
FOR HE1135 CASE STYLE, qg PIN CONNECTION, 75 OHM**



NOTE:

1. TRACE WIDTH IS SHOWN FOR R04350 WITH DIELECTRIC THICKNESS. $.030'' \pm .002''$. COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	RZ (RAVON) 2 MAR 06
	CHECKED	RZ (RAVON) 2 MAR 06
	APPROVED	HH (RAVON) 2 MAR 06



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235



PL, qg, HE1135, TB-381, 75 OHM

SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-238	REV: A
FILE: 98PL238	SCALE: 5:1	SHEET: 1 OF 1	

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 Mini-Circuits®

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215