

Surface Mount Phase Shifter

SCPHS-51+

50Ω 360° Voltage Variable 25 to 48 MHz

The Big Deal

- Low insertion loss, 2 dB typ.
- Wide phase shift, 360°
- Low frequency and small size



CASE STYLE: HU1371

Product Overview

Mini-Circuits' SCPHS-51+ is a voltage variable phase shifter providing 360° phase control from 25 to 48 MHz in a miniature surface mount package. This model has a control bandwidth of DC to 30 kHz and a control voltage range from 0 to +15V. Housed in a shielded, 12-lead package with wrap-around terminations, the unit measures only 0.87 x 0.80 x 0.25", offering a space-efficient, low-cost alternative to larger, expensive connectorized phase shifters typical for low frequency operation.

Feature	Advantages
Low insertion loss, 2.0 dB typ.	Enables good transmission of signal power from input to output and minimizes effect on system noise figure.
Wide phase shift, 360°	In test environments, 360° phase control allows the user to experiment with various incident phases. This can be used to test residual phase noise of amplifiers and to determine the influence of phase between two mismatched components in a system.
Low frequency operation and tiny size, 0.87 x 0.80 x 0.25"	Typically, lower frequency phase shifters are large, connectorized designs. SCPHS-51+ provides low frequency phase shift capability in a tiny surface mount package, saving space and reducing system cost.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Surface Mount Phase Shifter

50Ω 360° Voltage Variable 25 to 48 MHz

SCPHS-51+



Generic photo used for illustration purposes only

CASE STYLE: HU1371

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Available Tape and Reel at no extra cost

Reel Size Devices/Reel
13" 200

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Input Power	24 dBm max.
Control Voltage	20V

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

IN	1
OUT	6
BIAS	10,11 [^]
GROUND	2,3,4,5,7,8,9,12,13,14

[^] proper operation is achieved with pins 10 or 11 or both connected to BIAS.

Features

- low insertion loss, 2 dB typ.
- wide phase shift, 360°
- aqueous washable

Applications

- cellular
- PCS
- DCS

Electrical Specifications at 25°C

Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		25		48	MHz
Phase Range	25 - 48	360	—	—	Degrees
Insertion Loss	25 - 48	—	2	5	dB
Control Voltage	25 - 48	—	0-15	—	V
Control Bandwidth	25 - 48	—	DC-30	—	kHz
VSWR	25 - 48	—	1.3	—	:1


DC input resistance at Control port: 1460 ohms typ.

Typical Performance Data

Control Voltage (V)	Phase Shift* (Degrees)			VSWR (:1)			Insertion Loss (dB)		
	25 MHz	36 MHz	48 MHz	25 MHz	36 MHz	48 MHz	25 MHz	36 MHz	48 MHz
0	0.00	0.00	0.00	1.05	1.31	1.98	1.30	1.24	1.82
1	30.63	8.93	3.27	1.01	1.37	1.97	1.41	1.33	1.84
2	61.71	17.67	6.36	1.01	1.43	1.96	1.50	1.42	1.86
3	96.98	27.52	9.71	1.12	1.47	1.95	1.59	1.52	1.88
4	139.22	39.87	13.73	1.43	1.52	1.94	1.80	1.63	1.90
5	189.01	57.10	19.07	1.97	1.53	1.92	2.24	1.77	1.93
6	242.80	83.57	26.73	2.31	1.47	1.88	2.43	1.92	1.97
7	297.41	126.54	38.22	1.79	1.25	1.81	1.77	2.09	2.03
8	347.41	191.95	55.35	1.11	1.11	1.69	1.18	2.35	2.13
9	384.48	272.98	80.40	1.49	1.11	1.52	1.23	2.37	2.31
10	409.11	350.06	116.80	1.89	1.34	1.33	1.44	2.21	2.66
11	425.41	406.15	167.54	2.14	1.47	1.19	1.58	1.95	3.23
12	436.27	443.24	230.39	2.28	1.33	1.12	1.66	1.60	3.82
13	443.66	467.67	295.74	2.35	1.18	1.25	1.69	1.37	4.07
14	448.92	484.24	352.40	2.39	1.09	1.51	1.70	1.23	4.07
15	452.83	496.02	395.47	2.42	1.09	1.81	1.71	1.16	4.03

* Normalized at control voltage = 0V


Outline Drawing



Outline Dimensions (inch/mm)


A	B	C	D	E	F	G	H
.870	.800	.250	.100	.097	-.060	.040	
22.10	20.32	6.35	2.54	2.46	-1.52	1.02	
J	K	L	M	N	P	wt	
.105	.910	-	.060	.060	-	grams	
2.67	23.11	-	1.52	1.52	-	2.85	

Demo Board MCL P/N: TB-1141+ Suggested PCB Layout (PL-690)




- NOTES:
- TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS 0.002-.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.


SCPHS-51+ PHASE SHIFT




SCPHS-51+ VSWR



SCPHS-51+ INSERTION LOSS



Electrical Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
ECO-005108
SCPHS-51+
ZL/CP/AM
201208

PHASE SHIFTER




SCPHS-51+

Typical Performance Data

CONTROL VOLTAGE (V)	PHASE SHIFT* (Deg.)			VSWR (:1)			INSERTION LOSS (dB)		
	25 MHz	36 MHz	48 MHz	25 MHz	36 MHz	48 MHz	25 MHz	36 MHz	48 MHz
0	0.00	0.00	0.00	1.05	1.31	1.98	1.30	1.24	1.82
1	30.63	8.93	3.27	1.01	1.37	1.97	1.41	1.33	1.84
2	61.71	17.67	6.36	1.01	1.43	1.96	1.50	1.42	1.86
3	96.98	27.52	9.71	1.12	1.47	1.95	1.59	1.52	1.88
4	139.22	39.87	13.73	1.43	1.52	1.94	1.80	1.63	1.90
5	189.01	57.10	19.07	1.97	1.53	1.92	2.24	1.77	1.93
6	242.80	83.57	26.73	2.31	1.47	1.88	2.43	1.92	1.97
7	297.41	126.54	38.22	1.79	1.25	1.81	1.77	2.09	2.03
8	347.41	191.95	55.35	1.11	1.11	1.69	1.18	2.35	2.13
9	384.48	272.98	80.40	1.49	1.11	1.52	1.23	2.37	2.31
10	409.11	350.06	116.80	1.89	1.34	1.33	1.44	2.21	2.66
11	425.41	406.15	167.54	2.14	1.47	1.19	1.58	1.95	3.23
12	436.27	443.24	230.39	2.28	1.33	1.12	1.66	1.60	3.82
13	443.66	467.67	295.74	2.35	1.18	1.25	1.69	1.37	4.07
14	448.92	484.24	352.40	2.39	1.09	1.51	1.70	1.23	4.07
15	452.83	496.02	395.47	2.42	1.09	1.81	1.71	1.16	4.03


*Normalized at control voltage = 0V

Typical Performance Curves




Outline Dimensions

HU1371



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT, GRAM
HU1371	.870 (22.10)	.800 (20.32)	.25 (6.35)	.100 (2.54)	.097 (2.46)	-	.060 (1.52)	.040 (1.02)	.105 (2.67)	.910 (23.11)	-	.060 (1.52)	.060 (1.52)	-	2.85

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over .120-.240 μ inch (3.05-6.10 microns) Nickel plate. All models (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F21



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS



REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	ECO-003790	NEW RELEASE	08/24/20	ITG	IL

SUGGESTED MOUNTING CONFIGURATION FOR
HU1371 CASE STYLE



NOTES:

- TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030±.002"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
-  DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES	DRAWN	ITG	08/24/20
TOLERANCES ON:	CHECKED	GF	08/24/20
2 PL DECIMALS ±	APPROVED	IL	08/24/20
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, HU1371, TB-1141+

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-690	OR
FILE:	98PL690	SCALE:	SHEET:
		2.5:1	1 OF 1



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215