

SCN-3-28+
SCN-3-28

CASE STYLE F·FV1206-1

* Derate linearly to 6W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

PORT 1-3 resistor external 127 ohms

G	H	J	K	wt
.039	.024	.042	.123	grams
0.99	0.61	1.07	3.12	.020

MECHANICAL DRAWING OF A 179 PACKAGE. DIMENSIONS ARE IN INCHES. THE PACKAGE IS A DUT PACKAGE OUTLINE. KEY FEATURES AND DIMENSIONS:

- EXTERNAL RESISTORS:** R1, R2, R3, and R4 are indicated.
- LINE WIDTH:** .044, 4 PL. (SEE NOTE BELOW)
- PIN 1:** Indicated by a dashed line and a 45° angle.
- GROUND:** 6X .015 PTH FOR GROUND.
- OTHER DIMENSIONS:** .136, .064, .224, .108, .020, .020 TYP, .014 TYP, .012, .036, .138, .006, .179.

RESISTORS: R1-R2: 124 Ohm, 0603 SIZE; R3: 127 Ohm, 1206 SIZE.

NOTE:

1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350 WITH DIELECTRIC THICKNESS: .020 ± .0015; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. RESISTOR LAND PATTERNS ARE SHOWN AS PER IPC-SM-782A.

3. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. PURCHASED PARTS RETURN POLICY: All products are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms_iso




- isolation resistors, external
- low insertion loss, 0.8 dB typ.
- excellent amplitude unbalance, 0.2 dB typ.
- very good phase unbalance, 5 deg. typ.
- high isolation, 12 dB typ.
- excellent power handling, 15W as splitter
- small size, 0.12"X0.06"X0.035"
- ESD non-sensitive
- temperature stable LTCC technology
- wrap around, terminations for excellent solderability
- low cost

- PSC, DECT
- DSS
- WLAN
- satellite communication
- line of sight communication
- ISM applications
- WLL
- defense applications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 4.8		PHASE UNBALANCE (Degrees)		AMPLITUDE UNBALANCE (dB)		RETURN LOSS (dB)	
	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	INPUT Typ.	OUTPUT Typ.
1600-2800	12	10	0.8	1.2	5	8	0.2	0.6	10	12
1800-2000	14	12	0.8	1.2	5	8	0.2	0.6	10	13
2000-2200	16	13	0.8	1.2	5	8	0.2	0.5	11	12
2400-2500	20	17	0.8	1.2	5	8	0.2	0.5	11	12

Freq. (MHz)	Total Loss' (dB)			Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	Return Loss (dB)		
	S-1	S-2	S-3		1-2	1-3	2-3		S	1	2
1600.00	5.53	5.81	5.50	0.31	15.27	12.43	16.36	3.29	9.44	18.66	22.27
1700.00	5.50	5.78	5.48	0.29	16.66	13.09	17.87	3.64	9.73	17.30	22.33
1800.00	5.49	5.74	5.47	0.27	18.38	13.86	19.78	3.99	9.99	15.95	20.89
1900.00	5.48	5.71	5.47	0.24	20.57	14.75	22.29	4.31	10.23	14.71	19.12
2000.00	5.48	5.68	5.47	0.21	23.60	15.80	25.98	4.62	10.44	13.73	17.52
2100.00	5.48	5.66	5.48	0.18	28.40	17.05	32.67	4.79	10.63	12.94	16.11
2200.00	5.49	5.63	5.49	0.15	39.20	18.57	45.10	4.99	10.78	12.30	14.93
2300.00	5.49	5.62	5.50	0.12	33.16	20.43	29.60	5.06	10.95	11.85	14.05
2400.00	5.50	5.61	5.51	0.11	25.77	22.80	24.16	5.14	11.12	11.56	13.33
2500.00	5.50	5.60	5.52	0.09	21.75	25.66	20.80	5.14	11.30	11.41	12.83
2600.00	5.51	5.58	5.53	0.08	18.99	28.11	18.37	5.02	11.49	11.33	12.54
2700.00	5.50	5.59	5.54	0.08	16.91	27.40	16.50	4.88	11.65	11.46	12.34
2800.00	5.51	5.60	5.55	0.09	15.25	24.44	14.98	4.68	11.79	11.72	12.35

1. Total Loss = Insertion Loss + 4.8dB splitter loss.



3 Way-0° Power Splitter/Combiner

SCN-3-28

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)			
	S-1	S-2	S-3			1-2	1-3	2-3	S	1	2	3
10	6.06	6.06	6.04	0.02	0.38	6.10	6.08	6.05	3.00	2.95	2.95	2.93
50	6.09	6.05	6.01	0.08	0.58	6.11	6.07	6.08	3.00	2.92	2.92	2.89
100	6.10	6.07	6.03	0.07	0.47	6.15	6.15	6.15	2.99	2.87	2.88	2.85
200	6.09	6.09	6.04	0.05	0.40	6.29	6.37	6.37	2.96	2.73	2.78	2.71
300	6.07	6.10	6.03	0.07	0.46	6.50	6.68	6.66	2.93	2.54	2.64	2.51
400	6.06	6.12	6.03	0.09	0.51	6.77	7.05	7.01	2.92	2.35	2.47	2.30
500	6.05	6.13	6.01	0.12	0.53	7.11	7.47	7.44	2.89	2.14	2.29	2.09
600	6.04	6.16	5.99	0.17	0.46	7.51	7.91	7.94	2.86	1.94	2.11	1.90
700	6.03	6.16	5.96	0.20	0.50	7.95	8.35	8.46	2.84	1.77	1.94	1.72
800	6.00	6.17	5.94	0.23	0.54	8.46	8.82	9.05	2.80	1.61	1.78	1.57
900	5.98	6.17	5.91	0.26	0.76	9.01	9.28	9.69	2.77	1.48	1.65	1.44
1000	5.97	6.16	5.88	0.28	1.03	9.60	9.76	10.36	2.73	1.36	1.53	1.33
1100	5.94	6.14	5.85	0.29	1.39	10.26	10.25	11.06	2.69	1.27	1.42	1.24
1200	5.92	6.12	5.82	0.30	1.69	10.95	10.76	11.83	2.64	1.18	1.32	1.16
1300	5.88	6.09	5.79	0.30	1.96	11.73	11.30	12.66	2.59	1.12	1.24	1.12
1400	5.84	6.05	5.75	0.30	2.20	12.55	11.86	13.56	2.52	1.09	1.16	1.11
1500	5.80	6.01	5.71	0.30	2.47	13.48	12.46	14.55	2.44	1.11	1.09	1.14
1600	5.75	5.95	5.65	0.30	2.67	14.51	13.13	15.65	2.36	1.15	1.04	1.18
1650	5.72	5.91	5.62	0.29	2.76	15.06	13.49	16.26	2.31	1.18	1.02	1.21
1700	5.69	5.88	5.59	0.29	2.86	15.65	13.87	16.91	2.26	1.21	1.03	1.23
1750	5.66	5.85	5.57	0.28	2.95	16.28	14.25	17.59	2.22	1.23	1.05	1.26
1800	5.63	5.81	5.54	0.27	3.03	16.95	14.67	18.34	2.17	1.26	1.07	1.28
1850	5.59	5.78	5.51	0.27	3.10	17.69	15.11	19.16	2.11	1.28	1.10	1.31
1900	5.56	5.74	5.48	0.26	3.17	18.47	15.57	20.05	2.06	1.30	1.12	1.33
1950	5.53	5.70	5.44	0.26	3.21	19.35	16.07	21.04	2.00	1.32	1.14	1.35
2000	5.49	5.66	5.41	0.25	3.23	20.31	16.62	22.15	1.94	1.35	1.16	1.37
2050	5.46	5.61	5.37	0.24	3.26	21.42	17.21	23.37	1.88	1.37	1.18	1.39
2100	5.41	5.58	5.34	0.24	3.32	22.61	17.84	24.79	1.82	1.39	1.20	1.41
2150	5.38	5.54	5.30	0.24	3.33	23.98	18.54	26.36	1.76	1.41	1.22	1.43
2200	5.35	5.51	5.26	0.25	3.31	25.53	19.32	28.06	1.70	1.42	1.23	1.44
2250	5.31	5.47	5.23	0.24	3.34	27.19	20.15	29.62	1.64	1.44	1.25	1.46
2300	5.28	5.44	5.20	0.24	3.35	28.81	21.08	30.35	1.58	1.45	1.27	1.47
2350	5.25	5.41	5.18	0.23	3.35	29.93	22.13	29.93	1.52	1.46	1.28	1.48
2400	5.22	5.39	5.15	0.24	3.33	29.92	23.35	28.53	1.47	1.48	1.29	1.49
2450	5.20	5.37	5.13	0.24	3.32	28.71	24.71	26.83	1.41	1.49	1.31	1.50
2500	5.17	5.36	5.12	0.24	3.26	27.01	26.30	25.17	1.36	1.50	1.32	1.50
2550	5.16	5.35	5.11	0.24	3.22	25.29	28.01	23.68	1.32	1.51	1.34	1.51
2600	5.14	5.35	5.10	0.25	3.24	23.79	29.87	22.38	1.29	1.52	1.35	1.52
2650	5.13	5.36	5.10	0.26	3.22	22.40	31.25	21.18	1.27	1.53	1.36	1.53
2700	5.13	5.38	5.11	0.27	3.19	21.20	31.48	20.17	1.27	1.54	1.38	1.54
2750	5.14	5.41	5.13	0.28	3.18	20.11	30.48	19.24	1.28	1.55	1.39	1.55
2800	5.15	5.44	5.15	0.29	3.18	19.15	28.73	18.41	1.32	1.57	1.41	1.57
2850	5.17	5.49	5.18	0.32	3.16	18.30	27.01	17.67	1.37	1.59	1.43	1.58
2900	5.20	5.55	5.23	0.35	3.14	17.54	25.43	17.00	1.43	1.61	1.45	1.60
2950	5.24	5.61	5.28	0.37	3.12	16.86	24.10	16.42	1.50	1.63	1.48	1.63
3000	5.29	5.69	5.34	0.41	3.08	16.27	22.96	15.90	1.59	1.65	1.51	1.66
3100	5.42	5.90	5.50	0.48	3.00	15.24	21.05	15.00	1.80	1.72	1.58	1.73
3200	5.61	6.17	5.72	0.56	2.87	14.40	19.56	14.26	2.07	1.81	1.66	1.82
3250	5.71	6.33	5.84	0.63	2.83	14.04	18.99	13.97	2.22	1.85	1.72	1.87
3300	5.82	6.50	5.97	0.68	2.75	13.73	18.47	13.72	2.38	1.91	1.77	1.94
3400	6.09	6.90	6.29	0.82	2.55	13.23	17.64	13.32	2.75	2.03	1.91	2.08
3500	6.40	7.37	6.65	0.98	2.26	12.87	16.99	13.05	3.19	2.18	2.06	2.25
4000	8.64	10.85	9.22	2.21	2.58	12.91	16.30	13.66	6.89	3.29	3.27	3.58

¹ Total Loss = Insertion Loss+ 4.8dB Splitter Loss

REV. X2
SCN-3-28
100627
Page 1 of 3



Mini-Circuits®

RF/MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



3 Way-0° Power Splitter/Combiner

SCN-3-28

Typical Performance Data

TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = -55°C

FREQ. (MHz)	TOTAL LOSS ¹			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION			VSWR			
	(dB)					(dB)			(:1)			
	S-1	S-2	S-3			1-2	1-3	2-3	S	1	2	3
10	6.05	6.06	6.03	0.03	0.39	6.08	6.05	6.03	3.02	2.97	2.97	2.96
50	6.08	6.04	5.99	0.09	0.62	6.08	6.03	6.03	3.03	2.94	2.93	2.91
100	6.03	6.01	5.96	0.07	0.52	6.15	6.13	6.14	2.95	2.91	2.93	2.89
200	6.01	6.01	5.96	0.05	0.35	6.27	6.34	6.34	2.94	2.78	2.83	2.76
300	6.01	6.05	5.97	0.08	0.35	6.43	6.60	6.58	2.96	2.59	2.68	2.55
400	5.99	6.05	5.96	0.09	0.37	6.68	6.96	6.92	2.95	2.39	2.51	2.34
500	5.95	6.06	5.93	0.13	0.50	7.00	7.35	7.34	2.92	2.17	2.34	2.14
600	5.92	6.07	5.89	0.18	0.36	7.38	7.78	7.82	2.89	1.97	2.16	1.94
700	5.92	6.06	5.86	0.20	0.36	7.81	8.21	8.30	2.88	1.80	1.96	1.75
800	5.89	6.06	5.82	0.24	0.40	8.30	8.65	8.89	2.85	1.63	1.81	1.59
900	5.83	6.04	5.78	0.26	0.64	8.86	9.14	9.55	2.80	1.49	1.67	1.47
1000	5.82	6.03	5.74	0.29	0.89	9.45	9.58	10.20	2.77	1.38	1.55	1.34
1100	5.78	6.00	5.69	0.31	1.36	10.09	10.05	10.89	2.73	1.28	1.44	1.25
1200	5.75	5.97	5.66	0.31	1.65	10.78	10.56	11.65	2.68	1.20	1.34	1.18
1300	5.71	5.94	5.63	0.31	1.90	11.55	11.10	12.48	2.64	1.14	1.24	1.14
1400	5.67	5.89	5.58	0.31	2.13	12.40	11.67	13.40	2.58	1.12	1.16	1.13
1500	5.63	5.85	5.55	0.30	2.40	13.31	12.26	14.39	2.52	1.13	1.10	1.17
1600	5.56	5.78	5.48	0.30	2.62	14.36	12.94	15.52	2.43	1.18	1.05	1.22
1650	5.54	5.74	5.44	0.30	2.70	14.94	13.30	16.14	2.39	1.21	1.05	1.25
1700	5.51	5.71	5.42	0.29	2.79	15.58	13.71	16.85	2.34	1.24	1.06	1.28
1750	5.48	5.66	5.38	0.28	2.83	16.25	14.12	17.57	2.29	1.26	1.09	1.30
1800	5.45	5.63	5.36	0.27	2.95	16.97	14.56	18.39	2.25	1.30	1.11	1.33
1850	5.41	5.58	5.32	0.26	3.00	17.78	15.04	19.30	2.19	1.32	1.14	1.35
1900	5.37	5.54	5.28	0.26	3.03	18.67	15.55	20.30	2.13	1.34	1.16	1.37
1950	5.33	5.50	5.25	0.25	3.07	19.63	16.08	21.40	2.08	1.37	1.18	1.40
2000	5.29	5.46	5.21	0.25	3.10	20.71	16.67	22.70	2.01	1.39	1.20	1.42
2050	5.23	5.39	5.15	0.24	3.15	22.01	17.31	24.22	1.93	1.41	1.22	1.43
2100	5.18	5.35	5.11	0.24	3.26	23.45	18.02	25.94	1.86	1.43	1.23	1.46
2150	5.14	5.31	5.07	0.23	3.30	25.12	18.79	27.98	1.79	1.44	1.25	1.47
2200	5.10	5.26	5.02	0.24	3.35	27.19	19.68	30.37	1.72	1.47	1.26	1.48
2250	5.05	5.21	4.98	0.24	3.39	29.44	20.68	32.21	1.64	1.48	1.27	1.48
2300	5.01	5.18	4.94	0.24	3.42	31.28	21.72	32.06	1.57	1.49	1.29	1.49
2350	4.97	5.14	4.91	0.23	3.43	31.84	22.98	30.23	1.50	1.49	1.30	1.51
2400	4.94	5.11	4.88	0.23	3.43	29.96	24.53	27.71	1.43	1.50	1.30	1.50
2450	4.91	5.09	4.85	0.24	3.49	27.66	26.13	25.66	1.38	1.51	1.31	1.51
2500	4.88	5.08	4.84	0.24	3.52	25.67	28.16	23.91	1.32	1.52	1.33	1.52
2550	4.87	5.07	4.83	0.24	3.50	23.81	30.43	22.36	1.28	1.53	1.32	1.52
2600	4.85	5.07	4.82	0.25	3.45	22.28	32.28	21.08	1.25	1.54	1.34	1.53
2650	4.85	5.09	4.83	0.26	3.47	21.00	32.58	19.99	1.25	1.55	1.35	1.53
2700	4.85	5.12	4.84	0.28	3.51	19.88	31.24	19.01	1.26	1.55	1.37	1.55
2750	4.87	5.15	4.87	0.29	3.44	18.83	29.04	18.10	1.30	1.58	1.38	1.57
2800	4.88	5.20	4.90	0.32	3.45	17.95	27.02	17.34	1.36	1.58	1.40	1.58
2850	4.92	5.26	4.94	0.34	3.50	17.19	25.41	16.68	1.42	1.61	1.43	1.60
2900	4.96	5.31	4.99	0.36	3.43	16.49	23.93	16.03	1.50	1.65	1.43	1.62
2950	4.99	5.39	5.06	0.40	3.38	15.86	22.72	15.52	1.59	1.66	1.48	1.67
3000	5.05	5.48	5.11	0.43	3.33	15.33	21.74	15.04	1.68	1.69	1.50	1.68
3100	5.17	5.70	5.28	0.53	3.07	14.38	20.04	14.20	1.90	1.76	1.58	1.77
3200	5.32	5.96	5.47	0.64	2.97	13.65	18.76	13.58	2.16	1.86	1.70	1.89
3250	5.44	6.11	5.58	0.68	2.97	13.29	18.16	13.28	2.32	1.93	1.75	1.93
3300	5.53	6.29	5.72	0.76	2.87	13.01	17.69	13.07	2.50	2.00	1.83	2.02
3400	5.77	6.67	6.01	0.91	2.51	12.59	16.99	12.75	2.88	2.15	2.00	2.20
3500	6.04	7.15	6.37	1.12	2.45	12.30	16.43	12.58	3.36	2.33	2.21	2.43
4000	8.59	11.19	9.26	2.60	3.29	12.76	16.12	13.70	8.86	3.92	4.10	4.33

¹ Total Loss = Insertion Loss+ 4.8dB Splitter Loss

REV. X2
SCN-3-28
100627
Page 2 of 3



Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



3 Way-0° Power Splitter/Combiner

SCN-3-28

Typical Performance Data


TEST CONDITIONS: INPUT POWER = 0dBm @Temperature = +100°C

FREQ. (MHz)	TOTAL LOSS ¹			AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION			VSWR			
	(dB)					(dB)			(:1)			
	S-1	S-2	S-3			1-2	1-3	2-3	S	1	2	3
10	6.07	6.07	6.04	0.03	0.42	6.12	6.09	6.06	2.99	2.94	2.94	2.92
50	6.09	6.05	6.00	0.09	0.62	6.14	6.10	6.10	2.97	2.92	2.92	2.89
100	6.17	6.12	6.09	0.08	0.45	6.13	6.13	6.12	3.05	2.84	2.84	2.81
200	6.13	6.12	6.09	0.04	0.52	6.30	6.38	6.38	2.97	2.70	2.75	2.69
300	6.10	6.12	6.06	0.06	0.33	6.53	6.71	6.69	2.92	2.53	2.62	2.50
400	6.11	6.15	6.08	0.07	0.45	6.79	7.07	7.02	2.93	2.32	2.43	2.28
500	6.10	6.16	6.05	0.11	0.44	7.15	7.50	7.47	2.88	2.12	2.26	2.07
600	6.09	6.20	6.03	0.17	0.33	7.56	7.96	7.98	2.86	1.92	2.08	1.88
700	6.09	6.21	6.01	0.20	0.27	8.01	8.42	8.52	2.83	1.75	1.91	1.70
800	6.07	6.22	5.99	0.23	0.39	8.53	8.90	9.13	2.79	1.60	1.76	1.55
900	6.05	6.22	5.97	0.25	0.59	9.09	9.39	9.78	2.76	1.46	1.62	1.43
1000	6.03	6.22	5.94	0.28	0.87	9.71	9.87	10.47	2.71	1.35	1.51	1.32
1100	6.00	6.19	5.91	0.28	1.19	10.38	10.38	11.19	2.66	1.25	1.40	1.23
1200	5.98	6.17	5.88	0.29	1.47	11.08	10.90	11.97	2.60	1.17	1.31	1.15
1300	5.94	6.14	5.85	0.29	1.68	11.86	11.45	12.81	2.53	1.10	1.23	1.10
1400	5.90	6.11	5.81	0.30	1.91	12.68	12.00	13.69	2.46	1.06	1.16	1.08
1500	5.86	6.06	5.76	0.30	2.13	13.59	12.59	14.67	2.38	1.07	1.10	1.10
1600	5.80	6.01	5.71	0.30	2.33	14.58	13.23	15.72	2.29	1.12	1.05	1.14
1650	5.78	5.98	5.68	0.30	2.42	15.10	13.56	16.30	2.24	1.14	1.03	1.17
1700	5.75	5.96	5.66	0.30	2.50	15.66	13.92	16.91	2.20	1.17	1.02	1.19
1750	5.72	5.93	5.63	0.30	2.63	16.24	14.27	17.54	2.15	1.19	1.03	1.22
1800	5.69	5.90	5.60	0.30	2.74	16.87	14.66	18.23	2.10	1.22	1.04	1.24
1850	5.66	5.86	5.58	0.28	2.88	17.54	15.07	18.97	2.05	1.24	1.06	1.26
1900	5.64	5.84	5.55	0.29	2.99	18.26	15.49	19.77	2.00	1.27	1.08	1.29
1950	5.61	5.80	5.52	0.28	3.06	19.05	15.96	20.66	1.94	1.29	1.10	1.31
2000	5.58	5.77	5.49	0.28	3.19	19.90	16.46	21.65	1.89	1.31	1.12	1.33
2050	5.55	5.73	5.46	0.27	3.26	20.86	16.99	22.69	1.83	1.33	1.13	1.35
2100	5.52	5.70	5.44	0.26	3.38	21.88	17.57	23.85	1.78	1.35	1.15	1.37
2150	5.49	5.67	5.41	0.26	3.43	23.02	18.18	25.10	1.73	1.37	1.17	1.39
2200	5.47	5.64	5.38	0.26	3.50	24.28	18.89	26.47	1.68	1.39	1.19	1.41
2250	5.44	5.61	5.36	0.25	3.57	25.66	19.64	27.79	1.63	1.40	1.21	1.42
2300	5.41	5.59	5.34	0.25	3.62	27.01	20.45	28.67	1.58	1.41	1.22	1.44
2350	5.39	5.57	5.32	0.25	3.67	28.17	21.35	28.95	1.52	1.43	1.24	1.45
2400	5.37	5.55	5.30	0.25	3.68	28.81	22.39	28.45	1.48	1.45	1.26	1.47
2450	5.36	5.53	5.29	0.24	3.75	28.63	23.52	27.36	1.43	1.46	1.28	1.48
2500	5.33	5.52	5.28	0.24	3.77	27.72	24.85	26.08	1.39	1.48	1.29	1.49
2550	5.32	5.51	5.27	0.24	3.78	26.36	26.34	24.68	1.34	1.49	1.31	1.50
2600	5.30	5.51	5.26	0.25	3.79	24.96	28.00	23.43	1.31	1.50	1.32	1.52
2650	5.29	5.51	5.26	0.25	3.82	23.59	29.64	22.24	1.28	1.51	1.34	1.53
2700	5.29	5.53	5.26	0.27	3.79	22.33	30.92	21.15	1.27	1.53	1.36	1.54
2750	5.28	5.54	5.27	0.27	3.77	21.18	31.25	20.19	1.26	1.54	1.38	1.55
2800	5.29	5.57	5.29	0.28	3.81	20.16	30.34	19.33	1.27	1.55	1.40	1.56
2850	5.31	5.61	5.31	0.30	3.85	19.25	28.77	18.55	1.30	1.57	1.42	1.57
2900	5.32	5.65	5.35	0.33	3.81	18.43	27.06	17.81	1.35	1.59	1.44	1.60
2950	5.36	5.71	5.39	0.35	3.77	17.70	25.59	17.18	1.40	1.61	1.46	1.61
3000	5.39	5.78	5.44	0.39	3.71	17.04	24.24	16.63	1.47	1.63	1.49	1.64
3100	5.51	5.98	5.59	0.47	3.67	15.89	21.98	15.60	1.67	1.68	1.57	1.71
3200	5.69	6.23	5.79	0.55	3.61	14.99	20.31	14.81	1.92	1.76	1.65	1.79
3250	5.80	6.39	5.91	0.59	3.54	14.59	19.60	14.47	2.06	1.81	1.69	1.84
3300	5.92	6.57	6.05	0.65	3.47	14.23	18.99	14.19	2.22	1.86	1.75	1.90
3400	6.23	6.99	6.39	0.77	3.27	13.67	18.04	13.72	2.58	1.97	1.87	2.03
3500	6.58	7.48	6.79	0.91	3.09	13.28	17.29	13.39	3.02	2.11	2.02	2.19
4000	8.89	10.90	9.42	2.01	3.69	13.14	16.46	13.79	6.21	3.09	2.98	3.29


¹ Total Loss = Insertion Loss+ 4.8dB Splitter Loss

Typical Performance Curves


Total Loss




Total Loss S-1 vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE




Phase Unbalance vs. TEMPERATURE



Isolation



Isolation 1-2 vs. TEMPERATURE



REV. X2

SCN-3-28

100627

Page 1 of 2



RF/MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAM
FV1206-1	.126 (3.20)	.063 (1.60)	.035 (0.89)	.024 (0.61)	.022 (0.56)	.011 (0.28)	.039 (0.99)	.024 (0.61)	.042 (1.07)	.123 (3.12)	--	--	--	--	.020

Dimensions are in inches (mm). Tolerances: 2 PL. $\pm .01$; 3 PL. $\pm .005$

Notes:

- Open style, ceramic base.
- Termination finish: **as shown below or indicated on Data Sheet.**
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

DEVICE ORIENTATION IN T&R




ILLUSTRATION 1




ILLUSTRATION 2




ILLUSTRATION 3

Applicable Case Styles

FV1206-1
FV1206-3

Applicable Case Styles

FV1206-4
FV1206-5
FV1206-6
FV1206-7
FV1206-9

Applicable Case Styles

FV1206-11
FV1206-12
GE0805C-18
NL1008C-6
NL1008C-7
NL1008C-9
NL1008C-10
NL1008C-12

Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
8	4	7	Small quantity standards (see note)	20
				50
				100
				200
				500
				1000
			Standard	3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • **EUROPE** 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M94644	NEW RELEASE	10/12/04	MMG	ABD
A	M102713	ADDED "...WITH SMOBC", REMOVED NOTE 2	01/20/06	GT	IL

**SUGGESTED MOUNTING CONFIGURATION
FOR FV1206-1 CASE STYLE, "qc" PIN CONNECTION.**



RESISTORS: R1-R2: 124 Ohm, 0603 SIZE; R3: 127 Ohm, 1206 SIZE.

- NOTES:** 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS: .020" $\pm$.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

DRAWN

MMG

10/04/04

CHECKED

AV

10/12/04

APPROVED

ABD

10/12/04



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, qc, FV1206-1, SCN-3, TB-303

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-171


REV:
A

FILE: 98PL171


SCALE: 10:1

SHEET: 1 OF 1

Evaluation Board and Circuit



TB-303



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A