

Engineering Development Model

Power Splitter/Combiner

SCPSQJ-ED13503/1

4 Way-0°/90°/180°/270°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : HU1374

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1000		1900 MHz
Isolation	1000-1900 MHz		20	dB
Insertion Loss Above 6.0 dB	1000-1900 MHz		1.15	dB
Phase Unbalance* @ 90° Port	1000-1900 MHz		1	deg.
Phase Unbalance* @ 180° Port	1000-1900 MHz		1	deg.
Phase Unbalance* @ 270° Port	1000-1900 MHz		1	deg.
Amplitude Unbalance	1000-1900 MHz		0.45	dB
VSWR	SUM Port		1.09	(:1)
	OUT Ports		1.11	(:1)

*Phase Unbalance is referenced insertion phase @ 0° port

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	11
PORT 1 (0°)	9
PORT 2 (90°)	6
PORT 3 (180°)	2
PORT 4 (270°)	13
GROUND	1,3,4,5,7,8,10,12,14

electrical schematic



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS




REV. X1
SCPSQJ-ED13503/1
12/16/2008
Page 1 of 1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBALANCE ² (Deg.)			FREQ. (MHz)	VSWR (:1)				
	S-1	S-2	S-3	S-4		1-2	2-3	3-4	@ 90° Port	@ 180° Port	@ 270° Port		S	1	2	3	4
1000.0	6.49	7.27	6.39	7.47	1.07	22.21	32.11	21.79	88.11	180.52	269.51	1000.0	1.04	1.04	1.03	1.17	1.04
1050.0	6.64	7.15	6.53	7.35	0.82	21.93	32.33	21.97	88.20	180.63	269.45	1050.0	1.03	1.02	1.04	1.15	1.04
1100.0	6.79	7.06	6.66	7.24	0.58	21.61	32.27	22.03	88.34	180.75	269.44	1100.0	1.04	1.01	1.05	1.14	1.04
1125.0	6.86	7.02	6.73	7.20	0.47	21.45	32.13	22.05	88.45	180.81	269.47	1125.0	1.05	1.00	1.06	1.14	1.04
1150.0	6.93	6.98	6.78	7.15	0.37	21.29	31.94	22.07	88.55	180.87	269.47	1150.0	1.06	1.00	1.07	1.13	1.05
1175.0	6.99	6.95	6.84	7.12	0.28	21.13	31.69	22.08	88.65	180.93	269.48	1175.0	1.07	1.01	1.08	1.13	1.05
1200.0	7.05	6.93	6.90	7.08	0.19	21.00	31.39	22.09	88.76	180.99	269.50	1200.0	1.07	1.01	1.09	1.13	1.05
1225.0	7.11	6.91	6.95	7.05	0.20	20.89	31.05	22.11	88.87	181.06	269.53	1225.0	1.08	1.01	1.10	1.13	1.06
1250.0	7.16	6.89	7.00	7.02	0.27	20.79	30.69	22.16	88.98	181.12	269.55	1250.0	1.08	1.01	1.11	1.14	1.06
1275.0	7.20	6.88	7.05	7.00	0.33	20.71	30.29	22.20	89.11	181.18	269.58	1275.0	1.08	1.02	1.12	1.14	1.06
1300.0	7.25	6.87	7.10	6.98	0.38	20.67	29.89	22.27	89.26	181.24	269.66	1300.0	1.08	1.02	1.12	1.15	1.07
1350.0	7.31	6.86	7.18	6.95	0.46	20.65	29.04	22.48	89.55	181.36	269.81	1350.0	1.07	1.03	1.13	1.16	1.07
1400.0	7.36	6.86	7.25	6.94	0.50	20.71	28.18	22.77	89.82	181.47	269.96	1400.0	1.06	1.05	1.14	1.18	1.07
1450.0	7.39	6.89	7.32	6.95	0.50	20.90	27.34	23.20	90.08	181.55	270.15	1450.0	1.04	1.06	1.14	1.20	1.07
1500.0	7.40	6.92	7.37	6.97	0.48	21.16	26.53	23.73	90.30	181.62	270.32	1500.0	1.02	1.08	1.14	1.22	1.06
1525.0	7.39	6.94	7.39	6.99	0.45	21.33	26.13	24.04	90.43	181.65	270.44	1525.0	1.02	1.08	1.14	1.23	1.05
1550.0	7.39	6.97	7.42	7.01	0.44	21.53	25.75	24.40	90.55	181.67	270.55	1550.0	1.03	1.09	1.13	1.24	1.05
1575.0	7.37	7.01	7.43	7.04	0.43	21.74	25.36	24.80	90.65	181.68	270.65	1575.0	1.04	1.10	1.13	1.25	1.04
1600.0	7.35	7.04	7.45	7.07	0.41	21.98	25.01	25.22	90.76	181.68	270.78	1600.0	1.06	1.11	1.12	1.26	1.03
1625.0	7.33	7.08	7.46	7.11	0.38	22.25	24.66	25.66	90.87	181.68	270.92	1625.0	1.07	1.11	1.11	1.27	1.03
1650.0	7.31	7.13	7.47	7.16	0.34	22.54	24.32	26.18	90.96	181.67	271.04	1650.0	1.09	1.12	1.11	1.28	1.02
1675.0	7.28	7.18	7.48	7.21	0.30	22.85	23.99	26.75	91.06	181.65	271.20	1675.0	1.12	1.12	1.10	1.28	1.02
1700.0	7.25	7.24	7.48	7.27	0.24	23.17	23.68	27.35	91.13	181.60	271.33	1700.0	1.14	1.13	1.09	1.29	1.02
1725.0	7.21	7.30	7.49	7.34	0.27	23.52	23.39	27.99	91.21	181.56	271.47	1725.0	1.16	1.13	1.08	1.30	1.03
1750.0	7.18	7.36	7.49	7.42	0.31	23.87	23.11	28.69	91.26	181.51	271.60	1750.0	1.18	1.13	1.08	1.30	1.04
1775.0	7.13	7.44	7.48	7.50	0.37	24.24	22.84	29.45	91.29	181.44	271.72	1775.0	1.20	1.13	1.07	1.30	1.06
1800.0	7.09	7.51	7.48	7.58	0.50	24.59	22.59	30.27	91.33	181.38	271.87	1800.0	1.22	1.13	1.07	1.30	1.07
1900.0	6.88	7.88	7.43	8.01	1.13	25.85	21.74	33.93	91.53	181.10	272.60	1900.0	1.31	1.11	1.08	1.28	1.13


¹Total Loss = Insertion Loss + 6dB Splitter Loss²Phase Unbalance is referenced insertion phase at 0° port

Typical Performance Curves




Outline Dimensions

HU1374



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT, GRAM
HU1374	.870 (22.10)	.800 (20.32)	.25 (6.35)	.100 (2.54)	.097 (2.46)	-	.060 (1.52)	.040 (1.02)	.105 (2.67)	.910 (23.11)	-	.060 (1.52)	.060 (1.52)	-	2.85

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate. All models (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F21



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M119547	NEW RELEASE	09/17/08	AV	HY


SUGGESTED MOUNTING CONFIGURATION FOR HU1374 CASE STYLE, "14SQ05" PIN CODE



- NOTES: 1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
(SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

DRAWN

AY

09/12/08

TOLERANCES ON:

CHECKED

PW

09/17/08

2 PL DECIMALS $\pm$

APPROVED

HY

09/17/08

3 PL DECIMALS $\pm$.005ANGLES $\pm$ FRACTIONS $\pm$

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95



Mini-Circuits® 13 Neptune Avenue
Brooklyn NY 11235

PL, 14SQ05, HU1374, SCPSQJ-4+, TB-490+

SIZE
A

CODE IDENT
15542

DRAWING NO:
98-PL-292

REV:
OR


FILE: 98PL292

SCALE: 6:1

SHEET: 1 OF 1

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215