

Engineering Development Model

Power Splitter/Combiner 8 Way-0°

SCPA-ED13459/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE: HU1371

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		26		900	MHz
Isolation	26-260 MHz		25		dB
	260-450 MHz		20		dB
	450-900 MHz		22		dB
Insertion Loss Above 9.0 dB	26-260 MHz		1.10		dB
	260-450 MHz		1.55		dB
	450-900 MHz		1.85		dB
Phase Unbalance	26-260 MHz		0.85		deg.
	260-450 MHz		2.20		deg.
	450-900 MHz		3.95		deg.
Amplitude Unbalance	26-260 MHz		0.06		dB
	260-450 MHz		0.20		dB
	450-900 MHz		0.45		dB
VSWR	SUM Port		1.21		(:1)
	OUT Ports		1.14		(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	3
PORT 2	4
PORT 3	5
PORT 4	6
PORT 5	9
PORT 6	10
PORT 7	11
PORT 8	12
GROUND	2,7,8,13,14

Functional Diagram



Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350168, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4951 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. X1
SCPA-ED13459/1
11/19/2008
Page 1 of 1

8 Way-0° Power Splitter/Combiner

SCPA-ED13459/1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)						AMP. UNBAL. (dB)	ISOLATION (dB)				PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2	S-3	S-4	S-6	S-8		1-2	2-3	3-4	6-7			S	1	8
1.00	10.64	10.64	10.64	10.63	10.62	10.61	0.03	26.84	30.36	30.81	30.08	0.16	1.00	1.47	1.61	1.61
26.00	9.78	9.77	9.78	9.77	9.78	9.77	0.01	33.32	33.56	34.76	33.38	0.15	26.00	1.08	1.20	1.20
51.00	9.84	9.83	9.84	9.83	9.84	9.84	0.01	31.34	31.68	31.35	31.65	0.26	51.00	1.10	1.19	1.19
76.00	9.91	9.90	9.90	9.89	9.90	9.90	0.02	29.19	29.72	28.68	29.82	0.40	76.00	1.13	1.19	1.19
101.00	9.98	9.96	9.96	9.95	9.96	9.96	0.03	27.42	28.01	26.64	28.18	0.52	101.00	1.17	1.18	1.18
126.00	10.04	10.02	10.03	10.01	10.03	10.01	0.03	25.95	26.59	25.07	26.80	0.63	126.00	1.20	1.18	1.18
151.00	10.12	10.07	10.09	10.08	10.08	10.07	0.05	24.76	25.39	23.78	25.60	0.76	151.00	1.24	1.17	1.17
176.00	10.19	10.13	10.15	10.13	10.15	10.13	0.07	23.79	24.37	22.74	24.61	0.95	176.00	1.27	1.17	1.17
201.00	10.28	10.20	10.22	10.19	10.22	10.20	0.09	22.97	23.53	21.87	23.76	1.11	201.00	1.30	1.16	1.16
226.00	10.34	10.25	10.28	10.25	10.28	10.25	0.10	22.33	22.81	21.16	23.05	1.21	226.00	1.32	1.15	1.16
251.00	10.41	10.30	10.34	10.30	10.34	10.30	0.12	21.83	22.21	20.57	22.44	1.43	251.00	1.34	1.14	1.15
276.00	10.48	10.35	10.39	10.35	10.40	10.36	0.14	21.43	21.72	20.10	21.94	1.57	276.00	1.35	1.13	1.14
301.00	10.54	10.39	10.45	10.39	10.45	10.40	0.16	21.11	21.30	19.72	21.51	1.74	301.00	1.36	1.13	1.14
326.00	10.60	10.44	10.49	10.43	10.51	10.44	0.18	20.89	20.95	19.44	21.16	1.94	326.00	1.36	1.12	1.13
351.00	10.64	10.47	10.52	10.46	10.55	10.47	0.19	20.78	20.68	19.23	20.88	2.11	351.00	1.36	1.10	1.12
376.00	10.69	10.49	10.55	10.48	10.59	10.50	0.21	20.74	20.47	19.12	20.64	2.24	376.00	1.35	1.09	1.11
401.00	10.72	10.52	10.58	10.50	10.61	10.53	0.22	20.77	20.30	19.07	20.46	2.41	401.00	1.34	1.08	1.10
426.00	10.74	10.53	10.60	10.51	10.65	10.56	0.23	20.87	20.19	19.10	20.33	2.57	426.00	1.33	1.07	1.09
451.00	10.75	10.54	10.60	10.52	10.67	10.57	0.24	21.07	20.12	19.21	20.26	2.74	451.00	1.31	1.06	1.07
476.00	10.77	10.55	10.60	10.52	10.69	10.59	0.25	21.34	20.11	19.41	20.24	3.06	476.00	1.28	1.04	1.06
501.00	10.77	10.55	10.60	10.51	10.72	10.60	0.26	21.68	20.14	19.69	20.26	3.40	501.00	1.26	1.03	1.05
526.00	10.77	10.57	10.61	10.51	10.73	10.60	0.26	22.11	20.21	20.06	20.29	3.74	526.00	1.23	1.03	1.04
551.00	10.78	10.59	10.63	10.52	10.77	10.62	0.26	22.56	20.33	20.54	20.38	3.97	551.00	1.21	1.03	1.04
576.00	10.78	10.60	10.63	10.51	10.79	10.64	0.27	23.04	20.44	21.16	20.51	4.10	576.00	1.19	1.03	1.03
601.00	10.74	10.59	10.60	10.49	10.79	10.65	0.30	23.65	20.61	21.90	20.63	4.33	601.00	1.17	1.05	1.04
626.00	10.73	10.59	10.58	10.49	10.80	10.65	0.32	24.26	20.85	22.84	20.81	4.48	626.00	1.14	1.06	1.05
651.00	10.71	10.61	10.57	10.47	10.82	10.66	0.35	24.83	21.13	24.03	21.04	4.46	651.00	1.12	1.08	1.06
676.00	10.71	10.64	10.56	10.47	10.85	10.68	0.38	25.23	21.48	25.62	21.30	4.44	676.00	1.11	1.10	1.07
701.00	10.71	10.67	10.57	10.48	10.88	10.72	0.40	25.37	21.87	27.75	21.62	4.20	701.00	1.09	1.12	1.09
726.00	10.72	10.73	10.58	10.50	10.93	10.77	0.43	25.11	22.34	30.71	21.99	3.82	726.00	1.07	1.14	1.11
751.00	10.75	10.79	10.61	10.53	10.98	10.83	0.45	24.49	22.87	34.67	22.42	3.32	751.00	1.05	1.16	1.13
776.00	10.79	10.88	10.65	10.57	11.06	10.90	0.49	23.54	23.54	36.07	22.97	2.74	776.00	1.03	1.19	1.15
801.00	10.84	10.97	10.70	10.62	11.15	10.98	0.53	22.37	24.33	31.40	23.61	2.79	801.00	1.03	1.21	1.18
826.00	10.94	11.11	10.76	10.71	11.27	11.09	0.56	21.08	25.32	27.08	24.46	3.31	826.00	1.08	1.24	1.21
851.00	11.06	11.26	10.86	10.82	11.43	11.23	0.61	19.79	26.59	23.77	25.55	3.92	851.00	1.14	1.27	1.24
876.00	11.24	11.48	11.00	10.96	11.63	11.41	0.68	18.46	28.31	21.15	26.99	5.04	876.00	1.22	1.31	1.28
901.00	11.48	11.76	11.18	11.16	11.90	11.64	0.75	17.16	30.69	18.95	28.96	6.55	901.00	1.33	1.35	1.31
926.00	11.81	12.12	11.42	11.42	12.26	11.94	0.84	15.92	34.39	17.08	31.65	8.58	926.00	1.46	1.39	1.35

¹Total Loss = Insertion Loss + 9dB Splitter Loss




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS


REV. X2
SCPA-ED13459/1
9/13/2010
Page 1 of 1

Typical Performance Curves




Outline Dimensions

HU1371



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT, GRAM
HU1371	.870 (22.10)	.800 (20.32)	.25 (6.35)	.100 (2.54)	.097 (2.46)	-	.060 (1.52)	.040 (1.02)	.105 (2.67)	.910 (23.11)	-	.060 (1.52)	.060 (1.52)	-	2.85

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:

For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over .120-.240 μ inch (3.05-6.10 microns) Nickel plate. All models (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F21



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
32	32	13	200

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215