

Mini-Circuits

SURFACE MOUNT ^{top hat} RF Transformer

SCTX4-32HP-20W+

12.5/50Ω 1 to 310 MHz 20 Watt 1:4 Ratio

THE BIG DEAL

- High Power Input, 20 Watt max.
- Low Insertion Loss, 0.3 dB typ.
- Small size, 0.50 × 0.50 × 0.20"
- Excellent Return Loss, 23 dB typ.
- DC pass from IN to OUT



Generic photo used for illustration purposes only

CASE STYLE: CK2335

+RoHS Compliant

The +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- Military mobile
- PCS
- BALUN
- Diode matching

PRODUCT OVERVIEW

Mini-Circuits' SCTX4-32HP-20W+ is a high-power, surface-mount transformer with a secondary/primary impedance ratio of 1:4, covering the 1.0 to 320 MHz band. DC current pass IN to OUT, the transformer is capable of handling RF input power up to 20W. It provides low insertion loss (0.3 dB) as well as good matching VSWR 1.10:1. Featuring core and wire construction mounted on PCB, the unit comes enclosed in a miniature, shielded package measuring just 0.50 × 0.50 × 0.20", ideal for dense circuit board layouts.

KEY FEATURES

Feature	Advantages
High RF Power Handling (20W)	Supports systems with high power requirements in small device size.
Low Insertion Loss, 0.3 dB	Provides excellent transmission of signal power from input to output.
Good Return Loss, 20 dB typ	Provide good in to output impedance matching.
Small footprint, 0.50 × 0.50 × 0.20"	Accommodates tight space requirements for dense PCB layouts.

REV. B
ECO-029613
SCTX4-32HP-20W+
MCL NY
260604





SURFACE MOUNT top hat
RF Transformer

SCTX4-32HP-20W+

12.5/50Ω 1 to 310 MHz 20 Watt 1:4 Ratio

ELECTRICAL SPECIFICATIONS AT 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Impedance Ratio (secondary/primary)			4		
Frequency Range		1	—	310	MHz
Insertion Loss (average)	5 - 100 1 - 310	— —	0.3 0.5	0.5 0.9	dB
Return Loss	5 - 100 1 - 310	20 14	30 20	— —	dB
Input Power	5 - 100	—	—	20	Watt


** Below 30 MHz current need to be linary decreased to 0 mA to achieve specified performance.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to 85°C case*
Storage Temperature	-55°C to 100°C
DC Current	1A/max **

*Case temperature is defined as temperature on ground leads.
 Permanent damage may occur if any of these limits are exceeded.

CONFIGURATION D1





top hat
SURFACE MOUNT
RF Transformer

SCTX4-32HP-20W+

Mini-Circuits


12.5/50Ω 1 to 310 MHz 20 Watt 1:4 Ratio

PAD CONNECTIONS

PRIMARY (12.5 ohm)	4,5
SECONDARY (50 ohm)	8,9
DC IN	1,2
GND	all others

PRODUCT MARKING: N/A

**DEMO BOARD MCL P/N: TB-SCTX432HP20W
SUGGESTED PCB LAYOUT (PL-533)**




NOTES:


- TRACE WIDTH IS SHOWN FOR ROGERS R04350B, WITH DIELECTRIC THICKNESS .030"±.002". COPPER: 1/2 Oz. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

- DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
- DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK

OUTLINE DRAWING



PCB Land Pattern



Suggested Layout,
Tolerance to be within ±.002

OUTLINE DIMENSIONS (Inch mm)

A	B	C	D	E	F	G	H
.500	.500	.209	.100	.080	.115	.060	.040
12.70	12.70	5.31	2.54	2.03	2.92	1.52	1.02
J	K	L	M	N	P	T	wt.
.540	.060	.100	.135	.135	.115	.080	grams
13.72	1.52	2.54	3.43	3.43	2.92	2.03	1.0

TAPE & REEL INFORMATION: F37



SURFACE MOUNT top hat
RF Transformer


SCTX4-32HP-20W+

12.5/50Ω 1 to 310 MHz 20 Watt 1:4 Ratio


TYPICAL PERFORMANCE DATA

Frequency (MHz)	Insertion Loss (dB)	Primary Return Loss (dB)
1	0.17	20.57
51	0.17	34.31
100	0.22	31.23
130	0.25	28.86
160	0.29	27.77
190	0.33	25.54
220	0.38	23.53
250	0.43	21.43
280	0.50	19.39
310	0.58	17.40

SCTX4-32HP-20W+
INSERTION LOSS



SCTX4-32HP-20W+
INPUT RETURN LOSS



- NOTES**
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard. Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html





RF Transformer

SCTX4-32HP-20W+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
1	0.17	20.57
5	0.20	30.42
9	0.17	32.79
13	0.16	34.25
17	0.16	34.94
21	0.15	35.09
25	0.15	35.08
29	0.16	35.18
30	0.16	35.18
33	0.16	35.02
36	0.16	34.93
39	0.16	34.75
42	0.16	34.65
45	0.16	34.50
48	0.16	34.40
51	0.17	34.31
54	0.17	34.17
57	0.17	33.98
60	0.17	33.90
63	0.18	33.66
66	0.18	33.47
69	0.18	33.21
72	0.18	33.09
75	0.19	32.88
78	0.19	32.69
81	0.19	32.60
84	0.20	32.36
87	0.20	32.14
88	0.20	32.04
90	0.21	31.93
100	0.22	31.23
130	0.25	28.86
160	0.29	27.77
190	0.33	25.54
220	0.38	23.53
250	0.43	21.43
280	0.50	19.39
310	0.58	17.40
340	0.69	15.49
370	0.83	13.61
400	1.03	11.81

Typical Performance Data




Case Style


CK

Outline Dimensions

CK2335



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K
CK2335	.500 (12.70)	.500 (12.70)	.209 (5.31)	.100 (2.54)	.080 (2.03)	.115 (2.92)	.060 (1.52)	.040 (1.02)	.540 (13.72)	.060 (1.52)

CASE #	L	M	N	P	Q	R	S	T	WT. GRAM
CK2335	.100 (2.54)	.135 (3.43)	.135 (3.43)	.115 (2.92)	--	--	--	.080 (2.03)	1.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F37



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel	
24	16	7	Small quantity standards (see note)	10
				20
				50
				100
		13	Standard	200
			500	

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M164442	NEW RELEASE	12/14/17	ITG	TN


**SUGGESTED MOUNTING CONFIGURATION FOR
CK2335 CASE STYLE "16TD01" PIN CODE**



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B, WITH DIELECTRIC THICKNESS .030"±.002". COPPER: 1/2 Oz. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)

 DENOTES COPPER LAND PATTERN FREE OF SOLDERMASK



UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005" ANGLES ± FRACTIONS ±	DRAWN	ITG	12/14/17
	CHECKED	GF	12/14/17
	APPROVED	TN	12/14/17

 **Mini-Circuits®** 13 Neptune Avenue
Brooklyn NY 11235

PL, 16TD01, CK2335, TB-930+


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-533	REV: OR
FILE: 98PL533	SCALE: 5:1	SHEET: 1 OF 1	

Evaluation Board and Circuit



Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: ROGERS (R04350) or Equivalent
Dielectric Constant=3.48±.05, Thickness=.030 inch.

 **Mini-Circuits®**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 65° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Stabilization Bake	(non-operating) 125°C, 24 hours	- - -
Burn-in at Elevated Temp.	(DC on) 160 hours at 85° C	MIL-STD-202, Method 108
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, except 100°C