

Coaxial High Pass Filter

SHP-48+

50Ω 48 to 2150 MHz

The Big Deal

- Low insertion loss
- High rejection
- Connectorized package



Generic photo used for illustration purposes only
CASE STYLE: FF56

Product Overview

SHP-48+ is a High pass filter in a connectorized package covering 48 to 2150 MHz. This filter can be used in SATCOM, CATV, Broadband Fiber Networks and Multiband radio systems. It has repeatable performance across production lots and consistent performance across temperature.

Key Features

Feature	Advantages
Low insertion loss	Can be used in high performance applications.
Good rejection	This enables the filter to attenuate spurious signals and reject harmonics for broad band frequency.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial High Pass Filter

50Ω 48 to 2150 MHz

SHP-48+



Generic photo used for illustration purposes only

CASE STYLE: FF56

Connectors	Model
SMA-M/F	SHP-48+


Features

- Wide band, 48 MHz to 2150 MHz
- High rejection
- Connectorized package


Applications

- SATCOM
- Broadband Fiber Networks
- CATV
- Radio communications
- Receivers \ transmitters

Functional Schematic



Typical Frequency Response



Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	Rejection Loss	DC-F1	DC-18	20	31	-	dB
	VSWR	DC-F1	DC-18	-	40	-	:1
Pass Band	Insertion Loss	F2-F3	48-2150	-	0.6	1.2	dB
	VSWR	F2-F3	48-2150	-	1.15	-	:1

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	0.5 W.




Permanent damage may occur if any of these limits are exceeded.

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
0.5	94.13	1737.18
5.5	83.29	868.59
8.5	64.96	434.30
12.0	49.88	217.15
18.0	31.26	82.73
24.0	17.08	26.33
28.0	9.38	10.07
31.0	5.06	4.54
34.0	2.54	2.32
39.0	1.08	1.23
48.0	0.59	1.06
57.0	0.43	1.05
63.0	0.37	1.06
74.0	0.30	1.10
96.0	0.23	1.15
150.0	0.15	1.14
340.0	0.10	1.07
1150.0	0.18	1.04
1900.0	0.26	1.09
2150.0	0.31	1.11

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
ECO-005139
SHP-48+
EDU1367
URJ
201201
Page 2 of 3

Coaxial Connections

INPUT	SMA-Male
OUTPUT	SMA-Female

Outline Drawing



Outline Dimensions (^{inch}/_{mm})

B	D	E	wt
0.43	1.70	0.312	grams
10.92	43.18	7.92	18.0

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

High Pass Filter

SHP-48+







Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
0.5	96.25	104.95	103.83	0.00	0.00	0.00	0.00	0.00	0.00
1.0	106.54	99.80	98.18	0.00	0.00	0.00	0.00	0.00	0.00
2.0	94.45	99.39	99.72	0.01	0.01	0.01	0.00	0.00	0.00
3.0	106.58	101.72	112.91	0.00	0.00	0.00	0.00	0.01	0.00
4.0	103.64	98.29	100.96	0.03	0.04	0.03	0.01	0.01	0.00
6.0	79.98	80.91	78.65	0.02	0.02	0.03	0.02	0.02	0.03
8.0	67.92	67.78	67.73	0.03	0.04	0.04	0.03	0.04	0.05
10.0	58.05	58.07	57.94	0.05	0.06	0.07	0.05	0.07	0.08
12.0	50.02	49.94	49.90	0.06	0.08	0.09	0.06	0.09	0.10
14.0	43.05	42.99	42.92	0.10	0.12	0.14	0.10	0.11	0.13
16.0	37.06	37.00	36.94	0.12	0.15	0.18	0.11	0.15	0.18
18.0	31.53	31.44	31.41	0.17	0.22	0.25	0.16	0.21	0.25
20.0	26.43	26.40	26.34	0.25	0.31	0.35	0.24	0.30	0.35
22.0	21.72	21.68	21.64	0.37	0.44	0.49	0.35	0.43	0.49
24.0	17.33	17.31	17.30	0.56	0.66	0.74	0.53	0.64	0.73
26.0	13.27	13.29	13.29	0.90	1.03	1.14	0.87	1.01	1.12
28.0	9.59	9.64	9.69	1.53	1.70	1.84	1.47	1.65	1.81
30.0	6.46	6.57	6.66	2.66	2.88	3.06	2.60	2.83	3.01
35.0	1.98	2.15	2.29	9.31	9.53	9.69	9.18	9.39	9.52
40.0	0.88	0.99	1.09	22.31	22.31	22.32	22.07	21.72	21.27
45.0	0.61	0.69	0.76	36.96	37.59	36.54	35.72	36.26	35.10
50.0	0.48	0.55	0.60	30.59	29.91	28.74	29.73	30.38	30.58
55.0	0.40	0.46	0.50	33.07	31.08	29.00	31.54	31.85	31.72
60.0	0.35	0.40	0.43	35.17	32.97	30.58	33.86	34.42	34.54
65.0	0.31	0.35	0.38	31.49	32.03	31.55	31.83	33.35	35.16
70.0	0.28	0.32	0.34	28.17	29.70	31.14	28.83	30.57	32.77
75.0	0.25	0.29	0.30	26.05	27.81	29.98	26.69	28.40	30.42
80.0	0.24	0.27	0.28	24.68	26.44	28.78	25.32	26.93	28.71
90.0	0.20	0.23	0.24	23.27	24.91	27.04	23.85	25.26	26.63
100.0	0.18	0.20	0.21	22.83	24.23	26.00	23.36	24.53	25.55
150.0	0.11	0.13	0.14	24.86	25.07	25.19	25.31	25.41	25.32
200.0	0.09	0.11	0.11	27.40	27.45	27.60	27.73	27.75	28.02
300.0	0.06	0.10	0.11	45.40	33.48	29.57	43.59	33.34	29.49
400.0	0.06	0.10	0.10	43.44	43.66	33.86	41.59	40.87	33.13
500.0	0.06	0.10	0.11	36.85	47.86	36.86	37.88	49.96	35.48
600.0	0.06	0.11	0.12	33.62	38.18	41.59	35.41	42.05	40.72
700.0	0.07	0.12	0.13	30.84	34.35	41.89	32.48	37.26	43.29
800.0	0.07	0.14	0.15	29.49	32.08	38.37	31.29	34.59	41.30
900.0	0.06	0.13	0.16	27.93	30.64	35.48	29.60	32.74	37.96
1000.0	0.05	0.13	0.17	26.64	29.43	32.95	28.04	31.17	34.76
1100.0	0.04	0.14	0.17	25.91	28.56	31.31	27.18	30.02	32.71
1200.0	0.05	0.15	0.19	25.14	27.88	30.18	26.23	29.20	31.50
1300.0	0.04	0.14	0.19	24.66	27.34	29.14	25.63	28.37	30.43
1400.0	0.05	0.16	0.21	24.25	26.67	28.08	25.10	27.47	29.27
1500.0	0.10	0.20	0.25	23.52	25.69	26.91	24.22	26.36	27.88
1600.0	0.28	0.37	0.40	25.06	28.04	31.03	27.95	30.26	30.46
1700.0	0.15	0.23	0.26	25.00	27.40	28.11	25.51	27.92	29.87
1800.0	0.14	0.24	0.25	24.40	26.83	27.07	24.53	26.98	28.82
1900.0	0.16	0.25	0.29	24.37	26.48	26.46	24.34	26.56	28.16
2000.0	0.24	0.35	0.40	24.41	26.32	26.09	24.08	26.15	27.60
2100.0	0.26	0.38	0.45	24.24	25.91	25.65	23.94	25.73	26.85
2200.0	0.28	0.43	0.50	23.78	25.19	25.11	23.56	24.95	25.86
2300.0	0.32	0.50	0.60	22.77	23.70	23.92	23.04	23.71	23.83
2400.0	0.69	0.91	1.06	19.89	20.40	21.11	21.47	21.47	20.69
2500.0	0.91	1.07	1.15	20.71	21.54	23.40	23.99	24.77	24.14
2600.0	0.29	0.45	0.56	29.16	29.48	32.68	32.79	32.96	36.62
2700.0	0.22	0.36	0.45	34.24	33.78	34.92	39.63	32.71	30.53
2800.0	0.22	0.36	0.43	32.36	35.28	32.16	38.66	32.30	27.34
2900.0	0.21	0.38	0.47	29.06	34.86	29.95	32.57	31.83	25.27
3000.0	0.23	0.46	0.57	26.69	34.32	28.92	30.49	31.55	23.72

Typical Performance Data

FREQ. (MHz)	GROUP DELAY		
	(nsec)		
	@-40°C	@+25°C	@+85°C
50	9.70	9.63	9.61
51	9.22	9.17	9.14
52	8.79	8.73	8.69
53	8.39	8.35	8.33
54	8.01	7.99	7.96
55	7.66	7.65	7.60
56	7.40	7.34	7.30
57	7.05	7.04	7.00
58	6.78	6.75	6.68
59	6.60	6.53	6.50
60	6.31	6.27	6.21
61	6.06	6.05	6.00
62	5.86	5.80	5.80
63	5.67	5.61	5.63
64	5.43	5.43	5.39
65	5.29	5.23	5.24
66	5.09	5.06	5.04
67	4.94	4.93	4.88
68	4.76	4.74	4.71
69	4.63	4.57	4.55
70	4.47	4.47	4.44
71	4.38	4.32	4.32
72	4.23	4.19	4.17
73	4.12	4.09	4.06
74	4.01	3.98	3.97
75	3.88	3.87	3.81
76	3.78	3.78	3.76
77	3.70	3.69	3.65
78	3.60	3.59	3.56
79	3.51	3.48	3.44
80	3.44	3.40	3.39
81	3.32	3.30	3.27
83	3.17	3.15	3.14
85	3.00	3.00	2.97
90	2.71	2.69	2.67
100	2.18	2.14	2.12
125	1.53	1.52	1.50
150	1.13	1.11	1.09
200	0.72	0.71	0.69
250	0.55	0.53	0.52
300	0.46	0.43	0.42
400	0.36	0.34	0.32
500	0.31	0.30	0.28
600	0.29	0.27	0.25
700	0.27	0.26	0.25
800	0.27	0.25	0.23
900	0.26	0.24	0.23
1000	0.26	0.24	0.23
1100	0.25	0.23	0.22
1200	0.25	0.23	0.22
1300	0.25	0.23	0.22
1400	0.25	0.23	0.22
1500	0.26	0.24	0.23
1600	0.20	0.19	0.18
1700	0.27	0.24	0.23
1800	0.23	0.21	0.21
1900	0.23	0.22	0.21
2000	0.26	0.24	0.23
2050	0.26	0.24	0.22
2150	0.26	0.24	0.22


Typical Performance Curves



High Pass Filter

SHP-48+

Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS



REV. OR
SHP-48+
2/6/2013
Page 2 of 2

FF56
FF99

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF56	--	.46 (11.68)	--	1.70 (43.18)	.312 (7.92)	18.0
FF99	--	.70 (17.78)	--	1.98 (50.29)		42.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Notes:

1. Case material: Brass.
2. Case finish: Nickel plate.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I