Ceramic Surface Mount

Frequency Mixer WIDE BAND

SIM-83+

Level 7 (LO Power +7 dBm) 2300 to 8000 MHz

Generic photo used for illustration purposes only

CASE STYLE: HV1195

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Available Tape and Reel at no extra cost

Reel Size	Devices/Reel
7"	10, 20, 50, 100, 200, 500

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW

For extended temperature range, consult factory.

Permanent damage may occur if any of these limits are exceeded.

Pin Connections

LO	8
RF	4
IF	2
GROUND	1,3,5,6,7

Features

- wide bandwidth, 2300 to 8000 MHz
- low conversion loss, 6.0 dB typ.
- excellent IF BW, DC to 3000 MHz
- LTCC double balanced mixer
- tiny size, low profile, 0.08"
- useable as up and down converter
- aqueous washable
- protected by US patent 7,027,795

Applications

- satellite up and down converters
- defense radar and communications
- line of sight links
- WIFI
- blue tooth
- VSAT
- ISM

Outline Drawing



PCB Metal Land Pattern



Suggested Layout,
Tolerance to be within±.002

Outline Dimensions (inch / mm)

A	B	C	D	E	F	G
.200	.180	.087	.025	.050	.028	.043
5.08	4.57	2.2098	0.64	1.27	0.71	1.09

H	J	K	L	M	N	wt
.050	.030	.043	.204	.127	0.065	grams
1.27	0.76	1.09	5.18	3.23	1.65	0.08

Demo Board MCL P/N: TB-382
Suggested PCB Layout (PL-239)



NOTES:
1. TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020"±.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS* (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)
LO/RF f_L-f_U	IF	Typ.	σ	Max.	Typ.	Min.	Typ.	Min.	Typ.
2300-8000	**DC-3000**								
2300-3200		6.0	0.1	7.8	35	27	23	15	12
3200-3700		5.8	0.1	7.0	31	26	24	18	13
3700-4200		5.9	0.2	7.4	32	26	28	19	15
4200-8000		6.0	0.2	8.9	23	17	18	7	10

1 dB Compression: +1 dBm typ.

* Conversion loss at 30 MHz IF. σ is a measure of repeatability from unit to unit.

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm
2300.00	2331.00	6.58	33.75	18.78	2.30	3.23
2500.00	2531.00	6.26	37.97	19.66	2.67	2.46
2700.00	2731.00	5.89	39.45	21.43	2.68	2.07
3000.00	3031.00	5.65	32.22	25.41	2.65	1.93
3300.00	3331.00	5.77	30.68	25.94	2.47	1.94
3600.00	3631.00	5.87	30.39	25.71	2.19	2.14
3900.00	3931.00	6.05	31.52	32.26	2.40	2.43
4200.00	4231.00	6.19	31.06	28.64	3.09	2.54
4500.00	4531.00	6.00	28.97	18.58	2.77	2.60
4800.00	4831.00	6.85	30.21	15.63	4.27	2.62
5100.00	5131.00	6.53	27.21	16.08	3.22	2.80
5400.00	5431.00	5.91	26.54	19.19	2.91	2.93
5700.00	5731.00	5.66	23.69	20.99	2.45	3.38
6000.00	6031.00	5.36	23.52	25.50	1.73	2.68
6500.00	6531.00	5.49	22.36	27.85	1.42	1.31
6900.00	6931.00	5.51	22.41	27.41	1.28	1.12
7300.00	7331.00	5.76	21.74	19.64	1.56	1.88
7600.00	7631.00	6.61	22.46	16.02	2.19	2.56
7800.00	7831.00	6.79	24.63	13.98	2.12	3.07
8000.00	8031.00	7.56	26.32	10.64	2.67	2.95

Electrical Schematic



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Mini-Circuits®

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

SIM-83+
CONVERSION LOSS



SIM-83+
CONVERSION LOSS VARIABLE IF



SIM-83+
L-R ISOLATION



SIM-83+
L-I ISOLATION



SIM-83+
RF VSWR



SIM-83+
LO VSWR



SIM-83+
IF VSWR



SIM-83+
IP3



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Frequency Mixer SIM-83+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB) @LO (dBm)		
		+4	+7	+10
1500.1	1530.1	18.18	11.14	7.84
1680.1	1710.1	13.70	8.72	6.85
1860.1	1890.1	10.82	7.92	6.71
2040.1	2070.1	9.15	7.43	6.67
2220.1	2250.1	7.57	6.62	6.20
2400.1	2430.1	6.94	6.49	6.20
2580.1	2610.1	6.77	6.56	6.45
2760.1	2790.1	6.62	6.33	6.20
2940.1	2970.1	6.53	6.28	6.19
3120.1	3150.1	6.52	6.22	6.06
3300.1	3330.1	6.57	6.22	6.08
3480.1	3510.1	6.58	6.19	6.03
3660.1	3690.1	6.25	5.96	5.86
3840.1	3870.1	6.19	5.98	5.90
4020.1	4050.1	6.08	5.89	5.81
4200.1	4230.1	6.07	5.81	5.67
4380.1	4410.1	5.88	5.61	5.50
4560.1	4590.1	5.71	5.47	5.36
4720.1	4750.1	6.05	5.77	5.64
4900.1	4930.1	6.54	6.05	5.74
5060.1	5090.1	6.58	6.11	5.82
5240.1	5270.1	6.23	5.83	5.62
5400.1	5430.1	5.95	5.57	5.37
5580.1	5610.1	5.82	5.40	5.23
5740.1	5770.1	5.95	5.46	5.30
5920.1	5950.1	5.78	5.40	5.30
6080.1	6110.1	5.89	5.41	5.29
6260.1	6290.1	5.91	5.51	5.40
6420.1	6450.1	6.04	5.65	5.51
6600.1	6630.1	6.12	5.77	5.58
6760.1	6790.1	5.94	5.66	5.56
6940.1	6970.1	5.82	5.62	5.58
7100.1	7130.1	5.95	5.73	5.68
7280.1	7310.1	6.02	5.72	5.65
7440.1	7470.1	6.59	6.08	5.85
7620.1	7650.1	7.09	6.29	5.96
7780.1	7810.1	7.40	6.46	6.13
7960.1	7990.1	8.07	6.87	6.68
8120.1	8150.1	8.45	7.74	8.19
8300.1	8330.1	11.16	10.87	10.66

RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm) @LO (dBm)		
		+4	+7	+10
1500.1	1530.1	-6.78	0.75	7.25
1680.1	1710.1	-4.36	0.64	4.59
1860.1	1890.1	-1.82	3.43	12.08
2040.1	2070.1	3.06	8.66	12.77
2220.1	2250.1	7.74	11.68	13.07
2400.1	2430.1	9.61	10.66	11.12
2580.1	2610.1	9.76	9.56	9.18
2760.1	2790.1	10.23	10.41	11.18
2940.1	2970.1	12.96	11.63	9.82
3120.1	3150.1	16.47	16.76	14.74
3300.1	3330.1	17.90	16.40	16.90
3480.1	3510.1	12.10	11.49	15.52
3660.1	3690.1	9.89	12.46	16.29
3840.1	3870.1	14.52	18.09	21.05
4020.1	4050.1	16.39	19.82	21.09
4200.1	4230.1	10.89	12.20	12.96
4380.1	4410.1	11.84	12.85	14.54
4560.1	4590.1	14.43	14.53	14.58
4720.1	4750.1	12.80	13.38	14.09
4900.1	4930.1	11.53	10.39	9.77
5060.1	5090.1	8.87	9.36	9.87
5240.1	5270.1	8.30	9.57	9.53
5400.1	5430.1	7.39	9.23	9.66
5580.1	5610.1	6.63	8.78	9.81
5740.1	5770.1	6.38	8.32	9.79
5920.1	5950.1	8.03	8.31	9.99
6080.1	6110.1	8.68	8.67	10.45
6260.1	6290.1	11.07	10.57	11.16
6420.1	6450.1	12.17	11.84	11.79
6600.1	6630.1	10.57	11.15	11.63
6760.1	6790.1	11.08	13.02	13.73
6940.1	6970.1	12.65	14.56	14.70
7100.1	7130.1	11.13	12.82	14.33
7280.1	7310.1	12.95	11.74	13.63
7440.1	7470.1	13.32	13.50	13.27
7620.1	7650.1	8.82	9.66	10.53
7780.1	7810.1	7.45	9.32	7.53
7960.1	7990.1	4.63	6.52	4.76
8120.1	8150.1	1.73	3.90	7.03
8300.1	8330.1	2.59	11.69	16.30

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+1dBm (dB) @LO (dBm)		
		+4	+7	+10
1500.1	1530.1	-3.09	1.03	1.74
1680.1	1710.1	0.02	1.94	1.57
1860.1	1890.1	1.47	1.86	1.60
2040.1	2070.1	1.35	1.63	1.42
2220.1	2250.1	1.78	1.62	1.39
2400.1	2430.1	1.61	1.32	1.11
2580.1	2610.1	1.15	0.92	0.80
2760.1	2790.1	0.89	0.78	0.78
2940.1	2970.1	0.89	0.69	0.62
3120.1	3150.1	0.67	0.52	0.46
3300.1	3330.1	0.55	0.45	0.37
3480.1	3510.1	0.59	0.44	0.29
3660.1	3690.1	0.60	0.29	0.17
3840.1	3870.1	0.54	0.26	0.19
4020.1	4050.1	0.55	0.32	0.23
4200.1	4230.1	0.82	0.54	0.37
4380.1	4410.1	0.78	0.57	0.46
4560.1	4590.1	0.69	0.45	0.33
4720.1	4750.1	1.02	0.71	0.57
4900.1	4930.1	1.35	1.10	0.96
5060.1	5090.1	1.38	1.13	1.00
5240.1	5270.1	1.42	1.24	1.12
5400.1	5430.1	1.37	1.19	1.08
5580.1	5610.1	1.31	1.11	1.02
5740.1	5770.1	1.24	0.96	0.88
5920.1	5950.1	1.14	0.94	0.86
6080.1	6110.1	0.88	0.69	0.61
6260.1	6290.1	0.80	0.66	0.53
6420.1	6450.1	0.83	0.68	0.60
6600.1	6630.1	0.77	0.71	0.74
6760.1	6790.1	0.85	0.76	0.81
6940.1	6970.1	0.81	0.63	0.66
7100.1	7130.1	0.73	0.56	0.60
7280.1	7310.1	0.74	0.47	0.35
7440.1	7470.1	1.03	0.81	0.73
7620.1	7650.1	1.36	1.50	1.72
7780.1	7810.1	1.56	1.60	1.86
7960.1	7990.1	1.68	1.74	1.92
8120.1	8150.1	2.51	1.84	1.35
8300.1	8330.1	2.46	0.96	0.58

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=5150MHz (dB) @LO (dBm) +7
3649.9	1500.1	12.42
3456.1	1693.9	11.62
3262.2	1887.8	9.68
3068.4	2081.6	8.76
2874.5	2275.5	7.98
2680.7	2469.3	6.73
2486.9	2663.1	5.72
2293.0	2857.0	6.27
2099.2	3050.8	7.01
1905.3	3244.7	7.74
1711.5	3438.5	8.53
1517.7	3632.3	7.49
1323.8	3826.2	6.82
1130.0	4020.0	6.43
936.1	4213.9	6.36
742.3	4407.7	6.22
548.4	4601.6	5.99
354.6	4795.4	6.02
182.3	4967.7	5.78
10.0	5160.0	6.33
157.8	5307.8	5.84
324.0	5474.0	5.86
471.8	5621.8	5.85
638.0	5788.0	6.16
785.8	5935.8	6.13
952.0	6102.0	6.44
1099.8	6249.8	6.60
1266.0	6416.0	6.74
1413.8	6563.8	7.08
1580.1	6730.0	7.38
1727.8	6877.8	7.20
1894.1	7044.1	7.29
2041.8	7191.8	7.20
2208.1	7358.1	7.43
2355.8	7505.8	7.52
2522.1	7672.1	7.33
2669.8	7819.8	7.58
2836.1	7986.1	8.10
2983.9	8133.9	9.84
3150.1	8300.1	13.24

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=2190MHz (dB) @LO (dBm) +7
110.1	2300.1	6.36
210.1	2400.1	6.08
310.1	2500.1	6.17
410.1	2600.1	6.21
510.1	2700.1	6.17
610.1	2800.1	6.02
710.1	2900.1	6.02
810.1	3000.1	5.98
910.1	3100.1	6.08
1010.1	3200.1	6.21
1110.1	3300.1	6.52
1210.1	3400.1	7.00
1310.1	3500.1	7.21
1410.1	3600.1	7.08
1510.1	3700.1	7.08
1610.1	3800.1	7.36
1710.1	3900.1	7.22
1810.1	4000.1	7.11
1910.1	4100.1	7.05
2010.1	4200.1	7.16
2110.1	4300.1	7.28
2210.1	4400.1	7.49
2310.1	4500.1	7.51
2410.1	4600.1	7.56
2510.1	4700.1	7.70
2610.1	4800.1	7.81
2710.1	4900.1	7.97
2810.1	5000.1	8.04
2910.1	5100.1	7.96
3010.1	5200.1	7.83
3090.1	5280.1	7.80
3190.1	5380.1	7.52
3270.1	5460.1	7.72
3370.1	5560.1	7.92
3450.1	5640.1	8.09
3550.1	5740.1	8.25
3630.1	5820.1	8.63
3730.1	5920.1	9.11
3810.1	6000.1	9.72
3910.1	6100.1	10.66

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=8010.1MHz (dB) @LO (dBm) +7
3710.0	4300.1	10.48
3610.0	4400.1	9.79
3510.0	4500.1	9.09
3410.0	4600.1	8.24
3310.0	4700.1	8.15
3210.0	4800.1	8.08
3110.0	4900.1	8.04
3010.0	5000.1	8.09
2910.0	5100.1	8.08
2810.0	5200.1	8.10
2710.0	5300.1	8.07
2610.0	5400.1	7.81
2510.0	5500.1	7.55
2410.0	5600.1	7.43
2310.0	5700.1	7.45
2210.0	5800.1	7.63
2110.0	5900.1	7.82
2010.0	6000.1	7.89
1910.0	6100.1	7.85
1810.0	6200.1	7.80
1730.0	6280.1	7.66
1630.0	6380.1	7.47
1550.0	6460.1	7.41
1450.0	6560.1	7.25
1370.0	6640.1	7.22
1270.0	6740.1	7.12
1190.0	6820.1	6.92
1090.0	6920.1	6.91
1010.0	7000.1	6.78
910.0	7100.1	6.75
830.0	7180.1	6.74
730.0	7280.1	6.71
650.0	7360.1	6.62
550.0	7460.1	6.51
470.0	7540.1	6.41
370.0	7640.1	6.11
290.0	7720.1	6.14
190.0	7820.1	6.30
110.0	7900.1	6.52
10.0	8000.1	7.14

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB) @LO (dBm)			LO-IF ISOLATION (dB) @LO (dBm)		
	+4	+7	+10	+4	+7	+10
1530.1	48.75	42.90	36.95	21.84	22.22	22.83
1710.1	45.22	40.77	35.63	19.81	20.08	21.37
1890.1	37.62	33.70	31.76	17.96	19.22	21.21
2070.1	33.05	32.03	31.95	17.19	19.24	21.33
2250.1	34.66	34.58	34.80	17.74	19.97	22.13
2430.1	37.35	37.62	37.29	18.80	21.27	23.38
2610.1	38.73	37.99	36.80	20.30	22.54	24.03
2790.1	33.32	32.63	31.77	21.65	23.19	23.24
2970.1	32.09	30.28	29.08	22.34	23.37	23.26
3150.1	30.84	29.37	28.03	23.88	23.84	22.29
3330.1	31.01	28.95	27.61	26.19	24.48	22.91
3510.1	31.15	29.29	27.86	26.98	24.29	22.75
3690.1	30.98	29.05	27.85	27.74	25.22	23.85
3870.1	31.21	29.54	28.61	30.14	27.94	26.94
4050.1	31.91	30.82	29.47	32.70	32.69	32.25
4230.1	29.68	29.14	28.52	30.63	31.31	31.74
4410.1	28.42	27.95	27.75	24.16	23.21	22.79
4590.1	27.34	26.79	26.65	19.00	18.21	17.97
4750.1	27.42	27.03	26.95	16.56	16.12	16.04
4930.1	26.74	26.51	26.39	15.72	15.69	15.69
5090.1	25.94	25.50	25.42	15.92	16.05	16.33
5270.1	24.87	24.55	24.30	16.39	16.95	17.35
5430.1	23.94	23.59	23.30	17.02	17.91	18.57
5610.1	23.49	22.83	22.34	18.09	19.23	20.19
5770.1	23.33	22.09	21.40	19.29	20.59	21.93
5950.1	22.34	21.62	20.67	20.67	22.41	24.13
6110.1	21.80	20.58	19.73	22.60	24.40	26.30
6290.1	20.99	19.93	18.76	24.88	27.11	29.24
6450.1	20.59	19.76	18.68	25.84	26.31	26.68
6630.1	20.07	19.50	18.62	26.35	25.33	24.59
6790.1	19.92	19.83	19.00	28.42	27.20	26.12
6970.1	19.51	19.30	19.17	34.37	33.17	32.26
7130.1	18.71	19.16	19.16	28.39	28.59	28.68
7310.1	19.08	19.60	19.40	22.35	21.89	21.41
7470.1	19.50	20.09	20.35	18.86	18.42	18.11
7650.1	20.27	20.75	21.16	18.68	18.54	18.64
7810.1	20.07	20.56	21.02	15.75	15.19	15.40
7990.1	21.19	21.58	22.01	12.55	11.56	12.01
8150.1	23.19	23.54	23.48	10.18	9.17	9.69
8330.1	24.22	23.28	23.20	8.27	7.91	8.15

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB) @LO (dBm)		
		+4	+7	+10
1500.1	1530.1	21.65	26.43	39.20
1679.8	1709.8	20.20	18.75	13.81
1859.6	1889.6	16.45	12.12	10.22
2039.3	2069.3	12.86	11.11	10.40
2219.0	2249.0	13.42	12.09	11.48
2398.8	2428.8	15.37	14.36	13.70
2578.5	2608.5	18.12	17.51	17.15
2758.3	2788.3	19.77	19.20	18.98
2938.0	2968.0	20.95	20.73	20.39
3117.7	3147.7	21.67	21.55	20.93
3297.5	3327.5	21.24	20.94	20.51
3477.2	3507.2	20.31	19.78	19.32
3656.9	3686.9	20.10	19.74	19.28
3836.7	3866.7	20.36	20.14	19.93
4016.4	4046.4	20.99	20.79	20.58
4196.2	4226.2	23.38	23.03	22.74
4375.9	4405.9	28.08	27.40	26.83
4555.6	4585.6	31.93	31.25	30.58
4735.4	4765.4	34.67	34.19	33.99
4915.1	4945.1	30.51	30.11	29.87
5094.8	5124.8	27.18	27.04	26.86
5274.6	5304.6	24.45	24.15	23.94
5434.3	5464.3	23.57	23.23	23.05
5614.1	5644.1	22.93	22.65	22.40
5773.8	5803.8	22.82	22.42	22.32
5953.6	5983.6	23.99	23.07	22.58
6113.3	6143.3	24.04	23.47	22.99
6293.1	6323.1	22.10	21.05	20.49
6452.8	6482.8	24.73	23.19	22.24
6632.6	6662.6	29.18	27.87	26.86
6792.4	6822.4	31.42	29.81	28.71
6972.1	7002.1	37.73	35.23	33.27
7131.9	7161.9	47.21	46.45	38.07
7311.6	7341.6	39.61	38.66	34.28
7471.4	7501.4	29.70	28.29	28.29
7651.1	7681.1	24.60	25.60	25.43
7810.9	7840.9	26.75	28.79	29.26
7990.6	8020.6	24.14	27.85	29.92
8150.4	8180.4	22.63	26.47	27.09
8330.1	8360.1	24.84	25.93	24.45

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1) @LO (dBm)		
		+4	+7	+10
1500.1	1530.1	7.17	3.89	2.67
1679.8	1709.8	3.98	2.45	1.90
1859.6	1889.6	2.82	1.84	1.44
2039.3	2069.3	2.56	2.00	1.75
2219.0	2249.0	2.71	2.33	2.15
2398.8	2428.8	3.02	2.83	2.69
2578.5	2608.5	3.23	3.14	3.09
2758.3	2788.3	3.34	3.17	3.08
2938.0	2968.0	3.43	3.17	3.02
3117.7	3147.7	3.48	3.18	2.92
3297.5	3327.5	3.40	3.07	2.82
3477.2	3507.2	2.97	2.54	2.30
3656.9	3686.9	2.53	2.28	2.11
3836.7	3866.7	2.46	2.25	2.12
4016.4	4046.4	2.48	2.29	2.15
4196.2	4226.2	2.74	2.53	2.36
4375.9	4405.9	2.66	2.39	2.23
4555.6	4585.6	2.18	1.95	1.79
4735.4	4765.4	2.33	2.14	2.02
4915.1	4945.1	2.87	2.62	2.42
5094.8	5124.8	2.78	2.56	2.39
5274.6	5304.6	2.55	2.35	2.19
5434.3	5464.3	2.47	2.24	2.10
5614.1	5644.1	2.33	2.11	1.99
5773.8	5803.8	2.26	2.05	1.95
5953.6	5983.6	2.18	1.92	1.84
6113.3	6143.3	2.21	1.95	1.83
6293.1	6323.1	2.20	1.97	1.83
6452.8	6482.8	2.27	2.03	1.87
6632.6	6662.6	2.32	2.13	1.98
6792.4	6822.4	2.15	2.00	1.90
6972.1	7002.1	2.10	1.99	1.92
7131.9	7161.9	2.12	2.02	1.97
7311.6	7341.6	1.95	1.75	1.66
7471.4	7501.4	2.45	2.07	1.85
7651.1	7681.1	2.92	2.52	2.29
7810.9	7840.9	3.00	2.56	2.31
7990.6	8020.6	3.11	2.56	2.29
8150.4	8180.4	2.87	2.31	2.22
8330.1	8360.1	2.54	2.54	2.56

LO (MHz)	LO VSWR (:1) @LO (dBm)		
	+4	+7	+10
1530.1	31.60	28.03	22.00
1710.1	26.74	22.58	15.00
1890.1	19.11	11.85	8.51
2070.1	8.99	6.26	6.03
2250.1	4.72	4.26	4.63
2430.1	2.96	3.06	3.63
2610.1	2.15	2.40	3.00
2790.1	1.81	2.08	2.65
2970.1	1.81	2.02	2.53
3150.1	1.81	2.02	2.52
3330.1	1.85	2.10	2.61
3510.1	2.07	2.30	2.76
3690.1	2.05	2.26	2.78
3870.1	1.93	2.30	2.91
4050.1	1.93	2.47	3.18
4230.1	1.90	2.57	3.40
4410.1	1.99	2.74	3.63
4590.1	2.09	2.86	3.75
4750.1	2.17	2.88	3.71
4930.1	2.35	2.97	3.73
5090.1	2.53	3.08	3.81
5270.1	2.79	3.10	3.67
5430.1	3.04	3.17	3.61
5610.1	3.23	3.11	3.40
5770.1	3.31	2.95	3.04
5950.1	3.09	2.57	2.51
6110.1	2.70	2.18	2.05
6290.1	2.17	1.69	1.59
6450.1	1.77	1.32	1.35
6630.1	1.32	1.10	1.45
6790.1	1.08	1.34	1.78
6970.1	1.18	1.64	2.17
7130.1	1.58	1.97	2.51
7310.1	2.15	2.45	2.94
7470.1	2.65	2.87	3.29
7650.1	3.27	3.30	3.66
7810.1	4.00	3.63	3.81
7990.1	4.21	3.60	3.60
8150.1	3.70	3.26	3.28
8330.1	2.85	2.82	2.80

IF (OUT) (MHz)	IF VSWR @LO=8000MHz (:1) @LO (dBm)		
	+4	+7	+10
10.0	1.51	1.05	1.24
89.8	1.51	1.11	1.27
169.5	1.54	1.17	1.31
269.3	1.69	1.31	1.37
349.0	1.80	1.42	1.44
448.7	2.02	1.57	1.51
528.5	2.21	1.69	1.58
628.2	2.46	1.87	1.68
708.0	2.66	2.00	1.78
807.7	2.95	2.19	1.92
887.5	3.15	2.34	2.03
987.2	3.51	2.58	2.20
1067.0	3.75	2.75	2.33
1166.7	3.99	2.92	2.44
1246.5	4.15	3.03	2.53
1346.2	4.32	3.09	2.55
1425.9	4.51	3.21	2.66
1525.7	4.73	3.29	2.70
1605.4	4.92	3.40	2.77
1705.1	5.07	3.46	2.78
1784.9	5.30	3.64	2.89
1884.6	5.51	3.71	2.92
1964.4	5.63	3.79	2.97
2064.1	5.66	3.79	2.94
2143.9	5.63	3.76	2.93
2243.6	5.51	3.69	2.86
2323.4	5.38	3.60	2.80
2423.1	5.14	3.48	2.72
2502.9	4.98	3.39	2.69
2602.6	4.67	3.23	2.61
2682.3	4.39	3.10	2.57
2782.1	4.15	3.00	2.55
2861.8	3.88	2.94	2.60
2961.5	3.79	2.96	2.70
3041.3	3.58	2.94	2.80
3141.0	3.53	3.04	3.04
3220.8	3.27	3.02	3.18
3320.5	3.24	3.24	3.60
3400.3	3.13	3.42	3.96
3500.0	3.18	3.80	4.59

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Harmonics Tables

RF HARMONICS ORDER	(-dBm)	(-dBc)										
0	-	-	+11	11	18	27	---	---	---	---	---	---
1	-	20	+0	35	20	33	45	---	---	---	---	---
2	>90	51	55	51	51	53	51	>70	---	---	---	---
3	>90	57	55	>70	57	>70	>70	64	>70	---	---	---
4	>90	>70	>70	>70	>70	>70	>70	>70	>70	>70	---	---
5	---	---	>70	>70	>70	>70	>70	>70	>70	>70	>70	---
6	---	---	---	>70	>70	>70	>70	>70	>70	>70	>70	>70
7	---	---	---	---	>70	>70	>70	>70	>70	>70	>70	>70
8	---	---	---	---	---	>70	>70	>70	>70	>70	>70	>70
9	---	---	---	---	---	---	>70	>70	>70	>70	>70	>70
10	---	---	---	---	---	---	---	>70	>70	>70	>70	>70
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

Test conditions: RF IN: 5150 MHz; -14.00 dBm.
LO IN: 5180 MHz; +7.00 dBm
IF OUT: 30 MHz; -20.15 dBm

RF HARMONICS ORDER	(-dBm)	(-dBc)										
0	-	-	+1	20	28	39	---	---	---	---	---	---
1	-	19	+0	36	20	39	47	---	---	---	---	---
2	71	42	45	38	42	55	45	59	---	---	---	---
3	>90	36	34	60	35	60	53	49	59	---	---	---
4	>90	68	58	54	66	50	63	58	58	71	---	---
5	---	---	77	65	60	76	56	>80	68	63	76	---
6	---	---	---	>80	>80	70	>80	63	79	71	70	>80
7	---	---	---	---	>80	>80	78	>80	71	>80	78	76
8	---	---	---	---	---	>80	>80	>80	>80	74	>80	>80
9	---	---	---	---	---	---	>80	>80	>80	>80	>80	>80
10	---	---	---	---	---	---	---	>80	>80	>80	>80	>80
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 5150 MHz; -4.00 dBm.
LO IN: 5180 MHz; +7.00 dBm
IF OUT: 30 MHz; -10.12 dBm

Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Curves

Conversion Loss @ IF=30MHz



Conversion Loss vs. LO @ RF=5150MHz



Conversion Loss vs. IF @ RF=5150MHz



Conversion Loss vs. IF @ RF=2190MHz



Conversion Loss vs. IF @ RF=8010.1MHz



IP3 Input



Compression @ RF IN=+1dBm



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Typical Performance Curves

LO-RF Isolation



LO-IF Isolation



RF-IF Isolation



RF VSWR



LO VSWR



IF VSWR



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Harmonics Tables

RF HARMONICS ORDER	(-dBm)	(-dBc)										
0	-	-	+11	11	18	27	---	---	---	---	---	---
1	-	20	+0	35	20	33	45	---	---	---	---	---
2	>90	51	55	51	51	53	51	>70	---	---	---	---
3	>90	57	55	>70	57	>70	>70	64	>70	---	---	---
4	>90	>70	>70	>70	>70	>70	>70	>70	>70	>70	---	---
5	---	---	>70	>70	>70	>70	>70	>70	>70	>70	>70	---
6	---	---	---	>70	>70	>70	>70	>70	>70	>70	>70	>70
7	---	---	---	---	>70	>70	>70	>70	>70	>70	>70	>70
8	---	---	---	---	---	>70	>70	>70	>70	>70	>70	>70
9	---	---	---	---	---	---	>70	>70	>70	>70	>70	>70
10	---	---	---	---	---	---	---	>70	>70	>70	>70	>70
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

Test conditions: RF IN: 5150 MHz; -14.00 dBm.
LO IN: 5180 MHz; +7.00 dBm
IF OUT: 30 MHz; -20.15 dBm

RF HARMONICS ORDER	(-dBm)	(-dBc)										
0	-	-	+1	20	28	39	---	---	---	---	---	---
1	-	19	+0	36	20	39	47	---	---	---	---	---
2	71	42	45	38	42	55	45	59	---	---	---	---
3	>90	36	34	60	35	60	53	49	59	---	---	---
4	>90	68	58	54	66	50	63	58	58	71	---	---
5	---	---	77	65	60	76	56	>80	68	63	76	---
6	---	---	---	>80	>80	70	>80	63	79	71	70	>80
7	---	---	---	---	>80	>80	78	>80	71	>80	78	76
8	---	---	---	---	---	>80	>80	>80	>80	74	>80	>80
9	---	---	---	---	---	---	>80	>80	>80	>80	>80	>80
10	---	---	---	---	---	---	---	>80	>80	>80	>80	>80
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 5150 MHz; -4.00 dBm.
LO IN: 5180 MHz; +7.00 dBm
IF OUT: 30 MHz; -10.12 dBm

Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style HV

Outline Dimensions

HV1195



PCB Metal Land Pattern



Suggested Layout,
Tolerance to be within ±.002

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
HV1195	0.200 (5.08)	0.180 (4.57)	0.087 (2.21)	0.025 (0.64)	0.050 (1.27)	0.028 (0.71)	0.043 (1.09)	0.050 (1.27)	0.030 (0.76)	0.043 (1.09)	0.204 (5.18)	0.127 (3.23)	0.065 (1.65)

CASE#	WT, GRAM
HV1195	.08

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .01; 3 Pl. ± .005

Notes:

1. Case material: Plastic encapsulation on Ceramic base.
2. Termination finish: Palladium Silver.

This document and its contents are the property of Mini-Circuits.

Tape & Reel Packaging TR-F82

DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
12	8	7	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits.

THIRD ANGLE PROJECTION

REVISIONS					
REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M104559	NEW RELEASE	04/11/06	MMG	DJ
A	M109513	MODIFIED SMOBC AREA, REMOVED NOTE 3	01/31/07	PW	DJ
B	M176274	MODIFIED CASE STYLE	09/23/19	ITG	RB

SUGGESTED MOUNTING CONFIGURATION FOR HV1195 CASE STYLE, "rh" PIN CONNECTION



NOTES:

1. TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .020"±.0015"; COPPER: 1/2 OZ. EACH SIDE.
   FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.

DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN	MMG	04/10/06
TOLERANCES ON:	CHECKED	IL	04/11/06
2 PL DECIMALS ±	APPROVED	DJ	04/11/06
3 PL DECIMALS ± .005			
ANGLES ±			
FRACTIONS ±			

Mini-Circuits®
THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE , MANUFACTURING AND REPRODUCTION RIGHTS THERETO.
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235

PL, rh, HV1195, SIM, TB-382

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-239	B

FILE:	SCALE:	SHEET:
98PL239	10:1	1 OF 1

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



TB-382



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers RO4350 or equivalent, Dielectric Constant=3.5, Thickness=.020 inch.

Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.

Mini-Circuits

Environmental Specifications ENV10T1

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Case Temperature	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215

This document and its contents are the property of Mini-Circuits.