

2 Way-0° 50Ω 680 to 6000 MHz

The Big Deal

- >3 octave bandwidth, 680 to 6000 MHz
- Low insertion loss, 1.0 dB
- Small size, 1.25 x 1.0 x 0.2"



CASE STYLE: JF1258

Product Overview

Mini-Circuits' SEPS-2-63+ is a 50Ω 2-way 0° surface mount splitter/combiner covering the 680 to 6000 MHz frequency range, supporting a wide variety of applications. This model can handle up to 5W RF input power as a splitter and provides low insertion loss, low phase and amplitude unbalance, and good isolation. Housed in a miniature, shielded package (1.25 x 1.0 x 0.2") with wrap-around terminations this unit interfaces with gold over nickel plate termination finish.

Key Features

Feature	Advantages
Wideband, 680 to 6000 MHz	>3 octave bandwidth supports a wide range of broadband applications.
Low insertion loss, 1.0 dB	The combination of 5W power handling and low insertion loss makes this model a suitable candidate for distributing signals while maintaining signal power.
Low unbalance: • 0.2 dB amplitude unbalance • 1.5° phase unbalance	SEPS-2-63+ produces nearly equal output signals, ideal for parallel path / multichannel systems.
Good isolation, 22 dB	Minimizes interference between input ports.
Good output matching VSWR, 1.3:1 typ.	Provides excellent thru-path transmission with low signal reflection.
Small size, 1.25 x 1.0 x 0.2"	Saves space in crowded PCB layouts.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



2 Way-0° 50Ω 680 to 6000 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	5W max.
Internal Dissipation	0.4W max.
DC Current	1.5A (750 mA for each port)

Permanent damage may occur if any of these limits are exceeded.

Pin Connections


SUM PORT	17
PORT 1	4
PORT 2	8
GROUND	all others

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
1.250	1.000	.200	.125	.100	.060	.040
31.75	25.40	5.08	3.18	2.54	1.52	1.02
H	J	K	L	M	wt	
--	--	.050	.060	.920	grams	
--	--	1.27	1.52	23.37	4.4	

Demo Board MCL P/N: TB-760+
Suggested PCB Layout (PL-402)

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Features

- wideband 680-6000 MHz
- good output matching, VSWR 1.3 typ.
- excellent amplitude unbalance, 0.2 dB typ.

Applications

- SATCOM
- broadband wireless
- test and measurement
- wireless telecom



Generic photo used for illustration purposes only

CASE STYLE: JF1258


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		680		6000	MHz
Insertion Loss Above 3.0 dB	680 - 1200	—	0.6	1.0	
	1200 - 5000	—	0.8	1.5	dB
	5000 - 6000	—	1.0	2.5	
Isolation	680 - 1200	10	17.0	—	dB
	1200 - 6000	17	22.0	—	
Phase Unbalance	680 - 1200	—	0.3	2.0	Degree
	1200 - 6000	—	1.5	5.0	
Amplitude Unbalance	680 - 1200	—	0.1	0.4	dB
	1200 - 6000	—	0.2	0.6	
VSWR (Port S)	680 - 1200	—	1.6	2.0	
	1200 - 6000	—	1.5	1.82	:1
VSWR (Port 1-2)	680 - 6000	—	1.3	1.6	:1




Electrical Schematic



Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
680	3.47	3.43	0.04	11.58	0.27	1.75	1.18	1.15
700	3.46	3.42	0.04	11.91	0.26	1.74	1.17	1.15
800	3.43	3.37	0.05	13.63	0.18	1.67	1.18	1.16
900	3.39	3.32	0.07	15.47	0.10	1.59	1.19	1.19
1000	3.35	3.28	0.07	17.43	0.01	1.51	1.20	1.21
1500	3.22	3.17	0.04	23.19	0.01	1.14	1.14	1.17
2000	3.24	3.21	0.04	20.82	0.01	1.16	1.03	1.01
2500	3.37	3.31	0.06	23.43	0.21	1.34	1.14	1.18
3000	3.49	3.44	0.06	24.53	0.12	1.42	1.28	1.33
3500	3.38	3.37	0.01	22.04	0.18	1.23	1.21	1.23
4000	3.44	3.37	0.07	23.97	0.36	1.14	1.06	1.09
4500	3.66	3.57	0.09	30.87	0.11	1.34	1.19	1.24
5000	3.67	3.69	0.02	21.15	0.12	1.36	1.18	1.22
5500	4.08	4.03	0.05	21.83	0.41	1.26	1.13	1.19
6000	4.71	4.61	0.10	28.30	0.21	1.61	1.32	1.31

1. Total Loss = Insertion Loss + 3dB splitter theoretical loss.



Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

2 Way-0° Power Splitter/Combiner

SEPS-2-63+

Typical Performance Data

FREQUENCY	TOTAL LOSS ¹		AMPLITUDE UNBALANCE	ISOLATION	PHASE UNBALANCE	FREQUENCY	VSWR		
(MHz)	(dB)		(dB)	(dB)	(deg.)	(MHz)	(:1)		
	S-1	S-2		1-2			S	1	2
600	3.49	3.47	0.03	10.29	0.30	600	1.80	1.20	1.18
620	3.49	3.46	0.03	10.62	0.28	620	1.79	1.19	1.17
640	3.48	3.45	0.03	10.94	0.29	640	1.78	1.18	1.16
660	3.47	3.44	0.04	11.25	0.27	660	1.76	1.18	1.15
680	3.47	3.43	0.04	11.58	0.27	680	1.75	1.18	1.15
700	3.46	3.42	0.04	11.91	0.26	700	1.74	1.17	1.15
750	3.45	3.40	0.05	12.75	0.21	750	1.71	1.17	1.15
800	3.43	3.37	0.05	13.63	0.18	800	1.67	1.18	1.16
850	3.41	3.35	0.06	14.54	0.13	850	1.63	1.18	1.17
900	3.39	3.32	0.07	15.47	0.10	900	1.59	1.19	1.19
950	3.37	3.30	0.07	16.44	0.04	950	1.55	1.20	1.20
1000	3.35	3.28	0.07	17.43	0.01	1000	1.51	1.20	1.21
1200	3.27	3.22	0.06	21.37	0.08	1200	1.33	1.20	1.23
1400	3.23	3.18	0.05	23.41	0.02	1400	1.19	1.16	1.19
1500	3.22	3.17	0.04	23.19	0.01	1500	1.14	1.14	1.17
2000	3.24	3.21	0.04	20.82	0.01	2000	1.16	1.03	1.01
2200	3.28	3.24	0.04	21.19	0.09	2200	1.22	1.02	1.06
2400	3.33	3.28	0.05	22.51	0.19	2400	1.29	1.10	1.13
2500	3.37	3.31	0.06	23.43	0.21	2500	1.34	1.14	1.18
2600	3.41	3.34	0.07	24.39	0.23	2600	1.38	1.18	1.22
2800	3.47	3.39	0.07	25.33	0.23	2800	1.43	1.24	1.29
3000	3.49	3.44	0.06	24.53	0.12	3000	1.42	1.28	1.33
3200	3.45	3.42	0.03	23.26	0.12	3200	1.37	1.27	1.32
3400	3.40	3.39	0.01	22.32	0.14	3400	1.28	1.24	1.27
3500	3.38	3.37	0.01	22.04	0.18	3500	1.23	1.21	1.23
3600	3.37	3.36	0.01	21.89	0.24	3600	1.18	1.17	1.18
3800	3.39	3.35	0.04	22.26	0.32	3800	1.12	1.09	1.09
4000	3.44	3.37	0.07	23.97	0.36	4000	1.14	1.06	1.09
4100	3.49	3.40	0.09	25.72	0.35	4100	1.17	1.08	1.13
4200	3.52	3.43	0.09	28.32	0.30	4200	1.21	1.12	1.16
4300	3.56	3.46	0.10	31.78	0.23	4300	1.25	1.15	1.20
4400	3.62	3.52	0.10	33.63	0.17	4400	1.30	1.17	1.22
4500	3.66	3.57	0.09	30.87	0.11	4500	1.34	1.19	1.24
4600	3.70	3.63	0.07	27.58	0.07	4600	1.37	1.21	1.26
4700	3.75	3.70	0.05	25.25	0.04	4700	1.39	1.21	1.26
4800	3.80	3.77	0.03	23.51	0.12	4800	1.40	1.22	1.26
4900	3.73	3.74	0.01	21.93	0.16	4900	1.42	1.21	1.25
5000	3.67	3.69	0.02	21.15	0.12	5000	1.36	1.18	1.22
5100	3.67	3.68	0.01	20.81	0.22	5100	1.27	1.15	1.18
5200	3.72	3.72	0.00	20.67	0.36	5200	1.17	1.12	1.14
5300	3.84	3.83	0.01	20.68	0.48	5300	1.06	1.08	1.12
5400	4.07	4.05	0.03	20.70	0.50	5400	1.10	1.05	1.12
5500	4.08	4.03	0.05	21.83	0.41	5500	1.26	1.13	1.19
5600	3.95	3.86	0.09	24.67	0.29	5600	1.33	1.22	1.28
5700	3.95	3.84	0.11	28.85	0.21	5700	1.38	1.28	1.34
5800	4.05	3.93	0.13	33.97	0.12	5800	1.41	1.33	1.37
5900	4.27	4.14	0.12	32.45	0.00	5900	1.45	1.34	1.35
6000	4.71	4.61	0.10	28.30	0.21	6000	1.61	1.32	1.31
6100	5.55	5.48	0.07	28.39	0.47	6100	1.96	1.31	1.30

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com






IF/RF MICROWAVE COMPONENTS

REV. OR
 SEPS-2-63+
 7/25/2016
 Page 1 of 1

2 Way-0° Power Splitter/Combiner

SEPS-2-63+

Typical Performance Curves



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS




REV. OR
SEPS-2-63+
7/25/2016
Page 1 of 1

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAM
JF1258	1.250 (31.75)	1.000 (25.40)	.200 (5.08)	.125 (3.17)	.100 (2.54)	.060 (1.52)	.040 (1.02)	-	-	.050 (1.27)	.060 (1.52)	.920 (23.37)	4.4

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
For RoHS Case Styles: 3-5 μ inch (.08-.13 μ m) Gold over 120-240 μ inch (3-6 μ m) Nickel plate.
All models, (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F27



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
44	32	13	125

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



REVISIONS					
REV OR	ECN No.	DESCRIPTION	DATE	DR	AUTH
	M147511	NEW RELEASE	07/28/14	GF	JC

SUGGESTED MOUNTING CONFIGURATION FOR
JF1258 CASE STYLE, "22SP03" PIN CONNECTION



- NOTE: 1. TRACE WIDTH IS SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .030" $\pm$.002"; COPPER: 1/2 OZ. EACH SIDE.
 FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
 2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005 ANGLES $\pm$ FRACTIONS $\pm$	DRAWN	GF	07/22/14
	CHECKED	ITG	07/28/14
	APPROVED	JC	07/28/14





Mini-Circuits® 13 Neptune Avenue
 Brooklyn NY 11235

PL, 22SP03, JF1258, TB-760+

Mini-Circuits® THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.	
ASHEETA1.DWG REV:A	DATE:01/12/95

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-402	OR
FILE:	98PL402	SCALE:	SHEET:
		3:1	1 OF 1

Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent, Dielectric Constant=3.5, Thickness=.030 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutetic Process: 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215