

Frequency Mixer WIDE BAND

Level 13 (LO Power +13 dBm) 7300 to 20000 MHz

SIM-24MH+



Generic photo used for illustration purposes only

CASE STYLE: HV1195


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
For extended temperature range, consult factory.	
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

LO	8
RF	4
IF	2
GROUND	1,3,5,6,7

Outline Drawing




PCB Metal Land Pattern

Suggested Layout,
Tolerance to be within .002

Outline Dimensions (inch)

A	B	C	D	E	F	G
.200	.180	.087	.025	.050	.028	.043
5.08	4.57	2.2098	0.64	1.27	0.71	1.09
H	J	K	L	M	N	wt
.050	.030	.043	.204	.127	0.065	grams
1.27	0.76	1.09	5.18	3.23	1.65	0.08

Demo Board MCL P/N: TB-458+ Suggested PCB Layout (PL-284)



- NOTES:
- TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .0028±.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 - COPLANAR WAVEGUIDE: .038 LINE WIDTH & .015 GAP, 3 PL. (SEE NOTE BELOW)
 - PACKAGE OUTLINE
 - PIN 1
 - #.013 PTH FOR GROUND
 - DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Features

- wide bandwidth, 7300 to 20000 MHz
- low conversion loss, 5.7 dB typ.
- high L-R isolation, 36 dB typ.
- excellent IF BW, DC to 7500 MHz
- LTCC double balanced mixer
- tiny size, low profile, 0.08"
- useable as up and down converter
- aqueous washable
- protected under U.S. Patent 7,027,795

Applications

- fixed satellite
- mobile
- radio location

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS* (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)
LO/RF f_L - f_U	IF	Typ.	σ	Max.	Typ.	Min.	Typ.	Min.	Typ.
7300-20000	DC-7500								
7300-10000		7.0	0.2	8.5	43	31	19	13	20
10000-14500		5.7	0.1	7.5	36	29	18	13	16
14500-18000		7.6	0.3	9.3	26	19	15	10	18
18000-20000		8.5	0.3	10.9	28	22	25	16	25


1 dB COMPR. +9 dBm typ.

* Conversion loss at 30 MHz IF. σ is a measure of repeatability from unit to unit.

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm
7300.00	7330.10	6.65	43.77	18.89	3.94	6.09
7500.00	7530.10	6.32	39.57	19.63	3.47	8.37
8000.00	8030.10	6.12	35.84	20.35	2.76	4.99
9000.00	9030.10	7.38	48.14	19.20	4.81	2.76
9500.00	9530.10	7.00	48.23	17.30	3.84	2.56
10000.00	10030.10	6.73	45.78	16.83	3.38	2.62
10500.00	10530.10	6.29	42.22	17.92	3.17	3.22
11000.00	11030.10	5.93	40.36	19.17	2.35	2.25
12000.00	12030.10	5.84	35.97	18.67	1.99	3.49
12500.00	12530.10	5.55	34.02	18.08	1.92	2.31
13000.00	13030.10	5.70	33.28	18.18	1.48	2.28
14000.00	14030.10	5.74	34.81	19.35	1.87	2.77
14500.00	14530.10	6.21	36.04	21.54	2.52	3.07
15000.00	15030.10	6.80	35.11	28.80	2.98	4.28
15500.00	15530.10	6.92	31.74	22.63	2.49	3.20
16000.00	16030.10	7.08	27.52	16.03	2.47	2.97
17000.00	17030.10	7.94	26.56	15.86	4.43	1.25
18000.00	18030.10	8.16	29.19	24.93	2.49	1.99
19000.00	19030.10	7.75	31.50	28.10	3.12	2.04
20000.00	20030.10	9.60	26.59	22.49	2.54	1.27

Electrical Schematic











Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp


www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

 REV. C
 ECO-000060
 SIM-24MH+
 ED-13229/1
 DJ/CP/AM
 200821



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)		
		@LO (dBm)		
		+10	+13	+16
7020.0	7050.0	11.26	7.15	6.57
7080.0	7110.0	8.25	6.70	6.39
7140.0	7170.0	8.54	6.70	6.36
7180.0	7210.0	7.70	6.68	6.43
7540.0	7570.0	6.78	6.36	6.18
7900.0	7930.0	6.88	6.49	6.27
8260.0	8290.0	7.85	7.34	6.94
8620.0	8650.0	8.38	7.61	7.13
8980.0	9010.0	8.58	8.00	7.63
9340.0	9370.0	7.67	7.13	6.84
9700.0	9730.0	7.08	6.50	6.26
10060.0	10090.0	6.96	6.29	6.03
10420.0	10450.0	6.78	6.15	5.86
10780.0	10810.0	6.52	5.95	5.67
11140.0	11170.0	6.52	5.83	5.55
11500.0	11530.0	6.61	5.83	5.46
11860.0	11890.0	6.31	5.62	5.36
12220.0	12250.0	6.42	5.67	5.34
12580.0	12610.0	6.40	5.68	5.37
12940.0	12970.0	6.67	5.99	5.66
13300.0	13330.0	6.46	5.83	5.55
13660.0	13690.0	6.75	6.03	5.77
14020.0	14050.0	7.37	6.43	6.14
14380.0	14410.0	7.57	6.75	6.51
14740.0	14770.0	8.08	6.86	6.58
15100.0	15130.0	9.05	7.26	6.95
15460.0	15490.0	9.52	8.21	7.91
15800.0	15830.0	10.23	8.50	8.15
16160.0	16190.0	10.25	8.49	8.01
16500.0	16530.0	10.34	8.40	7.69
16860.0	16890.0	8.76	8.24	7.98
17200.0	17230.0	8.31	7.88	7.68
17560.0	17590.0	8.64	8.18	7.96
17900.0	17930.0	8.41	7.78	7.55
18260.0	18290.0	8.37	7.85	7.59
18600.0	18630.0	8.97	8.36	8.10
18960.0	18990.0	8.49	8.10	7.88
19300.0	19330.0	8.98	8.65	8.41
19660.0	19690.0	9.88	9.59	9.37
20000.0	20030.0	10.42	10.12	9.90

RF (IN) (MHz)	LO (MHz)	IP-3 INPUT (dBm)		
		@LO (dBm)		
		+10	+13	+16
7020.0	7050.0	7.42	12.10	15.54
7080.0	7110.0	9.68	13.38	16.26
7140.0	7170.0	9.30	13.16	15.85
7180.0	7210.0	10.65	14.29	16.80
7540.0	7570.0	12.87	15.06	16.98
7900.0	7930.0	13.58	14.96	16.26
8260.0	8290.0	19.00	20.08	20.55
8620.0	8650.0	19.70	21.66	23.15
8980.0	9010.0	17.20	17.69	18.67
9340.0	9370.0	19.50	19.64	19.55
9700.0	9730.0	19.14	19.60	19.85
10060.0	10090.0	18.58	18.72	19.41
10420.0	10450.0	17.30	17.71	18.55
10780.0	10810.0	16.38	16.87	17.51
11140.0	11170.0	15.43	16.13	16.58
11500.0	11530.0	14.88	15.42	16.37
11860.0	11890.0	14.63	15.15	16.22
12220.0	12250.0	14.51	14.92	16.34
12580.0	12610.0	13.56	14.23	15.76
12940.0	12970.0	14.09	14.26	16.38
13300.0	13330.0	14.28	14.62	16.10
13660.0	13690.0	13.31	14.59	16.19
14020.0	14050.0	12.81	15.32	17.11
14380.0	14410.0	14.66	17.14	18.04
14740.0	14770.0	14.76	17.69	18.12
15100.0	15130.0	14.76	17.20	18.07
15460.0	15490.0	14.09	16.90	20.46
15800.0	15830.0	12.54	19.01	22.55
16160.0	16190.0	14.14	21.84	24.29
16500.0	16530.0	14.89	26.50	23.01
16860.0	16890.0	17.60	23.02	22.62
17200.0	17230.0	20.98	23.69	25.73
17560.0	17590.0	22.12	23.46	23.01
17900.0	17930.0	18.26	23.18	22.06
18260.0	18290.0	20.40	24.83	23.61
18600.0	18630.0	19.04	25.79	26.98
18960.0	18990.0	22.72	23.65	24.02
19300.0	19330.0	24.75	26.38	27.32
19660.0	19690.0	23.75	24.51	24.18
20000.0	20030.0	30.79	30.94	31.05

RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+9dBm (dB)		
		@LO (dBm)		
		+10	+13	+16
7020.0	7050.0	0.04	2.01	0.92
7080.0	7110.0	2.26	1.81	0.85
7140.0	7170.0	2.70	1.56	0.74
7180.0	7210.0	2.70	1.56	0.74
7540.0	7570.0	2.97	1.35	0.62
7900.0	7930.0	2.15	0.94	0.52
8260.0	8290.0	1.48	0.95	0.69
8620.0	8650.0	0.94	0.64	0.48
8980.0	9010.0	0.69	0.59	0.46
9340.0	9370.0	0.64	0.48	0.40
9700.0	9730.0	0.82	0.56	0.46
10060.0	10090.0	0.79	0.56	0.45
10420.0	10450.0	0.91	0.58	0.45
10780.0	10810.0	0.97	0.61	0.45
11140.0	11170.0	1.21	0.59	0.43
11500.0	11530.0	1.14	0.57	0.39
11860.0	11890.0	1.18	0.67	0.48
12220.0	12250.0	1.24	0.68	0.45
12580.0	12610.0	1.51	0.80	0.55
12940.0	12970.0	0.98	0.52	0.38
13300.0	13330.0	1.19	0.59	0.44
13660.0	13690.0	1.30	0.52	0.37
14020.0	14050.0	1.22	0.50	0.38
14380.0	14410.0	1.06	0.45	0.32
14740.0	14770.0	0.94	0.49	0.41
15100.0	15130.0	0.61	0.55	0.47
15460.0	15490.0	0.78	0.52	0.42
15800.0	15830.0	0.68	0.57	0.35
16160.0	16190.0	0.63	0.54	0.26
16500.0	16530.0	0.41	0.28	0.24
16860.0	16890.0	1.17	0.43	0.37
17200.0	17230.0	0.98	0.39	0.27
17560.0	17590.0	0.57	0.24	0.17
17900.0	17930.0	0.82	0.26	0.19
18260.0	18290.0	0.47	0.20	0.17
18600.0	18630.0	0.86	0.24	0.20
18960.0	18990.0	0.41	0.21	0.19
19300.0	19330.0	0.36	0.23	0.19
19660.0	19690.0	0.27	0.19	0.16
20000.0	20030.0	0.37	0.16	0.14

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=13649.99MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=7299.9902MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=19999.99MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+13			+13			+13
7150.0	6500.0	13.22	10.0	7310.0	6.65	9310.0	10690.0	17.12
6789.8	6860.2	7.29	250.0	7550.0	6.40	9070.0	10930.0	16.63
6429.6	7220.3	5.95	490.0	7790.0	6.05	8830.0	11170.0	15.95
6069.5	7580.5	6.23	710.0	8010.0	5.75	8590.0	11410.0	14.79
5709.3	7940.7	6.62	950.0	8250.0	5.63	8350.0	11650.0	13.61
5349.1	8300.9	6.55	1170.0	8470.0	5.84	8110.0	11890.0	12.48
4988.9	8661.1	6.79	1410.0	8710.0	6.27	7870.0	12130.0	11.45
4628.8	9021.2	7.45	1630.0	8930.0	6.91	7630.0	12370.0	11.42
4268.6	9381.4	8.13	1870.0	9170.0	7.98	7390.0	12610.0	11.67
3908.4	9741.6	8.26	2090.0	9390.0	8.75	7150.0	12850.0	11.70
3548.2	10101.8	7.52	2330.0	9630.0	9.46	6910.0	13090.0	11.64
3188.0	10461.9	7.38	2550.0	9850.0	10.22	6670.0	13330.0	11.53
2827.9	10822.1	6.98	2790.0	10090.0	10.66	6430.0	13570.0	11.30
2467.7	11182.3	6.63	3010.0	10310.0	10.61	6190.0	13810.0	11.21
2107.5	11542.5	6.39	3250.0	10550.0	11.18	5950.0	14050.0	11.41
1747.3	11902.7	6.11	3470.0	10770.0	10.92	5710.0	14290.0	11.71
1366.0	12284.0	6.18	3710.0	11010.0	10.81	5470.0	14530.0	12.62
1005.8	12644.2	6.13	3930.0	11230.0	10.74	5230.0	14770.0	12.62
624.4	13025.6	6.11	4170.0	11470.0	10.90	4990.0	15010.0	12.45
264.2	13385.7	5.88	4390.0	11690.0	10.56	4750.0	15250.0	12.45
104.1	13754.1	6.02	4630.0	11930.0	10.47	4510.0	15490.0	12.53
423.9	14073.9	5.92	4850.0	12150.0	10.76	4270.0	15730.0	13.09
762.5	14412.5	6.40	5090.0	12390.0	10.41	4030.0	15970.0	13.07
1082.3	14732.3	6.63	5310.0	12610.0	10.19	3790.0	16210.0	13.03
1421.0	15071.0	6.59	5550.0	12850.0	10.03	3550.0	16450.0	13.02
1740.8	15390.8	6.87	5770.0	13070.0	9.40	3310.0	16690.0	12.39
2079.4	15729.4	7.15	6010.0	13310.0	8.91	3070.0	16930.0	12.49
2399.3	16049.2	7.29	6230.0	13530.0	8.52	2830.0	17170.0	12.08
2737.9	16387.9	7.43	6470.0	13770.0	8.46	2590.0	17410.0	11.84
3057.7	16707.7	7.32	6690.0	13990.0	8.56	2350.0	17650.0	11.79
3396.4	17046.3	6.90	6930.0	14230.0	8.62	2110.0	17890.0	11.38
3716.2	17366.2	6.94	7150.0	14450.0	8.61	1870.0	18130.0	11.41
4054.8	17704.8	6.67	7390.0	14690.0	8.87	1630.0	18370.0	11.20
4374.6	18024.6	6.96	7610.0	14910.0	9.29	1390.0	18610.0	11.08
4713.3	18363.3	7.12	7850.0	15150.0	9.62	1150.0	18850.0	10.94
5033.1	18683.1	7.45	8070.0	15370.0	10.38	930.0	19070.0	10.76
5371.7	19021.7	7.53	8310.0	15610.0	10.86	690.0	19310.0	10.45
5691.5	19341.5	7.45	8530.0	15830.0	11.64	470.0	19530.0	10.29
6030.2	19680.2	7.36	8770.0	16070.0	12.29	230.0	19770.0	10.18
6350.0	20000.0	7.89	8990.0	16290.0	13.24	10.0	19990.0	10.03

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+10	+13	+16	+10	+13	+16
7050.0	39.78	45.43	46.03	22.2	23.94	26.28
7110.0	43.04	45.42	45.73	20.26	22.56	24.81
7170.0	42.03	44.81	45.46	22.51	24.7	27.02
7210.0	42.20	44.12	44.62	21.06	23.53	25.70
7570.0	37.12	38.31	38.95	23.00	25.05	26.30
7930.0	34.42	34.98	34.81	25.00	26.20	26.36
8290.0	37.22	39.49	42.06	25.30	25.84	25.50
8650.0	38.70	39.37	39.99	26.66	25.43	24.69
9010.0	54.16	55.30	51.29	27.07	25.34	24.03
9370.0	46.23	45.96	44.65	26.98	25.04	23.59
9730.0	48.40	48.30	46.87	25.30	22.88	21.79
10090.0	59.20	50.53	45.87	23.90	21.67	20.58
10450.0	53.99	51.67	45.35	23.79	22.27	21.26
10810.0	44.84	46.78	44.33	24.28	23.46	22.42
11170.0	37.76	40.71	41.98	25.19	24.16	23.63
11530.0	33.69	36.26	38.26	25.56	25.12	24.38
11890.0	31.59	34.22	36.17	23.72	23.22	22.61
12250.0	30.54	33.29	35.43	20.85	20.51	19.74
12610.0	29.95	33.07	36.40	19.05	19.13	18.87
12970.0	29.51	32.60	35.53	20.40	20.87	20.74
13330.0	29.54	32.53	35.08	21.15	21.63	21.80
13690.0	31.77	33.92	34.74	22.12	22.80	23.31
14050.0	36.72	35.32	33.61	25.07	26.80	28.45
14410.0	39.17	32.62	29.33	28.09	29.12	29.73
14770.0	33.33	29.57	27.12	30.34	29.45	28.84
15130.0	27.46	26.70	25.07	27.50	25.85	24.95
15490.0	23.40	23.56	22.52	21.54	21.37	21.00
15830.0	20.23	21.75	21.31	22.25	22.05	22.20
16190.0	22.05	22.79	21.68	19.99	19.93	19.86
16530.0	27.46	24.54	22.87	22.25	21.37	20.71
16890.0	25.82	25.18	24.65	23.36	21.37	20.04
17230.0	23.75	24.50	24.48	24.61	21.56	19.11
17590.0	23.94	24.85	25.19	29.38	27.11	25.06
17930.0	23.80	24.45	25.43	31.34	29.07	27.19
18290.0	23.95	25.01	25.95	33.54	32.26	30.49
18630.0	24.32	24.76	25.20	40.21	39.87	38.44
18990.0	25.28	26.31	26.97	32.18	31.49	30.21
19330.0	27.73	30.11	31.56	32.59	31.76	30.37
19690.0	32.77	36.85	37.84	33.33	32.90	31.94
20030.0	31.50	30.84	29.44	39.69	39.35	38.90


RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+10	+13	+16
7020.0	7050.0	19.06	21.69	22.07
7080.0	7110.0	20.33	20.97	21.05
7140.0	7170.0	20.03	20.58	20.74
7180.0	7210.0	20.56	20.80	20.74
7540.0	7570.0	21.21	20.80	20.02
7900.0	7930.0	18.73	18.25	17.74
8260.0	8290.0	17.51	17.80	18.13
8620.0	8650.0	22.18	22.42	22.52
8980.0	9010.0	26.07	26.13	25.95
9340.0	9370.0	26.69	26.50	26.18
9700.0	9730.0	28.21	27.71	27.34
10060.0	10090.0	30.09	29.23	28.66
10420.0	10450.0	32.28	31.30	30.55
10780.0	10810.0	34.68	33.69	32.52
11140.0	11170.0	34.62	34.13	33.18
11500.0	11530.0	33.70	34.06	33.58
11860.0	11890.0	31.32	31.88	31.74
12220.0	12250.0	29.16	29.68	29.70
12580.0	12610.0	27.72	28.57	28.78
12940.0	12970.0	26.84	27.54	27.53
13300.0	13330.0	25.57	26.35	26.59
13660.0	13690.0	27.13	29.28	30.00
14020.0	14050.0	33.29	40.51	40.14
14380.0	14410.0	44.72	37.73	32.77
14740.0	14770.0	43.57	34.69	30.90
15100.0	15130.0	39.19	36.39	29.71
15460.0	15490.0	31.29	32.10	27.65
15800.0	15830.0	27.01	26.55	25.05
16160.0	16190.0	25.02	26.09	27.20
16500.0	16530.0	28.33	30.20	33.15
16860.0	16890.0	27.33	27.27	27.15
17200.0	17230.0	26.64	26.82	27.02
17560.0	17590.0	25.02	24.99	24.75
17900.0	17930.0	26.16	26.28	26.57
18260.0	18290.0	20.51	20.50	20.84
18600.0	18630.0	22.37	22.41	23.53
18960.0	18990.0	19.35	19.32	20.21
19300.0	19330.0	18.23	18.36	18.68
19660.0	19690.0	18.22	18.41	18.47
20000.0	20030.0	18.46	18.68	19.23

Typical Performance Data


RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=20029.99MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+10	+13	+16		+10	+13	+16		+10	+13	+16
7020.0	7050.0	5.66	3.65	3.21	7050.0	12.35	8.16	8.31	10.0	1.42	1.24	1.08
7080.0	7110.0	4.25	3.34	3.05	7110.0	9.04	7.44	8.05	230.0	1.48	1.30	1.15
7140.0	7170.0	4.38	3.43	3.09	7170.0	8.51	7.00	7.56	450.0	1.65	1.45	1.28
7180.0	7210.0	3.86	3.26	3.00	7210.0	7.14	6.73	7.56	670.0	1.87	1.66	1.48
7540.0	7570.0	3.47	3.11	2.94	7570.0	4.28	4.96	5.93	890.0	2.04	1.81	1.62
7900.0	7930.0	3.41	3.06	2.87	7930.0	3.18	4.00	4.86	1110.0	2.20	1.95	1.73
8260.0	8290.0	3.62	3.45	3.30	8290.0	2.54	3.31	4.13	1330.0	2.36	2.09	1.85
8620.0	8650.0	4.56	4.28	3.94	8650.0	2.38	3.03	3.74	1550.0	2.45	2.16	1.91
8980.0	9010.0	5.83	5.36	5.20	9010.0	2.31	2.74	3.25	1770.0	2.46	2.16	1.90
9340.0	9370.0	4.82	4.39	4.07	9370.0	2.17	2.39	2.72	1990.0	2.46	2.15	1.88
9700.0	9730.0	4.22	3.78	3.42	9730.0	2.13	2.27	2.56	2210.0	2.54	2.21	1.94
10060.0	10090.0	4.99	4.30	3.99	10090.0	2.22	2.36	2.69	2430.0	2.59	2.26	1.99
10420.0	10450.0	4.36	3.68	3.34	10450.0	2.42	2.48	2.74	2650.0	2.65	2.31	2.04
10780.0	10810.0	2.74	2.44	2.01	10810.0	2.57	2.55	2.75	2870.0	2.76	2.40	2.12
11140.0	11170.0	3.27	2.71	2.46	11170.0	2.83	2.65	2.82	3090.0	2.92	2.54	2.24
11500.0	11530.0	3.10	2.57	2.29	11530.0	3.19	2.84	2.91	3310.0	3.02	2.62	2.32
11860.0	11890.0	2.13	1.79	1.55	11890.0	3.42	2.94	2.92	3530.0	3.12	2.71	2.39
12220.0	12250.0	2.13	1.79	1.57	12250.0	3.40	2.80	2.67	3750.0	3.29	2.84	2.52
12580.0	12610.0	1.93	1.62	1.41	12610.0	3.33	2.64	2.47	3970.0	3.45	2.98	2.66
12940.0	12970.0	1.52	1.39	1.36	12970.0	3.38	2.66	2.50	4190.0	3.58	3.11	2.78
13300.0	13330.0	1.99	1.80	1.87	13330.0	3.58	2.71	2.48	4410.0	3.60	3.15	2.83
13660.0	13690.0	1.74	1.52	1.39	13690.0	3.70	2.71	2.43	4630.0	3.56	3.15	2.85
14020.0	14050.0	1.57	1.62	1.65	14050.0	4.45	2.95	2.47	4830.0	3.56	3.16	2.89
14380.0	14410.0	2.39	2.39	2.86	14410.0	5.13	3.30	2.67	5050.0	3.42	3.05	2.84
14740.0	14770.0	2.97	2.64	2.58	14770.0	5.74	3.45	2.60	5250.0	3.19	2.86	2.72
15100.0	15130.0	2.70	2.45	2.22	15130.0	5.14	3.27	2.39	5470.0	3.03	2.76	2.67
15460.0	15490.0	3.30	3.12	3.45	15490.0	3.76	2.65	1.99	5670.0	3.00	2.77	2.74
15800.0	15830.0	4.89	4.12	3.69	15830.0	3.62	2.63	1.97	5890.0	2.85	2.68	2.68
16160.0	16190.0	2.42	2.07	1.90	16190.0	3.20	2.31	1.70	6090.0	2.69	2.56	2.55
16500.0	16530.0	3.13	3.20	3.26	16530.0	2.82	2.16	1.58	6310.0	2.63	2.50	2.47
16860.0	16890.0	5.14	5.00	5.63	16890.0	1.95	1.55	1.36	6510.0	2.51	2.37	2.31
17200.0	17230.0	3.49	3.29	2.84	17230.0	1.98	1.58	1.45	6730.0	2.48	2.34	2.29
17560.0	17590.0	3.00	3.00	2.59	17590.0	2.05	1.71	1.72	6930.0	2.69	2.55	2.47
17900.0	17930.0	4.24	3.94	4.26	17930.0	2.87	2.20	2.03	7150.0	2.72	2.55	2.44
18260.0	18290.0	3.86	3.54	3.23	18290.0	2.89	2.16	1.91	7350.0	2.55	2.40	2.34
18600.0	18630.0	2.75	2.52	2.35	18630.0	3.25	2.18	1.71	7570.0	2.30	2.23	2.24
18960.0	18990.0	3.47	3.37	2.95	18990.0	2.28	1.60	1.24	7770.0	2.15	2.18	2.32
19300.0	19330.0	3.00	2.83	2.84	19330.0	1.76	1.25	1.08	7990.0	2.18	2.32	2.54
19660.0	19690.0	2.90	2.89	2.75	19690.0	1.14	1.20	1.54	8190.0	2.53	2.76	3.06
20000.0	20030.0	5.17	4.68	6.13	20030.0	1.43	1.56	1.87	8410.0	3.16	3.49	3.86

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. LO @ RF=13649.99MHz




Conversion Loss vs. IF @ RF=13649.99MHz




Conversion Loss vs. IF @ RF=7299.9902MHz




Conversion Loss vs. IF @ RF=19999.99MHz



IP-3 Input




Compression @ RF IN=+9dBm




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR




IF VSWR




Outline Dimensions

HV1195



PCB Metal Land Pattern



Suggested Layout,
Tolerance to be within $\pm.002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
HV1195	0.200 (5.08)	0.180 (4.57)	0.087 (2.21)	0.025 (0.64)	0.050 (1.27)	0.028 (0.71)	0.043 (1.09)	0.050 (1.27)	0.030 (0.76)	0.043 (1.09)	0.204 (5.18)	0.127 (3.23)	0.065 (1.65)

CASE#	WT, GRAM
HV1195	.08

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Case material: Plastic encapsulation on Ceramic base.
2. Termination finish: Palladium Silver.




P.O. Box 350186, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

Tape & Reel Packaging TR-F82



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel
12	8	7	500

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION		REVISIONS				
	REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
	OR	M116031	NEW RELEASE	02/14/08	MMG	DJ
	A	ECO-000060	MODIFIED CASE STYLE	10/16/19	ITG	RB

**SUGGESTED MOUNTING CONFIGURATION FOR
HV1195 CASE STYLE, "08MX05" PIN CODE**





NOTES:

1. TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020±.0015"; COPPER: 1/2 OZ. EACH SIDE.
FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



 DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).

 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED		INITIALS	DATE	 Mini-Circuits® 13 Neptune Avenue Brooklyn NY 11235		
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	MMG	02/13/08			
	CHECKED	AV	02/14/08			
	APPROVED	DJ	02/14/08			
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.				PL, 08MX05, HV1195, SIM, TB-458+		
		SIZE	CODE IDENT	DRAWING NO:	REV:	
		A	15542	98-PL-284	A	
		FILE:	98PL284	SCALE:	10:1	SHEET: 1 OF 1
 ASHEETA1.DWG REV:A DATE:01/12/95						

Evaluation Board and Circuit

For Pin Connections refer to Data Sheet of the DUT



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Case Temperature	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process: 225°C peak Pb-Free Process: 250°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215