

# Coaxial Low Pass Filter

## SLP-5+

50Ω DC to 5 MHz

### Maximum Ratings

Operating Temperature -55°C to +100°C

Storage Temperature -55°C to +100°C

RF Power Input 0.5 W max.

Permanent damage may occur if any of these limits are exceeded.

### Features

- Good Attenuation Rate, 1.35 Typ. 20 dB / 3 dB BW Ratio
- Rugged Shielded Case
- Other SLP Models Available with Wide Selection of Cut-Off Frequencies

### Applications

- Lab Use
- Test Equipment
- Video Equipment



Generic photo used for illustration purposes only

CASE STYLE: FF99

Connectors	Model
SMA	SLP-5+


### +RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


### Low Pass Filter Electrical Specifications

PASSBAND (MHz)	fco (MHz) Nom.	STOPBAND (MHz)		VSWR (:1)	
		(loss > 20 dB)	(loss > 40 dB)	Passband Typ.	Stopband Typ.
DC-5	6	8-10	10-200	1.7	18


### Outline Drawing



### typical frequency response



### electrical schematic





### Outline Dimensions (inch/mm)

B	D	E	WT GRAMS
.70	1.98	.312	42.0
(17.78)	(50.29)	(7.92)	

### Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)		Return Loss (dB)	Frequency (MHz)	Group Delay (nsec)
	$\bar{x}$	$\sigma$			
1.0	0.08	0.1	25.1	1.0	147.47
2.0	0.13	0.1	32.4	2.0	150.99
3.0	0.34	0.1	15.6	3.0	158.96
3.5	0.69	0.1	14.2	3.5	164.57
4.0	0.71	0.1	15.8	4.0	173.42
4.5	0.73	0.1	25.1	4.5	192.06
5.0	0.91	0.1	25.5	5.0	215.98
5.8	2.41	0.7	15.8	5.3	253.98
6.0	3.35	0.8	7.2	5.8	294.32
6.3	9.49	1.3	2.0	6.0	326.82
6.8	11.67	1.1	1.2	6.3	305.70
7.0	16.87	1.2	0.9	6.8	223.89
7.3	23.49	1.1	0.5	7.0	180.77
7.8	29.30	1.0	0.4	7.3	106.74
8.0	34.55	1.0	0.3	7.8	73.25
8.3	39.27	1.0	0.3	8.0	54.49
8.5	41.68	1.1	0.3	8.3	38.64
8.8	42.05	1.1	0.2	8.5	31.12
9.0	42.44	1.1	0.2	8.8	29.13
9.5	43.73	1.1	0.2	9.0	28.46
10.0	47.90	1.1	0.2	9.5	27.23
12.0	63.04	1.6	0.1	10.0	26.91
16.0	75.52	4.1	0.1	12.0	26.68
22.0	75.62	9.9	0.1	13.0	25.95
35.0	74.63	3.9	0.1	14.0	25.34
80.0	77.85	6.6	0.1	16.0	24.48
156.0	81.35	8.6	0.1	18.0	24.08
178.0	75.08	2.3	0.1	20.0	24.00
189.0	77.64	6.8	0.1	22.0	23.82
200.0	78.15	5.2	0.1	24.0	23.72



### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Coaxial Low Pass Filter

# SLP-5+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
0.30	0.10	28.00	0.30	144.960
1.00	0.16	19.75	1.00	144.330
1.50	0.19	19.17	1.50	146.040
2.00	0.18	21.70	2.00	149.710
2.50	0.19	30.59	2.50	155.440
3.00	0.22	31.12	3.00	159.820
3.40	0.26	25.05	3.40	164.710
3.50	0.27	24.57	3.50	166.240
3.80	0.29	24.79	3.80	172.250
3.90	0.30	25.46	3.90	174.360
4.10	0.31	28.01	4.10	179.620
4.30	0.33	32.79	4.30	185.870
4.80	0.40	26.94	4.80	205.130
5.00	0.44	25.55	5.00	216.020
6.00	2.20	6.21	6.00	348.030
7.50	21.26	0.30	7.50	96.850
8.00	26.88	0.22	8.00	70.100
8.20	28.97	0.20	8.20	62.870
8.40	30.97	0.18	8.40	56.580
8.80	34.76	0.16	8.80	46.170
9.00	36.56	0.15	9.00	43.770
9.20	38.31	0.14	9.20	39.540
9.40	40.03	0.14	9.40	36.970
9.50	40.86	0.13	9.50	37.380
10.00	44.93	0.12	10.00	26.970
100.00	86.26	0.04	100.00	1.730
500.00	64.78	0.08	500.00	0.830
1000.00	47.61	1.01	1000.00	2.070
1500.00	78.46	0.60	1500.00	3.190
2000.00	60.85	3.98	2000.00	7.110
3000.00	36.30	2.49	3000.00	1.670
4500.00	48.75	3.53	4500.00	0.660
5000.00	44.44	2.64	5000.00	0.520
5500.00	39.05	4.19	5500.00	0.880
6000.00	36.88	3.56	6000.00	1.030
6500.00	49.80	3.09	6500.00	0.580
7000.00	41.87	3.29	7000.00	0.940
8000.00	42.39	3.55	8000.00	0.690
8500.00	63.14	4.02	8500.00	1.090
9000.00	41.12	4.70	9000.00	0.230
9500.00	27.95	2.90	9500.00	0.410
10000.00	19.95	3.69	10000.00	0.690

REV. X1  
SLP-5+  
060921

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



## Typical Performance Curves



REV. X1  
SLP-5+  
060921  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



**FF56**  
**FF99**

## Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF56	--	.46 (11.68)	--	1.70 (43.18)	.312 (7.92)	18.0
FF99	--	.70 (17.78)	--	1.98 (50.29)		42.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

### Notes:

1. Case material: Brass.
2. Case finish: Nickel plate.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

<b>Specification</b>	<b>Test/Inspection Condition</b>	<b>Reference/Spec</b>
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I