



Super-Flexible Test Cable

SLC-2FT-SMSM+

Mini-Circuits

50Ω 2FT DC to 18 GHz SMA-Male

THE BIG DEAL

- Super Flexible design for easy connections & bend radius
- Double shield cable for excellent shielding effectiveness
- Stainless steel straight SMA connectors for long mating-cycle life
- 6 month guarantee*



Generic photo used for illustration purposes only

| | |
|-------------------|---------------|
| Model No. | SLC-2FT-SMSM+ |
| Case Style | PH2043-2 |
| Connectors | SMA-Male |

APPLICATIONS

- Test and Measurement
- Research & Development labs
- Environmental & Temperature Test Chambers
- Field RF testing

+RoHS Compliant
 The +Suffix identifies RoHS Compliance.
 See our website for methodologies and qualifications

Product Guarantee*
 Mini-Circuits® will repair or replace your test cable at its option if the connector attachment fails within six months of shipment. This guarantee excludes cable or connector interface damage from misuse or abuse.

PRODUCT OVERVIEW

Mini-Circuits' SLC-SMSM+ Series are super-flexible cables which provide wideband performance from DC to 18 GHz with low insertion loss and excellent VSWR. The cable is designed for stability of phase and amplitude versus flexure while offering tremendous durability and reliability. Its unique construction of a double shielded cable allows the cable to have the greatest of flexibility and yet handle the demanding lab environments where constant bending and flexing are required. In addition, they feature straight SMA to straight SMA stainless steel connectors. Available from stock in a variety of lengths to support many different requirements.

KEY FEATURES

| Feature | Advantages |
|--|--|
| Super-Flexible 0.25 inch static bend radius | Supports a wide range of test applications including R&D, military and defense, production test and more. |
| Excellent stability of phase and insertion loss versus flexure | SLC-SMSM+ Series test cables have been tested in bend radii as tight as 2.4 inches to qualify minimal change in insertion loss, insertion phase, and VSWR, providing reliable performance in a wide range of configurations. |
| Performance qualified to 100,000 flexures | Like all Mini-Circuits test cables, SLC-SMSM+ series models have been performance qualified up to 100,000 bend cycles, ensuring outstanding durability and extra long life. |

REV. B
 ECO-026117
 SLC-2FT-SMSM+
 MCL NY
 250707





Super-Flexible Test Cable

SLC-2FT-SMSM+

Mini-Circuits

50Ω 2FT DC to 18 GHz SMA-Male

ELECTRICAL SPECIFICATIONS AT +25°C

| Parameter | Frequency (GHz) | Min. | Typ. | Max. | Units |
|---------------------|-----------------|------|------|------|-------|
| Frequency Range | | DC | | 18 | GHz |
| Length ¹ | | | 2 | | FT |
| Insertion Loss | DC - 1 | — | 0.6 | 1.1 | dB |
| | 1 - 2 | — | 1.0 | 1.4 | |
| | 2 - 4 | — | 1.3 | 1.9 | |
| | 4 - 10 | — | 2.0 | 3.0 | |
| | 10 - 18 | — | 2.9 | 4.1 | |
| Return Loss | DC - 6 | 17.7 | 33.2 | — | dB |
| | 6 - 18 | 16.5 | 28.5 | — | |

1. Custom sizes available, consult factory.

PERFORMANCE CHANGE VS. FLEXURE (TYPICAL)²

| Parameter | Frequency (GHz) | Bend Radius (inches) | | | Units |
|------------------------------|-----------------|----------------------|-------|-------|-------|
| | | 10.0 | 3.25 | 2.40 | |
| Insertion Loss ³ | DC - 1 | 0.003 | 0.002 | 0.005 | dB |
| | 1 - 2 | 0.003 | 0.002 | 0.005 | |
| | 2 - 4 | 0.002 | 0.001 | 0.005 | |
| | 4 - 10 | 0.003 | 0.005 | 0.016 | |
| | 10 - 18 | 0.005 | 0.059 | 0.102 | |
| Insertion Phase ³ | DC - 1 | 0.05 | 0.13 | 0.18 | Deg |
| | 1 - 2 | 0.11 | 0.27 | 0.38 | |
| | 2 - 4 | 0.22 | 0.53 | 0.76 | |
| | 4 - 10 | 0.56 | 1.33 | 1.93 | |
| | 10 - 18 | 1.00 | 2.26 | 3.18 | |
| VSWR ³ | DC - 6 | 0.002 | 0.005 | 0.01 | :1 |
| | 6 - 18 | 0.005 | 0.017 | 0.028 | |

2. Performance change versus flexure with a 3 ft cable 360° around a 4" diameter mandrel.

3. Absolute values normalized to the reference position 0. See [AN-46-003](#) under Associated Application Notes

ABSOLUTE MAXIMUM RATINGS

| Parameter | Ratings |
|------------------------|----------------------|
| Operating Temperature | -55°C to +125°C |
| Storage Temperature | -55°C to +125°C |
| Power Handling at 25°C | 39.5 W Max at 1 GHz |
| | 28.4 W Max at 2 GHz |
| | 22 W Max at 4 GHz |
| | 11.8 W Max at 10 GHz |
| | 8 W Max at 18 GHz |

Permanent damage may occur if any of these limits are exceeded.






Super-Flexible Test Cable

SLC-2FT-SMSM+

Mini-Circuits

50Ω 2FT DC to 18 GHz SMA-Male


CABLE CONSTRUCTION



- Center Conductor: SilverPlated Copper Clad Steel
- Dielectric: (FEP)
- Inner Shield: Silver Plated Copper
- Outer Shield: Silver Plated Copper Braid
- Jacket: (Blue FEP)

Connectors:
 Passivated stainless steel (Body & Hex Nut)
 Gold plated beryllium copper center contacts
 PTFE Dielectric

OUTLINE DRAWING



* OVERALL CONNECTOR DIMENSION
 [CONNECTOR SHAPE MAY VARY]

OUTLINE DIMENSIONS (Inch/mm)

| A | B | C | D | E1 | E2 | F | T | wt | | |
|------|--------|------|------|------|------|------|----------|------|--------|-------|
| Feet | Meters | .36 | .313 | .250 | .313 | .250 | .062 Nom | Feet | Meters | grams |
| 2.00 | 0.61 | 9.14 | 7.95 | 6.35 | 7.95 | 6.35 | 1.57 Nom | 0.06 | 0.02 | 10.88 |





Super-Flexible Test Cable



SLC-2FT-SMSM+

Mini-Circuits

50Ω 2FT DC to 18 GHz SMA-Male

TYPICAL PERFORMANCE DATA AND CHARTS

| Frequency (MHz) | Insertion Loss (dB) | Return Loss (dB) | |
|-----------------|---------------------|------------------|------------|
| | | SMA-Male 1 | SMA-Male 2 |
| 10 | 0.14 | 30.97 | 31.54 |
| 100 | 0.30 | 35.08 | 35.13 |
| 200 | 0.39 | 44.50 | 44.68 |
| 400 | 0.52 | 44.15 | 43.97 |
| 1000 | 0.79 | 39.18 | 39.11 |
| 1500 | 0.95 | 30.17 | 30.20 |
| 2500 | 1.23 | 24.21 | 24.20 |
| 4000 | 1.52 | 37.04 | 37.03 |
| 6000 | 1.87 | 22.07 | 22.08 |
| 8000 | 2.15 | 27.25 | 27.28 |
| 10000 | 2.44 | 31.44 | 31.28 |
| 12000 | 2.81 | 20.24 | 20.29 |
| 14000 | 3.06 | 22.77 | 22.81 |
| 16000 | 3.17 | 19.36 | 19.35 |
| 18000 | 3.23 | 36.54 | 36.32 |



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data

| FREQUENCY (GHz) | INSERTION LOSS (dB) | SMA-MALE 1 RETURN LOSS (dB) | SMA-MALE 2 RETURN LOSS (dB) |
|--------------------|---------------------------|-----------------------------------|-----------------------------------|
| 0.01 | 0.14 | 30.97 | 31.54 |
| 0.1 | 0.30 | 35.08 | 35.13 |
| 0.2 | 0.39 | 44.50 | 44.68 |
| 0.4 | 0.52 | 44.15 | 43.97 |
| 0.6 | 0.62 | 57.53 | 56.69 |
| 0.8 | 0.71 | 46.78 | 46.93 |
| 1.0 | 0.79 | 39.18 | 39.11 |
| 1.5 | 0.95 | 30.17 | 30.20 |
| 2.0 | 1.10 | 26.09 | 26.08 |
| 2.5 | 1.23 | 24.21 | 24.20 |
| 3.0 | 1.33 | 24.91 | 24.92 |
| 3.5 | 1.42 | 29.14 | 29.14 |
| 4.0 | 1.52 | 37.04 | 37.03 |
| 4.5 | 1.61 | 43.20 | 43.19 |
| 5.0 | 1.70 | 35.69 | 35.71 |
| 5.5 | 1.78 | 26.61 | 26.61 |
| 6.0 | 1.87 | 22.07 | 22.08 |
| 6.5 | 1.98 | 19.78 | 19.79 |
| 7.0 | 2.07 | 20.20 | 20.25 |
| 7.5 | 2.12 | 22.27 | 22.31 |
| 8.0 | 2.15 | 27.25 | 27.28 |
| 8.5 | 2.19 | 41.08 | 40.22 |
| 9.0 | 2.27 | 32.97 | 33.60 |
| 9.5 | 2.36 | 31.31 | 31.49 |
| 10.0 | 2.44 | 31.44 | 31.28 |
| 10.5 | 2.53 | 27.30 | 27.14 |
| 11.0 | 2.62 | 23.38 | 23.40 |
| 11.5 | 2.72 | 21.93 | 21.98 |
| 12.0 | 2.81 | 20.24 | 20.29 |
| 12.5 | 2.87 | 22.15 | 22.20 |
| 13.0 | 2.94 | 27.04 | 26.99 |
| 13.5 | 3.00 | 33.30 | 33.33 |
| 14.0 | 3.06 | 22.77 | 22.81 |
| 14.5 | 3.12 | 18.58 | 18.62 |
| 15.0 | 3.17 | 17.69 | 17.71 |
| 15.5 | 3.21 | 17.22 | 17.21 |
| 16.0 | 3.17 | 19.36 | 19.35 |
| 16.5 | 3.16 | 21.72 | 21.74 |
| 17.0 | 3.17 | 26.57 | 26.67 |
| 17.5 | 3.20 | 39.32 | 39.06 |
| 18.0 | 3.23 | 36.54 | 36.32 |





P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS

Typical Performance Curves



Outline Dimensions



* OVERALL CONNECTOR DIMENSION
[CONNECTOR SHAPE MAY VARY]

PH2043 SERIES
SMA MALE (CONN-1)
SMA MALE (CONN-2)

| CASE STYLE # | A | | B | C1 | C2 | D | E1 | E2 | F | | T | | WEIGHT GRAMS |
|--------------|-------|-------|---------------|----------------|----------------|---------------|----------------|----------------|-------------------------|------------------------|------|------|--------------|
| | FEET | METER | | | | | | | SLC(U)-AFT-SMSM+ | SLC-AFT-SMSM+ | FEET | MM | |
| PH2043-2 | 2.00 | 0.61 | .36 (9.14) | .313 (7.95) | .250 (6.35) | .36 (9.14) | .313 (7.95) | .250 (6.35) | .047±.002 (1.19±.05) | .062 NOM (1.57 NOM) | .06 | 0.02 | 10.88 |
| PH2043-3 | 3.00 | 0.91 | | | | | | | | | .09 | 0.03 | 12.92 |
| PH2043-3.28 | 3.28 | 1.00 | | | | | | | | | .10 | 0.03 | 13.49 |
| PH2043-4 | 4.00 | 1.22 | | | | | | | | | .12 | 0.04 | 14.96 |
| PH2043-6 | 6.00 | 1.83 | | | | | | | | | .18 | 0.05 | 19.04 |
| PH2043-20 | 20.00 | 6.10 | | | | | | | | | .60 | 0.18 | 47.60 |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. Super flexible Coaxial Cable.
2. "A" Represents Length of Cable.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|-----------------------|--|--|
| Operating Temperature | -55° to 125° C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 125° C Ambient Environment | Individual Model Data Sheet |
| Thermal Shock | -55° to 100° C, 100 cycles | MIL-STD-202, Method 107, Condition A-3 |
| Mechanical Flexing | 100,000 cycles During each cycle, cable flexed from 90° through 0° to -90° and back with a Radii of 3 inches | --- |