

# Plug-In Frequency Mixer

## SRA-11+

Level 7 (LO Power +7 dBm) 5 to 2000 MHz

### Maximum Ratings


|                       |                |
|-----------------------|----------------|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature   | -55°C to 100°C |
| RF Power              | 50mW           |
| IF Current            | 40mA           |

Permanent damage may occur if any of these limits are exceeded.

### Pin Connections

|             |         |
|-------------|---------|
| LO          | 8       |
| RF          | 1       |
| IF          | 3       |
| GROUND      | 2,5,6,7 |
| CASE GROUND | 2,5,6,7 |
| NOT USED    | 4       |

### Outline Drawing



### Outline Dimensions (inch/mm)

| A     | B     | C    | D    | E    | F     |
|-------|-------|------|------|------|-------|
| .770  | .800  | .285 | .310 | .370 | .400  |
| 19.56 | 20.32 | 7.24 | 7.87 | 9.40 | 10.16 |

| G    | H    | J    | K    | wt    |
|------|------|------|------|-------|
| .200 | .20  | .14  | .031 | grams |
| 5.08 | 5.08 | 3.56 | 0.79 | 5.2   |

### Features

- excellent conversion loss, 6.72 dB typ.
- good L-R isolation, 35 dB typ. L-I isolation, 30 dB typ.
- broadband, 5 to 2000 MHz
- rugged welded construction
- hermetic

### Applications

- GPS
- defense & aeronautical systems
- cellular



Generic photo used for illustration purposes only

CASE STYLE: A06

**+RoHS Compliant**

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

### Electrical Specifications

| FREQUENCY (MHz) |        | CONVERSION LOSS (dB) |          |             |      | LO-RF ISOLATION (dB) |      |      |      |      |      | LO-IF ISOLATION (dB) |      |      |      |      |      |
|-----------------|--------|----------------------|----------|-------------|------|----------------------|------|------|------|------|------|----------------------|------|------|------|------|------|
| LO/RF           | IF     | Mid-Band             |          | Total Range | Max. | L                    |      | M    |      | U    |      | L                    |      | M    |      | U    |      |
|                 |        | $\bar{X}$            | $\sigma$ |             |      | Typ.                 | Min. | Typ. | Min. | Typ. | Min. | Typ.                 | Min. | Typ. | Min. | Typ. | Min. |
| 5-2000          | 10-600 | 6.72                 | .07      | 8.5         | 9.0  | 50                   | 45   | 35   | 25   | 30   | 20   | 45                   | 40   | 30   | 20   | 25   | 15   |


1 dB COMP.: +1 dBm typ.

L = low range [ $f_L$  to 10  $f_L$ ]  
m = mid band [ $2f_L$  to  $f_U/2$ ]  
M = mid range [10  $f_L$  to  $f_U/2$ ]  
U = upper range [ $f_U/2$  to  $f_U$ ]

### Typical Performance Data

| Frequency (MHz) |         | Conversion Loss (dB) | Isolation L-R (dB) | Isolation L-I (dB) | VSWR RF Port (:1) | VSWR LO Port (:1) |
|-----------------|---------|----------------------|--------------------|--------------------|-------------------|-------------------|
| RF              | LO      | LO +7dBm             | LO +7dBm           | LO +7dBm           | LO +7dBm          | LO +7dBm          |
| 5.00            | 35.00   | 5.85                 | 46.19              | >67.00             | 3.19              | 3.03              |
| 10.00           | 40.00   | 5.88                 | 46.23              | >67.00             | 2.54              | 2.69              |
| 20.00           | 50.00   | 6.11                 | 46.26              | >67.00             | 2.45              | 2.70              |
| 50.00           | 80.00   | 6.37                 | 45.89              | >67.00             | 2.62              | 2.61              |
| 100.00          | 70.00   | 6.25                 | 44.70              | 64.66              | 2.96              | 2.46              |
| 200.00          | 170.00  | 6.62                 | 41.17              | 55.90              | 3.21              | 2.31              |
| 311.92          | 281.92  | 6.71                 | 38.72              | 50.11              | 3.31              | 2.27              |
| 465.39          | 435.39  | 7.06                 | 37.94              | 46.15              | 3.42              | 2.13              |
| 618.85          | 588.85  | 7.40                 | 38.38              | 45.38              | 3.19              | 2.08              |
| 772.31          | 742.31  | 7.53                 | 38.07              | 45.67              | 2.96              | 1.93              |
| 849.04          | 819.04  | 7.22                 | 37.13              | 43.78              | 2.41              | 1.73              |
| 1000.00         | 970.00  | 7.05                 | 36.28              | 38.27              | 2.10              | 1.58              |
| 1156.00         | 1126.00 | 6.76                 | 35.18              | 43.23              | 1.86              | 1.45              |
| 1386.20         | 1356.20 | 7.53                 | 41.65              | 38.52              | 2.12              | 1.17              |
| 1462.90         | 1432.90 | 7.62                 | 41.43              | 41.57              | 2.27              | 1.17              |
| 1500.00         | 1470.00 | 7.48                 | 41.94              | 42.71              | 2.19              | 1.32              |
| 1616.40         | 1586.40 | 6.96                 | 43.41              | 43.97              | 2.08              | 1.39              |
| 1800.20         | 1770.00 | 6.79                 | 41.03              | 38.23              | 1.87              | 1.59              |
| 1923.30         | 1893.30 | 6.64                 | 38.49              | 30.27              | 1.79              | 1.70              |
| 2000.00         | 1970.00 | 6.69                 | 39.35              | 27.98              | 1.67              | 1.74              |

### Electrical Schematic









### Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B  
M151107  
SRA-11  
DJ/TD/CP/AM  
151005  
Page 1 of 2



## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# Frequency Mixer

**SRA-11+**

## Typical Performance Data

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>IF FIXED<br>@IF(OUT)=30MHz<br>(dB) |       |      |
|---------------------|-------------|-------------------------------------------------------|-------|------|
|                     |             | @LO (dBm)                                             |       |      |
|                     |             | +4                                                    | +7    | +10  |
| 10.1                | 40.1        | 6.56                                                  | 6.33  | 6.11 |
| 70.5                | 100.5       | 6.96                                                  | 6.68  | 6.52 |
| 131.0               | 161.0       | 7.10                                                  | 6.80  | 6.56 |
| 191.4               | 221.4       | 7.21                                                  | 6.79  | 6.51 |
| 272.0               | 302.0       | 7.41                                                  | 6.90  | 6.56 |
| 332.5               | 362.5       | 7.67                                                  | 7.01  | 6.59 |
| 413.1               | 443.1       | 7.96                                                  | 7.29  | 6.88 |
| 473.5               | 503.5       | 7.87                                                  | 7.22  | 6.85 |
| 554.1               | 584.1       | 7.86                                                  | 7.20  | 6.83 |
| 614.5               | 644.5       | 7.87                                                  | 7.28  | 6.91 |
| 695.1               | 725.1       | 8.38                                                  | 7.86  | 7.47 |
| 755.6               | 785.6       | 8.51                                                  | 8.13  | 7.86 |
| 836.2               | 866.2       | 8.37                                                  | 8.10  | 7.93 |
| 896.6               | 926.6       | 8.18                                                  | 7.90  | 7.75 |
| 977.2               | 1007.2      | 8.16                                                  | 7.87  | 7.70 |
| 1037.7              | 1067.7      | 8.09                                                  | 7.81  | 7.65 |
| 1118.2              | 1148.2      | 8.04                                                  | 7.70  | 7.57 |
| 1178.7              | 1208.7      | 8.11                                                  | 7.70  | 7.55 |
| 1259.3              | 1289.3      | 8.27                                                  | 7.78  | 7.57 |
| 1319.7              | 1349.7      | 8.40                                                  | 7.82  | 7.59 |
| 1400.3              | 1430.3      | 8.71                                                  | 8.00  | 7.69 |
| 1460.8              | 1490.8      | 8.95                                                  | 8.19  | 7.82 |
| 1541.4              | 1571.4      | 8.99                                                  | 8.23  | 7.81 |
| 1601.8              | 1631.8      | 8.83                                                  | 8.12  | 7.70 |
| 1682.4              | 1712.4      | 8.58                                                  | 7.97  | 7.58 |
| 1742.8              | 1772.8      | 8.34                                                  | 7.78  | 7.43 |
| 1823.4              | 1853.4      | 8.18                                                  | 7.71  | 7.42 |
| 1883.9              | 1913.9      | 8.05                                                  | 7.62  | 7.35 |
| 1964.5              | 1994.5      | 7.78                                                  | 7.39  | 7.18 |
| 2024.9              | 2054.9      | 7.58                                                  | 7.18  | 6.99 |
| 2105.5              | 2135.5      | 7.57                                                  | 7.19  | 7.01 |
| 2166.0              | 2196.0      | 7.72                                                  | 7.29  | 7.05 |
| 2246.5              | 2276.5      | 7.83                                                  | 7.41  | 7.17 |
| 2307.0              | 2337.0      | 8.03                                                  | 7.60  | 7.35 |
| 2387.6              | 2417.6      | 8.36                                                  | 7.92  | 7.63 |
| 2448.0              | 2478.0      | 8.55                                                  | 8.07  | 7.76 |
| 2528.6              | 2558.6      | 9.10                                                  | 8.53  | 8.19 |
| 2589.1              | 2619.1      | 9.80                                                  | 9.14  | 8.74 |
| 2669.7              | 2699.7      | 10.64                                                 | 9.84  | 9.39 |
| 2730.1              | 2760.1      | 11.08                                                 | 10.21 | 9.79 |

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | IP3 INPUT<br>(dBm) |       |       |
|---------------------|-------------|--------------------|-------|-------|
|                     |             | @LO (dBm)          |       |       |
|                     |             | +4                 | +7    | +10   |
| 10.1                | 40.1        | 12.15              | 12.70 | 12.13 |
| 70.5                | 100.5       | 8.80               | 8.20  | 8.03  |
| 131.0               | 161.0       | 5.87               | 7.05  | 9.10  |
| 191.4               | 221.4       | 5.54               | 7.91  | 11.18 |
| 272.0               | 302.0       | 6.74               | 10.01 | 13.48 |
| 332.5               | 362.5       | 7.06               | 10.94 | 15.12 |
| 413.1               | 443.1       | 9.04               | 11.65 | 12.69 |
| 473.5               | 503.5       | 10.22              | 11.80 | 11.99 |
| 554.1               | 584.1       | 9.88               | 11.27 | 12.22 |
| 614.5               | 644.5       | 9.83               | 11.36 | 12.75 |
| 695.1               | 725.1       | 8.15               | 9.48  | 10.87 |
| 755.6               | 785.6       | 8.16               | 9.13  | 10.21 |
| 836.2               | 866.2       | 8.95               | 9.78  | 10.54 |
| 896.6               | 926.6       | 9.70               | 10.44 | 11.10 |
| 977.2               | 1007.2      | 10.67              | 11.42 | 12.36 |
| 1037.7              | 1067.7      | 11.85              | 12.80 | 13.72 |
| 1118.2              | 1148.2      | 14.10              | 13.73 | 14.13 |
| 1178.7              | 1208.7      | 15.19              | 17.08 | 16.75 |
| 1259.3              | 1289.3      | 19.86              | 18.72 | 16.70 |
| 1319.7              | 1349.7      | 18.60              | 20.09 | 20.20 |
| 1400.3              | 1430.3      | 16.30              | 18.76 | 18.64 |
| 1460.8              | 1490.8      | 15.42              | 15.40 | 15.03 |
| 1541.4              | 1571.4      | 11.87              | 12.76 | 13.99 |
| 1601.8              | 1631.8      | 10.82              | 11.02 | 12.30 |
| 1682.4              | 1712.4      | 10.73              | 11.38 | 11.82 |
| 1742.8              | 1772.8      | 9.46               | 10.61 | 11.75 |
| 1823.4              | 1853.4      | 8.63               | 8.73  | 9.24  |
| 1883.9              | 1913.9      | 8.61               | 8.51  | 9.06  |
| 1964.5              | 1994.5      | 8.47               | 8.54  | 8.59  |
| 2024.9              | 2054.9      | 7.70               | 8.37  | 8.86  |
| 2105.5              | 2135.5      | 7.62               | 8.71  | 9.65  |
| 2166.0              | 2196.0      | 7.55               | 8.96  | 10.01 |
| 2246.5              | 2276.5      | 7.19               | 9.03  | 11.50 |
| 2307.0              | 2337.0      | 6.91               | 8.71  | 11.35 |
| 2387.6              | 2417.6      | 7.34               | 8.93  | 10.25 |
| 2448.0              | 2478.0      | 8.11               | 10.29 | 12.11 |
| 2528.6              | 2558.6      | 8.35               | 10.89 | 12.69 |
| 2589.1              | 2619.1      | 7.81               | 10.10 | 12.82 |
| 2669.7              | 2699.7      | 8.40               | 9.15  | 10.91 |
| 2730.1              | 2760.1      | 10.00              | 10.13 | 10.85 |

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | COMPRESSION<br>@RF IN=+1dBm<br>(dB) |      |      |
|---------------------|-------------|-------------------------------------|------|------|
|                     |             | @LO (dBm)                           |      |      |
|                     |             | +4                                  | +7   | +10  |
| 10.1                | 40.1        | 1.05                                | 0.97 | 0.84 |
| 70.5                | 100.5       | 1.26                                | 0.98 | 0.78 |
| 131.0               | 161.0       | 1.27                                | 1.00 | 0.80 |
| 191.4               | 221.4       | 1.46                                | 1.23 | 1.00 |
| 272.0               | 302.0       | 1.63                                | 1.43 | 1.25 |
| 332.5               | 362.5       | 1.74                                | 1.60 | 1.42 |
| 413.1               | 443.1       | 1.76                                | 1.59 | 1.37 |
| 473.5               | 503.5       | 1.85                                | 1.62 | 1.40 |
| 554.1               | 584.1       | 1.93                                | 1.69 | 1.46 |
| 614.5               | 644.5       | 1.89                                | 1.68 | 1.48 |
| 695.1               | 725.1       | 1.43                                | 1.29 | 1.18 |
| 755.6               | 785.6       | 1.14                                | 0.93 | 0.80 |
| 836.2               | 866.2       | 0.97                                | 0.75 | 0.60 |
| 896.6               | 926.6       | 0.85                                | 0.65 | 0.51 |
| 977.2               | 1007.2      | 0.62                                | 0.45 | 0.35 |
| 1037.7              | 1067.7      | 0.51                                | 0.35 | 0.27 |
| 1118.2              | 1148.2      | 0.46                                | 0.28 | 0.20 |
| 1178.7              | 1208.7      | 0.45                                | 0.27 | 0.18 |
| 1259.3              | 1289.3      | 0.47                                | 0.30 | 0.20 |
| 1319.7              | 1349.7      | 0.49                                | 0.36 | 0.25 |
| 1400.3              | 1430.3      | 0.44                                | 0.38 | 0.29 |
| 1460.8              | 1490.8      | 0.40                                | 0.37 | 0.30 |
| 1541.4              | 1571.4      | 0.38                                | 0.36 | 0.31 |
| 1601.8              | 1631.8      | 0.47                                | 0.43 | 0.39 |
| 1682.4              | 1712.4      | 0.67                                | 0.55 | 0.48 |
| 1742.8              | 1772.8      | 0.83                                | 0.71 | 0.60 |
| 1823.4              | 1853.4      | 0.95                                | 0.80 | 0.70 |
| 1883.9              | 1913.9      | 1.09                                | 0.89 | 0.76 |
| 1964.5              | 1994.5      | 1.23                                | 1.02 | 0.88 |
| 2024.9              | 2054.9      | 1.42                                | 1.18 | 1.02 |
| 2105.5              | 2135.5      | 1.45                                | 1.16 | 0.98 |
| 2166.0              | 2196.0      | 1.33                                | 1.06 | 0.93 |
| 2246.5              | 2276.5      | 1.46                                | 1.11 | 0.95 |
| 2307.0              | 2337.0      | 1.63                                | 1.17 | 0.93 |
| 2387.6              | 2417.6      | 1.81                                | 1.22 | 0.93 |
| 2448.0              | 2478.0      | 1.84                                | 1.23 | 0.93 |
| 2528.6              | 2558.6      | 1.87                                | 1.18 | 0.82 |
| 2589.1              | 2619.1      | 2.02                                | 1.25 | 0.78 |
| 2669.7              | 2699.7      | 2.02                                | 1.22 | 0.71 |
| 2730.1              | 2760.1      | 1.88                                | 1.12 | 0.63 |

REV. X3

SRA-11+

101031

Page 1 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350186, Brooklyn, New York 11235-0008 (718) 934-4500 Fax (718) 332-4861



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



## Typical Performance Data

| IF<br>(OUT)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>VS. IF FREQUENCY<br>@RF(IN)=1010.1MHz<br>(dB) | IF<br>(OUT)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>VS. IF FREQUENCY<br>@RF(IN)=10.1MHz<br>(dB) | IF<br>(OUT)<br>(MHz) | LO<br>(MHz) | CONVERSION LOSS<br>VS. IF FREQUENCY<br>@RF(IN)=2010.1MHz<br>(dB) |
|----------------------|-------------|------------------------------------------------------------------|----------------------|-------------|----------------------------------------------------------------|----------------------|-------------|------------------------------------------------------------------|
|                      |             | @LO (dBm)                                                        |                      |             | @LO (dBm)                                                      |                      |             | @LO (dBm)                                                        |
|                      |             | +7                                                               |                      |             | +7                                                             |                      |             | +7                                                               |
| 770.1                | 240.0       | 9.89                                                             | 10.0                 | 20.1        | 7.00                                                           | 1010.1               | 1000.0      | 10.99                                                            |
| 750.6                | 259.5       | 9.79                                                             | 50.0                 | 60.1        | 6.14                                                           | 989.7                | 1020.4      | 10.82                                                            |
| 731.1                | 279.0       | 9.70                                                             | 90.0                 | 100.1       | 6.07                                                           | 969.3                | 1040.8      | 10.50                                                            |
| 711.6                | 298.5       | 9.51                                                             | 110.0                | 120.1       | 5.91                                                           | 948.9                | 1061.2      | 10.28                                                            |
| 692.2                | 317.9       | 9.41                                                             | 150.0                | 160.1       | 5.86                                                           | 928.5                | 1081.6      | 10.11                                                            |
| 672.7                | 337.4       | 9.36                                                             | 170.0                | 180.1       | 5.93                                                           | 908.1                | 1102.0      | 9.91                                                             |
| 653.2                | 356.9       | 9.18                                                             | 210.0                | 220.1       | 5.95                                                           | 887.7                | 1122.4      | 9.76                                                             |
| 633.7                | 376.4       | 9.24                                                             | 230.0                | 240.1       | 5.90                                                           | 867.2                | 1142.9      | 9.53                                                             |
| 614.2                | 395.9       | 9.01                                                             | 270.0                | 280.1       | 5.95                                                           | 846.8                | 1163.3      | 9.46                                                             |
| 594.7                | 415.4       | 9.19                                                             | 290.0                | 300.1       | 5.85                                                           | 826.4                | 1183.7      | 9.37                                                             |
| 575.2                | 434.9       | 9.00                                                             | 330.0                | 340.1       | 5.90                                                           | 806.0                | 1204.1      | 9.28                                                             |
| 555.7                | 454.4       | 9.07                                                             | 350.0                | 360.1       | 5.85                                                           | 785.6                | 1224.5      | 9.13                                                             |
| 536.3                | 473.8       | 9.07                                                             | 390.0                | 400.1       | 6.02                                                           | 765.2                | 1244.9      | 9.06                                                             |
| 516.8                | 493.3       | 8.93                                                             | 410.0                | 420.1       | 6.20                                                           | 744.8                | 1265.3      | 8.97                                                             |
| 497.3                | 512.8       | 8.73                                                             | 450.0                | 460.1       | 5.97                                                           | 724.4                | 1285.7      | 8.97                                                             |
| 477.8                | 532.3       | 8.73                                                             | 470.0                | 480.1       | 5.96                                                           | 704.0                | 1306.1      | 8.82                                                             |
| 458.3                | 551.8       | 8.73                                                             | 510.0                | 520.1       | 6.20                                                           | 683.6                | 1326.5      | 8.77                                                             |
| 438.8                | 571.3       | 8.77                                                             | 530.0                | 540.1       | 6.21                                                           | 663.2                | 1346.9      | 8.68                                                             |
| 419.3                | 590.8       | 8.60                                                             | 570.0                | 580.1       | 6.21                                                           | 642.8                | 1367.3      | 8.65                                                             |
| 399.8                | 610.3       | 8.69                                                             | 590.0                | 600.1       | 6.54                                                           | 622.3                | 1387.8      | 8.61                                                             |
| 380.4                | 629.7       | 8.58                                                             | 630.0                | 640.1       | 6.84                                                           | 581.5                | 1428.6      | 8.48                                                             |
| 360.9                | 649.2       | 8.44                                                             | 650.0                | 660.1       | 6.87                                                           | 561.1                | 1449.0      | 8.33                                                             |
| 341.4                | 668.7       | 8.42                                                             | 690.0                | 700.1       | 7.01                                                           | 520.3                | 1489.8      | 8.20                                                             |
| 321.9                | 688.2       | 8.20                                                             | 710.0                | 720.1       | 7.17                                                           | 499.9                | 1510.2      | 8.14                                                             |
| 302.4                | 707.7       | 8.10                                                             | 750.0                | 760.1       | 7.72                                                           | 459.1                | 1551.0      | 7.90                                                             |
| 282.9                | 727.2       | 7.95                                                             | 770.0                | 780.1       | 7.83                                                           | 438.7                | 1571.4      | 7.72                                                             |
| 263.4                | 746.7       | 7.73                                                             | 810.0                | 820.1       | 8.21                                                           | 397.9                | 1612.2      | 7.50                                                             |
| 243.9                | 766.2       | 7.64                                                             | 830.0                | 840.1       | 8.21                                                           | 377.4                | 1632.7      | 7.42                                                             |
| 224.5                | 785.6       | 7.50                                                             | 870.0                | 880.1       | 8.61                                                           | 336.6                | 1673.5      | 7.23                                                             |
| 205.0                | 805.1       | 7.41                                                             | 890.0                | 900.1       | 8.79                                                           | 316.2                | 1693.9      | 7.17                                                             |
| 185.5                | 824.6       | 7.40                                                             | 930.0                | 940.1       | 8.88                                                           | 275.4                | 1734.7      | 7.10                                                             |
| 166.0                | 844.1       | 7.36                                                             | 950.0                | 960.1       | 9.27                                                           | 255.0                | 1755.1      | 7.00                                                             |
| 146.5                | 863.6       | 7.44                                                             | 990.0                | 1000.1      | 9.58                                                           | 214.2                | 1795.9      | 6.92                                                             |
| 127.0                | 883.1       | 7.48                                                             | 1010.0               | 1020.1      | 9.79                                                           | 193.8                | 1816.3      | 7.00                                                             |
| 107.5                | 902.6       | 7.58                                                             | 1050.0               | 1060.1      | 10.17                                                          | 153.0                | 1857.1      | 6.83                                                             |
| 88.0                 | 922.1       | 7.65                                                             | 1070.0               | 1080.1      | 10.32                                                          | 132.5                | 1877.6      | 6.80                                                             |
| 68.6                 | 941.5       | 7.69                                                             | 1110.0               | 1120.1      | 10.75                                                          | 91.7                 | 1918.4      | 6.83                                                             |
| 49.1                 | 961.0       | 7.76                                                             | 1130.0               | 1140.1      | 10.83                                                          | 71.3                 | 1938.8      | 6.87                                                             |
| 29.6                 | 980.5       | 7.96                                                             | 1170.0               | 1180.1      | 11.64                                                          | 30.5                 | 1979.6      | 7.11                                                             |
| 10.1                 | 1000.0      | 8.64                                                             | 1190.0               | 1200.1      | 11.98                                                          | 10.1                 | 2000.0      | 7.75                                                             |

## Typical Performance Data

| LO<br>(MHz) | LO-RF ISOLATION<br>(dB) |       |       | LO-IF ISOLATION<br>(dB) |       |       |
|-------------|-------------------------|-------|-------|-------------------------|-------|-------|
|             | @LO (dBm)               |       |       | @LO (dBm)               |       |       |
|             | +4                      | +7    | +10   | +4                      | +7    | +10   |
| 40.1        | 58.93                   | 57.35 | 57.07 | 47.78                   | 48.24 | 48.78 |
| 100.5       | 55.87                   | 55.03 | 54.21 | 45.31                   | 45.76 | 46.23 |
| 161.0       | 54.64                   | 54.17 | 53.47 | 43.61                   | 44.29 | 45.12 |
| 221.4       | 52.94                   | 52.87 | 52.32 | 42.45                   | 43.53 | 44.69 |
| 302.0       | 50.40                   | 51.08 | 51.31 | 41.07                   | 42.48 | 43.85 |
| 362.5       | 47.65                   | 48.63 | 49.48 | 40.46                   | 42.03 | 43.27 |
| 443.1       | 46.33                   | 46.65 | 47.05 | 39.05                   | 40.58 | 41.88 |
| 503.5       | 46.54                   | 47.27 | 47.57 | 39.38                   | 40.23 | 40.93 |
| 584.1       | 45.49                   | 47.10 | 48.31 | 42.72                   | 42.78 | 41.91 |
| 644.5       | 43.26                   | 44.54 | 45.64 | 44.60                   | 43.70 | 41.76 |
| 725.1       | 41.31                   | 42.60 | 43.92 | 47.35                   | 44.22 | 41.07 |
| 785.6       | 41.87                   | 43.42 | 44.98 | 48.70                   | 44.75 | 40.67 |
| 866.2       | 41.80                   | 44.25 | 46.67 | 50.54                   | 47.35 | 40.72 |
| 926.6       | 40.89                   | 43.07 | 45.03 | 48.20                   | 48.04 | 40.88 |
| 1007.2      | 41.83                   | 43.34 | 44.20 | 42.25                   | 50.89 | 42.27 |
| 1067.7      | 41.00                   | 42.18 | 42.73 | 38.30                   | 48.71 | 44.91 |
| 1148.2      | 38.78                   | 39.66 | 39.93 | 34.58                   | 42.57 | 55.45 |
| 1208.7      | 37.70                   | 38.20 | 38.30 | 32.23                   | 38.55 | 45.47 |
| 1289.3      | 36.96                   | 36.98 | 37.00 | 29.17                   | 33.12 | 34.17 |
| 1349.7      | 36.26                   | 36.16 | 36.37 | 27.04                   | 29.18 | 28.79 |
| 1430.3      | 33.50                   | 34.16 | 34.90 | 26.54                   | 26.47 | 24.83 |
| 1490.8      | 32.45                   | 32.40 | 32.10 | 30.33                   | 28.68 | 26.48 |
| 1571.4      | 31.82                   | 31.54 | 31.10 | 35.30                   | 33.28 | 31.54 |
| 1631.8      | 31.04                   | 30.75 | 30.69 | 32.26                   | 31.11 | 30.16 |
| 1712.4      | 30.39                   | 29.82 | 29.98 | 28.07                   | 26.45 | 25.31 |
| 1772.8      | 30.43                   | 29.89 | 29.88 | 25.58                   | 23.83 | 22.65 |
| 1853.4      | 29.67                   | 29.43 | 29.53 | 22.92                   | 21.38 | 20.35 |
| 1913.9      | 28.70                   | 28.40 | 28.08 | 21.25                   | 19.69 | 18.67 |
| 1994.5      | 27.58                   | 27.22 | 26.72 | 19.54                   | 18.15 | 17.16 |
| 2054.9      | 27.47                   | 26.75 | 26.11 | 18.72                   | 17.25 | 16.36 |
| 2135.5      | 26.47                   | 25.78 | 25.17 | 17.46                   | 16.45 | 15.74 |
| 2196.0      | 25.52                   | 24.91 | 24.21 | 16.75                   | 15.96 | 15.26 |
| 2276.5      | 24.68                   | 24.17 | 23.77 | 15.99                   | 15.60 | 15.13 |
| 2337.0      | 24.69                   | 24.19 | 23.95 | 15.51                   | 15.39 | 15.19 |
| 2417.6      | 24.50                   | 24.20 | 23.75 | 15.09                   | 15.36 | 15.39 |
| 2478.0      | 23.83                   | 23.72 | 23.46 | 15.05                   | 15.51 | 15.66 |
| 2558.6      | 23.16                   | 23.26 | 23.24 | 14.90                   | 15.73 | 16.23 |
| 2619.1      | 22.48                   | 22.77 | 22.70 | 14.45                   | 15.56 | 16.25 |
| 2699.7      | 20.90                   | 21.28 | 21.37 | 14.16                   | 15.35 | 16.12 |
| 2760.1      | 19.38                   | 19.76 | 20.15 | 14.02                   | 15.00 | 15.69 |

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | RF-IF ISOLATION<br>(dB) |       |       |
|---------------------|-------------|-------------------------|-------|-------|
|                     |             | @LO (dBm)               |       |       |
|                     |             | +4                      | +7    | +10   |
| 10.1                | 40.1        | 14.28                   | 14.75 | 16.03 |
| 70.5                | 100.5       | 20.54                   | 20.89 | 20.84 |
| 131.0               | 161.0       | 21.27                   | 21.47 | 21.19 |
| 191.4               | 221.4       | 21.98                   | 22.20 | 22.70 |
| 272.0               | 302.0       | 23.25                   | 23.46 | 23.85 |
| 332.5               | 362.5       | 24.81                   | 25.22 | 25.71 |
| 413.1               | 443.1       | 27.83                   | 28.10 | 28.10 |
| 473.5               | 503.5       | 29.85                   | 29.65 | 29.62 |
| 554.1               | 584.1       | 32.13                   | 31.01 | 30.36 |
| 614.5               | 644.5       | 32.40                   | 31.30 | 30.67 |
| 695.1               | 725.1       | 33.04                   | 32.67 | 32.51 |
| 755.6               | 785.6       | 32.83                   | 32.55 | 32.42 |
| 836.2               | 866.2       | 33.57                   | 33.31 | 33.15 |
| 896.6               | 926.6       | 37.22                   | 36.22 | 35.70 |
| 977.2               | 1007.2      | 36.02                   | 35.76 | 35.34 |
| 1037.7              | 1067.7      | 34.55                   | 33.99 | 33.66 |
| 1118.2              | 1148.2      | 34.00                   | 33.09 | 32.54 |
| 1178.7              | 1208.7      | 36.27                   | 35.18 | 34.10 |
| 1259.3              | 1289.3      | 50.95                   | 48.55 | 44.05 |
| 1319.7              | 1349.7      | 49.13                   | 53.73 | 54.35 |
| 1400.3              | 1430.3      | 32.95                   | 32.57 | 32.28 |
| 1460.8              | 1490.8      | 24.65                   | 24.82 | 24.86 |
| 1541.4              | 1571.4      | 21.91                   | 22.22 | 22.43 |
| 1601.8              | 1631.8      | 21.65                   | 21.94 | 22.23 |
| 1682.4              | 1712.4      | 21.79                   | 22.18 | 22.54 |
| 1742.8              | 1772.8      | 22.25                   | 22.61 | 22.98 |
| 1823.4              | 1853.4      | 23.16                   | 23.63 | 23.94 |
| 1883.9              | 1913.9      | 24.39                   | 24.85 | 25.21 |
| 1964.5              | 1994.5      | 25.05                   | 25.19 | 25.01 |
| 2024.9              | 2054.9      | 24.38                   | 23.95 | 23.36 |
| 2105.5              | 2135.5      | 22.40                   | 21.55 | 20.80 |
| 2166.0              | 2196.0      | 20.56                   | 19.73 | 19.03 |
| 2246.5              | 2276.5      | 18.95                   | 18.15 | 17.48 |
| 2307.0              | 2337.0      | 17.97                   | 17.35 | 17.03 |
| 2387.6              | 2417.6      | 16.88                   | 16.31 | 15.94 |
| 2448.0              | 2478.0      | 16.55                   | 16.24 | 16.04 |
| 2528.6              | 2558.6      | 16.38                   | 16.25 | 16.19 |
| 2589.1              | 2619.1      | 16.66                   | 16.78 | 16.79 |
| 2669.7              | 2699.7      | 16.82                   | 17.11 | 17.35 |
| 2730.1              | 2760.1      | 17.06                   | 17.25 | 17.35 |

## Typical Performance Data

| RF<br>(IN)<br>(MHz) | LO<br>(MHz) | RF VSWR<br>(:1) |      |      | LO<br>(MHz) | LO VSWR<br>(:1) |      |      | IF<br>(OUT)<br>(MHz) | IF VSWR<br>@LO=2000MHz<br>(:1) |      |      |
|---------------------|-------------|-----------------|------|------|-------------|-----------------|------|------|----------------------|--------------------------------|------|------|
|                     |             | @LO (dBm)       |      |      |             | @LO (dBm)       |      |      |                      | @LO (dBm)                      |      |      |
|                     |             | +4              | +7   | +10  |             | +4              | +7   | +10  |                      | +4                             | +7   | +10  |
| 10.1                | 40.1        | 1.21            | 1.28 | 1.15 | 40.1        | 1.87            | 2.74 | 3.86 | 10.0                 | 2.03                           | 2.12 | 2.19 |
| 70.5                | 100.5       | 1.11            | 1.05 | 1.05 | 100.5       | 1.70            | 2.44 | 3.37 | 50.0                 | 1.53                           | 1.67 | 1.79 |
| 131.0               | 161.0       | 1.21            | 1.14 | 1.11 | 161.0       | 1.73            | 2.46 | 3.40 | 90.0                 | 1.56                           | 1.70 | 1.82 |
| 191.4               | 221.4       | 1.36            | 1.28 | 1.24 | 221.4       | 1.78            | 2.54 | 3.50 | 110.0                | 1.56                           | 1.70 | 1.81 |
| 272.0               | 302.0       | 1.58            | 1.49 | 1.44 | 302.0       | 1.76            | 2.47 | 3.38 | 150.0                | 1.57                           | 1.70 | 1.80 |
| 332.5               | 362.5       | 1.83            | 1.71 | 1.64 | 362.5       | 1.78            | 2.45 | 3.30 | 170.0                | 1.63                           | 1.77 | 1.89 |
| 413.1               | 443.1       | 2.23            | 2.10 | 2.01 | 443.1       | 1.79            | 2.44 | 3.29 | 210.0                | 1.65                           | 1.77 | 1.86 |
| 473.5               | 503.5       | 2.52            | 2.37 | 2.27 | 503.5       | 1.81            | 2.46 | 3.31 | 230.0                | 1.69                           | 1.81 | 1.91 |
| 554.1               | 584.1       | 2.90            | 2.71 | 2.57 | 584.1       | 1.78            | 2.39 | 3.22 | 270.0                | 1.72                           | 1.84 | 1.94 |
| 614.5               | 644.5       | 3.26            | 3.06 | 2.92 | 644.5       | 1.79            | 2.33 | 3.10 | 290.0                | 1.77                           | 1.89 | 1.99 |
| 695.1               | 725.1       | 3.86            | 3.70 | 3.56 | 725.1       | 1.87            | 2.32 | 3.02 | 330.0                | 1.76                           | 1.88 | 1.98 |
| 755.6               | 785.6       | 4.02            | 3.95 | 3.87 | 785.6       | 1.94            | 2.32 | 2.98 | 350.0                | 1.79                           | 1.91 | 2.01 |
| 836.2               | 866.2       | 3.94            | 3.94 | 3.93 | 866.2       | 2.00            | 2.25 | 2.82 | 390.0                | 1.85                           | 1.98 | 2.08 |
| 896.6               | 926.6       | 3.93            | 3.91 | 3.90 | 926.6       | 2.03            | 2.18 | 2.66 | 410.0                | 1.79                           | 1.91 | 2.01 |
| 977.2               | 1007.2      | 3.82            | 3.77 | 3.73 | 1007.2      | 2.02            | 2.06 | 2.47 | 450.0                | 1.89                           | 2.02 | 2.13 |
| 1037.7              | 1067.7      | 3.67            | 3.59 | 3.54 | 1067.7      | 2.00            | 1.95 | 2.30 | 470.0                | 1.86                           | 1.99 | 2.11 |
| 1118.2              | 1148.2      | 3.52            | 3.35 | 3.26 | 1148.2      | 1.95            | 1.78 | 2.05 | 510.0                | 1.85                           | 1.99 | 2.11 |
| 1178.7              | 1208.7      | 3.51            | 3.27 | 3.14 | 1208.7      | 1.91            | 1.66 | 1.90 | 530.0                | 1.86                           | 2.01 | 2.15 |
| 1259.3              | 1289.3      | 3.43            | 3.14 | 2.95 | 1289.3      | 1.83            | 1.51 | 1.71 | 570.0                | 1.82                           | 1.97 | 2.11 |
| 1319.7              | 1349.7      | 3.52            | 3.20 | 3.02 | 1349.7      | 1.75            | 1.38 | 1.58 | 590.0                | 1.82                           | 1.98 | 2.14 |
| 1400.3              | 1430.3      | 3.83            | 3.48 | 3.29 | 1430.3      | 1.61            | 1.23 | 1.44 | 630.0                | 1.82                           | 1.99 | 2.15 |
| 1460.8              | 1490.8      | 4.09            | 3.72 | 3.48 | 1490.8      | 1.51            | 1.12 | 1.40 | 650.0                | 1.84                           | 2.02 | 2.20 |
| 1541.4              | 1571.4      | 4.00            | 3.67 | 3.42 | 1571.4      | 1.41            | 1.05 | 1.44 | 690.0                | 1.86                           | 2.05 | 2.24 |
| 1601.8              | 1631.8      | 3.82            | 3.50 | 3.26 | 1631.8      | 1.35            | 1.16 | 1.54 | 710.0                | 1.90                           | 2.09 | 2.28 |
| 1682.4              | 1712.4      | 3.55            | 3.29 | 3.06 | 1712.4      | 1.33            | 1.34 | 1.72 | 750.0                | 1.97                           | 2.17 | 2.36 |
| 1742.8              | 1772.8      | 3.34            | 3.11 | 2.92 | 1772.8      | 1.38            | 1.49 | 1.87 | 770.0                | 2.00                           | 2.20 | 2.40 |
| 1823.4              | 1853.4      | 2.97            | 2.78 | 2.63 | 1853.4      | 1.50            | 1.69 | 2.06 | 810.0                | 2.16                           | 2.37 | 2.57 |
| 1883.9              | 1913.9      | 2.64            | 2.43 | 2.28 | 1913.9      | 1.62            | 1.94 | 2.41 | 830.0                | 2.18                           | 2.38 | 2.57 |
| 1964.5              | 1994.5      | 2.25            | 2.06 | 1.92 | 1994.5      | 1.80            | 2.22 | 2.75 | 870.0                | 2.34                           | 2.54 | 2.73 |
| 2024.9              | 2054.9      | 2.04            | 1.85 | 1.70 | 2054.9      | 1.92            | 2.39 | 2.94 | 890.0                | 2.39                           | 2.58 | 2.76 |
| 2105.5              | 2135.5      | 1.74            | 1.56 | 1.42 | 2135.5      | 2.11            | 2.63 | 3.22 | 930.0                | 2.47                           | 2.66 | 2.83 |
| 2166.0              | 2196.0      | 1.53            | 1.37 | 1.24 | 2196.0      | 2.32            | 2.91 | 3.53 | 950.0                | 2.56                           | 2.74 | 2.91 |
| 2246.5              | 2276.5      | 1.28            | 1.13 | 1.01 | 2276.5      | 2.57            | 3.19 | 3.83 | 990.0                | 2.65                           | 2.82 | 2.99 |
| 2307.0              | 2337.0      | 1.17            | 1.04 | 1.08 | 2337.0      | 2.70            | 3.31 | 3.95 | 1010.0               | 2.72                           | 2.89 | 3.04 |
| 2387.6              | 2417.6      | 1.03            | 1.12 | 1.24 | 2417.6      | 2.93            | 3.54 | 4.16 | 1050.0               | 2.84                           | 2.99 | 3.13 |
| 2448.0              | 2478.0      | 1.18            | 1.31 | 1.44 | 2478.0      | 3.20            | 3.82 | 4.45 | 1070.0               | 2.92                           | 3.06 | 3.19 |
| 2528.6              | 2558.6      | 1.39            | 1.56 | 1.71 | 2558.6      | 3.46            | 4.03 | 4.64 | 1110.0               | 2.99                           | 3.11 | 3.20 |
| 2589.1              | 2619.1      | 1.53            | 1.71 | 1.87 | 2619.1      | 3.52            | 4.02 | 4.56 | 1130.0               | 3.06                           | 3.17 | 3.26 |
| 2669.7              | 2699.7      | 1.76            | 1.97 | 2.15 | 2699.7      | 3.65            | 4.06 | 4.53 | 1170.0               | 3.12                           | 3.20 | 3.27 |
| 2730.1              | 2760.1      | 2.01            | 2.24 | 2.44 | 2760.1      | 3.64            | 4.01 | 4.44 | 1190.0               | 3.12                           | 3.19 | 3.25 |

## Harmonics Tables

### RF HARMONICS ORDER

|        | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|--------|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0      | -      | -      | 23  | 24  | 7   | 37  | 27  | 49  | 39  | 50  | 46  | 40  |
| 1      | -      | 27     | +0  | 30  | 19  | 34  | 32  | 38  | 42  | 48  | 46  | 44  |
| 2      | 87     | 67     | 56  | 66  | 55  | >68 | 52  | >68 | 65  | >68 | >68 | >68 |
| 3      | >90    | >68    | 65  | >68 | 60  | >68 | 64  | >68 | >68 | >68 | >68 | >68 |
| 4      | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 5      | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 6      | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 7      | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 8      | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 9      | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 10     | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| RF CAL | 0      | 1      | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |     |

Test conditions: RF IN: 1002.5 MHz; -14.00 dBm.  
LO IN: 1032.5 MHz; +7.00 dBm  
IF OUT: 30 MHz; -22.12 dBm

### RF HARMONICS ORDER

|        | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|--------|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0      | -      | -      | 31  | 34  | 18  | 48  | 39  | 63  | 52  | 65  | 61  | 56  |
| 1      | -      | 26     | +0  | 30  | 19  | 35  | 34  | 41  | 46  | 54  | 54  | 52  |
| 2      | 67     | 59     | 47  | 55  | 47  | 63  | 45  | 72  | 59  | 71  | 67  | >78 |
| 3      | >90    | 56     | 48  | 54  | 43  | 53  | 49  | 57  | 56  | 56  | 62  | 66  |
| 4      | >90    | >78    | 72  | >78 | 74  | 74  | 69  | 73  | 66  | >78 | 76  | >78 |
| 5      | >90    | >78    | >78 | 72  | 71  | 70  | 60  | 69  | 62  | 74  | 71  | 70  |
| 6      | >90    | >78    | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 |
| 7      | >90    | >78    | >78 | >78 | >78 | >78 | >78 | >78 | 76  | >78 | 77  | >78 |
| 8      | >90    | >78    | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 |
| 9      | >90    | >78    | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 |
| 10     | >90    | >78    | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 |
| RF CAL | 0      | 1      | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |     |

### LO HARMONICS ORDER

Test conditions: RF IN: 1002.5 MHz; -4.00 dBm.  
LO IN: 1032.5 MHz; +7.00 dBm  
IF OUT: 30 MHz; -12 dBm


- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.  
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.  
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

# Frequency Mixer


SRA-11+

## Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=1010.1MHz




Conversion Loss vs. IF @ RF=10.1MHz




Conversion Loss vs. IF @ RF=2010.1MHz



IP3 Input



Compression @ RF IN=+1dBm



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




# Frequency Mixer


SRA-11+

## Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



REV. X3

SRA-11+

101031

Page 2 of 3

**Mini-Circuits®**

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



# Frequency Mixer

SRA-11+

## Harmonics Tables

RF HARMONICS ORDER

|    | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|----|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0  | -      | -      | 23  | 24  | 7   | 37  | 27  | 49  | 39  | 50  | 46  | 40  |
| 1  | -      | 27     | +0  | 30  | 19  | 34  | 32  | 38  | 42  | 48  | 46  | 44  |
| 2  | 87     | 67     | 56  | 66  | 55  | >68 | 52  | >68 | 65  | >68 | >68 | >68 |
| 3  | >90    | >68    | 65  | >68 | 60  | >68 | 64  | >68 | >68 | >68 | >68 | >68 |
| 4  | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 5  | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 6  | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 7  | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 8  | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 9  | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
| 10 | >90    | >68    | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 | >68 |
|    | RF CAL | 0      | 1   | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |

Test conditions: RF IN: 1002.5 MHz; -14.00 dBm.  
LO IN: 1032.5 MHz; +7.00 dBm  
IF OUT: 30 MHz; -22.12 dBm

RF HARMONICS ORDER

|    | (-dBm) | (-dBc) |     |     |     |     |     |     |     |     |     |     |
|----|--------|--------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| 0  | -      | -      | 31  | 34  | 18  | 48  | 39  | 63  | 52  | 65  | 61  | 56  |
| 1  | -      | 26     | +0  | 30  | 19  | 35  | 34  | 41  | 46  | 54  | 54  | 52  |
| 2  | 67     | 59     | 47  | 55  | 47  | 63  | 45  | 72  | 59  | 71  | 67  | >78 |
| 3  | >90    | 56     | 48  | 54  | 43  | 53  | 49  | 57  | 56  | 56  | 62  | 66  |
| 4  | >90    | >78    | 72  | >78 | 74  | 74  | 69  | 73  | 66  | >78 | 76  | >78 |
| 5  | >90    | >78    | >78 | 72  | 71  | 70  | 60  | 69  | 62  | 74  | 71  | 70  |
| 6  | >90    | >78    | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 |
| 7  | >90    | >78    | >78 | >78 | >78 | >78 | >78 | >78 | 76  | >78 | 77  | >78 |
| 8  | >90    | >78    | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 |
| 9  | >90    | >78    | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 |
| 10 | >90    | >78    | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 | >78 |
|    | RF CAL | 0      | 1   | 2   | 3   | 4   | 5   | 6   | 7   | 8   | 9   | 10  |

### LO HARMONICS ORDER

Test conditions: RF IN: 1002.5 MHz; -4.00 dBm.  
LO IN: 1032.5 MHz; +7.00 dBm  
IF OUT: 30 MHz; -12 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.  
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.  
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

A01  
A04  
A05  
A06

## Outline Dimensions



| CASE# | A               | B               | C              | D               | E              | F               | G              | H             | J             | K             | WT,<br>GRAM |
|-------|-----------------|-----------------|----------------|-----------------|----------------|-----------------|----------------|---------------|---------------|---------------|-------------|
| A01   | .770<br>(19.56) | .800<br>(20.32) | .385<br>(9.78) | .400<br>(10.16) | .370<br>(9.40) | .400<br>(10.16) | .200<br>(5.08) | .20<br>(5.08) | .14<br>(3.56) | .031<br>(.79) | 5.2         |
| A04   |                 |                 | .200<br>(5.08) | .210<br>(5.33)  |                |                 |                |               |               |               | 3.7         |
| A05   |                 |                 | .240<br>(6.10) | .250<br>(6.35)  |                |                 |                |               |               |               | 3.7         |
| A06   |                 |                 | .285<br>(7.24) | .310<br>(7.87)  |                |                 |                |               |               |               | 5.2         |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

### Notes:

- Header material: C.R.S.  
Pin material: #52 alloy.  
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-045-01.
- Tolerance on pin diameter  $\pm .005$  inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                  | Test/Inspection Condition                                                                                                                                       | Reference/Spec                                                                                       |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| Operating Temperature          | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Storage Temperature            | -55° to 100° C<br>Ambient Environment                                                                                                                           | Individual Model Data Sheet                                                                          |
| Thermal Shock                  | -55° to 100°C, 100 cycles                                                                                                                                       | MIL-STD-202, Method 107, Condition A-3, except +100°C                                                |
| Vibration (High Frequency)     | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                                                             | MIL-STD-202, Method 204, Condition D                                                                 |
| Mechanical Shock               | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                                                               | MIL-STD-202, Method 213, Condition A                                                                 |
| Moisture Resistance            | 10 cycles, 24 hours per cycle                                                                                                                                   | MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours |
| Solderability                  | 10X Magnification                                                                                                                                               | J-STD-002, 95% Coverage                                                                              |
| Resistance to Solder Heat      | 260°C for 10 seconds                                                                                                                                            | MIL-STD-202, Method 210, Condition B                                                                 |
| Marking Resistance to Solvents | Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C;<br>distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C | MIL-STD-202, Method 215                                                                              |
| Terminal Strength              | 4 1/2 Pound Pull                                                                                                                                                | MIL-STD-202, Method 211, Condition A                                                                 |



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification       | Test/Inspection Condition | Reference/Spec                       |
|---------------------|---------------------------|--------------------------------------|
| Gross Leak          | 125°C Bubble Test         | MIL-STD-202, Method 112, Condition D |
| Barometric Pressure | 100,000 Feet              | MIL-STD-202, Method 105, Condition D |