

Plug-In Frequency Mixer

SRA-3H+

Level 17 (LO Power +17 dBm) 0.05 to 200 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	200mW
IF Current	40mA


Permanent damage may occur if any of these limits are exceeded.

Pin Connections

LO	8
RF	1
IF	3,4 [^]
GROUND	2,5,6,7
CASE GROUND	2

[^] pins must be connected together externally

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F
.770	.800	.385	.400	.370	.400
19.56	20.32	9.78	10.16	9.40	10.16
G	H	J	K	wt	
.200	.20	.14	.031	grams	
5.08	5.08	3.56	0.79	5.2	

Features

- excellent conversion loss, 5.18 dB typ.
- high L-R isolation, 40 dB typ. L-I isolation, 40 dB typ.
- rugged welded construction
- hermetic

Applications

- VHF/UHF
- FM broadcast radio
- maritime communications
- defense & federal communications



Generic photo used for illustration purposes only

CASE STYLE: A01

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)					
LO/RF f_L - f_U	IF	Mid-Band m		Total Range Max.		L		M		U		L		M		U	
		$\bar{X}$	σ	Max.	Max.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.
0.05-200	DC-200	5.18	.05	7.0	7.5	50	45	40	30	35	25	45	35	40	30	30	20


1 dB COMP.: +10 dBm typ.

L = low range [f_L to $10 f_L$]
m = mid band [$2 f_L$ to $f_U/2$]
M = mid range [$10 f_L$ to $f_U/2$]
U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm	LO +17dBm
0.05	30.05	5.79	61.52	58.47	1.22	2.35
0.20	30.20	5.33	61.30	55.83	1.23	2.27
1.00	31.00	5.25	61.00	55.41	1.22	2.14
5.00	35.00	5.18	58.85	54.15	1.21	2.17
10.00	40.00	5.36	54.85	51.92	1.20	2.19
20.00	50.00	5.40	48.89	47.33	1.20	2.19
41.42	71.42	5.37	41.07	40.89	1.19	2.18
50.00	80.00	5.37	39.79	39.78	1.18	2.27
69.00	99.00	5.34	39.34	38.19	1.15	2.20
89.68	59.68	5.33	38.45	35.45	1.15	2.21
103.47	73.37	5.34	36.25	36.39	1.13	2.14
110.37	80.37	5.37	35.73	35.84	1.13	2.07
117.26	87.26	5.38	35.17	35.59	1.11	2.12
131.05	101.05	5.40	34.48	35.04	1.10	2.15
137.95	107.95	5.42	33.95	34.10	1.10	2.24
151.74	121.74	5.50	32.91	31.97	1.11	2.21
165.53	135.53	5.66	31.97	30.09	1.12	2.17
179.31	149.31	5.76	31.41	28.67	1.14	2.13
193.10	163.10	5.77	31.62	28.17	1.17	2.20
200.00	170.00	5.75	32.02	28.21	1.19	2.23

Electrical Schematic









Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M151107
SRA-3H
DJ/TD/CP/AM
200402
Page 1 of 2



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Frequency Mixer

SRA-3H+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	CONVERSION LOSS IF FIXED @IF(OUT)=30MHz (dB)			RF (IN) (MHz)	LO (MHz)	IP3 INPUT (dBm)			RF (IN) (MHz)	LO (MHz)	COMPRESSION @RF IN=+10dBm (dB)		
		@LO (dBm)					@LO (dBm)					@LO (dBm)		
		+14	+17	+20			+14	+17	+20			+14	+17	+20
0.1	30.1	5.94	5.79	5.69	10.1	40.1	23.94	24.93	25.19	10.1	40.1	1.06	0.77	0.53
0.2	30.2	5.43	5.33	5.26	22.7	52.7	23.60	23.52	27.81	22.7	52.7	0.86	0.60	0.39
1.0	31.0	5.36	5.25	5.17	35.2	65.2	23.06	24.81	32.90	35.2	65.2	0.85	0.58	0.39
5.0	35.0	5.30	5.18	5.09	47.8	77.8	21.65	25.55	28.45	47.8	77.8	0.80	0.55	0.38
10.0	40.0	5.45	5.36	5.31	60.4	90.4	22.89	31.98	23.92	60.4	90.4	0.73	0.49	0.34
22.7	52.7	4.91	4.75	4.68	72.9	102.9	23.24	28.65	23.21	72.9	102.9	0.67	0.48	0.34
35.2	65.2	4.94	4.80	4.73	85.5	115.5	22.74	26.86	23.72	85.5	115.5	0.62	0.46	0.33
47.8	77.8	4.98	4.83	4.76	98.0	128.0	31.41	23.98	22.34	98.0	128.0	0.64	0.45	0.32
60.4	90.4	4.95	4.83	4.77	110.6	140.6	20.07	18.48	18.36	110.6	140.6	0.64	0.47	0.35
72.9	102.9	4.99	4.86	4.79	123.2	153.2	20.84	19.34	19.26	123.2	153.2	0.67	0.49	0.38
85.5	115.5	5.01	4.89	4.83	135.7	165.7	27.83	21.62	20.64	135.7	165.7	0.66	0.49	0.37
98.0	128.0	5.01	4.89	4.84	148.3	178.3	22.78	21.85	21.80	148.3	178.3	0.61	0.49	0.37
110.6	140.6	4.99	4.88	4.83	160.9	190.9	20.96	19.08	19.11	160.9	190.9	0.61	0.47	0.37
123.2	153.2	5.00	4.88	4.83	173.4	203.4	21.28	19.35	18.63	173.4	203.4	0.71	0.55	0.42
135.7	165.7	5.09	4.92	4.84	186.0	216.0	20.42	19.06	18.77	186.0	216.0	0.83	0.60	0.44
148.3	178.3	5.24	5.04	4.90	198.6	228.6	18.38	17.64	19.05	198.6	228.6	0.96	0.63	0.43
160.9	190.9	5.33	5.18	5.04	211.1	241.1	17.60	18.38	20.60	211.1	241.1	1.13	0.70	0.47
186.0	216.0	5.34	5.24	5.20	223.7	253.7	17.85	19.52	21.88	223.7	253.7	1.34	0.80	0.52
198.6	228.6	5.36	5.30	5.29	236.3	266.3	16.26	19.66	21.77	236.3	266.3	1.57	0.91	0.62
211.1	241.1	5.46	5.38	5.36	248.8	278.8	12.77	17.92	22.16	248.8	278.8	1.49	1.06	0.71
223.7	253.7	5.62	5.49	5.43	261.4	291.4	10.23	13.85	19.36	261.4	291.4	1.60	1.24	0.92
236.3	266.3	5.84	5.60	5.52	273.9	303.9	9.64	11.78	15.66	273.9	303.9	1.55	1.24	1.09
248.8	278.8	6.15	5.75	5.54	286.5	316.5	9.61	11.11	13.74	286.5	316.5	1.56	1.31	1.20
261.4	291.4	6.36	5.98	5.61	299.1	329.1	10.19	11.45	12.70	299.1	329.1	1.43	1.26	1.09
273.9	303.9	6.55	6.20	5.71	311.6	341.6	10.75	11.86	13.70	311.6	341.6	1.37	1.21	1.10
286.5	316.5	6.65	6.31	5.84	324.2	354.2	11.56	12.61	15.14	324.2	354.2	1.31	1.09	0.94
299.1	329.1	6.79	6.44	6.11	336.8	366.8	12.38	14.05	17.70	336.8	366.8	1.24	0.99	0.87
324.2	354.2	6.95	6.66	6.44	349.3	379.3	13.09	15.58	21.23	349.3	379.3	1.33	1.03	0.90
336.8	366.8	7.05	6.78	6.60	361.9	391.9	14.51	17.75	28.76	361.9	391.9	1.30	1.00	0.87
349.3	379.3	6.97	6.77	6.62	374.5	404.5	15.71	19.27	22.84	374.5	404.5	1.41	1.11	0.94
361.9	391.9	7.05	6.88	6.74	387.0	417.0	16.40	20.36	22.12	387.0	417.0	1.43	1.10	0.84
374.5	404.5	7.02	6.87	6.79	399.6	429.6	16.41	19.89	22.08	399.6	429.6	1.52	1.11	0.80
387.0	417.0	7.13	7.05	7.03	412.2	442.2	16.39	19.59	22.00	412.2	442.2	1.48	1.00	0.68
399.6	429.6	7.27	7.22	7.24	424.7	454.7	16.94	19.58	22.03	424.7	454.7	1.42	0.94	0.61
424.7	454.7	7.78	7.83	7.98	437.3	467.3	17.89	19.29	20.75	437.3	467.3	1.25	0.82	0.52
437.3	467.3	8.14	8.21	8.43	449.8	479.8	17.99	18.39	19.00	449.8	479.8	1.05	0.68	0.46
449.8	479.8	8.68	8.75	8.95	462.4	492.4	16.82	16.98	17.36	462.4	492.4	0.98	0.65	0.49
475.0	505.0	9.62	9.76	9.96	475.0	505.0	16.56	16.41	16.96	475.0	505.0	0.94	0.67	0.57
487.5	517.5	9.98	10.08	10.26	487.5	517.5	16.83	15.94	16.26	487.5	517.5	1.12	0.87	0.79
500.1	530.1	10.46	10.58	10.78	500.1	530.1	17.96	15.94	15.80	500.1	530.1	1.15	0.90	0.84

REV. X2

SRA-3H+

100818

Page 1 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Frequency Mixer

SRA-3H+

Typical Performance Data

IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=100.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=10.1MHz (dB)	IF (OUT) (MHz)	LO (MHz)	CONVERSION LOSS VS. IF FREQUENCY @RF(IN)=200.1MHz (dB)
		@LO (dBm)			@LO (dBm)			@LO (dBm)
		+17			+17			+17
90.0	10.1	5.04	10.0	20.1	4.60	190.0	10.1	5.74
87.9	12.2	5.03	14.6	24.7	4.45	185.4	14.7	5.67
85.9	14.2	5.02	19.2	29.3	4.40	180.8	19.3	5.60
83.8	16.3	5.00	23.8	33.9	4.38	176.2	23.9	5.54
81.8	18.3	4.98	28.5	38.6	4.37	171.5	28.6	5.50
79.7	20.4	4.96	33.1	43.2	4.40	166.9	33.2	5.45
77.7	22.4	4.93	37.7	47.8	4.40	162.3	37.8	5.43
75.6	24.5	4.92	42.3	52.4	4.42	157.7	42.4	5.41
73.6	26.5	4.92	46.9	57.0	4.43	153.1	47.0	5.40
71.5	28.6	4.91	51.5	61.6	4.45	148.5	51.6	5.39
69.5	30.6	4.89	56.2	66.3	4.45	143.8	56.3	5.38
67.4	32.7	4.89	60.8	70.9	4.46	139.2	60.9	5.37
65.4	34.7	4.87	65.4	75.5	4.48	134.6	65.5	5.34
63.3	36.8	4.86	70.0	80.1	4.51	130.0	70.1	5.33
61.3	38.8	4.86	74.6	84.7	4.53	125.4	74.7	5.33
59.2	40.9	4.85	79.2	89.3	4.54	120.8	79.3	5.32
57.2	42.9	4.85	83.8	93.9	4.53	116.2	83.9	5.32
55.1	45.0	4.84	88.5	98.6	4.54	111.5	88.6	5.30
53.1	47.0	4.83	93.1	103.2	4.57	106.9	93.2	5.29
51.0	49.1	4.81	97.7	107.8	4.58	102.3	97.8	5.26
49.0	51.1	4.81	102.3	112.4	4.61	97.7	102.4	5.27
46.9	53.2	4.83	106.9	117.0	4.62	93.1	107.0	5.26
44.9	55.2	4.84	111.5	121.6	4.64	88.5	111.6	5.24
42.8	57.3	4.84	116.2	126.3	4.65	83.8	116.3	5.22
40.8	59.3	4.84	120.8	130.9	4.66	79.2	120.9	5.22
38.7	61.4	4.84	125.4	135.5	4.67	74.6	125.5	5.23
36.7	63.4	4.84	130.0	140.1	4.66	70.0	130.1	5.23
34.6	65.5	4.85	134.6	144.7	4.68	65.4	134.7	5.25
32.6	67.5	4.85	139.2	149.3	4.68	60.8	139.3	5.28
30.5	69.6	4.85	143.8	153.9	4.69	56.2	143.9	5.30
28.5	71.6	4.85	148.5	158.6	4.70	51.5	148.6	5.32
26.4	73.7	4.85	153.1	163.2	4.71	46.9	153.2	5.32
24.4	75.7	4.85	157.7	167.8	4.73	42.3	157.8	5.30
22.3	77.8	4.86	162.3	172.4	4.79	37.7	162.4	5.31
20.3	79.8	4.87	166.9	177.0	4.87	33.1	167.0	5.32
18.2	81.9	4.87	171.5	181.6	4.98	28.5	171.6	5.31
16.2	83.9	4.89	176.2	186.3	5.11	23.8	176.3	5.33
14.1	86.0	4.92	180.8	190.9	5.19	19.2	180.9	5.35
12.1	88.0	4.97	185.4	195.5	5.25	14.6	185.5	5.38
10.0	90.1	5.08	190.0	200.1	5.32	10.0	190.1	5.55

REV. X2
SRA-3H+
100818
Page 2 of 5

Typical Performance Data

LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
	@LO (dBm)			@LO (dBm)		
	+14	+17	+20	+14	+17	+20
0.1	63.58	61.52	59.06	63.39	58.47	54.35
0.2	63.56	61.30	59.59	63.01	55.83	51.32
1.0	63.21	61.00	59.26	62.31	55.41	51.09
5.0	59.91	58.85	57.26	59.04	54.15	50.39
10.0	55.77	54.85	53.74	54.60	51.92	49.03
22.7	70.04	71.06	71.64	63.22	62.55	61.77
35.2	67.90	70.66	71.70	58.52	58.40	59.74
47.8	66.71	70.65	72.02	54.85	56.13	57.98
60.4	65.59	69.66	72.56	52.60	54.47	56.23
72.9	63.90	69.89	73.38	50.94	53.08	54.58
85.5	66.92	72.32	71.26	49.99	52.05	53.41
98.0	63.60	90.00	66.85	49.05	50.85	51.79
110.6	60.01	65.71	83.36	48.69	50.27	50.61
123.2	72.93	71.10	65.28	48.12	49.76	49.14
135.7	62.73	57.43	56.62	46.53	47.86	47.92
148.3	59.93	56.46	54.89	46.86	47.24	46.80
160.9	57.36	57.29	55.27	46.30	46.31	45.01
186.0	51.21	57.07	58.44	43.36	42.41	41.07
198.6	50.81	58.29	59.79	42.36	41.13	39.93
211.1	54.05	58.95	48.65	42.22	39.97	37.97
223.7	56.30	53.07	46.16	41.71	38.01	35.17
236.3	60.00	49.85	45.46	41.59	35.54	33.08
248.8	71.79	48.95	44.39	41.88	34.61	32.06
261.4	61.12	47.30	42.93	43.75	34.58	31.53
273.9	54.90	46.17	42.03	43.71	34.67	30.88
286.5	52.37	44.57	40.26	39.65	34.00	30.05
299.1	48.25	42.81	38.04	37.15	33.84	29.35
324.2	49.25	44.47	40.43	34.40	31.90	28.29
336.8	46.01	40.69	36.83	33.77	30.89	26.67
349.3	44.35	39.11	34.53	32.54	28.85	24.25
361.9	43.73	37.26	32.75	30.95	26.17	21.97
374.5	40.64	34.40	30.51	28.99	24.08	20.07
387.0	37.44	31.83	28.32	27.07	22.36	19.06
399.6	35.40	30.18	26.87	25.31	21.10	18.01
424.7	30.87	26.99	24.33	22.82	19.04	16.35
437.3	29.12	25.70	23.41	21.58	18.27	15.91
449.8	27.36	24.35	22.39	20.45	17.39	15.36
475.0	23.91	22.07	20.40	18.11	16.16	14.42
487.5	22.88	21.40	19.82	17.31	15.67	14.06
500.1	22.26	20.82	19.46	17.00	15.35	13.88

RF (IN) (MHz)	LO (MHz)	RF-IF ISOLATION (dB)		
		@LO (dBm)		
		+14	+17	+20
10.1	40.1	36.43	35.78	37.11
22.7	52.7	30.60	30.97	31.33
35.2	65.2	27.80	27.99	28.14
47.8	77.8	25.90	26.16	26.49
60.4	90.4	24.66	25.07	25.45
72.9	102.9	23.81	24.06	24.31
85.5	115.5	23.93	24.34	24.55
98.0	128.0	23.68	24.43	25.07
110.6	140.6	23.28	23.93	24.63
123.2	153.2	23.11	23.63	24.15
135.7	165.7	23.16	23.62	24.11
148.3	178.3	23.82	24.27	24.68
160.9	190.9	24.02	24.46	24.93
173.4	203.4	22.95	23.36	23.78
186.0	216.0	21.10	21.48	21.78
198.6	228.6	19.00	19.22	19.35
211.1	241.1	17.50	17.60	17.65
223.7	253.7	16.17	16.19	16.20
236.3	266.3	15.43	15.49	15.52
248.8	278.8	14.93	15.00	15.19
261.4	291.4	14.49	14.65	14.92
273.9	303.9	14.43	14.75	15.13
286.5	316.5	14.22	14.56	15.19
299.1	329.1	14.24	14.45	14.91
311.6	341.6	14.27	14.38	14.55
324.2	354.2	14.04	13.97	13.98
336.8	366.8	13.87	13.72	13.67
349.3	379.3	13.41	13.23	13.01
361.9	391.9	12.89	12.65	12.31
374.5	404.5	12.31	11.97	11.49
387.0	417.0	11.56	11.06	10.32
399.6	429.6	10.85	10.22	9.49
412.2	442.2	9.94	9.36	8.75
424.7	454.7	9.02	8.54	8.02
437.3	467.3	8.14	7.83	7.48
449.8	479.8	7.36	7.17	6.96
462.4	492.4	6.78	6.65	6.57
475.0	505.0	6.38	6.28	6.24
487.5	517.5	6.14	6.03	6.03
500.1	530.1	5.82	5.68	5.65

Frequency Mixer

SRA-3H+

Typical Performance Data

RF (IN) (MHz)	LO (MHz)	RF VSWR (:1)			LO (MHz)	LO VSWR (:1)			IF (OUT) (MHz)	IF VSWR @LO=200.1MHz (:1)		
		@LO (dBm)				@LO (dBm)				@LO (dBm)		
		+14	+17	+20		+14	+17	+20		+14	+17	+20
5.0	35.0	1.32	1.22	1.15	5.0	1.61	2.35	3.15	5.0	1.63	1.53	1.40
10.0	40.0	1.33	1.23	1.15	10.0	1.57	2.27	3.04	10.0	1.64	1.54	1.41
22.7	52.7	1.30	1.20	1.14	22.7	1.61	2.31	3.13	14.9	2.13	1.99	1.80
35.2	65.2	1.29	1.19	1.13	35.2	1.65	2.39	3.24	19.7	2.08	1.92	1.75
47.8	77.8	1.27	1.17	1.11	47.8	1.66	2.39	3.26	24.6	1.99	1.87	1.68
60.4	90.4	1.24	1.14	1.08	60.4	1.66	2.37	3.20	29.5	1.98	1.88	1.69
72.9	102.9	1.21	1.12	1.06	72.9	1.64	2.32	3.13	34.4	1.95	1.84	1.66
85.5	115.5	1.17	1.08	1.04	85.5	1.62	2.29	3.06	39.2	1.89	1.78	1.62
98.0	128.0	1.14	1.04	1.03	98.0	1.62	2.28	3.05	44.1	1.86	1.75	1.58
110.6	140.6	1.13	1.05	1.03	110.6	1.64	2.31	3.08	49.0	1.83	1.73	1.57
123.2	153.2	1.11	1.06	1.05	123.2	1.67	2.35	3.13	53.8	1.83	1.71	1.56
135.7	165.7	1.09	1.05	1.08	135.7	1.69	2.38	3.15	58.7	1.82	1.72	1.57
148.3	178.3	1.09	1.05	1.10	148.3	1.70	2.37	3.14	63.6	1.85	1.74	1.58
160.9	190.9	1.05	1.05	1.11	160.9	1.71	2.36	3.10	68.5	1.88	1.77	1.61
173.4	203.4	1.06	1.11	1.17	173.4	1.73	2.36	3.08	73.3	1.91	1.80	1.65
186.0	216.0	1.11	1.18	1.24	186.0	1.74	2.38	3.10	78.2	1.97	1.85	1.69
198.6	228.6	1.19	1.26	1.32	198.6	1.76	2.41	3.14	83.1	2.03	1.91	1.75
211.1	241.1	1.23	1.30	1.33	211.1	1.79	2.44	3.17	87.9	2.10	1.98	1.80
223.7	253.7	1.25	1.30	1.32	223.7	1.81	2.46	3.19	92.8	2.15	2.02	1.84
236.3	266.3	1.24	1.28	1.30	236.3	1.84	2.46	3.19	97.7	2.19	2.07	1.88
248.8	278.8	1.26	1.26	1.26	248.8	1.87	2.47	3.18	102.6	2.24	2.11	1.91
261.4	291.4	1.29	1.25	1.23	261.4	1.92	2.50	3.18	107.4	2.27	2.14	1.95
273.9	303.9	1.31	1.24	1.18	273.9	1.96	2.55	3.20	112.3	2.30	2.17	1.97
286.5	316.5	1.32	1.25	1.17	286.5	2.00	2.60	3.25	117.2	2.32	2.18	1.98
299.1	329.1	1.31	1.23	1.14	299.1	2.03	2.66	3.31	122.1	2.31	2.17	1.98
311.6	341.6	1.33	1.22	1.13	311.6	2.07	2.70	3.35	126.9	2.32	2.18	1.99
324.2	354.2	1.28	1.18	1.12	324.2	2.09	2.72	3.37	131.8	2.31	2.18	1.99
336.8	366.8	1.29	1.22	1.18	336.8	2.10	2.73	3.37	136.7	2.33	2.20	2.01
349.3	379.3	1.28	1.24	1.22	349.3	2.11	2.73	3.34	141.5	2.35	2.22	2.03
361.9	391.9	1.35	1.33	1.32	361.9	2.13	2.73	3.31	146.4	2.38	2.25	2.07
374.5	404.5	1.38	1.37	1.38	374.5	2.15	2.73	3.29	151.3	2.42	2.29	2.10
387.0	417.0	1.46	1.46	1.47	387.0	2.17	2.73	3.27	156.2	2.46	2.33	2.15
399.6	429.6	1.54	1.55	1.55	399.6	2.19	2.73	3.25	161.0	2.52	2.39	2.20
412.2	442.2	1.59	1.61	1.61	412.2	2.20	2.73	3.22	165.9	2.56	2.43	2.25
424.7	454.7	1.67	1.68	1.68	424.7	2.20	2.70	3.17	170.8	2.62	2.49	2.30
437.3	467.3	1.71	1.73	1.74	437.3	2.20	2.68	3.13	175.6	2.67	2.53	2.35
449.8	479.8	1.77	1.78	1.78	449.8	2.21	2.67	3.11	180.5	2.70	2.57	2.39
462.4	492.4	1.78	1.79	1.79	462.4	2.24	2.67	3.09	185.4	2.74	2.61	2.43
475.0	505.0	1.82	1.81	1.81	475.0	2.28	2.69	3.08	190.3	2.76	2.63	2.46
487.5	517.5	1.83	1.81	1.81	487.5	2.33	2.72	3.09	195.1	2.79	2.67	2.48
500.1	530.1	1.86	1.83	1.83	500.1	2.38	2.76	3.10	200.0	2.88	2.75	2.57

REV. X2

SRA-3H+

100818

Page 4 of 5



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	22	44	18	28	16	39	21	47	33	54
1	-	19	+0	27	12	43	18	37	37	51	39	48
2	>100	61	51	63	51	62	51	66	56	65	60	70
3	>100	60	56	62	62	65	58	60	66	68	59	72
4	>100	90	79	>90	69	77	77	83	77	>90	>90	87
5	>100	87	84	85	88	75	88	90	85	83	80	>90
6	>100	>90	>90	>90	>90	>90	86	>90	>90	>90	>90	>90
7	>100	>90	>90	>90	>90	>90	85	87	>90	>90	>90	>90
8	>100	>90	>90	>90	>90	>90	>90	77	85	>90	>90	>90
9	>100	>90	>90	>90	>90	>90	>90	>90	66	>90	>90	>90
10	>100	>90	>90	>90	>90	>90	>90	>90	85	79	>90	>90
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 100.1 MHz; -5.00 dBm.
LO IN: 130.01 MHz; +17.00 dBm
IF OUT: 29.91 MHz; -9.82 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	30	59	29	38	28	53	33	59	46	63
1	-	20	+0	28	12	42	19	40	35	55	42	60
2	86	60	51	61	52	63	49	60	50	62	54	70
3	>100	48	44	55	45	53	43	50	47	53	55	61
4	>100	72	62	70	62	71	61	72	61	75	71	73
5	>100	68	59	63	62	62	59	64	58	60	62	69
6	>100	97	74	91	74	84	73	87	73	85	72	89
7	>100	81	77	76	67	70	71	74	70	71	73	74
8	>100	>100	89	>100	86	94	86	96	83	94	82	>100
9	>100	99	82	85	88	81	83	77	80	82	80	78
10	>100	>100	>100	>100	97	>100	93	>100	86	85	89	94
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 100.1 MHz; 5.00 dBm.
LO IN: 130.01 MHz; +17.00 dBm
IF OUT: 29.91 MHz; .09 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
SRA-3H+
100818
Page 5 of 5




Frequency Mixer


SRA-3H+

Typical Performance Curves


Conversion Loss @ IF=30MHz




Conversion Loss vs. IF @ RF=100.1MHz




Conversion Loss vs. IF @ RF=10.1MHz




Conversion Loss vs. IF @ RF=200.1MHz



IP3 Input



Compression @ RF IN=+10dBm



REV. X2
SRA-3H+
100818
Page 1 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




Typical Performance Curves


LO-RF Isolation




LO-IF Isolation




RF-IF Isolation




RF VSWR



LO VSWR



IF VSWR



Harmonics Tables

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	22	44	18	28	16	39	21	47	33	54
1	-	19	+0	27	12	43	18	37	37	51	39	48
2	>100	61	51	63	51	62	51	66	56	65	60	70
3	>100	60	56	62	62	65	58	60	66	68	59	72
4	>100	90	79	>90	69	77	77	83	77	>90	>90	87
5	>100	87	84	85	88	75	88	90	85	83	80	>90
6	>100	>90	>90	>90	>90	>90	86	>90	>90	>90	>90	>90
7	>100	>90	>90	>90	>90	>90	85	87	>90	>90	>90	>90
8	>100	>90	>90	>90	>90	>90	>90	77	85	>90	>90	>90
9	>100	>90	>90	>90	>90	>90	>90	>90	66	>90	>90	>90
10	>100	>90	>90	>90	>90	>90	>90	>90	85	79	>90	>90
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 100.1 MHz; -5.00 dBm.
LO IN: 130.01 MHz; +17.00 dBm
IF OUT: 29.91 MHz; -9.82 dBm

RF HARMONICS ORDER

	(-dBm)	(-dBc)										
0	-	-	30	59	29	38	28	53	33	59	46	63
1	-	20	+0	28	12	42	19	40	35	55	42	60
2	86	60	51	61	52	63	49	60	50	62	54	70
3	>100	48	44	55	45	53	43	50	47	53	55	61
4	>100	72	62	70	62	71	61	72	61	75	71	73
5	>100	68	59	63	62	62	59	64	58	60	62	69
6	>100	97	74	91	74	84	73	87	73	85	72	89
7	>100	81	77	76	67	70	71	74	70	71	73	74
8	>100	>100	89	>100	86	94	86	96	83	94	82	>100
9	>100	99	82	85	88	81	83	77	80	82	80	78
10	>100	>100	>100	>100	97	>100	93	>100	86	85	89	94
	RF CAL	0	1	2	3	4	5	6	7	8	9	10

LO HARMONICS ORDER

Test conditions: RF IN: 100.1 MHz; 5.00 dBm.
LO IN: 130.01 MHz; +17.00 dBm
IF OUT: 29.91 MHz; .09 dBm

- Notes: 1. All Harmonics are in (dBc) relative to IF OUTPUT.
2. + entry denotes harmonics are in (dBc) above IF OUTPUT.
3. RF Cal represent the Harmonics level of the RF input signal to the mixer.

REV. X2
SRA-3H+
100818
Page 3 of 3



A01
A04
A05
A06

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	WT, GRAM
A01	.770 (19.56)	.800 (20.32)	.385 (9.78)	.400 (10.16)	.370 (9.40)	.400 (10.16)	.200 (5.08)	.20 (5.08)	.14 (3.56)	.031 (.79)	5.2
A04			.200 (5.08)	.210 (5.33)							3.7
A05			.240 (6.10)	.250 (6.35)							3.7
A06			.285 (7.24)	.310 (7.87)							5.2

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Header material: C.R.S.
Pin material: #52 alloy.
Cover material: Cupro-Nickel.
- Pin finish: Electro Tin-Silver.
- Insulated spacer available. Request P/N B14-045-01.
- Tolerance on pin diameter $\pm .005$ inch.
- Glass meniscus 0.015 inch max.
- Blue bead indicates Pin 1. Pin numbers do not appear on unit, for reference only.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Moisture Resistance	10 cycles, 24 hours per cycle	MIL-STD-202, Method 106, Condition A, except 50°C and end point electrical test done within 12 hours
Solderability	10X Magnification	J-STD-002, 95% Coverage
Resistance to Solder Heat	260°C for 10 seconds	MIL-STD-202, Method 210, Condition B
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215
Terminal Strength	4 1/2 Pound Pull	MIL-STD-202, Method 211, Condition A



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Gross Leak	125°C Bubble Test	MIL-STD-202, Method 112, Condition D
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D